



Product	High Power Chip Resistors<Wide Terminal type><Anti-surge>	Series	LTR series	Type	LTR50 UZP	Rated Power	1.0W
---------	---	--------	------------	------	-----------	-------------	------

Test conditions①

Ambient temperature: : 25°C
 Board specifications : FR-4 t = 1.6 mm
 Cu foil thickness : 35μm
 Number of layers of Cu foil : 1
 Sample size : 3pcs
 Direct current application

Test conditions②

Ambient temperature: : 25°C
 Board specifications : FR-4 t = 1.6 mm
 Cu foil thickness : 70μm
 Number of layers of Cu foil : 4
 Sample size : 3pcs
 Direct current application



【Caution】

This data is the value of specific lot and specific resistance value only. It does not guarantee the variations due to different lot and product.
 This data is not guaranteed. This data shall be utilized as reference data of the actual product characteristic.
 When deciding the usage of the product, we cordially ask you not to only rely on this data but to have own evaluation and verification.
 Partial or complete quote / copy / distribution and disclosure to third party of the data is not permissible without agreement with ROHM.
 ROHM does not warrant any loss related to this data (including intellectual property right violation) neither the loss caused by the usage of the data.