



Test Result of Electrical Static Discharge (Machine Model) [Reference Data]

Products	SiC SBD	Part No.	SCS205K*	Measurement	ESS-606 AT-T700	Measurement	C=200 pF R=0 Ω
				Instrument	(Noise Laboratory co.,ltd)	Condition	T _a =25°C






(Notice) This data is made from representative value of a specific lot. The data indicates neither the worst nor guaranteed value.


SCS205K*_MM



Test Result of Electrical Static Discharge (Human Body Model) [Reference Data]

Products	SiC SBD	Part No.	SCS205K*	Measurement	ESS-606 AT-T700	Measurement	C=100 pF	R=1.5 kΩ
				Instrument	(Noise Laboratory co.,ltd)	Condition	$T_a=25^{\circ}C$	5 pulses





More than 6 kV, above the efficiency of the apparatus.

More than 6 kV, above the efficiency of the apparatus.