





Test Result of Electrical Static Discharge (Machine Model) [Reference Data]

Products	SiC SBD	Part No.	SCS240AE2	Measurement Instrument	ESS-606 AT-T700 (Noise Laboratory co.,ltd)	Measurement Condition	C=200 pF R=0 Ω T _a =25°C
----------	---------	----------	-----------	------------------------	---	-----------------------	--




(Notice) This data is made from representative value of a specific lot. The data indicates neither the worst nor guaranteed value.

SCS240AE2_MM




Test Result of Electrical Static Discharge (Human Body Model) [Reference Data]

Products	SiC SBD	Part No.	SCS240AE2	Measurement Instrument	ESS-606 AT-T700 (Noise Laboratory co.,ltd)	Measurement Condition	C=100 pF T _a =25°C	R=1.5 kΩ 5 pulses
----------	---------	----------	-----------	------------------------	---	-----------------------	----------------------------------	----------------------



More than 6 kV, above the efficiency of the apparatus.



More than 6 kV, above the efficiency of the apparatus.

(Notice) This data is made from representative value of a specific lot. The data indicates neither the worst nor guaranteed value.

SCS240AE2_HBM