







# Test Result of Electrical Static Discharge (Machine Model) [ Reference Data ]

Products	SiC MOSFET	Part No.	SCT3022KL	Measurement Instrument	ESS-606 AT-T700 (Noise Laboratory co.,ltd)	Measurement Condition	C=200 pF R=0 Ω T <sub>a</sub> =25°C
----------	------------	----------	-----------	------------------------	---	-----------------------	--







(Notice) This data is made from representative value of a specific lot. The data indicates neither the worst nor guaranteed value.

SCT3022KL\_MM



# Test Result of Electrical Static Discharge (Human Body Model) [ Reference Data ]

Products	SiC MOSFET	Part No.	SCT3022KL	Measurement Instrument	ESS-606 AT-T700 (Noise Laboratory co.,ltd)	Measurement Condition	C=100 pF T <sub>a</sub> =25°C	R=1.5 kΩ 5 pulses
----------	------------	----------	-----------	------------------------	---	-----------------------	----------------------------------	----------------------



(Notice) This data is made from representative value of a specific lot. The data indicates neither the worst nor guaranteed value.

SCT3022KL\_HBM