Anti-whisker formation of leadfree plating

1. The Applicable Product

BU7205HFV-TR

2. Evaluation Package

No	Item	Information
1	Subject	LSI product of Leadfree plating
2	Type of Terminal Plating	Sn
3	Plating Grain Size	2μm to 10μm
4	Bath type	Alkyl sulfonic acid, Electro plating
5	Matt or Bright	Matt
6	Under Plating	None
7	Type of Frame	Cu Alloy frame

3. Compliance standerds

Tin Whisker Acceptance Test Requirements (NEMI Tin Whisker Users Group, July 28, 2004)

4. Test Flow

No	Test Flow	Test Condition
1	Preparation	M.P. condition
2	Pre Inspection	SEM x 250, Top/Side/Forming Section
3	Preconditioning-1	Storage at ambient temp. for 4 weeks
4	Preconditioning-2	215°C Reflow, 255°C Reflow
5	Applying Stress	1. 30°C, 70% RH, 4,000hr 2. 60°C, 87% RH, 4,000hr 3. -55/+85°C, 2,000cyc 4. 30°C, 70%, Bias, 4,000hr
6	Screening Inspection	x 50, Top/Side/Forming Section
7	Detailed Inspection	SEM x 250, Top/Side/Forming Section

5. Test Result

Criteria : Not allow, the whisker is larger than 40μm between lead to lead.

No	Preconditioning-1	Preconditioning-2	Stress Condition	Result:Pn/n (pcs)
1	Storage at ambient temprature. 4 weeks	None	30°C, 70% RH 4,000hr	0 / 96
2			60°C, 87% RH 4,000hr	0 / 96
3		215°C Reflow Simulation	30°C, 70% RH 4,000hr	0 / 96
4			60°C, 87% RH 4,000hr	0 / 96
5		255°C Reflow Simulation	30°C, 70% RH 4,000hr	0 / 96
6			60°C, 87% RH 4,000hr	0 / 96
7		215°C Reflow Simulation	–55/+85°C 2,000cyc	0 / 96
8		255°C Reflow Simulation	–55/+85°C 2,000cyc	0 / 96
9		215°C Reflow Assembly	30°C, 70%, Bias 4,000hr	0 / 96

Therefore, wisker is no problem.

02.Nov.2015

Yoshitaka Ichise
General Manager Quality Control Division
LSI Production Headquarters ROHM Co., Ltd.

©2015 ROHM Co., Ltd. All rights reserved

Notes

1) The information contained herein is subject to change without notice.

2) Before you use our Products, please contact our sales representative and verify the latest specifications :

3) Although ROHM is continuously working to improve product reliability and quality, semiconductors can break down and malfunction due to various factors.
Therefore, in order to prevent personal injury or fire arising from failure, please take safety measures such as complying with the derating characteristics, implementing redundant and fire prevention designs, and utilizing backups and fail-safe procedures. ROHM shall have no responsibility for any damages arising out of the use of our Poducts beyond the rating specified by ROHM.

4) Examples of application circuits, circuit constants and any other information contained herein are provided only to illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.

5) The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM or any other parties. ROHM shall have no responsibility whatsoever for any dispute arising out of the use of such technical information.

6) The Products are intended for use in general electronic equipment (i.e. AV/OA devices, communication, consumer systems, gaming/entertainment sets) as well as the applications indicated in this document.

7) The Products specified in this document are not designed to be radiation tolerant.

8) For use of our Products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a ROHM representative : transportation equipment (i.e. cars, ships, trains), primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, servers, solar cells, and power transmission systems.

9) Do not use our Products in applications requiring extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters.

10) ROHM shall have no responsibility for any damages or injury arising from non-compliance with the recommended usage conditions and specifications contained herein.

11) ROHM has used reasonable care to ensur the accuracy of the information contained in this document. However, ROHM does not warrants that such information is error-free, and ROHM shall have no responsibility for any damages arising from any inaccuracy or misprint of such information.

12) Please use the Products in accordance with any applicable environmental laws and regulations, such as the RoHS Directive. For more details, including RoHS compatibility, please contact a ROHM sales office. ROHM shall have no responsibility for any damages or losses resulting non-compliance with any applicable laws or regulations.

13) When providing our Products and technologies contained in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.

14) This document, in part or in whole, may not be reprinted or reproduced without prior consent of ROHM.

ROHM SEMICONDUCTOR

Thank you for your accessing to ROHM product informations.
More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

http://www.rohm.com/contact/

© 2015 ROHM Co., Ltd. All rights reserved.