#### **Diode series**

# Advantages of YQ Series: Compact and Highly Power Conversion Efficiency Schottky Barrier Diodes for Automotive

Schottky barrier diodes (SBDs) are semiconductor devices that feature low forward voltage (VF) and low recovery loss compared with common PN junction diodes. They have significantly contributed to the improvement in power conversion efficiency of various power circuits, including PFC circuits and boost and buck converters, as well as reverse current protection circuits. Furthermore, demand for various automotive equipment including automotive LED lamps, in-vehicle infotainment, and ECU, solar power generation systems, and compact mobile devices represented by USB battery chargers has greatly increased in recent years.

To meet this demand, ROHM has developed the "YQ Series" as an addition to the previous RBS, RBR, RBQ, and RBxx8 series. Employing the latest Schottky process enables industry-leading low V<sub>F</sub> and low capacitance characteristics, contributing to the improvement in power conversion efficiency of circuits. Furthermore, listing the compact and thin TO-277 package with high heat dissipation in its product lineup, the YQ series is also ideal for automotive equipment and compact mobile devices that have strict requirements for heat generation and mounting space.

This application note provides an easy-to understand explanation about the advantages of the YQ series with respect to its characteristics based on comparison with common competing products. It also explains its advantages in actual circuits based on results of comparative evaluation using an LED driver.

#### 1. ROHM SBD roadmap

Figure 1 shows the SBD selection map developed by ROHM. The trade-off between V<sub>F</sub> and I<sub>R</sub> (reverse current) is significantly improved in the new products of the YQ series (red frame) compared with the previous RBS, RBR, RBQ, and RBxx8 series. While V<sub>F</sub> is kept equivalent, I<sub>R</sub> is reduced to approximately 1/10 compared with the previous series. Therefore, the new products can be conveniently applied and achieve a lower loss especially in the automotive equipment under a harsh temperature environment. Although the breakdown voltage V<sub>RM</sub> setting is currently only 100 V, other settings will be added gradually.



Figure 1. SBD selection map developed by ROHM

#### 2. Application example using the YQ series (automotive LED headlamp)

As an application example using the YQ series, Figure 2 shows peripheral circuits of an automotive LED headlamp. SBDs (red frame) are generally used for rectification of the boost block.

Since these circuits are generally energized under a sealed condition for automotive LED headlamps, the temperature can be very high. Furthermore, with the increase in the number of bulbs in a headlamp and downsizing of circuit boards in recent years, the operating condition is increasingly harsher with respect to heat generation. Therefore, as the characteristics required for SBD, in addition to low V<sub>F</sub> (low conduction loss), the low I<sub>R</sub> characteristics and the heat dissipation performance of packages are very important in terms of reduction in the thermal runaway risk. Since the trade-off between V<sub>F</sub> and I<sub>R</sub> is significantly improved in the YQ series as described in Chapter 1, it has a huge advantage with respect to these points (when comparing products with similar V<sub>F</sub>, I<sub>R</sub> can be significantly reduced from the previous series). Furthermore, a wide range of packages with superior heat dissipation performance, including TO-252 and TO-277, is listed in its lineup (the lineup is described in detail in Chapter 5). This allows for flexible applications to various usages and mounting spaces.

In addition, since a recovery loss occurs if the boost circuit is operated in the continuous mode, the recovery characteristics of SBD also becomes very important. Since this recovery loss is superimposed over the switching cycle, it is more important at a higher operation frequency.



Figure 2. Peripheral circuits of automotive LED headlamps

#### 3. Comparison of device characteristics with products from other companies

Figures 3 and 4 show the comparison results of the  $I_F-V_F$  and capacitance- $V_R$  characteristics for the TO-277 package products in the 100 V/10 A class from other companies. ROHM YQ10RSM10SD [1] has one of the lowest  $V_F$  characteristics, nearly equivalent to the Company-A product. Therefore, it can be predicted that ROHM YQ10RSM10SD and the Company-A product have the lowest conduction loss when they are used in an actual circuit. In contrast,  $V_F$  of Companies-B and C products are higher by approximately 10 to 20%. Therefore, it can be expected that their conduction losses are higher compared with those of ROHM YQ10RSM10SD and the Company-A product. Furthermore, based on the capacitance- $V_R$  characteristics, it can be predicted that ROHM YQ10RSM10SD has the lowest switching loss, because its capacitance is the smallest (approximately a half) compared with the competing products.



© 2022 ROHM Co., Ltd.

#### 4. Comparative evaluation of competing products in actual equipment

Using ROHM automotive LED driver BD18353EFV-M<sub>[2]</sub> and its evaluation board, we compared the power conversion efficiency and heat generation of ROHM YQ10RSM10SD (100V/10A/TO-277) with similar products from other companies.

#### 4-1. Evaluation board and circuit diagram

Figure 5 shows a full view of the evaluation board and its circuit diagram.

In this evaluation, a comparative evaluation was performed by exchanging the rectifier diode (red frame) in the boost block. For the switching MOSFET (blue frame), ROHM RD3P100SNFRA (100V/10A/TO-252) was used.



Figure 5. Picture of board and circuit diagram

#### 4-2. Evaluation results

Figure 6 shows the comparison results of the efficiency and package surface temperature Tc.

As shown, it is confirmed that YQ10RSM10SD with superior characteristics of both  $V_F$  and capacitance has the highest power conversion efficiency and can keep Tc the lowest even with the same package. The efficiency of products from Companies-B and C are specifically lower and their Tc is higher. This is because of their high  $V_F$  as described in Chapter 3. Furthermore, although the Company-A product has the  $V_F$  characteristics equivalent to ROHM YQ10RSM10SD, its efficiency is lower and Tc is higher because its switching loss is higher.



Figure 6. Comparison results of the efficiency and package surface temperature

### 5. Lineup

Figure 7 shows the lineup of the YQ series. A wide product lineup is prepared for various applications, including YQ10RSM10SD which was used for the evaluation of the LED driver described above. Products other than the following will be gradually added to the product lineup. Please feel free to contact us.



Schottky Barrier Diodes - YQ Series | ROHM Semiconductor - ROHM Co., Ltd.

Figure 7. YQ series lineup

#### 6. Summary

- The products of the YQ series have lower V<sub>F</sub> and lower I<sub>R</sub> simultaneously compared with the previous RBS, RBR, RBQ, and RBxx8 series. Therefore, they can contribute to improved power conversion efficiency in various applications.
- The TO-252 and TO-277 packages with superior heat dissipation performance are also listed in the product lineup. Combination with low I<sub>R</sub> dies can significantly contribute to reduction in the thermal runaway risk compared with previous products. This means they are especially useful for automotive equipment under harsh temperature environment.
- Compared with products in the same class from other companies, the YQ series has superior characteristics of V<sub>F</sub> and capacitance. Therefore, it can be considered that it has a great advantage with respect to improvement in the power conversion efficiency and reduction in heat generation when it is used in an actual circuit such as automotive LED headlamps.

## 7. References

- Trench MOS Barrier Structure, 100V, 10A, TO-277A, Highly Efficient SBD for Automotive, YQ10RSM10SDTF Data sheet (Rev.001) ROHM Co., Ltd., April 2023.
- [2] 1ch High Current LED Controller for Automotive, BD18353EFV-M, BD18353MUF-M Data sheet (No. TSZ02201-0T1T0B400330-1-1 Rev.002) ROHM Co., Ltd., February 2021.

Notice	
1)	The information contained in this document is intended to introduce ROHM Group (hereafter referred to asROHM) products. When using ROHM products, please verify the latest specifications or datasheets before use.
2)	ROHM products are designed and manufactured for use in general electronic equipment and applications (such as Audio Visual equipment, Office Automation equipment, telecommunication equipment, home appliances, amusement devices, etc.) or specified in the datasheets. Therefore, please contact the ROHM sales representative before using ROHM products in equipment or devices requiring extremely high reliability and whose failure or malfunction may cause danger or injury to human life or body or other serious damage (such as medical equipment, transportation, traffic, aircraft, spacecraft, nuclear power controllers, fuel control, automotive equipment including car accessories, etc. hereafter referred to as Specific Applications). Unless otherwise agreed in writing by ROHM in advance, ROHM shall not be in any way responsible or liable for any damages, expenses, or losses incurred by you or third parties arising from the use of ROHM Products for Specific Applications.
3)	Electronic components, including semiconductors, can fail or malfunction at a certain rate. Please be sure to implement, at your own responsibilities, adequate safety measures including but not limited to fail-safe design against physical injury, and damage to any property, which a failure or malfunction of products may cause.
4)	The information contained in this document, including application circuit examples and their constants, is intended to explain the standard operation and usage of ROHM products, and is not intended to guarantee, either explicitly or implicitly, the operation of the product in the actual equipment it will be used. As a result, you are solely responsible for it, and you must exercise your own independent verification and judgment in the use of such information contained in this document. ROHM shall not be in any way responsible or liable for any damages, expenses, or losses incurred by you or third parties arising from the use of such information.
5)	When exporting ROHM products or technologies described in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, such as the Foreign Exchange and Foreign Trade Act and the US Export Administration Regulations, and follow the necessary procedures in accordance with these provisions.
6)	The technical information and data described in this document, including typical application circuits, are examples only and are not intended to guarantee to be free from infringement of third parties intellectual property or other rights. ROHM does not grant any license, express or implied, to implement, use, or exploit any intellectual property or other rights owned or controlled by ROHM or any third parties with respect to the information contained herein.
7)	No part of this document may be reprinted or reproduced in any form by any means without the prior written consent of ROHM.
8)	All information contained in this document is current as of the date of publication and subject to change without notice. Before purchasing or using ROHM products, please confirm the latest information with the ROHM sales representative.
9)	ROHM does not warrant that the information contained herein is error-free. ROHM shall not be in any way responsible or liable for any damages, expenses, or losses incurred by you or third parties resulting from errors contained in this document.



Thank you for your accessing to ROHM product informations. More detail product informations and catalogs are available, please contact us.

# ROHM Customer Support System

https://www.rohm.com/contactus