

## **Battery Charger Series**

# Linear Charger for Low Voltage Battery BD71631QWZ EVK

BD71631QWZ-EVK-001 (5V→4.2V, 0.1A)

## Introduction

This user's guide provides the necessary steps to operate the EVK of ROHM's BD71631QWZ linear charger for low charge voltage battery. This include the external parts, operating procedures, and application data.

## Description

This EVK is for evaluating the linear charging IC BD71631QWZ, and charges 4.2V from the 5V input voltage. BD71631QWZ accepts a power supply input range of 2.9V to 5.5V and generates a charging battery voltage ranging from 2.0V to 4.7V using external resistors. If the charging current is VIN  $\geq$  4 V, it can be used up to 300 mA under the condition of VIN-VOUT  $\geq$  1 V and up to 100 mA under the condition of VIN-VOUT  $\geq$  0.3 V. If 2.9 V  $\leq$  VIN  $\leq$  5.5 V, it can be used up to 30 mA under the condition of VIN-VOUT  $\geq$  0.3 V. If 2.9 V  $\leq$  VIN  $\leq$  5.5 V, it can be used up to 30 mA under the condition of VIN-VOUT  $\geq$  0.3 V. If 2.9 V  $\leq$  VIN  $\leq$  5.5 V, it can be used up to 30 mA under the condition of VIN-VOUT  $\geq$  0.3 V. The charging current can be set with an external resistor. The termination current can be set from 50  $\mu$ A to 10 mA using external resistors. Additional protection functions include a built-in Fixed 10-hour Safety Timer, UVLO (Under Voltage Lock Out), TSD (Thermal Shutdown Detection), and Battery Over Voltage Protection.

## Application

Low Voltage Battery Products Li-ion 1Cell Battery Products

## **Operating Limits**

Table 1. Operating Limits Parameter Symbol Max Units Conditions Min Тур Input Voltage VIN 4.5 5.0 5.5 V Charge Voltage Vснg 4.2 V RVFB1=180k $\Omega$ , RVFB2=30k $\Omega$ Pre Charge Voltage VPRE 0.7 V V Re Charge Voltage VRECHG 3.0 RVFBRE1=120k $\Omega$ , RVFBRE2=30k $\Omega$ Charge Current 98 mΑ RICHG1=5.1kΩ ICHG **Termination Current** 0.98 RITERM=51kΩ ITERM mΑ **VOUT Leak Current** 0 μA 1 VIN=Open **IBAT** 



Figure 1. BD71631QWZ-EVK-001(Top View)

## **EVK Schematic**




Figure 2. BD71631QWZ-EVK-001 Circuit Diagram

# **Operating Procedure**

- 1. Turn off the DC power supply and connect the GND terminal of the power supply to the GND1 terminal of the EVK.
- 2. Connect the positive terminal of the DC power supply to the VIN pin of the EVK.
- 3. Connect the positive terminal of the DC power supply that can sink to the VOUT pin of the EVK.
- 4. Connect a current meter between the VOUT terminal of the EVK and the positive terminal of DC power supply of VOUT.
- 5. Connect a voltmeter between the VOUT terminal and GND terminal of EVK.
- 6. Turn on the DC power supply of VOUT.
- 7. Turn on the DC power supply of VIN. The power supply on the VOUT side is set to 4.2V or lower, charging will start and current will flow through the ammeter.

(Caution) This EVK does not support hot plug. Do not perform hot plug test.

## **Charging State**

Below is a charging state of BD71631QWZ.




Figure 3. Charging profile

Charging stop section on the left in Figure 3 is in the state of SUSPEND in Figure 4, and charging is stopped. In the Charge section, charging starts and the charging current IPRE or ICHG flows.

The Pre-charge current IPRE flows until the battery voltage reaches the Pre-charge voltage VPRE. IPRE is ICHG / 2 that is charged at Constant Current (CC) and the charging current IPRE flows.

When the battery voltage reaches the Pre-Charge voltage VPRE, it is charged at Constant Current (CC) and the charging current ICHG flows.

When the battery voltage reaches the V<sub>CHG</sub> voltage, it is charged at Constant Voltage (CV) and the charging current decreases. When the charging current reaches the Termination current I<sub>TERM</sub>, it will be in the TOP-OFF state, and after 15 seconds have passed, it will be in the DONE state.




Figure 4. Charging state

| No.        | State transition          | Condition                                    |
|------------|---------------------------|--|
| -          | SUSPEND -> CHARGE         | UVLO. TSD not detect                         |
| 1          |                           | and VIN > VBAT+0.3 V                         |
|            |                           | and VBAT OVP not detect                      |
|            |                           | and Temp Error not detect                    |
|            |                           | Continue to satisfy the condition for 25 ms  |
| 2          | CHARGE -> TOP OFF         | Charge current < ITERM                       |
| e          | _                         | Continue to satisfy the condition for 25 ms  |
| 3          | TOP_OFF -> CHARGE         | Charge current > ITERM                       |
| •          |                           | Continue to satisfy the condition for 25 ms  |
| 4          | TOP_OFF -> DONE           | Continue to satisfy the ③ condition for 15 s |
| (5)        | CHARGE or TOP_OFF or      | VBAT OVP detect                              |
| C          | TEMP_ERROR_1 or           | or 10 hours safety timer expired             |
|            | TEMP_ERROR_2              |  |
|            | -> BATTERY ERROR          |  |
| (6)        | DONE -> CHARGE            | VBAT < Re-charge voltage                     |
| 0          |                           | Continue to satisfy the condition for 25 ms  |
| $\bigcirc$ | CHARGE -> TEMP_ERROR_1 or | Temp Error detect                            |
| _          | TOP_OFF -> TEMP_ERROR_2   | Continue to satisfy the condition for 25 ms  |
| (8)        | TEMP_ERROR_1 -> CHARGE or | Temp Error not detect                        |
| _          | TEMP_ERROR_2 -> TOP_OFF   | Continue to satisfy the condition for 25 ms  |
| 9          | ALL State -> SUSPEND      | UVLO, TSD detect                             |
|            |                           | or VIN < VBAT+0.3 V                          |

Table 3. Safety timer and Internal control settings for each state of LEDCNT

| State         | Battery charge | 10 hours safety timer | LEDCNT |
|---------------|----------------|-----------------------|--------|
| SUSPEND       | Stop           | Stop and reset        | Hi-Z   |
| CHARGE        | Charge         | Count                 | Low    |
| TOP_OFF       | Charge         | Count                 | Low    |
| DONE          | Stop           | Stop and reset        | Hi-Z   |
| BATTERY_ERROR | Stop           | Stop and reset        | Hi-Z   |
| TEMP_ERROR_1  | Stop           | Count                 | Hi-Z   |
| TEMP_ERROR_2  | Stop           | Count                 | Hi-Z   |

#### **Peripheral Components Setting**

#### 1. Charging voltage (VCHG), Recharge voltage (VRECHG) setting

The resistance values of the charging voltage VCHG and re-charge voltage VRECHG can be set by the following formula.




Figure 5. Resistor setting of VCHG and VRECHG

The charge voltage is determined as follows :

$$V_{CHG} = (RFB1 + RFB2)/RFB2 \times 0.6 [V]$$

The re-charge voltage is determined as follows :

$$V_{RECHG} = (RFBRE1 + RFBRE2)/RFBRE2 \times 0.6 [V]$$

About total feedback resistance, the following is a reference example of operation settings. .

٦

| Table 4. Resister reference value |                            |                         |                                    |  |  |
|-----------------------------------|----------------------------|-------------------------|------------------------------------|--|--|
| Charge<br>Condition               | $V_{CHG} = 4.2 V$          | $V_{CHG} = 2.2 V$       | $V_{CHG} = 4.2 V$                  |  |  |
|                                   | $V_{\text{RECHG}} = 3.0 V$ | $V_{RECHG} = Disenable$ | $V_{\text{RECHG}} = 3.9 \text{ V}$ |  |  |
| Resistor value [Ω]                |                            |                         |                                    |  |  |
| RFB1                              | 180 k                      | 200 k                   | 600 k                              |  |  |
| RFB2                              | 30 k                       | 75 k                    | 100 k                              |  |  |
| RFBRE1                            | 120 k                      | -*                      | 1.1 M                              |  |  |
| RFBRE2 30 k                       |                            | _*                      | 200 k                              |  |  |

| Tabla 1 | Docistor | reference  | valua |
|---------|----------|------------|-------|
|         | NESISIEL | TELETETICE | value |

#### \*VFBRE pin connect to GND

A capacity of  $10\mu$ F or more is required between the VOUT terminal and GND terminal of BD71631QWZ. Connect C<sub>SPU</sub> for stable operation when the battery capacity is too small. The capacitance of C<sub>SPU</sub> is determined as follows :

 $C_{SPU} = 1/(2\pi \times 300 \times RFB1) [F]$ 

#### About the current of the external resistor that generated by the FB terminal and FBRE terminal

Nch FET is built in between the VFBG terminal and the GND terminal.

When the VIN terminal is connected, the Nch FET turns on and current flows from the battery to the external resistor. When the VIN terminal is disconnected, the Nch FET turns off and no current flows from the battery to the external resistor. If the VFBRE terminal is connected to GND and recharging is disabled, the internal Nch FET will be turned off when charging is completed even if VIN is connected.

#### 2. Charge current, Termination current setting

The charging current ICHG can be set by the following formula using the external resistor RICHG1.

 $I_{CHG} = (500000 / \text{RICHG1} [\Omega])[\text{mA}]$ 

The charging current can be set up to 300 mA (VIN  $\ge$  4 V, VIN-VOUT  $\ge$  1 V), 100 mA (VIN  $\ge$  4 V, VIN-VOUT  $\ge$  0.3 V), and 30 mA (2.9 V  $\le$  VIN  $\le$  5.5 V, VIN-VOUT  $\ge$  0.3V). There is a limit to the voltage between VIN and VOUT in the usage range of the charging current.

The termination current ITERM can be set by the following equation using the external resistor RITERM. The termination current can be set from 50  $\mu$ A to 10 mA.






Figure 6. Resistor setting of ICHG and ITERM

#### 3. Charge Current vs Battery Temperature

It is possible to monitor the temperature of the battery using NTC thermistor. The charging current is controlled by the battery temperature, as shown in the temperature profile in Figure 7. It is set by the NTC thermistor and pull-up resistor in Figure 8.

The component constants can be set according to the voltage of the NTC terminal at each temperature.




Figure 7. Charge Current vs Battery Temperature




Figure 8. Resistor setting of NTC terminal

How to find the external resistance of the NTC terminal and the NCT constant is as follows.

When calculating RNTC and RNTCR1, firstly calculate the resistance voltage dividers VHot and VCold when charging stops with the NTC thermistor temperature profile in Figure 7. The error of the %VCold and %VHot thresholds will depend on temperature coefficient B of the chosen NTC thermistor resistor.

By simulated calculation, the resistance value is calculated so that the error of the NTC terminal voltage at each temperature becomes small.

$$V_{Cold} = \left(\frac{RNTC\_cold}{RNTC1 + RNTC\_cold}\right) \times VIN [V]$$
$$V_{Hot} = \left(\frac{RNTC\_Hot}{RNTC1 + RNTC\_Hot}\right) \times VIN [V]$$
$$\% V_{Cold} = \frac{V_{Cold}}{V_{NTC\_Cold}}$$
$$\% V_{Hot} = \frac{V_{Hot}}{V_{NTC\_Hot}}$$

Where the NTC thermistor resistance at the T\_cold and T\_Hot temperatures must be resolved as follows:

 $R_{NTC\_Cold} = Ro \times e^{B\left(\frac{1}{T\_Cold} - \frac{1}{T_o}\right)}$  $R_{NTC\_Hot} = Ro \times e^{B\left(\frac{1}{T\_Hot} - \frac{1}{T_o}\right)}$ 

VCold: The value of the voltage divided by the resistance at low temperature VHot: The value of the voltage divided by the resistance at hot temperature VNTC\_Cold: Detection voltage of NTC terminal at low temperature . 3.605 V at Ta=2 °C VNTC\_Hot: Detection voltage of NTC terminal at high temperature. 1.535 V at Ta=48 °C RNTC\_Cold: NTC thermistor resistance at cold temperature RNTC\_Hot: NTC thermistor resistance at hot temperature Ro: NTC thermistor resistance at Ta 25°C B: B constant of NTC thermistor T\_Cold: Low temperature T\_Hot: High temperature To: 25°C

## Parts list


| arts  | list                        |                |            | Table 5. Parts li    | ist                         |                         |                               |
|-------|-----------------------------|----------------|------------|----------------------|-----------------------------|-------------------------|-------------------------------|
| Count | Parts No.                   | Туре           | Value      | Description          | Manufacturer<br>Part Number | Manufacturer            | Size<br>[Unit: mm(inch)]      |
|       |                             |                |            | IC                   |                             |                         |                               |
| 1     | U1                          | Charger        | -          | Linear Charger       | BD71631QWZ-E2               | ROHM                    | 1.8 x 2.4<br>(0.071x0.094)    |
|       |                             |                |            | Capacito             | pr                          | •                       |                               |
| 1     | CVIN1                       | MLCC           | 4.7µF      | 16V, X5R, ±10%       | GRM188R61C475KAAJD          | MURATA                  | 1608(0603)                    |
| 1     | CVOUT1                      | MLCC           | 1µF        | 25V, X5R, ±10%       | GRM155R61E105KA12D          | MURATA                  | 1005(0402)                    |
| 1     | CNTC                        | MLCC           | 0.01µF     | 16V, B, ±10 %        | GRM155B11C103KA01           | MURATA                  | 1005(0402)                    |
| 2     | CVIN2,<br>CVOUT2            | MLCC           | OPEN       | -                    | -                           | -                       | -                             |
|       |                             |                |            | Resisto              | r                           |                         |                               |
| 3     | RLED,<br>RNTC1,<br>RNTC2    | Resistor       | 10kΩ       | 1/10W, 50V,<br>±0.5% | MCR03EZPD1002               | ROHM                    | 1608(0603)                    |
| 1     | RICHG1                      | Resistor       | 5.1kΩ      | 1/10W, 50V,<br>±0.5% | MCR03EZPD5101               | ROHM                    | 1608(0603)                    |
| 1     | RITERM                      | Resistor       | 51kΩ       | 1/10W, 50V,<br>±0.5% | MCR03EZPD5102               | ROHM                    | 1608(0603)                    |
| 1     | RVFB1                       | Resistor       | 180kΩ      | 1/10W, 50V,<br>±0.5% | MCR03EZPD1803               | ROHM                    | 1608(0603)                    |
| 1     | RVFBRE1                     | Resistor       | 120kΩ      | 1/10W, 50V,<br>±0.5% | MCR03EZPD1203               | ROHM                    | 1608(0603)                    |
| 2     | RVFB2,<br>RVFBRE2           | Resistor       | 30kΩ       | 1/10W, 50V,<br>±0.5% | MCR03EZPD3002               | ROHM                    | 1608(0603)                    |
| 1     | RNTC3                       | -              | SHORT      | -                    | -                           | -                       | -                             |
|       |                             |                |            | LED                  |                             |                         |                               |
| 1     | LED                         | -              | LED        | White, Clear         | SML312WBCW1                 | ROHM                    | 1608(0603)                    |
| 1     | 14                          | -              | OPEN       | Connect              | -                           | 1                       | [                             |
| 1     | J1<br>CN1                   | -<br>Connector | 4terminals | -<br>3.81mm pitch    | -<br>MKDS 1/ 4-3,81         | -<br>Phoenix<br>contact | -<br>15.23x 7.3<br>(0.6x0.29) |
|       | l                           |                |            | Optional parts (Boo  | ost converter)              | contact                 | (0.0/0.20)                    |
| 1     | U2                          | -              | OPEN       | -                    | -                           | -                       | -                             |
| 1     | L3                          | -              | OPEN       | -                    | -                           | -                       | -                             |
| 2     | CDCDCIN1,<br>CDCDCIN2       | -              | OPEN       | -                    | -                           | -                       | -                             |
| 2     | CDCDCOUT1,<br>CDCDCOUT2     | -              | OPEN       | -                    | -                           | -                       | -                             |
| 3     | REN,<br>RVSEL_H,<br>RVSEL_L | -              | OPEN       | -                    | -                           | -                       | -                             |

The product and manufacturer names listed in the parts list are current at the time this user's guide was prepared, and some parts may not be available. Please select the equivalent product based on the characteristics listed in the table. Select a ceramic capacitor with the same actual capacitance in consideration of the DC bias characteristics.

## **Board Layout**

| EVK PCB information |                  |          |                     |                  |  |
|---------------------|------------------|----------|---------------------|------------------|--|
|                     | Number of Layers | Material | Board Size          | Copper Thickness |  |
|                     | 4                | FR-4     | 46mm x 36mm x 1.6mm | 1oz (35µm)       |  |

The layout of BD71631QWZ-EVK-001 is shown below.







Figure 9. Top Silkscreen Layout (Top View)

Figure 10. Top Layer Layout (Top View)






Figure 11. Middle1 Layer Layout (Top View) Figure 12. Middle2 Layer Layout (Top View)




Figure 13. Bottom Layer Layout (Top View)

# **Reference Application Data**




Figure 14. Charge Current vs VOUT Voltage

Figure 15. Charge Voltage vs Input Voltage




Figure 16. VOUT Leak Current vs VOUT Voltage (VIN = Open)

# **Revision History**

| - | Date          | Revision           | Description     |
|---|---------------|--------------------|-----------------|
|   | Dale          | Number Description |                 |
|   | 24. May. 2021 | 001                | Initial release |

|     | Notes  |
|-----|--|
|     | Notes  |
| 1)  | The information contained herein is subject to change without notice.  |
| 2)  | Before you use our Products, please contact our sales representative and verify the latest specifica-<br>tions :   |
| 3)  | Although ROHM is continuously working to improve product reliability and quality, semicon-<br>ductors can break down and malfunction due to various factors.<br>Therefore, in order to prevent personal injury or fire arising from failure, please take safety<br>measures such as complying with the derating characteristics, implementing redundant and<br>fire prevention designs, and utilizing backups and fail-safe procedures. ROHM shall have no<br>responsibility for any damages arising out of the use of our Poducts beyond the rating specified by<br>ROHM. |
| 4)  | Examples of application circuits, circuit constants and any other information contained herein are provided only to illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.  |
| 5)  | The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM or any other parties. ROHM shall have no responsibility whatsoever for any dispute arising out of the use of such technical information.  |
| 6)  | The Products specified in this document are not designed to be radiation tolerant.   |
| 7)  | For use of our Products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a ROHM representative : transportation equipment (i.e. cars, ships, trains), primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, servers, solar cells, and power transmission systems.   |
| 8)  | Do not use our Products in applications requiring extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters.   |
| 9)  | ROHM shall have no responsibility for any damages or injury arising from non-compliance with the recommended usage conditions and specifications contained herein.   |
| 10) | ROHM has used reasonable care to ensure the accuracy of the information contained in this document. However, ROHM does not warrants that such information is error-free, and ROHM shall have no responsibility for any damages arising from any inaccuracy or misprint of such information.  |
| 11) | Please use the Products in accordance with any applicable environmental laws and regulations, such as the RoHS Directive. For more details, including RoHS compatibility, please contact a ROHM sales office. ROHM shall have no responsibility for any damages or losses resulting non-compliance with any applicable laws or regulations.  |
| 12) | When providing our Products and technologies contained in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.  |
| 13) | This document, in part or in whole, may not be reprinted or reproduced without prior consent of ROHM.  |
|     |  |



Thank you for your accessing to ROHM product informations. More detail product informations and catalogs are available, please contact us.

# ROHM Customer Support System

https://www.rohm.com/contact/