USB Type-C Sink Port Detection and Protection IC BD91N01NUX Function Description

This product is a USB Type-C detection IC that is compatible with USB Type-C Rev2.1 standard for applications which require to sink power. When a Type-C plug is inserted, the product enters stand-alone operation where it supplies power from VBUS to the system. Through this product, a Type-C interface can be introduced to receive voltage and current of up to 5V/3A which is the Type-C standard.

It can be used in applications that operate up to 15W of power, allowing the user to combine the ports of applications that had separate traditional power like USB Standard/Micro/Mini B ports.

Specification Description

ROHI

This product is dedicated for the Sink application. When a Source device is connected via Type-C, a series of operations are performed; the product operates through the VBUS power, then detects the orientation of Type-C, insertion and removal detection, then selects the USB Type-C current. The connection status is relayed to the system via output terminals. When a Type-C connection is detected, the Pch-MOS FET in the VBUS power line turns ON, supplying power to the system.

The status of the Type-C connection can be monitored by checking each digital output using an MCU. Since the product does not have an input setting terminal, configuring the MCU is not required.

The Pch-MOS FET on the VBUS power line automatically turns off when Source device is disconnected.

[Power Supply Specification]

- •VBUS =4.0 to 5.5V
- •VDDIO =1.7 to 5.5V

[Type-C Connection specification] •SNK / UFP

[SNK (Power Sink) Specification]Inform the system of the Type-C connection condition via both TCC1 and TCC0.

[Protection Function specification]

- VBUS Over Voltage protection
- VBUS Under Voltage Lockout

[Digital Output terminals]

The following features are assigned to digital output terminals.

Table 1. Digital output terminals

Terminal #	Name	Output Voltage Level	Features
6	TCC1	VDDIO	The 2-bit data of
7	TCC0	VDDIO	Type-C current capability
8	ORIENT	VDDIO	Plug Orientation
9	SWMONI	VDDIO	Status of external Pch-MOS FET

Note: All digital terminals have NO pull-down or pullup.

Unsupported Features

Table 2 lists the following features which the product does not support since it only supports Type-C Sink and UFP. Please check our USB PD controllers if the following listed features are needed.

Table 2. Features not supported by BD91N01NUX

Unsupported features		
OTG	Power Delivery	
Dual Role Power Port	Power Role Swap	
Dual Role Data Port	Data Role Swap	
Source	PPS	
DFP	Fast Role Swap	
BC1.2	VBUS OCP	
Sink that requires over 15W	Sink that requires over 5V	

Specifications Detail

Power Supply of this device

(VB Power Supply)

The power of this product is supplied at the VB terminal. When a Type-C plug is inserted, VBUS supplies power to the VB terminal where a power-on reset is performed to start-up the product.

(VDDIO Power Supply)

Power to VDDIO is not required when all functions assigned to the digital output pin are not used.

VDDIO supplies power to each digital output pin. VDDIO can be turned on at any time. As a simple application shown in Figure 5, VDDIO is connected to the powerline of Pch-MOS FET, and power is supplied from the VBUS to VDDIO after a series of connection detections.

In addition, the output terminals reflect the Type-C connection status after the TCC Detection Removal Pulse Width t_F has elapsed

Please see the datasheet for further information.

Boot-up time and Operation Mode

The product notifies the status of the Pch-MOS FET by asserting the SWMONI terminal after taking SWDRV Turn on Time t_2 when the voltage on VB terminal is higher than VBUS supply detection voltage V_{UVREL}. After the Detection Data Invalid Time t_1 . elapses, TCC1 and TCC0 stabilizes and notifies the current capability of the connected Source.

Please see the datasheet for further information.

The voltage clamper on CC1/2 terminal

The product is designed to operate under dead battery conditions; therefore, it does not require power from the system. Voltage clampers are integrated into CC1 and CC2 pins to enable connection detection from the Source even there is no power supply in the system. In cases where dead battery operation is required in Stand-alone operation, the product asserts the clampers as the Rd resistor to enable detection from the

Source. These clampers are automatically released and disables as soon as the VBUS voltage is above $V_{\mbox{UVREL}}.$

Note that the clampers are for detecting the plugged source under the dead battery conditions and is not intended for voltage protection of CC terminals. On the other hand, the CC terminals has an absolute maximum rating of 28V, and an external protective element is not required.

Power supply from VBUS

The product performs a series of connection detection according to the USB Type-C standard, then turns on the Pch-MOS FET on the VBUS power line via the SWDRV terminal to automatically supply the power to the system. After that, the detected Type-C capability is notified to the external components through TCC1 and TCC2.

The SWDRV terminal and the detection of the connection failures

Unlike the legacy USB standard, the Type-C standard is capable of cold plug function. The Type-C port supplies power on VBUS after a successful connection between port-pair by both CC1 and CC2 being stable.

The product uses cold plug function to determine connection failures. The detection finds any failures that are caused by the plugged source or the attached cable to observe both CC1 and CC2 terminals at the point where the VB terminal voltage rises equal to or over V_{UVREL} .

In the regular connection, the device turns on the Pch-MOS FET at the SWDRV for the VBUS power line to supply the power to the system as described above. On the other hand, if any failures were detected, the device turns off the switch to isolate the system from the VBUS power line.

Please refer to Table 3 for further information in addition to "CC Detection" on page.4 in the datasheet.

CC1 terminal	CC2 terminal	Result	SWDRV
< 0.15V	< 0.15V	Failures*	OFF(H)
0.25V~2.18V	< 0.15V	Normal	
< 0.15V	0.25V to 2.18V	Normai	
0.25V~2.18V	0.25V to 2.18V	Not comply with Type-C	
> 2.5V	Don't care	Failures on	OFF(H)
Don't care	> 2.5V	pull up in Source side	

Table 3. The result of the detection.

*In case of the power is applied to VB terminal.

Table 4 shows the specification in the Type-C standard and this product finds any failures according to these thresholds.

Table 4. The definition of the CC voltage range in Type-C standard.

Connect to	Definition CC terminal voltage	
Sink	Open	< 0.15V
	Connection range 0.25V to 2.18V	
	USB Default	0.25V to 0.61V
	USB Type-C 1.5A 0.70V to 1.16V	
	USB Type-C 3.0A	1.31V to 2.04V
Source	Open	> 2.5V

Regardless of the determined state (normal or failure), the corresponding SWDRV terminal is NOT released until the VBUS voltage falls equal to or below V_{UVDET}.

Note that the state of SWDRV terminal is fixed and not released even if different voltages are applied to both CC1 and CC2 pins to confirm the behavior of the device by using an external power source on the evaluation in a Lab. This case may occur in a Lab, but it doesn't happen in the actual environment.

VBUS Over Voltage Protection

This product has an overvoltage protection function for the VB terminal voltage (VBUS voltage). When a voltage exceeding V_{OVDET} is detected, the device turns off the Pch-MOS FET and isolates the system from Type-C receptacle.

This condition latches off when the VBUS pin's overvoltage detection state persists and is not released until the VBUS voltage falls below V_{UVDET} .

The latched off-state does not occur when the overvoltage pulse width is less than "Auto Recovery Pulse Width" t_3 , which then the device recovers to normal condition immediately, where t_3 is defined at up

to 10µs, therefore, the product always recovers from the latched off-state if the pulse width applied is less than t₃.

Specifically, the product recovers from the latched offstate even if a pulse width of over 10μ s is applied. Note that the t₃ value does not define the transition from the latched-off state.

The detection result and VBUS Current limitation

The product notifies the current capability of the Type-C by asserting both TCC1 and TCC0, on the other hand the product does not provide the current limitation for the detected current capability. A system shall control the current limitation for its drawing current according to the current capability of the source device.

Under Voltage Lockout on VBUS

The product turns off the Pch-MOS FET on the VBUS power line once the applied VBUS voltage is below V_{UVDET} . Once the VBUS voltage is below V_{UVDET} all connection states are cleared. From this, when the VBUS voltage is greater than or equal to V_{UVREL} connection detection is performed again, considering the previous connection is maintained.

Removing Type-C plug from receptacle causes disconnection from the Source and losing VBUS power supply. Therefore, the device enters power off / reset status. This behavior doesn't depend on the VDDIO.

Power supplying to a system during booting up

Since this product uses a Pch-MOS FET to control the VBUS power line, the VBUS voltage is supplied to the later stage until BD91N01NUX applies the Gate voltage of the Pch-MOS FET at startup and the off is confirmed as shown in Figure 1.

Please note that the supplied voltage and its duration strongly depend on the capacitance between Pch-MOS FET or something in the actual system. Please use any Pch-MOS FETs that have less gate capacitance (C_{iss}) or add an appropriate resistor between VBUS and SWDRV as applications if a system requires to reduce

the supplied voltage to the second stage. Please note that there is a built-in 50kohm resistor between VB terminal and SWDRV terminal.



Figure 1. The waveform of VSRC at the bootup time

A measure for Overshoot / Undershoot voltage at the timing of the connection to the source.

This product does not take countermeasures against overshoot / undershoot voltage when powering the Source device. Please consider it separately on the system load side.

In addition, since the standard mask is set for the overshoot / undershoot during the voltage rise and fall in USBPD, please refer to the USBPD standard manual (e.g., Chapter 7.1.4,) for more details.

Type-C Connection Detection

When a connection is established with the Source device and VBUS is equal or greater than VUVREL and the voltage of CC1 and CC2 are within 0.25V and 2.18V as defined in the Type-C standard, the product outputs the connection result via TCC1 and TCC0 after one Detection Data Invalid Time t_1 .

TCC1 and TCC0 also change with respect to the change in CC1 and CC2 after the connection, but this situation shall not occur and should not affect the system in an actual case according to Type-C standard.

When connected to a Type-C/PD device, a PD source communicates with CC1 or CC2 for a specific duration depending on its voltage. This communication does not affect the system because the product has a dedicated filter to ignore these signals.

The other charging standards, outside of Type-C standard

This product only supports Type-C and does not support vendor-specific charging such as DCP / CDP in BC1.2 and any proprietary charging methods like Quick Charge. If connected, the product interprets it like it is connected to a standard USB port through a standardcompliant Type-A to C cable, then turns on the Pch-MOS FET on the VBUS power line.

USB-IF had released BC1.2 Standard as official, coexisting with Type-C. The detected BC1.2 port (i.e., DCP or CDP) can allow the sink to draw current up to 1.5A exceeding the Type-C default current capability. In this case, the external BC1.2 port detector is required.

The connection to PD Source device

The product only supports Type-C and doesn't support USB PD. But USB PD standard assumes USB Type-C, so the device detects and interprets the PD source device according to the USB Type-C standard. In this case, the device informs the asserted Rp by the PD source to a system via both TCC0 and TCC1 as well as the connection to Type-C source.

The connection via Type-A to C Cable

This product supports connection via Type-A to C cable. Type-A to C cable has a built-in Rp in its Type-C plug. In addition, the Rp is the resistor that asserts USB default current according to Type-C standard for it not to draw excess current from Source. Therefore, when connected, TCC1 and TCC0 is TCC1=L, TCC0=H, which indicates USB default.

If a Type-B to C cable is connected, the product cannot boot up since the Type-B side port does not supply power to the VBUS.

Table 5 shows the representative devices andconnection results via TCC0 / TCC1.

Table 5. The results of the connection detection to the representative devices.

Connected device	Cable	TCC1	TCC0
Source Type-C Default*		L	Н
Source Type-C 1.5A		Н	L
Source Type-C 3.0A	Turne C	Н	Н
Source Type-C USB PD	туре-С	Н	Н
Sink Type-C		L	L
Sink Type-C USB PD		L	L
Legacy-A (with BC1.2)	Type-A to C	L	Н
Legacy-B	Type-B to C	L	L

*Type-C default is according to implemented USB standard version.

The device is designed with an assumption that a Type-A to C cable to be used is Type-C standard compliant and has a $56k\Omega$ Rp to indicate USB default.

ORIENT function

The ORIENT function is used to determine the direction of the normal/flip side of the Type-C cable and determine its pin assignment for USB communication. The ORIENT terminal asserts "L" upon startup and maintains it if CC1 is connected, while it is "H" if CC2 is connected.

Basically, this function can be used to determine the assignment of high-speed operating signals from USB3.x or later. The Type-C standard allows D+ (Dp1 / Dp2) terminals and D- (Dn1 / Dn2) terminals, which is used for USB2.0 LS/FS/HS communication, to be shorted to each other near the Type-C receptacle.

Therefore, the architecture can allow a system not to implement any multiplexor for USB2.0 data lines. A system can also utilize the ORIENT function for multiplexing USB2.0 signal lines due to PCB layout constraints, as shown in Figure 2.





SWMONI Function

SWMONI function constantly asserts "H" whenever SWDRV turns on. Therefore, it can be used for detecting the power supplied from the Source, to the system. The signal can also be applied as an enable input on POL that generates internal power, or on any GPIOs in an MCU to control internal signals.

Current detection by TCC0/TCC1

As explained in the following paragraph, this product has no current limitation or protection according to asserted TCC1 and TCC0. A separate system shall control the current limit depending on the Source device.

TCC0 and TCC1 can be utilized to notify the information regarding the current capability of the connected Source device. Referring to the current capability defined by TCC0 and TCC1, charging current and overcurrent protection settings can be set to chargers and POL via MCUs and logic components. In the case of the default current in USB standard, there is no method for the Type-C architecture to specify the USB default current. Therefore, a system shall determine the current limitation according to the USB version of the implemented USB PHY. Note that for USB3.2 and later, these standards require Type-C port and USB Power Delivery, so it does not fall into this category.

Table 6. The definition of default current in USB.

USB Standard	Current limitation
Before enumeration	100mA
regardless of USB1.0 to	
3.1	
USB1.x and 2.0	500mA
USB3.0 and 3.1*	900mA

*USB3.2 or later requires Type-C 1.5A as its default.

The determined current capability by TCC0 and TCC1 indicates the maximum current capability of the Source device. The minimum power consumption and actual power consumption by the Sink device should be less than the capability of the Source.

In addition, this product always turns on the Pch-MOS FET of the VBUS power line and powers the system if there is a connected Source device. Therefore, it is necessary for a system to limit the power consumption from VBUS if the power supplied by the detected Source device is less than the minimum operating power required by the Sink.

Connected device	Cable	Max power of a Sink
		USB2.0: 2.5W
Source Type-C Default		USB3.x: 4.5W**
Source Type-C 1.5A	Type-C	7.5W
Source Type-C 3.0A		15W
Source Type-C USB PD		15W
Legacy-A (with BC1.2)	Type-A to C	7.5W*

Table 7. The power limitation between Source and Sink

*BC1.2 detector is required in addition.

**1.5A is required as default on USB3.2 or later

Disconnection and the detection timing of TCC0 / TCC1

Since the change in the CC1/CC2 to TCC terminals strongly depends on the stabilization time of chattering for the insertion/removal of type-C plugs, timing from CC1/CC2 is not specified by the datasheet of BD91N01NUX.

Especially, when determining the time of removal, the stability of the TCC0 and TCC1 terminals is such that SWMONI will drop within 500 µs when VBUS falls below 3.1 V due to the removal of the Type-C plug, so by triggering this, TCC will be determined stably.



Figure 3.The stability of TCC0 and TCC1 at the unplugging

Table 8.	The timing	characteristic of	TCC0 and TCC1
----------	------------	-------------------	---------------

Parameter	Symbol	Min	Тур	Max	Unit
The stability timing from VBUS 3.1V threshold	t4	-	-	500	μs

Regarding EXP-PAD

EXP-PAD is not connected to internal GND and can be connected to GND or Open.



Recommended Application Example







Recommended application parts and its selection

Symbol Name	Contents	Characteristic	Comment/Recommendation
U1	IC	3.0mm×2.0.mm, VSON010X3020	BD91N01NUX
C1	Capacitor	0.1µF, ≥ 16V, X5R/X7R	
C2	Capacitor	1µF, ≥ 16V, X5R/X7R	
С3	Capacitor	1μF to 10μF, ≥16V, X5R/X7R	USB PD standard specifies the total capacitance before Q1 turning on as cSnkBulk. Please adjust the sum of C1 and C3 capacitance within 1µF to 10µF.
C4	Capacitor	1μF to 100μF, ≥16V, X5R/X7R	USB PD standard specifies the total capacitance after Q1 turning on as cSnkBulkPd. Please adjust the sum of C1, C3 and C4 capacitance within 1μ F to 100μ F according to the second stage of a system.
Q1, Q2*	FET	Pch-MOS FET	RW4C045BC

Tabla Q	Pecommended	application	narte	solaction
i able 9.	Recommended	application	parts	Selection

*For preventing the reverse back current from VSRC, both Q1 and Q2 compose Back-to-Back architecture. Q1 is only required if the feature is not required.

Revision History

Date	Revision Number	Description
Oct. 14. 2021	001	Initial Release
Oct. 31. 2024	002	Fix Туро

Notice	
1)	The information contained in this document is intended to introduce ROHM Group (hereafter referred to asROHM) products. When using ROHM products, please verify the latest specifications or datasheets before use.
2)	ROHM products are designed and manufactured for use in general electronic equipment and applications (such as Audio Visual equipment, Office Automation equipment, telecommunication equipment, home appliances, amusement devices, etc.) or specified in the datasheets. Therefore, please contact the ROHM sales representative before using ROHM products in equipment or devices requiring extremely high reliability and whose failure or malfunction may cause danger or injury to human life or body or other serious damage (such as medical equipment, transportation, traffic, aircraft, spacecraft, nuclear power controllers, fuel control, automotive equipment including car accessories, etc. hereafter referred to as Specific Applications). Unless otherwise agreed in writing by ROHM in advance, ROHM shall not be in any way responsible or liable for any damages, expenses, or losses incurred by you or third parties arising from the use of ROHM Products for Specific Applications.
3)	Electronic components, including semiconductors, can fail or malfunction at a certain rate. Please be sure to implement, at your own responsibilities, adequate safety measures including but not limited to fail-safe design against physical injury, and damage to any property, which a failure or malfunction of products may cause.
4)	The information contained in this document, including application circuit examples and their constants, is intended to explain the standard operation and usage of ROHM products, and is not intended to guarantee, either explicitly or implicitly, the operation of the product in the actual equipment it will be used. As a result, you are solely responsible for it, and you must exercise your own independent verification and judgment in the use of such information contained in this document. ROHM shall not be in any way responsible or liable for any damages, expenses, or losses incurred by you or third parties arising from the use of such information.
5)	When exporting ROHM products or technologies described in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, such as the Foreign Exchange and Foreign Trade Act and the US Export Administration Regulations, and follow the necessary procedures in accordance with these provisions.
6)	The technical information and data described in this document, including typical application circuits, are examples only and are not intended to guarantee to be free from infringement of third parties intellectual property or other rights. ROHM does not grant any license, express or implied, to implement, use, or exploit any intellectual property or other rights owned or controlled by ROHM or any third parties with respect to the information contained herein.
7)	No part of this document may be reprinted or reproduced in any form by any means without the prior written consent of ROHM.
8)	All information contained in this document is current as of the date of publication and subject to change without notice. Before purchasing or using ROHM products, please confirm the latest information with the ROHM sales representative.
9)	ROHM does not warrant that the information contained herein is error-free. ROHM shall not be in any way responsible or liable for any damages, expenses, or losses incurred by you or third parties resulting from errors contained in this document.



Thank you for your accessing to ROHM product informations. More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

https://www.rohm.com/contactus