ROHM Solution Simulator


500mA 3.3V Output LDO Regulator BD433M5FP2-C – Load Response simulation

This circuit simulates the load response of BD433M5FP2-C. You can observe the fluctuation of the output voltage when the load current is abruptly changed. You can customize the parameters of the components shown in blue, such as VCC, or peripheral components, and simulate the load response with the desired operating condition.

General Cautions

- *Caution 1:* The values from the simulation results are not guaranteed. Please use these results as a guide for your design. Caution 2: These model characteristics are specifically at Ta=25°C. Thus, the simulation result with temperature variances may significantly differ from the result with the one done at actual application board (actual measurement).
- Caution 3: Please refer to the datasheet and application notes of LDO Regulators for details of the technical information. Caution 4: The characteristics may change depending on the actual board design and ROHM strongly recommend to double check those characteristics with actual board where the chips will be mounted on.

1 Simulation Schematic




2 How to simulate

The simulation settings, such as parameter sweep or convergence options, are configurable from the 'Simulation Settings' shown in Figure 2, and Table 1 shows the default setup of the simulation.

In case of simulation convergence issue, you can change advanced options to solve. Nothing is stated in the default statement in 'Manual Options'. You can modify it.

Table 1 Simulation settings default setup



Ξ

Figure 2. Simulation Settings and execution

	sellings deladil selup	
Parameters	Default	Note
Simulation Type	Time-Domain	Do not change Simulation Type
End Time	1.5ms	-
Advanced options	Balanced	-
	Convergence Assist	-
Manual Options	-	-

3 Simulation Conditions

Table 2. List of the simulation condition parameters

Instance	Turco	Parameters	Default	Variable	e Range	Units
Name	Туре	Farameters	Value	Min	Max	Units
		Voltage_level	13.5	4	42	V
VCC	Voltage Source	AC_magnitude	0.0	fixed		V
	-	AC_phase	0.0	fixed		0
	IOUT Current Source	Initial_value	10	0	500	mA
		Pulse_value	250	0	500	mA
		Ramptime_initial_to_pulse	12.5	free ^(Note1)		μs
IOUT		Ramptime_pulse_to_initial	12.5	free ^(Note1)		μs
		Start_delay	300	free ^(Note1)		μs
		Pulse_width	400	free ^(Note1)		μs
		Period	1	free	(Note1)	S

(Note 1) Set it to the guaranteed operating range of the LDO Regulators.

3.1 IOUT parameter setup

Figure 3 shows how the IOUT parameters correspond to the IOUT stimulus waveform.




Figure 3. IOUT parameters and its waveform

4 BD433M5FP2 model

Table 3 shows the model terminal function implemented. Note that BD433M5FP2 is the behavior model for its load/line response operation, and no protection circuits or the functions not related to the purpose are not implemented.

Table 3. BD433M5FP2 model terminals used for the simulation

Terminals	Description	
VOUT	Output Pin	
GND	Ground Pin	
VCC	Supply Voltage Input Pin	

(Note 2) This model is not compatible with the influence of ambient temperature.

(Note 3) Use the simulation results only as a design guide and the data reported herein is not a guaranteed value.

5 Peripheral Components

5.1 Bill of Material

Table 4 shows the list of components used in the simulation schematic. Each of the capacitors has the parameters of equivalent circuit shown below. The parameters' value of equivalent components are set to default except for the ESR of C. You can modify the values of each component.

Turne	Instance Name	Parameters	Default Value	Variable Range		Linita
Туре				Min	Max	Units
Capacitor	CIN	Capacitance_value	4.7	0.1	free	μF
		ESR	5m	1m	10	Ω
	COUT	Capacitance_value	10	10	free	μF
		ESR	5m	1m	10	Ω

Table 4. Lis	t of capacitors	used in the	e simulation	circuit

5.2 Capacitor Parameters

Property Editor	-14	×
Capacitor - datasheet		
Label COUT		0
CAPACITANCE_VALUE		
10u	F	0
ESR		
5m	Ohm	0
ESL		
0.0	н	0
LEAK		
0.0	A	0
rc		
0.0	1.0/degC	0
USE_DEVICE_TEMI	P	8
DEVICE_TEMP		
27.0	degC	0
USE_INITIAL_VOLT	AGE	8
/OLTAGE_MAX		
100.0	V	0
POWER_AVG_MAX		
0.25	W	0
rau .		
1.0e-2	sec	0

Figure 4. Capacitor property editor

The default value of ESR is $5m\Omega$.

(*Note 4*) These parameters can take any positive value or zero in simulation but it does not guarantee the operation of the IC in any condition. Refer to the datasheet to determine adequate value of parameters.

6 Recommended Product

6.1 LDO Regulator

BD433M5FP2-C: 500mA 3.3V Output LDO Regulator. [JP] [EN] [CN] [KR] [TW] [DE]

Technical Articles and Tools can be found in the Design Resources on the product web page.

	Notes
1)	The information contained herein is subject to change without notice.
2)	Before you use our Products, please contact our sales representative and verify the latest specifica- tions :
3)	Although ROHM is continuously working to improve product reliability and quality, semicon- ductors can break down and malfunction due to various factors. Therefore, in order to prevent personal injury or fire arising from failure, please take safety measures such as complying with the derating characteristics, implementing redundant and fire prevention designs, and utilizing backups and fail-safe procedures. ROHM shall have no responsibility for any damages arising out of the use of our Poducts beyond the rating specified by ROHM.
4)	Examples of application circuits, circuit constants and any other information contained herein are provided only to illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.
5)	The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM or any other parties. ROHM shall have no responsibility whatsoever for any dispute arising out of the use of such technical information.
6)	The Products specified in this document are not designed to be radiation tolerant.
7)	For use of our Products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a ROHM representative : transportation equipment (i.e. cars, ships, trains), primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, servers, solar cells, and power transmission systems.
8)	Do not use our Products in applications requiring extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters.
9)	ROHM shall have no responsibility for any damages or injury arising from non-compliance with the recommended usage conditions and specifications contained herein.
10)	ROHM has used reasonable care to ensure the accuracy of the information contained in this document. However, ROHM does not warrants that such information is error-free, and ROHM shall have no responsibility for any damages arising from any inaccuracy or misprint of such information.
11)	Please use the Products in accordance with any applicable environmental laws and regulations, such as the RoHS Directive. For more details, including RoHS compatibility, please contact a ROHM sales office. ROHM shall have no responsibility for any damages or losses resulting non-compliance with any applicable laws or regulations.
12)	When providing our Products and technologies contained in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.
13)	This document, in part or in whole, may not be reprinted or reproduced without prior consent of ROHM.



Thank you for your accessing to ROHM product informations. More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

https://www.rohm.com/contact/