

AC/DC Convertor Non-Isolated PWM type, 7.2 W (12 V/0.6 A) BM2PAA1Y-Z Evaluation Board



<High Voltage Safety Precautions>

 \bigcirc Read all safety precautions before use

Please note that this document covers only the BM2PAA1Y-Z evaluation board (BM2PAA1Y-EVK-001) and its functions. For additional information, please refer to the datasheet.

To ensure safe operation, please carefully read all precautions before handling the evaluation board



Depending on the configuration of the board and voltages used,

Potentially lethal voltages may be generated.

Therefore, please make sure to read and observe all safety precautions described in the red box below.

Before Use

- [1] Verify that the parts/components are not damaged or missing (i.e. due to the drops).
- [2] Check that there are no conductive foreign objects on the board.
- [3] Be careful when performing soldering on the module and/or evaluation board to ensure that solder splash does not occur.
- [4] Check that there is no condensation or water droplets on the circuit board.

During Use

- [5] Be careful to not allow conductive objects to come into contact with the board.
- [6] Brief accidental contact or even bringing your hand close to the board may result in discharge and lead to severe injury or death.

Therefore, DO NOT touch the board with your bare hands or bring them too close to the board.

In addition, as mentioned above please exercise extreme caution when using conductive tools such as tweezers and screwdrivers.

- [7] If used under conditions beyond its rated voltage, it may cause defects such as short-circuit or, depending on the circumstances, explosion or other permanent damages.
- [8] Be sure to wear insulated gloves when handling is required during operation.

After Use

- [9] The ROHM Evaluation Board contains the circuits which store the high voltage. Since it stores the charges even after the connected power circuits are cut, please discharge the electricity after using it, and please deal with it after confirming such electric discharge.
- [10] Protect against electric shocks by wearing insulated gloves when handling.

This evaluation board is intended for use only in research and development facilities and should by handled **only by qualified personnel familiar with all safety and operating procedures.**

We recommend carrying out operation in a safe environment that includes the use of high voltage signage at all entrances, safety interlocks, and protective glasses.



AC/DC Converter

Non-Isolated Buck Convertor 12 V 7.2W Output **BM2PAA1Y-Z Evaluation Board**

BM2PAA1Y-EVK-001

Feature

- (1) Adjustable Output Voltage with External Resistor
- (2) Frequency 65 kHz
- (3) Internal Start up Circuit 730 V(peak)
- (4) Internal Super Junction FET 730 V(peak) (Ron = 1.2Ω)
- (5) Internal Current Sense Resistor (Detection Current 1.76 A)
- (6) Contributes to Low EMI by Internal Hopping Function



Figure 1. BM2PAA1Y-EVK-001



Figure 2. BM2PAA1Y-EVK-001 Simple Schematic

Specification

Table	1	Input Range
Ianc	۰.	inputitange

Parameter	Min	Тур	Max	Units	Conditions
Input Voltage Range	90	230	264	Vac	
Input Frequency Range	47	50 / 60	63	Hz	
Operating Temperature	-10	25	+65	O°	

Table 2. Evaluation board specification

These are representative values and not a guarantee of the characteristics, unless stated otherwise use VIN = 230 Vac, IOUT = 0.6 A, Ta = 25 ° C.

Parameter	Min	Тур	Мах	Units	Conditions
Output Voltage	11.04	12.0	12.6	V	
Output Maximum Power	-	-	7.2	W	
Output Current Range (Note 1)	0	-	0.6	Α	
No Load Power Consumption	-	230	-	mW	Iout = 0 A
Efficiency	-	79	-	%	
Output Ripple Voltage (Note 2)	-	-	100	mVpp	

(Note 1) Adjust the operating time so that surface temperature of no component exceeds 105 °C

(Note 2) Do not consider spike nois

Nov.2021

Operation Procedure

- 1. Operation equipment
 - (1) AC power supply 90 Vac to 264 Vac, 15 W or more
 - (2) Electronic Load capacity 0.6 A
 - (3) Multimeter

2. Connection Instruments

- (1) Turn off each power supply and connect the measuring instrument as shown below.
- (2) Turn on the power supply setting between 90 Vac to 264 Vac
- (3) Turn on the electrical load setting between 0 to 0.6 A.
- (4) Connect the multimeter directly to the output and check the voltage by sensing.



Figure 3. Connection Circuit

Circuit

 V_{IN} = 90 to 264 Vac, V_{OUT} = 12 V



Figure 4. Application Circuit

BOM List

Item		Specifications	Parts name	Manufacture
	C1	12 µF, 450 V	UCY2W120MP01TD	NICHICON
	C2	12 µF, 450 V	UCY2W120MP01TD	NICHICON
	C3	-	NON MOUNTED	-
	C4	0.22 µF, 100 V	UMK107B7224KA-T	TAIYO YUDEN
	C5	1000 pF, 100 V	HMK107B7102KA-T	TAIYO YUDEN
Capacitor	C6	1000 pF, 100 V	HMK107B7102KA-T	TAIYO YUDEN
	C8	-	NON MOUNTED	-
	C9	-	NON MOUNTED	-
	C10	-	NON MOUNTED	-
	C11	-	NON MOUNTED	-
	C12	1000 µF, 25 V	25ZLJ1000M10x20	RUBYCON
Connector	CN1	-	B02P-NV	JST
	D1	FRD, 3 A, 600 V	RFN3BM6S	ROHM
Diode	D2	FRD, 0.2 A, 600 V	RFU02VSM6S	ROHM
	DB1	1 A, 800 V	D1UBA80	SHINDENGEN
Fuse	F1	1.6 A, 300 V	36911600000	LITTELFUSE
IC	IC1	-	BM2PAA1Y-Z	ROHM
Jumper	J1	0 Ω	MCR18EZPJ000	ROHM
	L1	100 µH	RFS1317NP-104KL	COIL CRAFT
Inductor	L2	-	NON MOUNTED	-
	L3	470 μH	7447462471	WURTH ELECTRONIK
Photocoupler	PC1	-	NON MOUNTED	-
PCB	PCB1	-	PCB0178	ROHM
	R1	-	SHORT	-
	R2	-	SHORT	-
	R3	1 MΩ	MCR03EZPFX1004	ROHM
Resistor	R4	200 kΩ	MCR03EZPFX2003	ROHM
	R6	1 kΩ	MCR18EZPJ102	ROHM
	R7	-	NON MOUNTED	-
	R9	-	NON MOUNTED	-

Layout

Size 70 mm x 30 mm



Figure 5. Top Silkscreen (Top view)



Figure 6. Bottom Layout (Bottom view)

BM2Pxx1Y Overview

Features

- PWM Current Mode
- Built-in Frequency Hopping Function
- Burst Operation at Light Load
- Built-in 730 V(peak) Starter Circuit
- Built-in 730 V(peak) Super Junction MOSFET
- VCC UVLO (Under Voltage Lockout)
- VCC OVP (Over Voltage Protection)
- Over Current Limiter Function per Cycle
- Soft Start Function
- Sleep Mode



Figure 7. Pin Configuration

Line Up

Model Name	Switching Frequency	Frequency Reduction	OCP Current
BM2PAA1Y-Z	65 kHz	0	1.76 A
BM2PAB1Y-Z	25 kHz	-	1.70 A
BM2PDA1Y-Z	65 kHz	0	0.93 A
BM2PDB1Y-Z	25 kHz	-	0.93 A

Key Specifications

	Operating	Power	Supply	Voltage	Range
--	-----------	-------	--------	---------	-------

VCC	11.10 V to 26.00 V
DRAIN	730 V(peak) (Max)
Operating Current (Normal):	650 µA (Typ)
Operating Current (Burst):	350 µА (Тур)
Operating Current (Sleep):	65 µА (Тур)
Switching Frequency:	25 kHz / 65 kHz (Typ)
Operation Temperature:	-40 °C to +105 °C
MOSFET ON Resistance:	1.2 Ω (Typ)

Application

Washing machine, Air conditioner, Other white goods

Package

DIP7K

W(Typ) x D(Typ) x H(Typ) 9.27 mm x 6.35 mm x 8.63 mm Pitch 2.54 mm



Table 3. BM2Pxx1Y-Z Pin Description

No.	Name	I/O	Function
1	N.C.	-	Non connection
2	SLEEP	I	Sleep/Normal modes witching pin
3	GND_IC	I/O	GND pin
4	FB	I	Output voltage feedback pin
5	VCC	I	Input voltage pin
6	DRAIN	I/O	MOSFET drain pin
7	DRAIN	I/O	MOSFET drain pin

0.6

Measurement Data

Constant Load Regulations



Figure 8. IOUT vs. VOUT



Figure 10. IOUT vs. Frequency





Figure 11. IOUT vs. Power Loss

Waveform



Figure 12. Vds and IL VIN = 90 Vac, IOUT = 0 A







Figure 16. Vds and IL VIN = 90 Vac, IOUT = 0.6 A



Figure 13. Vds and IL VIN = 264 Vac, IOUT = 0 A



Figure 15. Vds and IL VIN = 264 Vac, IOUT = 0.3 A





Waveform (Start Up)



Figure 18. Vds and Vout VIN = 90 Vac, IOUT = 0 A



Figure 19. Vds and Vout VIN = 264 Vac, IOUT = 0 A



Figure 20. Vds and Vout VIN = 90 Vac, IOUT = 0.6 A





Waveform (Load Response)



Figure 22. lout and Vout VIN = 90 Vac, IOUT = 0.1 A to 0.6 A



Figure 24. lout and Vout VIN = 90 Vac, IOUT = 0.6 A to 0.1 A



Figure 23. lout and Vout VIN = 264 Vac, IOUT = 0.1 A to 0.6 A



Figure 25. lout and Vout VIN = 264 Vac, IOUT = 0.6 A to 0.1 A

Waveform (Ripple Voltage)



Figure 26. Vout Ripple Voltage (5 MHz Filter) VIN = 90 Vac, IOUT = 0.6 A

Operation Temperature

Condition lout=0.6 A. 20 min

VIN=90 Vac



IC 63.8 °C



Diode 67.2 °C







Figure 27. Vout Ripple Voltage (5MHz filter) VIN = 264 Vac, IOUT = 0.6 A

VIN= 264 Vac



IC 60.8 °C



Diode 65.6 °C



Inductor 67.5 °C

Figure 28. Each device Temperature with maximum output current

Consider selecting parts after checking the temperature range of the parts used.



Figure 29. Conduction Noise VIN = 90 Vac



.5M .7M 1M

.3M

		Rea	ding		Res	ults	Lit	nit	Mai	gin		
No.	Freq.	<qp></qp>	<av></av>	C.Fac	<qp></qp>	<av></av>	<qp></qp>	<av></av>	<qp></qp>	<av></av>	Phase	Comment
	[MHz]	[dBuV]	[dBuV]	[dB]	[dBuV]	[dBuV]	[dBuV]	[dBuV]	[dB]	[dB]		
1	0.15501	33.4	15.6	10.2	43.6	25.8	65.7	55.7	22.1	29.9	VA	
2	0.35962	29.8	20.6	10.3	40.1	30.9	58.7	48.7	18.6	17.8	VA	
3	0.50797	29.9	21.1	10.4	40.3	31.5	56.0	46.0	15.7	14.5	VA	
4	1.01835	28.8	20.7	10.4	39.2	31.1	56.0	46.0	16.8	14.9	VA	
5	0.15217	34.7	15.8	10.2	44.9	26.0	65.8	55.8	20.9	29.8	VB	
6	0.35369	32.2	18.9	10.3	42.5	29.2	58.8	48.8	16.3	19.6	VB	
7	0.50123	31.5	18.8	10.3	41.8	29.1	56.0	46.0	14.2	16.9	VB	
8	1.02724	31.4	21.3	10.4	41.8	31.7	56.0	46.0	14.2	14.3	VB	
9	4.57709	29.4	18.5	10.6	40.0	29.1	56.0	46.0	16.0	16.9	VB	
10	4.79505	29.7	19.5	10.6	40.3	30.1	56.0	46.0	15.7	15.9	VB	

3M Frequency [Hz] 5M 7M 10M

2M

20M 30M

Figure 30. Conduction Noise VIN = 264 Vac

Revision History

Date	Rev.	Changes
Mar.2021	001	New Release
Nov.2021	002	Maximum Output Current =0.75 A -> 0.6 A Maximum Output Power =9 W -> 7.2 W OCP Detection Current =2.0 A -> 1.76 A FET=650 V-> 730 V(peak) Figure 8 to 30 modified

	Notes
1)	The information contained herein is subject to change without notice.
2)	Before you use our Products, please contact our sales representative and verify the latest specifica- tions :
3)	Although ROHM is continuously working to improve product reliability and quality, semicon- ductors can break down and malfunction due to various factors. Therefore, in order to prevent personal injury or fire arising from failure, please take safety measures such as complying with the derating characteristics, implementing redundant and fire prevention designs, and utilizing backups and fail-safe procedures. ROHM shall have no responsibility for any damages arising out of the use of our Poducts beyond the rating specified by ROHM.
4)	Examples of application circuits, circuit constants and any other information contained herein are provided only to illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.
5)	The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM or any other parties. ROHM shall have no responsibility whatsoever for any dispute arising out of the use of such technical information.
6)	The Products specified in this document are not designed to be radiation tolerant.
7)	For use of our Products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a ROHM representative : transportation equipment (i.e. cars, ships, trains), primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, servers, solar cells, and power transmission systems.
8)	Do not use our Products in applications requiring extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters.
9)	ROHM shall have no responsibility for any damages or injury arising from non-compliance with the recommended usage conditions and specifications contained herein.
10)	ROHM has used reasonable care to ensure the accuracy of the information contained in this document. However, ROHM does not warrants that such information is error-free, and ROHM shall have no responsibility for any damages arising from any inaccuracy or misprint of such information.
11)	Please use the Products in accordance with any applicable environmental laws and regulations, such as the RoHS Directive. For more details, including RoHS compatibility, please contact a ROHM sales office. ROHM shall have no responsibility for any damages or losses resulting non-compliance with any applicable laws or regulations.
12)	When providing our Products and technologies contained in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.
13)	This document, in part or in whole, may not be reprinted or reproduced without prior consent of ROHM.



Thank you for your accessing to ROHM product informations. More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

http://www.rohm.com/contact/