

ROHM Solution Simulator

4.5 V to 28 V Input, 2.0 A Integrated MOSFET Single Synchronous Buck DC/DC Converter

BD9E201FP4-Z / Frequency Response

This circuit simulates the frequency response of BD9E201FP4-Z. You can observe the loop gain and measure phase margin. You can customize the simulation conditions by changing the parameters of components highlighted in blue. You can simulate the circuit in the published application note: Measurement Method for Phase Margin with FRA. [JP] [EN] [CN]

General Cautions

- Caution 1: The values from the simulation results are not guaranteed. Use these results as a guide for your design.
- Caution 2: These model characteristics are specifically at Ta = 25 °C. Thus, the simulation result with temperature variances may significantly differ from the result with the one done at actual application board (actual measurement).
- Caution 3: Please refer to the datasheet for details of the technical information.
- Caution 4: The characteristics may change depending on the actual board design and ROHM strongly recommend to double check those characteristics with actual board where the chips will be mounted on.

Simulation Schematic




Figure 1. Simulation Circuit

How to simulate

The simulation settings, such as frequency range or convergence options, are configurable from the 'Simulation Settings' shown in Figure 2, and Table 1 shows the default setup of the simulation.

In case of simulation convergence issue, you can change advanced options to solve.

The parameters V_VIN, V_VO, I_IO, and L are defined in the 'Manual Options'.



Figure 2. Simulation Settings and execution

Table 1. Simulation settings default setup

Parameters	Default	Note
Simulation Type	Frequency-Domain	(Do not change Simulation Type)
Start Frequency	1k Hz	Simulate the frequency response for the
End Frequency	1Meg Hz	frequency range from 1 kHz to 1 MHz.
Advanced options	Balanced Convergence Assist	
Manual Options	".param V_VIN=12 V_VO=3.3 I_IO=2 L=10u"	See "Simulation Condition" for details

©2023 ROHM Co., Ltd. No. 65UG081E Rev.001 Jan.2023 1/5

Simulation Conditions 3

3.1 How to define V_{IN} , V_{OUT} , I_{OUT} , and L

These parameters are used to setup the simulation conditions and BD9E201FP4-Z_AVE model parameters, therefore these are defined in the Manual Options as the common variables.


Table 2 shows the default value of V_{IN}, V_{OUT}, I_{OUT}, and L. Those values are defined and can be set in the 'Manual Options' text box from Simulation Settings as shown in Figure 3.

The input voltage VIN, output inductance of L1, and the load resistance of RL are automatically set according to those parameters. Note that feedback resistors are not automatically set by V_VO. Set Rfb1 and Rfb2 manually.

Table 2. Simulation Conditions

Parameters	Variable Name	Default Value	Units	Descriptions	
V_{IN}	V_VIN	12	V	Input Voltage	
V _{OUT}	V_VO	3.3	V	Output Voltage	
l _{out}	I_IO	2	Α	Output Current	
L	L	10u	Н	Output Inductor	

(Note 1) Set it to the guaranteed operating range of the DC/DC Converter.



3.2 Resistive Load RL

RL is the resistive load and its resistance is determined from V_{OUT} and I_{OUT}. The resistance value is determined by the equation below.

Table 3. Resistive load

Instance Name	Default Value	Unit
RL	{ V_VO / I_IO }	Ω

No. 65UG081E Rev.001 ©2023 ROHM Co., Ltd. 2/5

4 BD9E201FP4-Z AVE model

The simulation model in this circuit is designed for frequency response, and the functions not related to frequency response are not implemented.

Table 4. BD9E201FP4-Z_AVE model pins used for frequency response

Pin Name	Description	
VIN	Power supply input.	
EN	Enable input.	
BOOT	Pin for bootstrap.	
SW	Switching node.	
FB	Output voltage feedback pin.	
GND	Ground.	

4.1 BD9E201FP4-Z_AVE Model Parameters

BD9E201FP4-Z_AVE model has its parameters shown in Table 5. All the parameters are pre-defined and fixed in the simulation. V_VIN is substituted to V_VIN, V_VO is substituted to V_VO, and L is substituted to L as shown in Table 5.

Table 5. Parameter List

Parameters	Default Values	Description
V_VIN	V_VIN	VIN voltage
V_VO	V_VO	VOUT voltage
L	L	Output inductance




Figure 4. Property Editor of BD9E201FP4-Z_AVE model

No. 65UG081E Rev.001 ©2023 ROHM Co., Ltd. Jan.2023 3/5

5 **Peripheral Components**

To set parameters of components, open 'property' by double clicking or right clicking on a component. You can input a value to a property text box if available. Please refer to the hands-on manual for more details.

5.1 **Bill of Material**


Table 6 shows the list of components used in the simulation schematic. Each of the capacitor and inductor has the parameters of equivalent circuit shown below. The default value of equivalent components are set to zero except for the parallel and series resistance of L1, series resistance of capacitors, and series inductance of output capacitors. You can modify the values of each component.

Table 6. List of components used in the simulation circuit

Type	Instance Name	Default Value	Units
Capacitor	Cboot	0.1	μF
	Cout1	19.8	μF
	Cout2	19.8	μF
Inductor	L1	10	μH
Resistor	Rfb1	100	kΩ
	Rfb2	22.1	kΩ

5.2 Capacitor Equivalent Circuits





Property editor


(b) Equivalent circuit

Figure 5. Capacitor property editor and equivalent circuit

The default value of ESR is 2 m Ω and ESL is 1 pH.

5.3 Inductor Equivalent Circuits





Property editor

(b) Equivalent circuit

Figure 6. Inductor property editor and equivalent circuit

The default value of PAR_RES is 6.6 k Ω and SER_RES is 50 m Ω .

(Note 2) These parameters can take any positive value or zero in simulation but it does not guarantee the operation of the IC in any condition. Refer to the datasheet to determine adequate value of parameters.

6 Open Loop Transfer Function (OLTF) Monitor

OLTF1 is the insert model to measure AC open loop transfer function and is inserted to acquire the gain and phase output. To monitor the gain and phase from OLTF1, select probe items 'dbMag' for gain and 'phase' for phase plot, respectively from 'property' of OLTF1.




Figure 7. Probe Items of OLTF1

7 Link to the product information and tools

7.1 DC/DC Converter BD9E201FP4-Z : Integrated MOSFET Single Synchronous Buck DC/DC Converter. [JP] [EN] [CN] [KR] [TW] [DE]

7.2 General Purpose Chip Resistors

MCR01MZPF: Thick Film Chip Resistors. [JP] [EN] [CN] [KR] [TW] [DE]

Technical Articles and Tools can be found in the Design Resources on the product web page.

©2023 ROHM Co., Ltd.

No. 65UG081E Rev.001

Jan.2023

Notes

- 1) The information contained herein is subject to change without notice.
- Before you use our Products, please contact our sales representative and verify the latest specifications:
- 3) Although ROHM is continuously working to improve product reliability and quality, semiconductors can break down and malfunction due to various factors. Therefore, in order to prevent personal injury or fire arising from failure, please take safety measures such as complying with the derating characteristics, implementing redundant and fire prevention designs, and utilizing backups and fail-safe procedures. ROHM shall have no responsibility for any damages arising out of the use of our Poducts beyond the rating specified by ROHM.
- 4) Examples of application circuits, circuit constants and any other information contained herein are provided only to illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.
- 5) The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM or any other parties. ROHM shall have no responsibility whatsoever for any dispute arising out of the use of such technical information.
- 6) The Products specified in this document are not designed to be radiation tolerant.
- 7) For use of our Products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a ROHM representative: transportation equipment (i.e. cars, ships, trains), primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, servers, solar cells, and power transmission systems.
- 8) Do not use our Products in applications requiring extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters.
- 9) ROHM shall have no responsibility for any damages or injury arising from non-compliance with the recommended usage conditions and specifications contained herein.
- 10) ROHM has used reasonable care to ensure the accuracy of the information contained in this document. However, ROHM does not warrants that such information is error-free, and ROHM shall have no responsibility for any damages arising from any inaccuracy or misprint of such information.
- 11) Please use the Products in accordance with any applicable environmental laws and regulations, such as the RoHS Directive. For more details, including RoHS compatibility, please contact a ROHM sales office. ROHM shall have no responsibility for any damages or losses resulting non-compliance with any applicable laws or regulations.
- 12) When providing our Products and technologies contained in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.
- 13) This document, in part or in whole, may not be reprinted or reproduced without prior consent of ROHM.



Thank you for your accessing to ROHM product informations. More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

http://www.rohm.com/contact/