# **MG7216WZ**

# 1200V 200A Insulated Gate Bipolar Transistor

Datasheet


$V_{CES}$	1200V
I <sub>C (Nominal)</sub>	200A
V <sub>CE(sat) (Typ.)</sub>	1.7V
Max. Possible Chips per Wafer	56pcs

# •Outline Wafer

### Features

- 1) Trench Light Punch Through Type
- 2) Low Collector Emitter Saturation Voltage
- 3) Short Circuit Withstand Time 10µs

## ●Inner Circuit



# Application

General Inverter

for Industrial Use

Absolute Maximum Ratings

PADSOIDE MAXIMUM Ratings					
Parameter	Symbol	Value	Unit		
Collector - Emitter Voltage, T <sub>j</sub> = 25°C	V <sub>CES</sub>	1200	V		
Gate - Emitter Voltage	$V_{GES}$	±30	V		
Collector Current	I <sub>C</sub> <sup>*1</sup>	*1)	А		
Pulsed Collector Current	I <sub>CP</sub> *2	600	А		
Operating Junction Temperature	T <sub>j</sub>	-40 to +175	°C		

<sup>\*1</sup> Depending on thermal properties of assembly

<sup>\*2</sup> Pulse width limited by  $T_{jmax.}$ 

# ●Design Assurance

Parameter	Parameter Symbol Conditions		Values			Unit
raiailletei	Symbol	Conditions	Min. Typ.		Max.	Offic
		$V_{CC} \le 600V$ ,				
Short Circuit Withstand Time	t <sub>sc</sub> *3	$V_{CC} \le 600V$ , $V_{GE} = 15V$ , $T_j = 25^{\circ}C$	10	-	-	μs
		T <sub>j</sub> = 25°C				
		$V_{CC} \le 600V$ ,				
Short Circuit Withstand Time	t <sub>sc</sub> *3	$V_{GE} = 15V$ , $T_j = 150^{\circ}C$	8	-	-	μs
		T <sub>j</sub> = 150°C				
		$I_C = 600A, V_{CC} = 1050V,$	FULL SQUARE			
Reverse Bias Safe Operating Area	RBSOA*3	$V_P = 1200V, V_{GE} = 15V,$			-	
		$I_C = 600A, V_{CC} = 1050V,$ $V_P = 1200V, V_{GE} = 15V,$ $R_G = 50\Omega, T_j = 175^{\circ}C$				


<sup>\*3</sup> Design assurance without measurement

# ●Electrical Characteristics (at T<sub>i</sub> = 25°C unless otherwise specified)

Davamatar	Cumbal	Conditions	Values			l limit	
Parameter	Symbol	Conditions	Min.	Тур.	Max.	Unit	
Collector - Emitter Breakdown Voltage	BV <sub>CES</sub>	$I_{C} = 10 \mu A, V_{GE} = 0 V$	1200	-	-	V	
Collector Cut - off Current	I <sub>CES</sub>	$V_{CE} = 1200V, V_{GE} = 0V$	-	-	10	μΑ	
Gate - Emitter Leakage Current	I <sub>GES</sub>	$V_{GE} = \pm 30V, V_{CE} = 0V$	-	-	±500	nA	
Gate - Emitter Threshold Voltage	$V_{\text{GE(th)}}$	$V_{CE} = 5V, I_{C} = 30.2mA$	5.0	6.0	7.0	V	
Collector - Emitter Saturation Voltage		$I_{C} = 200A, V_{GE} = 15V,$ $T_{j} = 25^{\circ}C$ $T_{j} = 175^{\circ}C$	-	1.7 2.2	2.1	V	
Input Capacitance	C <sub>ies</sub>	V <sub>CE</sub> = 30V,	-	16610	-		
Output Capacitance	C <sub>oes</sub>	$V_{GE} = 0V$ ,	-	777	-	pF	
Reverse transfer Capacitance	$C_{res}$	f = 1MHz	-	85	-		
Total Gate Charge	$Q_g$	V <sub>CE</sub> = 500V,	-	540	-		
Gate - Emitter Charge	$Q_ge$	$I_C = 200A,$	-	148	-	nC	
Gate - Collector Charge	$Q_{gc}$	V <sub>GE</sub> = 15V	-	199	-		

<sup>\*3</sup> Design assurance without measurement


# **●Chip Information**



① : Gate Bonding Pad

2 : Emitter Bonding Pad

Backside : Collector



Wafer Size	150mm
Wafer Thickness	0.14±0.01mm
Chip Size	14.30mm×14.30mm
Cut Line Width	0.10±0.03mm
Top Side Metallization	AlSiCu:4.4µm
Back Side Metallization	Ti/Ni:0.4µm/Au:0.05µm
Passivation	Polyimide
	·

### •Further Electrical Characteristics

Switching characteristics and thermal properties are depending strongly on module design and mounting technology and can therefore not be specified for a bare die.

This chip data sheet refers to the device data sheet	-
--	---

Technology qualified in TO-247N package.

### Notes

- 1) The information contained herein is subject to change without notice.
- Before you use our Products, please contact our sales representative and verify the latest specifications.
- 3) Although ROHM is continuously working to improve product reliability and quality, semiconductors can break down and malfunction due to various factors.

  Therefore, in order to prevent personal injury or fire arising from failure, please take safety measures such as complying with the derating characteristics, implementing redundant and fire prevention designs, and utilizing backups and fail-safe procedures. ROHM shall have no responsibility for any damages arising out of the use of our Poducts beyond the rating specified by ROHM.
- 4) Examples of application circuits, circuit constants and any other information contained herein are provided only to illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.
- 5) The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM or any other parties. ROHM shall have no responsibility whatsoever for any dispute arising out of the use of such technical information.
- 6) The Products specified in this document are not designed to be radiation tolerant.
- 7) For use of our Products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a ROHM representative: transportation equipment (i.e. cars, ships, trains), primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, and power transmission systems.
- 8) Do not use our Products in applications requiring extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters.
- 9) ROHM shall have no responsibility for any damages or injury arising from non-compliance with the recommended usage conditions and specifications contained herein.
- 10) ROHM has used reasonable care to ensure the accuracy of the information contained in this document. However, ROHM does not warrants that such information is error-free, and ROHM shall have no responsibility for any damages arising from any inaccuracy or misprint of such information.
- 11) Please use the Products in accordance with any applicable environmental laws and regulations, such as the RoHS Directive. For more details, including RoHS compatibility, please contact a ROHM sales office. ROHM shall have no responsibility for any damages or losses resulting non-compliance with any applicable laws or regulations.
- 12) When providing our Products and technologies contained in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.
- 13) This document, in part or in whole, may not be reprinted or reproduced without prior consent of ROHM.



Thank you for your accessing to ROHM product informations. More detail product informations and catalogs are available, please contact us.

# ROHM Customer Support System

http://www.rohm.com/contact/

### **General Precaution**

- 1. Before you use our Products, you are requested to carefully read this document and fully understand its contents. ROHM shall not be in any way responsible or liable for failure, malfunction or accident arising from the use of any ROHM's Products against warning, caution or note contained in this document.
- 2. All information contained in this document is current as of the issuing date and subject to change without any prior notice. Before purchasing or using ROHM's Products, please confirm the latest information with a ROHM sales representative.
- 3. The information contained in this document is provided on an "as is" basis and ROHM does not warrant that all information contained in this document is accurate and/or error-free. ROHM shall not be in any way responsible or liable for any damages, expenses or losses incurred by you or third parties resulting from inaccuracy or errors of or concerning such information.

Notice – WE Rev.001