

650V 50A Field Stop Trench IGBT

V _{CES}	650V
I _{C(100°C)}	50A
V _{CE(sat) (Typ.)}	1.6V
P _D	277W

Features

- 1) Low Collector Emitter Saturation Voltage
- 2) High Speed Switching
- 3) Low Switching Loss & Soft Switching
- 4) Built in Very Fast & Soft Recovery FRD (RFN - Series)
- 5) Pb free Lead Plating ; RoHS Compliant

Applications


PFC

UPS


Power Conditioner

IH

Outline



Inner Circuit



Packaging Specifications

	Packaging	Tube
	Reel Size (mm)	-
Type	Tape Width (mm)	-
Туре	Basic Ordering Unit (pcs)	600
	Packing code	C13
	Marking	RGTH00TS65D

•Absolute Maximum Ratings (at T_C = 25°C unless otherwise specified)

Parameter		Symbol	Value	Unit
Collector - Emitter Voltage		V _{CES}	650	V
Gate - Emitter Voltage		V _{GES}	±30	V
Callester Oursent	$T_{C} = 25^{\circ}C$	Ι _C	85	А
Collector Current	T _C = 100°C	Ι _C	50	А
Pulsed Collector Current		I _{CP} *1	200	А
Diada Famuland Culumant	$T_{C} = 25^{\circ}C$	١ _F	50	А
Diode Forward Current	T _C = 100°C	١ _F	30	А
Diode Pulsed Forward Current		I _{FP} ^{*1}	200	А
Dower Dissinction	$T_{C} = 25^{\circ}C$	P _D	277	W
Power Dissipation	T _C = 100°C	P _D	138	W
Operating Junction Temperature		T _j	-40 to +175	°C
Storage Temperature		T _{stg}	-55 to +175	°C
*1 Pulso width limited by T				

*1 Pulse width limited by T_{jmax.}

RGTH00TS65DGC13

•Thermal Resistance

Parameter	Symbol	Values			Unit
Parameter	Symbol	Min.	Тур.	Max.	Unit
Thermal Resistance IGBT Junction - Case	$R_{\theta(j\text{-}c)}$	-	-	0.54	°C/W
Thermal Resistance Diode Junction - Case	$R_{\theta(j\text{-}c)}$	-	-	1.42	°C/W

●IGBT Electrical Characteristics (at T_j = 25°C unless otherwise specified)

Parameter	Symbol	Conditions	Values			Unit	
Faranieler	Farameter Symbol Conditions		Min.	Тур.	Max.		
Collector - Emitter Breakdown Voltage	BV _{CES}	I _C = 10μΑ, V _{GE} = 0V	650	-	-	V	
Collector Cut - off Current	I _{CES}	V _{CE} = 650V, V _{GE} = 0V	-	-	10	μA	
Gate - Emitter Leakage Current	I _{GES}	V_{GE} = ±30V, V_{CE} = 0V	-	-	±200	nA	
Gate - Emitter Threshold Voltage	V _{GE(th)}	V _{CE} = 5V, I _C = 34.7mA	4.5	5.5	6.5	V	
Collector - Emitter Saturation Voltage	V _{CE(sat)}	I _C = 50A, V _{GE} = 15V T _j = 25°C T _j = 175°C	-	1.6 2.1	2.1 -	V	



•IGBT Electrical Characteristics (at $T_j = 25^{\circ}C$ unless otherwise specified)

Deremeter	Cumph of	Conditions		Unit			
Parameter	Symbol	Conditions	Min.	Тур.	Max.	Unit	
Input Capacitance	C _{ies}	V _{CE} = 30V	-	2740	-		
Output Capacitance	C _{oes}	V _{GE} = 0V	-	106	-	pF	
Reverse Transfer Capacitance	C _{res}	f = 1MHz	-	43	-		
Total Gate Charge	Qg	V _{CE} = 300V	-	94	-		
Gate - Emitter Charge	Q _{ge}	I _C = 50A	-	22	-	nC	
Gate - Collector Charge	Q_{gc}	V _{GE} = 15V	-	31	-		
Turn - on Delay Time	t _{d(on)}	I _C = 50A, V _{CC} = 400V	-	39	-		
Rise Time	t _r	V_{GE} = 15V, R_{G} = 10 Ω	-	63	-	20	
Turn - off Delay Time	t _{d(off)}	T _j = 25°C	-	143	-	ns	
Fall Time	t _f	Inductive Load	-	50	-		
Turn - on Delay Time	t _{d(on)}	I _C = 50A, V _{CC} = 400V	-	39	-		
Rise Time	t _r	V_{GE} = 15V, R_G = 10 Ω	-	63	-	20	
Turn - off Delay Time	$t_{d(off)}$	T _j = 175°C	-	159	-	ns	
Fall Time	t _f	Inductive Load	-	62	-		
		I _C = 200A, V _{CC} = 520V			<u>.</u>		
Reverse Bias Safe Operating Area	RBSOA	V _P = 650V, V _{GE} = 15V	FU	LL SQUA	RE	-	
		R _G = 60Ω, T _j = 175°C					

•IGBT Electrical Characteristics (at $T_j = 25^{\circ}C$ unless otherwise specified)

Deremeter	Symbol	Conditions	Values			Unit	
Parameter	Symbol	Conditions	Min.	Тур.	Max.	Unit	
Diode Forward Voltage	V _F	I _F = 30A T _i = 25°C		1.45	2.0	V	
Diode Forward Voltage	VF	T _j = 175°C	-	1.45	-	v	
Diode Reverse Recovery Time	t _{rr}	I _F = 30A	-	54	-	ns	
Diode Peak Reverse Recovery Current	I _{rr}	V _{CC} = 400V di _F /dt = 200A/µs	-	7.4	-	А	
Diode Reverse Recovery Charge	Q _{rr}	T _j = 25°C	-	0.22	-	μC	
Diode Reverse Recovery Time	t _{rr}	I _F = 30A	-	225	-	ns	
Diode Peak Reverse Recovery Current	I _{rr}	V _{CC} = 400V di _F /dt = 200A/µs	-	12.8	-	А	
Diode Reverse Recovery Charge	Q _{rr}	T _j = 175°C	-	1.60	-	μC	





Fig.1 Power Dissipation vs. Case Temperature

Fig.2 Collector Current vs. Case Temperature

Fig.3 Forward Bias Safe Operating Area

Fig.4 Reverse Bias Safe Operating Area








Fig.5 Typical Output Characteristics





Fig.8 Typical Collector To Emitter Saturation Voltage vs. Junction Temperature

Fig.6 Typical Output Characteristics



www.rohm.com © 2021 ROHM Co., Ltd. All rights reserved.

175

Fig.10 Typical Collector To Emitter Saturation Voltage

•Electrical Characteristic Curves







Fig.9 Typical Collector To Emitter Saturation Voltage vs. Gate To Emitter Voltage





Collector To Emitter Voltage : $V_{CE}[V]$

Fig.16 Typical Gate Charge






Fig.19 Typical Diode Reverse Recovery Current vs. Forward Current





Fig.20 Typical Diode Reverse Recovery Charge vs. Forward Current






Fig.21 IGBT Transient Thermal Impedance

Pulse Width : t1[s]




Fig.22 Diode Transient Thermal Impedance

Pulse Width : t1[s]



●Inductive Load Switching Circuit and Waveform




Fig.23 Inductive Load Circuit




Fig.25 Diode Reverce Recovery Waveform




Fig.24 Inductive Load Waveform



	Notes
1)	The information contained herein is subject to change without notice.
2)	Before you use our Products, please contact our sales representative and verify the latest specifica tions.
3)	Although ROHM is continuously working to improve product reliability and quality, semicon ductors can break down and malfunction due to various factors. Therefore, in order to prevent personal injury or fire arising from failure, please take safety measures such as complying with the derating characteristics, implementing redundant and fire prevention designs, and utilizing backups and fail-safe procedures. ROHM shall have no responsibility for any damages arising out of the use of our Poducts beyond the rating specified by ROHM.
4)	Examples of application circuits, circuit constants and any other information contained herein are provided only to illustrate the standard usage and operations of the Products. The periphera conditions must be taken into account when designing circuits for mass production.
5)	The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly any license to use or exercise intellectual property or other rights held by ROHM or any othe parties. ROHM shall have no responsibility whatsoever for any dispute arising out of the use of such technical information.
6)	The Products specified in this document are not designed to be radiation tolerant.
7)	For use of our Products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a ROHM representative : transportation equipment (i.e cars, ships, trains), primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, servers, solar cells, and power transmission systems.
8)	Do not use our Products in applications requiring extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters.
9)	ROHM shall have no responsibility for any damages or injury arising from non-compliance with the recommended usage conditions and specifications contained herein.
10)	ROHM has used reasonable care to ensure the accuracy of the information contained in thi document. However, ROHM does not warrants that such information is error-free, and ROHM shall have no responsibility for any damages arising from any inaccuracy or misprint of such information.
11)	Please use the Products in accordance with any applicable environmental laws and regulations such as the RoHS Directive. For more details, including RoHS compatibility, please contact a ROHM sales office. ROHM shall have no responsibility for any damages or losses resulting non-compliance with any applicable laws or regulations.
12)	When providing our Products and technologies contained in this document to other countries you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.
13)	This document, in part or in whole, may not be reprinted or reproduced without prior consent or ROHM.



Thank you for your accessing to ROHM product informations. More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

http://www.rohm.com/contact/

General Precaution

- 1. Before you use our Products, you are requested to care fully read this document and fully understand its contents. ROHM shall not be in an y way responsible or liable for failure, malfunction or accident arising from the use of a ny ROHM's Products against warning, caution or note contained in this document.
- 2. All information contained in this docume nt is current as of the issuing date and subject to change without any prior notice. Before purchasing or using ROHM's Products, please confirm the latest information with a ROHM sale s representative.
- 3. The information contained in this document is provided on an "as is" basis and ROHM does not warrant that all information contained in this document is accurate an d/or error-free. ROHM shall not be in an y way responsible or liable for any damages, expenses or losses incurred by you or third parties resulting from inaccuracy or errors of or concerning such information.