SiC Power Module

BSM300D12P4G101


Datasheet

Application

- · Motor drive
- · Inverter, Converter
- · Photovoltaics, wind power generation.
- · Induction heating equipment.

Features


- 1) Low surge, low switching loss.
- 2) High-speed switching possible.
- 3) Reduced temperature dependence.



●Construction

This product is a half bridge module consisting of SiC-UMOSFET from ROHM.

● Dimensions & Pin layout (Unit : mm)




● Absolute maximum ratings (T_i = 25°C)

Parameter	Symbol	Conditions	Ratings	Unit	
Drain - Source Voltage	V_{DSS}	/ _{DSS} G-S short			
Gate - Source Voltage (+)	V_{GSS}	D-S short	21	V	
Gate - Source Voltage (-)	V_{GSS}	D-S short	-4		
G - S Voltage (t _{surge} <300nsec)	V _{GSSsurge}	D-S short Note 1)	-4 to 23]	
Drain Current Note 2)	I _D	DC(Tc=60°C) V _{GS} =18V	291		
	I _{DRM}	Pulse (Tc = 60° C) 1ms V _{GS} = $18V$ _{Note 3)}	600		
Source Current Note 2)	I _S DC(Tc=60°C) V _{GS} =18V		291	А	
	I _{SRM}	Pulse (Tc = 60° C) 1ms V _{GS} = $18V_{\text{Note 3}}$			
	I _{SRM}	Pulse (Tc = 60° C) 1.5µs V _{GS} = 0 V _{Note 3) 4)}	600		
Total Power Dissipation Note 5)	Ptot	Tc = 25°C	925	W	
Max Junction Temperature	ature Tjmax		175		
Junction Temperature	Tjop		-40 to 150	°C	
Storage Temperature	rage Temperature Tstg		-40 to 125		
Isolation Voltage	Visol	Terminals to baseplate f = 60Hz AC 1 min.	2500	Vrms	
Mounting Torque		Main Terminals : M6 screw	4.5	N -m	
Mounting Torque	-	Mounting to heat sink M5 screw	3.5	N·m	

- Note 1) Please note especially when using driver source that V_{GSSsurge} must be in the range of absolute maximum rating.
- Note 2) Case temperature (Tc) is defined on the surface of base plate just under the chips.
- Note 3) Repetition rate should be kept within the range where temperature rise if die should not exceed Tjmax.
- Note 4) Repititive pulse, PW \leq 1.5 μ s, Duty cycle \leq 5%
- Note 5) Tj is less than 175°C.

Example of acceptable V_{GS} waveform

<Wavelength for Switching Test>



●Electrical characteristics (T_i=25°C)

Parameter	Symbol	Conditions			Ratings		
- Syllibol Syllibol		Conditions	Conditions		Тур.	Max.	Unit
On-state static	Vos(on)		Tj=25°C	_	1.2	1.6	V
Drain-Source		$I_D=300A, V_{GS}=18V$	Tj=125°C	_	1.9		
Voltage			Tj=150°C	_	2.2	2.9	
Drain Cutoff Current	IDSS	V _{DS} =1200V,V _{GS} =0V		_	_	1	mA
Souce-Drain Voltage	V_{SD}	Vgs=0V,Is=300A	Tj=25°C	_	3.9	_	V
			Tj=125°C	_	4.1	_	
			Tj=150°C	_	4.2	_	
		V _{GS} =18V,I _S =300A	Tj=25°C	_	1.2	_	
			Tj=125°C	_	1.8	_	
			Tj=150°C	_	2.1	_	
Gate-Source Threshold Voltage	Vgs(th)	V _{DS} =10V,I _D =145.6mA _{Note 6)}		2.8	_	4.8	V
Gate-Source	lgss	Vgs=21V,Vds=0V		_	_	0.5	
Leak Current		VGS=-4V,VDS=0V			_	_	μA
Switching Characteristics	td(on)	Vgs(on)=18V, Vgs(off)=0V Vps=600V Ip=300A			63	_	ns
	tr				45	_	
	trr				24	_	
	td (off)	Rg(on)=3.9 ohm, Rg(off)=3.3 ohm Inductive load		_	270	_	
	tf			_	57	_	
Input Capacitance	Ciss	VDS=10V,VGS=0V,200kHz		_	30	_	nF
Gate Registance	RGint	Tj=25°C		_	0.25	_	Ω
NTC Rated Resistance	R ₂₅			_	5.0	_	kΩ
NTC B Value	B _{25/50}			_	3370	_	K
Stray Inductance	Ls			_	14.5	_	nH
Creepage Distance	-	Terminal to heat sink		_	16.7	_	mm
		Terminal to terminal		_	16.7	_	mm
Clearance Distance	-	Terminal to heat sink		_	12.0	_	mm
		Terminal to terminal		_	11.0	_	mm
Junction-to -Case Thermal Resistance	Rth(j-c)	UMOSFET(1/2 module) Note 7)			_	162	°C/kW
Case-to -heat sink Thermal Resistance	Rth(c-f)	Case to heat sink, per 1 module. Thermal grease applied. Note 8)			15	_	

- Note 6) Tested after applying $V_{GS} = 21V$ for 100ms.
- Note 7) Measurement of Tc is to be done at the point just under the chip.
- Note 8) Typical value is measured by using thermally conductive grease of $\lambda=0.9W/(m\cdot K)$.
- Note 9) SiC devices have lower short cuicuit withstand capability due to high current density. Please be advised to pay careful attention to short cuicuit accident and try to adjust protection time to shutdown them as short as possible.
- Note 10) If the Product is used beyond absolute maximum ratings defined in the Specifications, as its internal structure may be dameged, please replace such Product with a new one.


Fig.1 Output characteristic 25°C (TYP) 600 $V_{GS}=14V$ 500 V_{GS}=16V Drain Current I_D (A) 400 V_{GS}=12V $V_{GS}=18V$ 300 V_{GS}=20V 200 V_{GS}=10V 100 0 1.5 0 0.5 2.5 Drain source voltage V_{DS} (V)

(TYP) 3.5 Tj=150°C Drain source voltage V_{DS} (V) V_{GS}=18V 3 2.5 Tj=125°C 2 1.5 Tj=25°C 0.5 0 100 200 300 400 500 600 0 Drain current I_D (A)

Fig.2 Drain source voltage characteristic

25°C (TYP) 2 Drain source voltage V_{DS} (V) 1.5 ID=300A 1 ID=200A 0.5 ID=150A ID=100A 0

Fig.3 Drain source voltage characteristic



12



Fig.5 Forward characteristic of Diode (TYP)

1000

V_{GS}=18V

V_{GS}=0V

Tj=150°C

Tj=25°C

0.1

Source drain voltage V_{SD} (V)

Fig.6 Forward characteristic of Diode (TYP) 600 Tj=25°C 500 V_{GS}=18∖ Source current Is (A) 400 300 200 Tj=150°C 100 Tj=125°C 0 5

Fig.7 Drain Current vs Gate Voltage (TYP)




Fig.8 Drain Current vs Gate Voltage (TYP)




Fig.9 Switching time vs drain current at 25°C (TYP)




Fig.10 Switching time vs drain current at 125°C (TYP)




Fig.11 Switching time vs drain current at 150°C (TYP)




Fig.12 Switching loss vs drain current at 25°C (TYP)




Fig.13 Switching loss vs drain current at 125°C (TYP)




Fig.14 Switching loss vs drain current at 150°C (TYP)




Fig.15 Recovery characteristic vs drain current at 25°C (TYP)




Fig.16 Recovery characteristic vs drain current at 125°C (TYP)




Fig.17 Recovery characteristic vs drain current at 150°C (TYP) 100 1000 trr Recovery time trr (ns) Recovery current Irr(A) Irr 10 100 V_{DS}=600V V_{GS} (on)=18V V_{GS} (off)=0V R_{G} =3.9 Ω INDUCTIVE LOAD 1 10 600 0 200 400 Drain current I_D (A)

at 25°C (TYP)

1000 $V_{DS}=600V$ $V_{DS}=600V$ $V_{GS}(on)=18V$ $V_{GS}(off)=0V$ INDUCTIVE LOAD td(on) tr 10 $Gate resistance <math>R_G$ (Ω)

Fig.18 Switching time vs gate resistance

Fig.19 Switching time vs gate resistance at 125°C (TYP)




Fig.20 Switching time vs gate resistance at 150°C (TYP)




Fig.21 Switching loss vs gate resistance at 25°C (TYP)




Fig.22 Switching loss vs gate resistance at 125°C (TYP)




Fig.23 Switching loss vs gate resistance at 150°C (TYP)





Fig.24 Capacitance vs Drain source voltage (TYP) 1.E-07 Ciss 1.E-08 Coss Tj=25°C V_{GS}=0V 200kHz 1.E-10 Crss 1.E-11 0.01 0.1 10 100 1000 Drain source voltage V_{DS} (V)

Fig.25 Gate charge characteristic (TYP)

Fig.26 Transient thermal impedance (TYP)



Notes

- 1) The information contained herein is subject to change without notice.
- Before you use our Products, please contact our sales representative and verify the latest specifications.
- 3) Although ROHM is continuously working to improve product reliability and quality, semiconductors can break down and malfunction due to various factors.

 Therefore, in order to prevent personal injury or fire arising from failure, please take safety measures such as complying with the derating characteristics, implementing redundant and fire prevention designs, and utilizing backups and fail-safe procedures. ROHM shall have no responsibility for any damages arising out of the use of our Poducts beyond the rating specified by ROHM.
- 4) Examples of application circuits, circuit constants and any other information contained herein are provided only to illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.
- 5) The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM or any other parties. ROHM shall have no responsibility whatsoever for any dispute arising out of the use of such technical information.
- 6) The Products specified in this document are not designed to be radiation tolerant.
- 7) For use of our Products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a ROHM representative: transportation equipment (i.e. cars, ships, trains), primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, and power transmission systems.
- 8) Do not use our Products in applications requiring extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters.
- 9) ROHM shall have no responsibility for any damages or injury arising from non-compliance with the recommended usage conditions and specifications contained herein.
- 10) ROHM has used reasonable care to ensure the accuracy of the information contained in this document. However, ROHM does not warrants that such information is error-free, and ROHM shall have no responsibility for any damages arising from any inaccuracy or misprint of such information.
- 11) Please use the Products in accordance with any applicable environmental laws and regulations, such as the RoHS Directive. For more details, including RoHS compatibility, please contact a ROHM sales office. ROHM shall have no responsibility for any damages or losses resulting non-compliance with any applicable laws or regulations.
- 12) When providing our Products and technologies contained in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.
- This document, in part or in whole, may not be reprinted or reproduced without prior consent of ROHM.



Thank you for your accessing to ROHM product informations. More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

http://www.rohm.com/contact/

General Precaution

- 1. Before you use our Products, you are requested to carefully read this document and fully understand its contents. ROHM shall not be in any way responsible or liable for failure, malfunction or accident arising from the use of any ROHM's Products against warning, caution or note contained in this document.
- 2. All information contained in this document is current as of the issuing date and subject to change without any prior notice. Before purchasing or using ROHM's Products, please confirm the latest information with a ROHM sales representative.
- 3. The information contained in this document is provided on an "as is" basis and ROHM does not warrant that all information contained in this document is accurate and/or error-free. ROHM shall not be in any way responsible or liable for any damages, expenses or losses incurred by you or third parties resulting from inaccuracy or errors of or concerning such information.

Notice – WE Rev.001