SCS215KGHR

Automotive Grade SiC Schottky Barrier Diode

Datasheet

V_R	1200V
I _F	15A
Q_{C}	51nC

Outline TO-220AC


Features

- 1) AEC-Q101 qualified
- 2) Low forward voltage
- 3) Negligible recovery time/current
- 4) Temperature independent switching behavior

Applications

- · On Board Charger
- DC/DC Converter
- · Wireless Charger
- EV Charger

•Inner circuit



Packaging specifications

	<u> </u>	- .
	Packaging	Tube
	Reel size (mm)	-
Type	Tape width (mm)	-
Туре	Basic ordering unit (pcs)	50
	Packing code	С
	Marking	SCS215KG

● Absolute maximum ratings (T_i = 25°C)

Parameter		Symbol	Value	Unit
Reverse voltage (re	petitive peak)	V_{RM}	1200	V
Reverse voltage (D	C)	V _R	1200	V
Continuous forward	current (T _c = 140°C)	I _F	15	А
Surge non-	PW=10ms sinusoidal, T _j =25°C		62	А
repetitive forward	PW=10ms sinusoidal, T _j =150°C	I _{FSM}	46	А
current	PW=10μs square, T _j =25°C		240	А
Repetitive peak forward current		I _{FRM}	68 *1	А
PW=10ms, T _j =25°C		$\int i^2 dt$	19	A ² s
i ² t value	PW=10ms, T _j =150°C	J i⁻dt	10	A ² s
Total power dissipation		P_{D}	180 ^{*2}	W
Junction temperature		T _j	175	°C
Range of storage temperature		T_{stg}	-55 to +175	°C

^{*1} T_c=100°C, T_i=150°C, Duty cycle=10% *2 T_c=25°C

•Electrical characteristics $(T_j = 25^{\circ}C)$

Parameter	Symbol	Conditions	Values			Unit
			Min.	Тур.	Max.	Unit
DC blocking voltage	V_{DC}	I _R =0.3mA	1200	-	-	V
	V _F	I _F =15A,T _j =25°C	-	1.4	1.6	V
Forward voltage		I _F =15A,T _j =150°C	-	1.8	-	V
		I _F =15A,T _j =175°C	-	1.9	-	V
Reverse current	I _R	V _R =1200V,T _j =25°C	-	15	300	μΑ
		V _R =1200V,T _j =150°C	-	120	-	μΑ
		V _R =1200V,T _j =175°C	-	195	-	μΑ
Total capacitance	С	V _R =1V,f=1MHz	-	790	-	pF
		V _R =800V,f=1MHz	-	64	-	pF
Total capacitive charge	Q _C	V _R =800V,di/dt=500A/μs	-	51	-	nC
Switching time	t _C	V _R =800V,di/dt=500A/μs	-	18	-	ns


●Thermal characteristics

Parameter	Symbol	Conditions	Values			Unit
			Min.	Тур.	Max.	Offic
Thermal resistance	$R_{\text{th(j-c)}}$	-	-	0.67	0.80	°C/W

●Typical Transient Thermal Characteristics

Symbol	Value	Unit
R _{th1}	1.24E-01	
R _{th2}	3.92E-01	K/W
R _{th3}	1.54E-01	

Symbol	Value	Unit
C_{th1}	3.81E-03	
C_{th2}	4.44E-03	Ws/K
C_{th3}	6.02E-02	



•Electrical characteristic curves

Fig.1 V_F - I_F Characteristics





Fig.2 V_F - I_F Characteristics



Forward Voltage : V_F [V]

Fig.3 V_R - I_R Characteristics





Fig.4 V_R - C_t Characteristics



Reverse Voltage : V_R [V]

•Electrical characteristic curves






Fig.6 Power Dissipation



Case Temperature : T_c [°C]



Case Temperature : T_c [°C]
*3 Based on max Vf, max R_{th(j-c)}
Valid for switching of above 10kHz, excluding D.C. curve.


derating curve I_P - T_c (Not guaranteed) 180 160 Duty=0.1 Peak Forward Current: Ip [A] 140 120 Duty=0.2 100 80 Duty=0.5 60 40 20 Duty=0.8 D.C. 0 25 50 75 100 125 150 175

Fig.8*4 Typical peak forward current

Case Temperature : T_c [°C] *4 Based on typ Vf, typ R_{th(j-c)} Typical value, not guaranteed Valid for switching of above 10kHz, excluding D.C. curve


• Electrical characteristic curves

Fig.9 Surge non-repetitive forward current vs. Pulse width (Sinusoidal waveform)



Pulse Width: PW [s]

Fig.10 Typical capacitance store energy




Capacitance stored energy : E_C[μJ]

Reverse Voltage: V_R [V]

Symplified forward characteristic model

Fig.11 Equivalent forward current curve



Forward Voltage : $V_{\rm F}$

$$V_F = V_{th} + R_{diff} I_F$$

$$\begin{aligned} &V_{th} \left(\ T_{j} \ \right) = a_{0} + a_{1} \, T_{j} \\ &R_{diff} \left(\ T_{j} \ \right) = b_{0} + b_{1} \, T_{j} + b_{2} \, T_{j}^{2} \end{aligned}$$

Symbol	Typical Value	Unit
a_0	9.93E-01	V
a ₁	-1.27E-03	V/°C
b ₀	2.43E-02	Ω
b ₁	1.37E-04	Ω/°C
b ₂	8.87E-07	$\Omega/^{\circ}C^{2}$

 T_i in °C; -55 °C < T_i < °C; I_F < 30 A

Forward Current: IF

Notes

- 1) The information contained herein is subject to change without notice.
- Before you use our Products, please contact our sales representative and verify the latest specifications:
- 3) Although ROHM is continuously working to improve product reliability and quality, semiconductors can break down and malfunction due to various factors. Therefore, in order to prevent personal injury or fire arising from failure, please take safety measures such as complying with the derating characteristics, implementing redundant and fire prevention designs, and utilizing backups and fail-safe procedures. ROHM shall have no responsibility for any damages arising out of the use of our Poducts beyond the rating specified by ROHM.
- 4) Examples of application circuits, circuit constants and any other information contained herein are provided only to illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.
- 5) The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM or any other parties. ROHM shall have no responsibility whatsoever for any dispute arising out of the use of such technical information.
- 6) The Products specified in this document are not designed to be radiation tolerant.
- 7) For use of our Products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a ROHM representative: transportation equipment (i.e. cars, ships, trains), primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, and power transmission systems.
- 8) Do not use our Products in applications requiring extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters.
- 9) ROHM shall have no responsibility for any damages or injury arising from non-compliance with the recommended usage conditions and specifications contained herein.
- 10) ROHM has used reasonable care to ensur the accuracy of the information contained in this document. However, ROHM does not warrants that such information is error-free, and ROHM shall have no responsibility for any damages arising from any inaccuracy or misprint of such information.
- 11) Please use the Products in accordance with any applicable environmental laws and regulations, such as the RoHS Directive. For more details, including RoHS compatibility, please contact a ROHM sales office. ROHM shall have no responsibility for any damages or losses resulting non-compliance with any applicable laws or regulations.
- 12) When providing our Products and technologies contained in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.
- 13) This document, in part or in whole, may not be reprinted or reproduced without prior consent of ROHM.



Thank you for your accessing to ROHM product informations.

More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

http://www.rohm.com/contact/