
General purpose chip resistors <High power> MCRS series

Datasheet

Features

- 1) Guaranteed the same rated power as one size larger product by changing the design of the resistive element.
- 2) Circuit space can be saved. (reducing the area by about 60% by replacing 0603 size with 0402 size)
- 3) ROHM resistors have obtained ISO9001 / IATF16949 certification.
- 4) Corresponds to AEC-Q200.



Products list

Part No.	Si	ze	Rated power	Rated ambient temperatur	Rated terminal temperatur	Limiting element voltage	Resistance tolerance	Temperature coefficient	Resistance range	Operating temperature range	Automotive grade Available		
	(mm)	(inch)	(W)	(°C)	(°C)	(V)	(%)	(ppm/°C)	(Ω)	(°C)	(AEC-Q200)		
						75	F (±1%) J (±5%)	±100 ±400	10≦R≦10M (E24/96 series) 1≦R<10 (E24 series)				
MCR01S	1005	0402	0.1	70	-		J (±5%)	±200	10≦R≦10M (E24 series)	− -55 ~ +155	Yes		
						(Jumi	, ,		OmΩMax., Rated current : 1.5A	-			
						(*****)	F (±1%)	±100	10≦R≦10M (E24/96 series)				
						150	J (±5%)	±400	1≦R<10 (E24 series)				
MCR03S	1608	0603	0.125	70	-		J (±5%)	±200	10≦R≦10M (E24 series)	− -55 ~ +155	Yes		
						(Jum	, ,	istance : Max . 5	50mΩMax., Rated current : 2A				
						`	F (±1%)	±250	1≦R<10 (E24 series)				
							F (±1%)	±100	10≦R≦2.2M (E24/96 series)				
MCR10S	2012	0805	0.25	70	-	200	J (±5%)	±400	1≦R<10 (E24 series)	-55 ∼ +155	Yes		
							J (±5%)	±200	10≦R≦10M (E24 series)				
						(Jump	per type) Resis	stance : Max . 50	DmΩMax., Rated current : 2.5A				
							F (±1%)	±250	1≦R<10 (E24 series)				
							F (±1%)	±100	10≦R≦2.2M (E24/96 series)				
MCR18S	3216	1206	0.4	70	-	200	J (±5%)	±400	1≦R<10 (E24 series)	-55 ~ +155	Yes		
									J (±5%)	±200	10≦R≦10M (E24 series)		
						(Jump	per type) Resis	stance : Max . 50	DmΩMax., Rated current : 2.5A				
							F (±1%)	±200	1≦R<10 (E24 series)				
Now							F (±1%)	±100	10≦R≦2.2M (E24/96 series)				
New MCR25S	3225	1210	0.5	70	110	200	J (±5%)	±400	1≦R<5.6 (E24 series)	-55 ∼ +155	Yes		
							J (±5%)	±200	5.6≦R≦3.3M (E24 series)				
						(Jun	per type) Res	istance : Max . 5	50mΩMax., Rated current : 2A				
							F (±1%)	±200	1≦R<10 (E24 series)				
							E (40()	+100/-150 ^{*1}	10 CD 07 (F01/00 :)				
New						050	F (±1%)	±100 ^{*2}	10≦R<27 (E24/96 series)				
MCR50S	5025	2010	1.5	70	105	250	F (±1%)	±100	27≦R≦2.2M (E24/96 series)	-55 ∼ +155	Yes		
							J (±5%)	±400	1≦R<10 (E24 series)				
							J (±5%)	±200	10≦R≦4.7M (E24 series)				
						(Jun	nper type) Res	istance : Max . 5	50mΩMax., Rated current : 4A				
							F (±1%)	±200	1≦R<10 (E24 series)				
							E (.40()	+100/-150 ^{*1}	40 CD 07 (F04/00)				
Now						050	F (±1%)	±100 ^{*2}	- 10≦R<27 (E24/96 series)				
MCR100S	6432	2512	2	70	105	250	F (±1%)	±100	27≦R≦2.2M (E24/96 series)	-55 ∼ +155	Yes		
							J (±5%)	±400	1≦R<10 (E24 series)				
							J (±5%)	±200	10≦R≦4.7M (E24 series)				
						(Jun	nper type) Res	istance : Max . 5	50mΩMax., Rated current : 4A				

Design and specifications are subject to change without notice. Carefully check the specification sheet supplied with the product before using or ordering it. E24 : Standard products, E96 : Build to order

Rated voltage is determined from the following.

When rated voltage exceeds the limiting element voltage, the limiting element voltage shall be the rated voltage. Rated voltage = Rated power x Resistance

*1 : Test temperature +25°C/-55°C

*2 : Test temperature +25°C/+125°C

Part number description

MCR

10S

EQP

F

L

1R00

1

Part No.

MCR

General purpose chip resistors

2		
Size	(mm)	[inch]
01S	(1005)	[0402]
03S	(1608)	[0603]
10S	(2012)	[0805]
18S	(3216)	[1206]
25S	(3225)	[1210]
50S	(5025)	[2010]
100S	(6432)	[2512]

Packing specifications code Part No. Code Packing specifications Quantity pcs/reel MCR01S MQP Paper tape (2mm Pitch) 10,000 MCR03S EQP Paper tape (4mm Pitch) 5,000 MCR10S EQP Paper tape (4mm Pitch) 5,000 MCR18S EQP 5,000 Paper tape (4mm Pitch) MCR25S JQP Embossed tape (4mm Pitch) 4,000 MCR50S JQP Embossed tape (4mm Pitch) 4,000 MCR100S JQP 4,000 Embossed tape (4mm Pitch)


Tolerance
F (±1%)
J (±5%) (Including jumper type)

Special part code
L(1Ω≦R<10Ω)*3
*3:10S/18S F class
25S/50S/100S F/J class

0							
	Nomina	l res	istance				
Resistance code, 3 or 4 digits.							
000 de	enotes jumper t	уре.					
	Resistance		Resistance				
	tolerance		code				
	F	:	4 digits				
	J	:	3 digits				
EX)							
	1Ω	=	1R00 (±1%)				
			1R0 (±5%)				
	9.1Ω	=	9R10 (±1%)				
			9R1 (±5%)				
	10Ω	=	10R0 (±1%)				
			100 (±5%)				
	1ΜΩ	=	1004 (±1%)				
			105 (±5%)				

Chip resistor dimensions and markings

MCR01S/03S/10S/18S/25S/50S/100S




<Marking method>
No marking

(Unit: mm)

Part No.	Type code	(mm)	(inch)	L	W	t	а	b
MCR01S	MQP	1005	0402	1.00±0.05	0.50±0.05	0.35±0.05	0.20±0.10	0.25+0.05 -0.10
MCR03S	EQP	1608	0603	1.60±0.10	0.80±0.10	0.45±0.10	0.30±0.20	0.30±0.20
MCR10S	EQP	2012	0805	2.00±0.10	1.25±0.10	0.55±0.10	0.40±0.20	0.40±0.20
MCR18S	EQP	3216	1206	3.20+0.15 -0.20	1.60±0.15	0.55±0.10	0.50±0.25	0.50±0.25
MCR25S	JQP	3225	1210	3.20+0.15 -0.20	2.50±0.15	0.55±0.10	0.40±0.20	0.50±0.25
MCR50S	JQP	5025	2010	5.00±0.15	2.50±0.15	0.55±0.15	0.60±0.25	0.60±0.25
MCR100S	JQP	6432	2512	6.40±0.15	3.15±0.15	0.55±0.15	0.60±0.25	1.00±0.25

● Land pattern example



(Unit: mm)

Dimensions Part No.	А	В	С	D
MCR01S	0.50	1.30	0.50	0.40
MCR03S	1.00	2.00	0.80	0.50
MCR10S	1.20	2.60	1.15	0.70
MCR18S	2.20	4.00	1.50	0.90
MCR25S	2.20	4.00	2.30	0.90
MCR50S	3.80	6.00	2.30	1.10
MCR100S	5.10	8.10	3.00	1.50



MCRS series Datasheet

Derating curve

■MCR01S/03S/10S/18S

For resistors operated at the ambient temperature in excess 70°C, the load shall be derated in accordance with Fig.1.

■MCR25S

For resistors operated at the ambient temperature in excess 70°C or terminal temperature ^{*4} in excess the rated terminal temperature, load shall be derated in accordance with Fig.1 and Fig.2.


■MCR50S/100S

For resistors operated at the ambient temperature in excess 70°C or terminal temperature^{*4} in excess the rated terminal temperature, load shall be derated in accordance with Fig.1 and Fig.3.

*4: The measurement part of terminal temperature is center of fillet's surface with load.


Fig.1< Ambient temperature>

■MCR01S/03S/10S/18S/25S/50S/100S




Ambient temperature Ta (°C)

Fig.2< Terminal temperature>
■MCR25S



Terminal temperature Tk (°C)

Fig.3< Terminal temperature>
■MCR50S/100S



Terminal temperature Tk (°C)



4/7

MCRS series

Characteristics

Testitems	Guarante	ed value	Test conditions		
restilents	Resistor type	Jumper type	Test conditions		
Resistance	See "Prod	ducts list"	20°C		
Variation of resistance	See "Prod	ducts list"	Test temperature : +25/+125°C (MCR01S/03S/10S/18S)		
with temperature			Test temperature : +25/-55°C,+25/+125°C (MCR25S/50S/100S)		
Overload	±(2.0%+0.1Ω)	MAX. 50mΩ	Test voltage is the smaller one of ① or ②		
			①Rated voltage (current)×2.5		
			②Maximum overload voltage*5		
			Test time: 2s (MCR01S/03S/10S/18S)		
	'		Test time : 5s (MCR25S/50S/100S)		
Solderability	A new uniform coating	of minimum of 95%	Rosin-ethanol solution (25% mass)		
	of the surface being im	mersed and no	Soldering condition : 245±5°C		
	soldering damage.		Duration of immersion : 2.0±0.5s		
Resistance to soldering	±(1.0%+0.05Ω)	MAX. 50mΩ	Soldering condition : 260±5°C		
heat	No remarkable al	onormality on the	Duration of immersion : 10±1s		
	appea	rance.			
Rapid change of	\pm (1.0%+0.05Ω) MAX. 50mΩ		Test temp.:-55°C~+125°C 1,000cycles		
temperature					
Temperature	±(3.0%+0.1Ω) MAX. 100mΩ		85°C, 85% (Relative humidity)		
humidity storage			Test time: 1,000h		
Endurance at 70°C	±(3.0%+0.1Ω)	MAX. 100mΩ	Ambient temperature : Ta=70°C		
			(MCR01S/03S/10S/18S/25S/50S/100S)		
			Terminal temperature : Tk=110°C (MCR25S)		
			Terminal temperature : Tk=105°C (MCR50S/100S)		
			Rated voltage (current)		
			1.5h : ON - 0.5h : OFF		
			Test time: 1,000h		
Endurance	±(3.0%+0.1Ω)	MAX. 100mΩ	155°C		
			Test time: 1,000h		
Resistance to solvent	±(1.0%+0.05Ω)	MAX. 50mΩ	23±5°C, Immersion cleaning, 5±0.5min		
			Solvent: 2-propanol		
Bend strength of the end	±(1.0%+0.05Ω)	MAX. 50mΩ	Endurance with 90mm width		
face plating			Deflection: 3mm (MCR01S/03S/10S/18S)		
	Without mechanica	•	Deflection : 1mm (MCR25S/50S/100S)		
	brea	aks.			

Compliance Standards: IEC 60115-1 / IEC 60115-8 JIS C 5201-1 / JIS C 5201-8


^{*5} Maximum overload voltage (Test voltage)

MCR01S	MCR03S	MCR10S	MCR18S	MCR25S	MCR50S	MCR100S
150V	300V	400V	400V	400V	500V	500V



● Tape dimensions


■Paper tape



(Unit: mm)

Part No.	Type code	W	F	E	A0	В0	D0	P0	P1	P2	T2
MCR01S	MQP	8.0±0.3	3.5±0.05	1.75±0.1	0.7±0.1	1.2±0.1	Φ1.5+0.1 0	4.0±0.1	2.0±0.05	2.0±0.05	MAX1.1
MCR03S	EQP	8.0±0.3	3.5±0.05	1.75±0.1	1.1±0.1	1.9±0.1	Φ1.5+0.1 0	4.0±0.1	4.0±0.1	2.0±0.05	MAX1.1
MCR10S	EQP	8.0±0.3	3.5±0.05	1.75±0.1	1.65+0.2 -0.1	2.4+0.2 -0.1	Φ1.5+0.1 0	4.0±0.1	4.0±0.1	2.0±0.05	MAX1.1
MCR18S	EQP	8.0±0.3	3.5±0.05	1.75±0.1	1.95+0.1 -0.05	3.5+0.15 -0.05	Φ1.5+0.1 0	4.0±0.1	4.0±0.1	2.0±0.05	MAX1.1

■Embossed tape



(Unit:mm)

Part No.	Type code	W	F	E	AO	В0	D0	P0	P1	P2	K
MCR25S	JQP	8.0±0.3	3.5±0.05	1.75±0.1	3.0±0.1	3.5±0.1	Φ1.5+0.1 0	4.0±0.1	4.0±0.1	2.0±0.05	MAX1.1
MCR50S	JQP	12.0±0.3	5.5±0.05	1.75±0.1	3.4±0.2	5.6±0.2	Φ1.5+0.1 0	4.0±0.1	4.0±0.1	2.0±0.05	MAX1.1
MCR100S	JQP	12.0±0.3	5.5±0.05	1.75±0.1	3.5±0.2	6.7±0.2	Φ1.5+0.1 0	4.0±0.1	4.0±0.1	2.0±0.05	MAX1.1


6/7




Reel dimensions

Using two kinds of reels for taping.

■MCR01S/03S/10S/18S/25S



■ MCR50S/100S



(Unit: mm)

Part No.	А	В	С	D
MCR01S				
MCR03S	Ф180 0 -1.5			
MCR10S		Ф60 +1.0 0	9 +1.0 0	Ф13±0.2
MCR18S				
MCR25S				
MCR50S			13 +1.0	
MCR100S			0	

Notice

Precaution on using ROHM Products

1. If you intend to use our Products in devices requiring extremely high reliability (such as medical equipment (Note 1), aircraft/spacecraft, nuclear power controllers, etc.) and whose malfunction or failure may cause loss of human life, bodily injury or serious damage to property ("Specific Applications"), please consult with the ROHM sales representative in advance. Unless otherwise agreed in writing by ROHM in advance, ROHM shall not be in any way responsible or liable for any damages, expenses or losses incurred by you or third parties arising from the use of any ROHM's Products for Specific Applications.

(Note1) Medical Equipment Classification of the Specific Applications

ſ	JÁPAN	USA	EU	CHINA	
Ī	CLASSⅢ	CL ACCIII	CLASS II b	СГУССШ	
ſ	CLASSIV	CLASSⅢ	CLASSⅢ	CLASSIII	

- 2. ROHM designs and manufactures its Products subject to strict quality control system. However, semiconductor products can fail or malfunction at a certain rate. Please be sure to implement, at your own responsibilities, adequate safety measures including but not limited to fail-safe design against the physical injury, damage to any property, which a failure or malfunction of our Products may cause. The following are examples of safety measures:
 - [a] Installation of protection circuits or other protective devices to improve system safety
 - [b] Installation of redundant circuits to reduce the impact of single or multiple circuit failure
- 3. Our Products are not designed under any special or extraordinary environments or conditions, as exemplified below. Accordingly, ROHM shall not be in any way responsible or liable for any damages, expenses or losses arising from the use of any ROHM's Products under any special or extraordinary environments or conditions. If you intend to use our Products under any special or extraordinary environments or conditions (as exemplified below), your independent verification and confirmation of product performance, reliability, etc, prior to use, must be necessary:
 - [a] Use of our Products in any types of liquid, including water, oils, chemicals, and organic solvents
 - [b] Use of our Products outdoors or in places where the Products are exposed to direct sunlight or dust
 - [c] Use of our Products in places where the Products are exposed to sea wind or corrosive gases, including Cl₂, H₂S, NH₃, SO₂, and NO₂
 - [d] Use of our Products in places where the Products are exposed to static electricity or electromagnetic waves
 - [e] Use of our Products in proximity to heat-producing components, plastic cords, or other flammable items
 - [f] Sealing or coating our Products with resin or other coating materials
 - [g] Use of our Products without cleaning residue of flux (Exclude cases where no-clean type fluxes is used. However, recommend sufficiently about the residue.); or Washing our Products by using water or water-soluble cleaning agents for cleaning residue after soldering
 - [h] Use of the Products in places subject to dew condensation
- 4. The Products are not subject to radiation-proof design.
- 5. Please verify and confirm characteristics of the final or mounted products in using the Products.
- 6. In particular, if a transient load (a large amount of load applied in a short period of time, such as pulse, is applied, confirmation of performance characteristics after on-board mounting is strongly recommended. Avoid applying power exceeding normal rated power; exceeding the power rating under steady-state loading condition may negatively affect product performance and reliability.
- 7. De-rate Power Dissipation depending on ambient temperature. When used in sealed area, confirm that it is the use in the range that does not exceed the maximum junction temperature.
- 8. Confirm that operation temperature is within the specified range described in the product specification.
- ROHM shall not be in any way responsible or liable for failure induced under deviant condition from what is defined in this document.

Precaution for Mounting / Circuit board design

- 1. When a highly active halogenous (chlorine, bromine, etc.) flux is used, the residue of flux may negatively affect product performance and reliability.
- 2. In principle, the reflow soldering method must be used on a surface-mount products, the flow soldering method must be used on a through hole mount products. If the flow soldering method is preferred on a surface-mount products, please consult with the ROHM representative in advance.

For details, please refer to ROHM Mounting specification

Precautions Regarding Application Examples and External Circuits

- 1. If change is made to the constant of an external circuit, please allow a sufficient margin considering variations of the characteristics of the Products and external components, including transient characteristics, as well as static characteristics.
- 2. You agree that application notes, reference designs, and associated data and information contained in this document are presented only as guidance for Products use. Therefore, in case you use such information, you are solely responsible for it and you must exercise your own independent verification and judgment in the use of such information contained in this document. ROHM shall not be in any way responsible or liable for any damages, expenses or losses incurred by you or third parties arising from the use of such information.

Precaution for Electrostatic

This Product is electrostatic sensitive product, which may be damaged due to electrostatic discharge. Please take proper caution in your manufacturing process and storage so that voltage exceeding the Products maximum rating will not be applied to Products. Please take special care under dry condition (e.g. Grounding of human body / equipment / solder iron, isolation from charged objects, setting of lonizer, friction prevention and temperature / humidity control).

Precaution for Storage / Transportation

- 1. Product performance and soldered connections may deteriorate if the Products are stored in the places where:
 - [a] the Products are exposed to sea winds or corrosive gases, including Cl₂, H₂S, NH₃, SO₂, and NO₂
 - [b] the temperature or humidity exceeds those recommended by ROHM
 - [c] the Products are exposed to direct sunshine or condensation
 - [d] the Products are exposed to high Electrostatic
- Even under ROHM recommended storage condition, solderability of products out of recommended storage time period
 may be degraded. It is strongly recommended to confirm solderability before using Products of which storage time is
 exceeding the recommended storage time period.
- 3. Store / transport cartons in the correct direction, which is indicated on a carton with a symbol. Otherwise bent leads may occur due to excessive stress applied when dropping of a carton.
- 4. Use Products within the specified time after opening a humidity barrier bag. Baking is required before using Products of which storage time is exceeding the recommended storage time period.

Precaution for Product Label

A two-dimensional barcode printed on ROHM Products label is for ROHM's internal use only.

Precaution for Disposition

When disposing Products please dispose them properly using an authorized industry waste company.

Precaution for Foreign Exchange and Foreign Trade act

Since concerned goods might be fallen under listed items of export control prescribed by Foreign exchange and Foreign trade act, please consult with ROHM in case of export.

Precaution Regarding Intellectual Property Rights

- 1. All information and data including but not limited to application example contained in this document is for reference only. ROHM does not warrant that foregoing information or data will not infringe any intellectual property rights or any other rights of any third party regarding such information or data.
- 2. ROHM shall not have any obligations where the claims, actions or demands arising from the combination of the Products with other articles such as components, circuits, systems or external equipment (including software).
- 3. No license, expressly or implied, is granted hereby under any intellectual property rights or other rights of ROHM or any third parties with respect to the Products or the information contained in this document. Provided, however, that ROHM will not assert its intellectual property rights or other rights against you or your customers to the extent necessary to manufacture or sell products containing the Products, subject to the terms and conditions herein.

Other Precaution

- 1. This document may not be reprinted or reproduced, in whole or in part, without prior written consent of ROHM.
- 2. The Products may not be disassembled, converted, modified, reproduced or otherwise changed without prior written consent of ROHM.
- In no event shall you use in any way whatsoever the Products and the related technical information contained in the Products or this document for any military purposes, including but not limited to, the development of mass-destruction weapons.
- 4. The proper names of companies or products described in this document are trademarks or registered trademarks of ROHM, its affiliated companies or third parties.

Notice-PAA-E Rev.004

General Precaution

- 1. Before you use our Products, you are requested to carefully read this document and fully understand its contents. ROHM shall not be in any way responsible or liable for failure, malfunction or accident arising from the use of any ROHM's Products against warning, caution or note contained in this document.
- 2. All information contained in this document is current as of the issuing date and subject to change without any prior notice. Before purchasing or using ROHM's Products, please confirm the latest information with a ROHM sales representative.
- 3. The information contained in this document is provided on an "as is" basis and ROHM does not warrant that all information contained in this document is accurate and/or error-free. ROHM shall not be in any way responsible or liable for any damages, expenses or losses incurred by you or third parties resulting from inaccuracy or errors of or concerning such information.

Notice – WE Rev.001