A-002. Boost PFC Vin=200V, Iin=2.5A, CCM


Simulation Circuit

ROHM Solution Simulator Schematic Information

2023. Feb 64UG061E Rev.004

ROHM

Simulation Parameters Component Component Setting Range name Vin 200Vac 50Hz Input voltage Input current 2.5Aac lin Vo Output voltage 400Vdc 300 - 500Vdc fsw Switching frequency 100kHz 10k – 300k Temperature 100°C Τj Vd Gate Drive voltage 18V 10 – 20V



Devices

Component name	Component	Default	Simulation Setting Range	
Q1	SIC MOSFET	Selectable		
D1	SiC SBD	Selectable		
GD-IC	Gate Driver	BM61S41RFV-C		
R sink	Resistor for sink	ESR18 2Ω	0.1 -	
R source	Resistor for source	ESR18 5Ω	0.1 -	
L1	Inductor	150µH	10µH - 1mH	
C1	Capacitor	200nF		
BR	Bridge Diode	600V 10A ideal of	diode	

© 2022 ROHM Co., Ltd.

results of circuit operation or performance.

P. 1


A-002. Boost PFC Vin=200V, Iin=2.5A, CCM

ROHM Solution Simulator Schematic Information

Selectable Devices			Selectable Devices			2023. Feb 64UG061E Rev.004	
Component name	Component	Product No.	feature	Component name	Component	Product No.	feature
Q1	SIC MOSFET	SCT2080KE	1200V, 80mΩ, 40A	D1	SiC SBD	SCS205KG	1200V, 5A
		SCT2120AF	650V, 120mΩ, 29A			SCS206AG	650V, 6A
		SCT2160KE	1200V, 160mΩ, 22A			SCS208AG	650V, 8A
		SCT2280KE	1200V, 280mΩ, 14A			SCS210AG	650V, 10A
		SCT2450KE (*)	1200V, 450mΩ, 10A			SCS210KG	1200V, 10A
		SCT2750NY	1700V, 750mΩ, 6A			SCS212AG	650V, 12A
		SCT2H12NZ	1700V, 1150mΩ, 3.7A			SCS215AG	650V, 15A
		SCT3017AL	650V, 17mΩ, 118A			SCS215KG	1200V, 15A
		SCT3022AL	650V, 22mΩ, 93A			SCS220AG	650V, 20A
		SCT3022KL	1200V, 22mΩ, 95A			SCS220KG	1200V, 20A
		SCT3030AL	650V, 30mΩ, 70A			SCS302AHG (*)	650V, 2A, High surge resistance
		SCT3030KL	1200V, 30mΩ, 72A			SCS304AHG	650V, 4A, High surge resistance
		SCT3040KL	1200V, 40mΩ, 55A			SCS306AHG	650V, 6A, High surge resistance
		SCT3060AL	650V, 60mΩ, 39A			SCS308AHG	650V, 8A, High surge resistance
		SCT3080AL	650V, 80mΩ, 30A			SCS310AHG	650V, 10A, High surge resistance
		SCT3080KL	1200V, 80mΩ, 31A			SCS312AHG	650V, 12A, High surge resistance
		SCT3105KL	1200V, 105mΩ, 24A			SCS315AHG	650V, 15A, High surge resistance
		SCT3120AL	650V, 120mΩ, 21A			SCS320AHG	650V, 20A, High surge resistance
		SCT3160KL	1200V, 160mΩ, 17A			* Default device	9


* Default device

ROHM Solution Simulator Schematic Information




Simulation Waveform2

ROHM Solution Simulator Schematic Information




Efficiency, Power Dissipation 1

ROHM Solution Simulator Schematic Information



Efficiency, Power Dissipation 2


ROHM Solution Simulator Schematic Information



How to change the devices

ROHM Solution Simulator Schematic Information

2023. Feb 64UG061E Rev.004




Q2

Q2 G

Loss Calculation Model

ROHM Solution Simulator Schematic Information



Loss Calculation Model outputs the instantaneous value of power loss and its integration.

Loss calculation model 'Loss_calc'



2023. Feb

Þ

64UG061E Rev.004

Vds of MOSFET

Id of MOSFET

Vgs of MOSFET

g2_vd

q2/i(drain)

q2_g

loss2

loss out

loss2_integ

5.040m

5.045m

5.050m

>

loss_integ_out

Notes					
1)	The information contained herein is subject to change without notice.				
2)	Before you use our Products, please contact our sales representative and verify the latest specifica- tions :				
3)	Although ROHM is continuously working to improve product reliability and quality, semicon- ductors can break down and malfunction due to various factors. Therefore, in order to prevent personal injury or fire arising from failure, please take safety measures such as complying with the derating characteristics, implementing redundant and fire prevention designs, and utilizing backups and fail-safe procedures. ROHM shall have no responsibility for any damages arising out of the use of our Poducts beyond the rating specified by ROHM.				
4)	Examples of application circuits, circuit constants and any other information contained herein are provided only to illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.				
5)	The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM or any other parties. ROHM shall have no responsibility whatsoever for any dispute arising out of the use of such technical information.				
6)	The Products specified in this document are not designed to be radiation tolerant.				
7)	For use of our Products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a ROHM representative : transportation equipment (i.e. cars, ships, trains), primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, servers, solar cells, and power transmission systems.				
8)	Do not use our Products in applications requiring extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters.				
9)	ROHM shall have no responsibility for any damages or injury arising from non-compliance with the recommended usage conditions and specifications contained herein.				
10)	ROHM has used reasonable care to ensure the accuracy of the information contained in this document. However, ROHM does not warrants that such information is error-free, and ROHM shall have no responsibility for any damages arising from any inaccuracy or misprint of such information.				
11)	Please use the Products in accordance with any applicable environmental laws and regulations, such as the RoHS Directive. For more details, including RoHS compatibility, please contact a ROHM sales office. ROHM shall have no responsibility for any damages or losses resulting non-compliance with any applicable laws or regulations.				
12)	When providing our Products and technologies contained in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.				
13)	This document, in part or in whole, may not be reprinted or reproduced without prior consent of ROHM.				



Thank you for your accessing to ROHM product informations. More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

http://www.rohm.com/contact/