

# A-008. Interleaved PFC $V_{in}=200V$ , $I_{in}=5.0A$ , DCM


## Simulation Parameters

Parameters	Descriptions	Default	Simulation Setting Range
$V_{in}$	Input voltage	200Vac 50Hz	
$I_{in}$	Input current	5Aac	
$V_o$	Output voltage	500Vdc	300 – 500Vdc
fsw1,2	Switching frequency	100kHz	10k – 300k
$T_j$	Temperature	100°C	
$V_{d1,2}$	Gate Drive voltage	18V	10 – 20V

## Devices

Component Name	Component	Default	Simulation Setting Range
Q1, Q2	SIC MOSFET SJ MOSFET IGBT	Selectable	
D1, D2	SiC SBD	Selectable	
GD-IC1,2	Gate Driver	Selectable	
R sink1,2	Resistor for sink	ESR18 2Ω	0.1 -
R source1,2	Resistor for source	ESR18 5Ω	0.1 -
L1, L2	Inductor	100μH	10μH - 2mH
C1	Capacitor	1μF	
BR	Bridge Diode	600V 10A ideal diode	

## Simulation Circuit



Note: The Loss\_calc component is a utility module to support power loss calculation and does not affect the simulation results of circuit operation or performance.


# A-008. Interleaved PFC $V_{in}=200V$ , $I_{in}=5.0A$ , DCM

## Selectable Devices


Component name	Component
Q1,Q2	SiC MOSFET

## SiC MOSFET part number information

**SCT4036KR**



For more information, go to “**More Info**” and click on “**Link to Datasheet**”.



**Model Links:**

- [Link To Product](#)
- [Link To Datasheet](#)
- [Link To Buy](#)
- [Search on CSE...](#)

Product Lineup: [SiC MOSFETs](#)


# A-008. Interleaved PFC $V_{in}=200V$ , $I_{in}=5.0A$ , DCM



## Selectable Devices


Component name	Component	Product
Q1,Q2	SJ MOSFET	RxxxxKN series RxxxxYN series

For more information, go to “**More Info**” and click on “**Link to Datasheet**”.



Model Links:  
[Link To Product](#)  
[Link To Datasheet](#)  
[Link To Buy](#)  
[Search on CSE...](#)

## SJ MOSFET part number information



Product Lineup: [Super Junction MOSFETs](#)

# A-008. Interleaved PFC $V_{in}=200V$ , $I_{in}=5.0A$ , DCM


IGBT part number information

**R G S 6 0 T S 6 5 D H R**

Selectable Devices

Component name	Component	Product
Q1,Q2	IGBT	RGW series

For more information, go to “More Info” and click on “Link to Datasheet”.



- Model Links:
- [Link To Product](#)
  - [Link To Datasheet](#)
  - [Link To Buy](#)
  - [Search on CSE...](#)

**Product category**

RG: IGBT

**Product series**

- C: For voltage resonant, Reverse Conducting IGBT (RC-IGBT)
- CL: Low  $V_{CE(sat)}$
- S: For Automotive Inverter, Short circuit capability guaranteed 8 to 10 $\mu$ s
- T: For inverter, Short circuit capability guaranteed 5 $\mu$ s
- TV: For converter / inverter, High speed switching, Short circuit capability guaranteed 2 $\mu$ s
- TH: For converter, High speed switching
- W: For converter, Ultra high-speed switching
- WS: For converter, Ultra high-speed switching, Popular edition

**Rated collector current  $I_C(T_C=100^\circ C)$**

- 8: 4 A
- 16: 8 A
- 20: 10 A
- 30: 15 A
- 40: 20 A
- 50: 25 A
- 60: 30 A
- 80: 40 A
- 00: 50 A
- X2: 60 A
- X5: 75 A
- X6: 80 A

\* See datasheet for current values that may differ in some cases.

**Package**

- BM: TO-252, TO-252GE
- NS: TO-263S, TO-262
- NL: TO-263L
- TM: TO-220NFM
- TS: TO-247N, TO-247GE
- TK: TO-3PFM

**Rated voltage  $V_{CES}$**

- 60: 600 V
- 65: 650 V
- X2: 1200 V
- X8: 1800 V

**Grade**

- G: Standard
- GV: Standard
- HR: Automotive (AEC-Q101)
- HRB: Automotive (AEC-Q101)

**Built-in diode configuration**


- None: Without diode
- C: SiC Schottky barrier diode
- D: Fast recovery diode
- E: Larger size Fast recovery diode
- R: Body diode with reverse conducting (RC) structure

Product Lineup: [Field Stop Trench IGBT](#)


## Selectable Devices

Component name	Component
D1, 2	SiC Schottky Barrier Diode

## SiC Schottky Barrier Diode part number information



For more information, go to “**More Info**” and click on “**Link to Datasheet**”.



- Model Links:
- [Link To Product](#)
  - [Link To Datasheet](#)
  - [Link To Buy](#)
  - [Search on CSE...](#)

➡ Product Lineup: [SiC Schottky Barrier Diodes](#)

# A-008. Interleaved PFC $V_{in}=200V$ , $I_{in}=5.0A$ , DCM



## Selectable Devices

Component name	Component	Product No.	feature
GD-IC1,2	Gate Driver	BM61S41RFV-C (*)	<b>for SiC MOSFET</b> Isolation Voltage : 3750 Vrms I/O Delay Time (max) : 65ns Miller Clamp : Built-in UVLO : 14.5V
		BM61M41RFV-C	<b>for SJ-MOS / IGBT</b> Isolation Voltage : 3750 Vrms I/O Delay Time (max) : 65ns Miller Clamp : Built-in UVLO : 7.4V




\* Default device

# Simulation Waveform1



Q1,Q2 : SiC MOSFET  
SCT2450KE  
D1,D2 : SiC SBD  
SCS302AHG

2025. Nov.  
64UG104E Rev.006



# Simulation Waveform2



ROHM Solution Simulator Schematic Information

2025. Nov.



Rev.006

Q1,Q2 : SiC MOSFET

SCT2450KE

D1,D2 : SiC SBD





SCS302AHG



# Efficiency, Power Dissipation 1




Q1,Q2 : SiC MOSFET  
SCT2450KE  
D1,D2 : SiC SBD  
SCS302AHG



# Efficiency, Power Dissipation 2




Q1,Q2 : SiC MOSFET  
SCT2450KE  
D1,D2 : SiC SBD  
SCS302AHG



# How to change the devices


Right-click on the device → Select Properties → Pull down “SpiceLib Part” → Select the product



Loss Calculation Model outputs the instantaneous value of power loss and its integration.

2025. Nov.  
64UG104E Rev.006

## Loss calculation model 'Loss\_calc'




$$loss\_out(t) = I(t) \times V(t)$$

$$loss\_integ\_out = \int_0^t loss\_out(t)dt$$

I : Current through p1 to p1s

V : Voltage between p1s and p2

## Waveform example



### Notice

- 1) The information contained in this document is intended to introduce ROHM Group (hereafter referred to as ROHM) products. When using ROHM products, please verify the latest specifications or datasheets before use.
- 2) ROHM products are designed and manufactured for use in general electronic equipment and applications (such as Audio Visual equipment, Office Automation equipment, telecommunication equipment, home appliances, amusement devices, etc.) or specified in the datasheets. Therefore, please contact the ROHM sales representative before using ROHM products in equipment or devices requiring extremely high reliability and whose failure or malfunction may cause danger or injury to human life or body or other serious damage (such as medical equipment, transportation, traffic, aircraft, spacecraft, nuclear power controllers, fuel control, automotive equipment including car accessories, etc. hereafter referred to as Specific Applications). Unless otherwise agreed in writing by ROHM in advance, ROHM shall not be in any way responsible or liable for any damages, expenses, or losses incurred by you or third parties arising from the use of ROHM Products for Specific Applications.
- 3) Electronic components, including semiconductors, can fail or malfunction at a certain rate. Please be sure to implement, at your own responsibilities, adequate safety measures including but not limited to fail-safe design against physical injury, and damage to any property, which a failure or malfunction of products may cause.
- 4) The information contained in this document, including application circuit examples and their constants, is intended to explain the standard operation and usage of ROHM products, and is not intended to guarantee, either explicitly or implicitly, the operation of the product in the actual equipment it will be used. As a result, you are solely responsible for it, and you must exercise your own independent verification and judgment in the use of such information contained in this document. ROHM shall not be in any way responsible or liable for any damages, expenses, or losses incurred by you or third parties arising from the use of such information.
- 5) When exporting ROHM products or technologies described in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, such as the Foreign Exchange and Foreign Trade Act and the US Export Administration Regulations, and follow the necessary procedures in accordance with these provisions.
- 6) The technical information and data described in this document, including typical application circuits, are examples only and are not intended to guarantee to be free from infringement of third parties intellectual property or other rights. ROHM does not grant any license, express or implied, to implement, use, or exploit any intellectual property or other rights owned or controlled by ROHM or any third parties with respect to the information contained herein.
- 7) No part of this document may be reprinted or reproduced in any form by any means without the prior written consent of ROHM.
- 8) All information contained in this document is current as of the date of publication and subject to change without notice. Before purchasing or using ROHM products, please confirm the latest information with the ROHM sales representative.
- 9) ROHM does not warrant that the information contained herein is error-free. ROHM shall not be in any way responsible or liable for any damages, expenses, or losses incurred by you or third parties resulting from errors contained in this document.



Thank you for your accessing to ROHM product informations.  
More detail product informations and catalogs are available, please contact us.

## ROHM Customer Support System

<https://www.rohm.com/contactus>