

AC100V input, 12V/200mA output

Non-isolated AC/DC converter

BP5037B12

Absolute Maximum Ratings


Parameter	Symbol	Limits	Unit
Input voltage	Vi	170	V
Maximum Output current	Iomax	200	mApk
ESD endurance	Vsurge	2	kV
Operating temperature range	Topr	-25 to +80	°C
Storage temperature range	Tstg	-25 to +105	°C
Maximum surface temperature	Tcmax	105	°C

Electrical Characteristics

Parameter	Symbol	Min.	Тур.	Max.	Unit	Conditions
Input voltage range	Vi	113	141	170	V	DC(80 to 120VAC)
Output voltage	Vo	11.0	12.0	13.0	V	Vi=141V, Io=100mA
Output current	lo	0	_	200	mA	Vi=141V *1
Line regulation	Vr	-	0.05	0.15	V	Vi=113 to 170' ,ω- J0mA
Load regulation	VI	-	0.07	0.20	V	Vi=141V, Io: 10 nA
Output ripple voltage	Vp	-	0.05	0.15	Vp-p	Vi=14′ =1 *2
Power conversion efficiency	η	70	78	_	%	Vi-1 V, OmA

^{*1} Maximum output current varies depending on ambient temperature; please refer to derating curve *2 Spike noise is not included in output ripple voltage.

Application circuit



evaluate and confirm our part mounted in your product, For actual usage, Pluar Especial Please mak to confirm whether the load current exceed Max, rated current by usi current phobe

Ripple current is 0.13Arms above.

External compo

FUSE: Fuse

C1: Capacitor for input voltage smoothing

C2: For noise terminal voltage reduction

C3: Capacitor for Output voltage smoothing

D1: Rectifier diode

L1: Choke coil

R1: For noise terminal voltage reduction

Film capacitor or ceramic capacitor. Reduce the noise terminal voltage.

Please make sure to use quick acting fuse 1A

The constant value should be evaluated in the set.

Capacitance: 100 to 470µF Rated voltage: 25V or higher, ESR is 0.25Ω max. Ripple current is 0.4Arms above.

Capacitance: 22 to 100µF Rated voltage: 200V or higher

Capacitance: 0.1 to 0.22µF Rated voltage: 200V or higher

Output noise voltage is influenced. Please evaluate it in the actual set. In the absolute maximum ratings, the reverse peak voltage should be

400V or higher, the average rectifying current should be 0.5A or higher, and the peak surge current should be 20A or higher.

(Full-wave rectifier can be used in our part.)

Otherwise heating or abnormal oscillation occurs.

Coil for switching regulator. The inductance should be $820\mu\text{H}\text{,}$ the rated direct current should be 0.42A above.


Reduce the noise terminal voltage. Please set it, if necessary.

The constant value should be evaluated in set.


Varistor must be used. It protects this part from lightning surge and static ZNR: Varistor

electricity.


Dimensions (Unit : mm)




ating Curve




Conversion Efficiency



Load Regulation



Surface Temperature Rising



Power Module Usage Precautions

Safety Precautions

- 1) The products are designed and manufactured for use in ordinary electronic equipment (i.e. AV/OA/ telecommunication/amusement equipment, home appliances). Please consult with the Company's (ROHM) sales staff if intended for use in devices requiring high reliability (e.g. medical/transport/ aircraft/spacecraft equipment, nuclear power/fuel controllers, automotive/safety devices) and whose malfunction may result in injury or death. In this case, failsafe measures must be taken, including the following:
 - [a] Installation of protection circuits in order to improve system safety
 - [b] Incorporation of redundant circuits in the case of single-circuit failure
- 2) The products are designed for use under normal conditions. Application in special environments can cause a deterioration in product performance. Therefore, verification and confirmation of product performance, prior to use, is recommended. The following environments are considered to be 'special':
 - [a] Outdoors, exposed to direct sunlight or dust
 - [b] In contact with liquids, such as water, oils, chemicals, or organic solvents
 - [c] In areas where exposure to the sea air or corrosive gases (i.e. Cl₂, H₂S, NH₃, SO₂, an occur
 - [d] In places where the products may be in contact with static electricity or electron energy aves
 - [e] In proximity to heat-producing items, plastic cords, or flammable materials
 - [f] In contact with sealing or coating products, such as resin
 - [g] In contact with unclean solder or exposed to water or water-solutions agents used after soldering
 - [h] In areas where dew condensation occurs
- 3) The products are not designed to be radiation resistant
- 4) The Company is not responsible for any problems resulting from use of the products under conditions not recommended herein.
- 5) The Company should be notified of any product safety issue periodically monitored by the customer.

Application Notes

- 1) A sufficient margin must be allowed if changes are made to the peripheral circuit due to variations in the inherent tolerances of the expression of the e
- 2) The application example, their constants, and other types of information contained herein are applicable only when the present accordance with standard methods.
 - Therefore, if makes the action is intended, sufficient consideration to external conditions must be made.

Notes Regarding Industrial Property

- 1) The specifications included herein contain information related to the Company's industrial property. Their use other than pertaining to the relevant products is forbidden. Duplication and/or disclosure to a third party without express written permission is strictly prohibited.
- 2) Product information and data, including application examples, contained in the specifications are for reference purposes only; the Company does not guarantee the industrial/intellectual property rights or any other rights of a third party. Accordingly, the Company shall not bear responsibility for:
 - [a] Infringement of the intellectual property rights of a third party
 - [b] Problems arising from the use of the products listed herein
- 3) The Company prohibits the purchaser from exercising or using the intellectual/industrial property rights or any rights belonging to or are controlled by the Company, other than the right to use, sell, or dispose of the products.

Notes

- 1) The information contained herein is subject to change without notice.
- Before you use our Products, please contact our sales representative and verify the latest specifications.
- 3) Although ROHM is continuously working to improve product reliability and quality, semiconductors can break down and malfunction due to various factors. Therefore, in order to prevent personal injury or fire arising from failure, please take safety measures such as complying with the derating characteristics, implementing redundant and fire prevention designs, and utilizing backups and fail-safe procedures. ROHM shall have no responsibility for any damages arising out of the use of our Poducts beyond the rating specified by ROHM.
- 4) Examples of application circuits, circuit constants and any other information contained herein are provided only to illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.
- 5) The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM or any other parties. ROHM shall have no responsibility whatsoever for any dispute arising out of the use of such technical information.
- 6) The Products are intended for use in general electronic equipment (i.e. AV/OA devices, communication, consumer systems, gaming/entertainment sets) as well as the applications indicated in this document.
- 7) The Products specified in this document are not designed to be radiation tolerant.
- 8) For use of our Products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a ROHM representative : transportation equipment (i.e. cars, ships, trains), primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, servers, solar cells, and power transmission systems.
- Do not use our Products in applications requiring extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters.
- 10) ROHM shall have no responsibility for any damages or injury arising from non-compliance with the recommended usage conditions and specifications contained herein.
- 11) ROHM has used reasonable care to ensure the accuracy of the information contained in this document. However, ROHM does not warrants that such information is error-free, and ROHM shall have no responsibility for any damages arising from any inaccuracy or misprint of such information.
- 12) Please use the Products in accordance with any applicable environmental laws and regulations, such as the RoHS Directive. For more details, including RoHS compatibility, please contact a ROHM sales office. ROHM shall have no responsibility for any damages or losses resulting non-compliance with any applicable laws or regulations.
- 13) When providing our Products and technologies contained in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.
- 14) This document, in part or in whole, may not be reprinted or reproduced without prior consent of ROHM.



Thank you for your accessing to ROHM product informations. More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

http://www.rohm.com/contact/