# B-011. 3-level NPC-T Inverter P<sub>OUT</sub>=10kW




**ROHM Solution Simulator Schematic Information** 

Simulation Parameters **Component** Component Setting Range name Vin1.2 240Vdc Input voltage Vo Output voltage 200Vac Output current 50Aac lo fsw1 Switching frequency 10kHz 10k – 300kHz Temperature 100°C Τj Vd1-8 Gate Drive voltage H 18V 10 – 20V Signal voltage level Vdin 5V

### Devices

Component Name	Component	Default	Simulation Setting Range
Q1-8	SIC MOSFET	Selectable	
GD-IC1-8	Gate Driver	BM61S41RFV-C	
R sink1-8	Resistor for sink	ESR18 1Ω	0.1 -
R source1-8	Resistor for source	ESR18 2Ω	0.1 -
L1	Inductor	500µH	10µH - 2mH
Ro1	Output Resistor	{Vo/lo}	



Note: The Loss\_calc component is a utility module to support power loss calculation and does not affect the simulation results of circuit operation or performance.

# B-011. 3-level NPC-T Inverter P<sub>OUT</sub>=10kW

feature

**ROHM Solution Simulator Schematic Information** 

Hame	
Q1-8	SiC M

Component

Selectable Devices

Component

name			
Q1-8	SIC MOSFET	SCT2080KE	1200V, 80mΩ, 40A
		SCT2120AF	650V, 120mΩ, 29A
		SCT2160KE	1200V, 160mΩ, 22A
		SCT2280KE	1200V, 280mΩ, 14A
		SCT2450KE	1200V, 450mΩ, 10A
		SCT2750NY	1700V, 750mΩ, 6A
		SCT2H12NZ	1700V, 1150mΩ, 3.7A
		SCT3017AL (*)	650V, 17mΩ, 118A
		SCT3022AL	650V, 22mΩ, 93A
		SCT3022KL	1200V, 22mΩ, 95A
		SCT3030AL	650V, 30mΩ, 70A
		SCT3030KL	1200V, 30mΩ, 72A
		SCT3040KL	1200V, 40mΩ, 55A
		SCT3060AL	650V, 60mΩ, 39A
		SCT3080AL	650V, 80mΩ, 30A
		SCT3080KL	1200V, 80mΩ, 31A
		SCT3105KL	1200V, 105mΩ, 24A
		SCT3120AL	650V, 120mΩ, 21A
		SCT3160KL	1200V, 160mΩ, 17A

Product No.

\* Default device




2023. Feb

64UG107E Rev.006



### **ROHM Solution Simulator Schematic Information**




2023. Feb 64UG107E Rev.006

## How to change the devices

**ROHM Solution Simulator Schematic Information** 

### 2023. Feb 64UG107E Rev.006

ROHM



Q2

Q2 G

SCT2450KE

# loss\_integ\_ou Lossz\_meg x4

oss out

LU332

# $loss_out(t) = I(t) \times V(t)$ $loss_integ_out = \int_0^t loss_out(t)dt$

I: Current through p1 to p1s

V: Voltage between p1s and p2

### Waveform example

### Ô https://app.systemvision.com/Viewer?stateid=01e9 Þ Simulation Results g2\_vd 500.0 400.0 -A-003\_ACDC\_PFC\_ 300.0 -A-003\_ACDC\_PFC\_ 200.0 -Vds of MOSFET 100.0 -Loss1 q2/i(drain) loss1\_integ 4.0 3.0 Current (A) loss2 2.0 -Id of MOSFET 1.0 loss2\_integ 0.0 -1.0 . net93 20.0 . net96 **q2\_g** S 15.0 \_\_\_\_\_\_net108 10.0 Vgs of MOSFET 5.0 . net109 0.0 . net110 -5.0 \_\_\_\_\_ net113 loss2 2.0 . net114 8 1.5k . net115 loss out 1.0k 0.5k ... net125 0.0k . net135 21.1m -21.0m -20.9m -20.8m -20.7m loss2\_integ . net139 ≷ \_\_\_\_\_ net153 loss\_integ\_out 20.6m -20.5m -20.4m -. net155 . net156 20.3m ... net158 5.005m 5.010m 5.015m 5.020m 5.025m 5.030m 5.035m 5.040m 5.045m 5.050m 5.000m Time (s) >

## Loss Calculation Model

Loss\_calc


T

Loss calculation model 'Loss\_calc'

02 V-

Loss Calculation Model outputs the instantaneous value of power loss and its integration.

**ROHM Solution Simulator Schematic Information** 





2023. Feb

64UG107E Rev.006

Notes				
1)	The information contained herein is subject to change without notice.			
2)	Before you use our Products, please contact our sales representative and verify the latest specifica- tions :			
3)	Although ROHM is continuously working to improve product reliability and quality, semicon- ductors can break down and malfunction due to various factors. Therefore, in order to prevent personal injury or fire arising from failure, please take safety measures such as complying with the derating characteristics, implementing redundant and fire prevention designs, and utilizing backups and fail-safe procedures. ROHM shall have no responsibility for any damages arising out of the use of our Poducts beyond the rating specified by ROHM.			
4)	Examples of application circuits, circuit constants and any other information contained herein are provided only to illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.			
5)	The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM or any other parties. ROHM shall have no responsibility whatsoever for any dispute arising out of the use of such technical information.			
6)	The Products specified in this document are not designed to be radiation tolerant.			
7)	For use of our Products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a ROHM representative : transportation equipment (i.e. cars, ships, trains), primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, servers, solar cells, and power transmission systems.			
8)	Do not use our Products in applications requiring extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters.			
9)	ROHM shall have no responsibility for any damages or injury arising from non-compliance with the recommended usage conditions and specifications contained herein.			
10)	ROHM has used reasonable care to ensure the accuracy of the information contained in this document. However, ROHM does not warrants that such information is error-free, and ROHM shall have no responsibility for any damages arising from any inaccuracy or misprint of such information.			
11)	Please use the Products in accordance with any applicable environmental laws and regulations, such as the RoHS Directive. For more details, including RoHS compatibility, please contact a ROHM sales office. ROHM shall have no responsibility for any damages or losses resulting non-compliance with any applicable laws or regulations.			
12)	When providing our Products and technologies contained in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.			
13)	This document, in part or in whole, may not be reprinted or reproduced without prior consent of ROHM.			



Thank you for your accessing to ROHM product informations. More detail product informations and catalogs are available, please contact us.

### ROHM Customer Support System

http://www.rohm.com/contact/