## REF66003-ML7661-EVK-001 Parts List

X1\_A, X1\_B

Part	Туре	Value	Part Number	Manufacture	Package size	Qty
C1	Capacitor, Surface Mount	47uF	GRM21BR61A476ME15#	Murata	2012	1
C1_A, C1_B, C2_A, C2_B, C9_A, C9_B	Capacitor, Surafce Mount	0.1uF	GRM033R61C104KE18#	Murata	0603	6
C3 A, C3 B, C26 A, C26 B, C28 A, C28 B	Capacitor, Surafce Mount	N.M.	-	-	0603	6
C4 A, C4 B	Capacitor, Surafce Mount	0.47uF	GMD155R61A474KE11#	Murata	1005	2
C5 A, C5 B, C6 A, C6 B	Capacitor, Surafce Mount	560pF	GRM033R11C561KA01#	Murata	0603	4
C7 A, C7 B, C12 A, C12 B	Capacitor, Surafce Mount	0.47uF	GRM033R60J474KE90#	Murata	0603	4
C8 A, C8 B, C20 A, C20 B, C21 A, C21 B	Capacitor, Surafce Mount	2.2uF	GRM035R61C225ME01#	Murata	0603	6
C10 A, C10 B, C14 A, C14 B	Capacitor, Surafce Mount	10pF	GRM0335C1H100GA01#	Murata	0603	4
C11 A, C11 B, C15 A, C15 B	Capacitor, Surafce Mount	1uF	GRM153B31A105ME95#	Murata	1005	4
C13 A, C13 B	Capacitor, Surafce Mount	1nF	GRM033B11E102KA01#	Murata	0603	2
C16 A, C16 B	Capacitor, Surafce Mount	1nF	GRM0335C1E102FA01#	Murata	0603	2
C17 A, C17 B, C18 A, C18 B	Capacitor, Surafce Mount	47pF	GRM0335C1E470JA01#	Murata	0603	4
C19_A, C19_B	Capacitor, Surafce Mount	47uF	GRM21BR61A476ME15#	Murata	2012	2
С22_А, С22_В	Capacitor, Surafce Mount	82pF	GQM1875C2E820FB12#	Murata	1608	2
C23 A, C23 B, C24 A, C24 B	Capacitor, Surafce Mount	100pF	GRM0335C1H101FA01#	Murata	0603	4
C25 A, C25 B	Capacitor, Surafce Mount	N.M.	-	-	1005	2
С27 А, С27 В	Capacitor, Surafce Mount	470pF	GRM1555C1H471GA01#	Murata	1005	2
C29 A, C29 B	Capacitor, Surafce Mount	1.5nF	GRM1882C1H152JA01#	Murata	1608	2
С30 А. С30 В	Capacitor, Surafce Mount	100pF	GRM0335C2A101GA01#	Murata	0603	2
C31 A. C31 B	Capacitor, Surafce Mount	82pF	GRM0335C1H820GA01#	Murata	0603	2
C32 A, C32 B	Capacitor, Surafce Mount	18pF	GRM0335C1H180GA01#	Murata	0603	2
CN1	2pin Pin header	-	-	-	$2.54$ mm pitch. $\omega = 1.02$ mm	1
E1	FUSE	-	MF-MSMF110/16-2	Bourns	4.55mm×3.24mm	1
FB1, FB1, A, FB1, B, FB2	-	-	BLM15AG100SN1D	Murata	1005	4
FB3	-	-	-	-	1005	1
L1 A. L1 B	Inductor, Surface Mount	3.3uH	LOM2MPN3R3NG0L	Murata	2mm×1.6mm	2
L2 A. L2 B	Inductor, Surface Mount	240nH	LOM2MPNR24MEHL	Murata	2mm×1.6mm	2
L3 A. L3 B	Inductor, Surface Mount	N.M.	-	-	2mm×1.6mm	2
LED1 A. LED1 B	3-color LED	-	SMLP34RGB2W	Rohm	1mm×1mm	2
01 A. 01 B		-	RO5E035BN	Rohm	SOT-346T	2
R1 A, R1 B	Resistor, Surface Mount	2.2kΩ	-	Rohm	0603	2
R2 A, R2 B, R3 A, R3 B, R4 A, R4 B	Resistor, Surface Mount	1.8kΩ	-	Rohm	0603	6
R5 A, R5 B	Resistor, Surface Mount	18kΩ	-	Rohm	1005	2
R6 A, R6 B	Resistor, Surface Mount	3.6kΩ	-	Rohm	1005	2
R7 A, R7 B	Resistor, Surface Mount	0Ω	-	-	0603	2
R8 A, R8 B	Resistor, Surface Mount	51Ω	-	Rohm	0603	2
R9 A, R9 B	Resistor, Surface Mount	510Ω	-	Rohm	0603	2
R10 A, R10 B	Resistor, Surface Mount	220mΩ	-	Rohm	1.2mm×2.0mm	2
R11 A R11 B	Resistor, Surface Mount	N.M.	-	-	0603	2
RSW1 A, RSW1 B	Resistor, Surface Mount	N.M.	-	Rohm	1608	2
RSW2 A, RSW2 B	Resistor, Surface Mount	0Ω	-	Rohm	1608	2
U1 A, U1 B		-	ML7661-311GDZ05BX	LAPIS Technology	P-WQFN40-0606-0.50-63	2
U2_A, U2_B	LDO	-	BD00GC0	Rohm	HTSOP-J8	2

Kyocera

2.0mm×1.6mm

CX2016DB27120D0

ROHM GROUP TECHNOLOGY

## Important Notes on the Use of Reference Designs

- 1) The contents of this document are subject to change without notice for the purpose of improvement.
- 2) ROHM provides reference designs (including, but not limited to, circuit diagrams, layout data, parts lists, reference boards and their evaluation results, etc.) and all materials related to evaluation boards (hereinafter collectively referred to as "Reference Designs, etc.") to customers for the purpose of referencing them in the development of devices, equipment, software, etc. incorporating ROHM products (hereinafter collectively referred to as "Customer Products"). The design, verification, etc. required for the development of the Customer's Product shall be done at the customer's responsibility and expense. In no event shall the customer use the Reference Designs, etc. for any purpose other than the purpose mentioned above.
- 3) Reference Designs, etc. are provided on an "as is" basis. ROHM disclaims all warranties, express or implied, including, but not limited to, warranties of usefulness, functionality, accuracy, merchantability, and fitness for a particular purpose. In no event shall ROHM be liable for any damages (including, but not limited to, lost profits or other incidental, consequential, or punitive damages) arising out of, related to or in connection with the use of or application of the Reference Designs, etc. whether in contract or tort. For the avoidance of doubt, ROHM does not warrant that the Reference Designs, etc. will work with the Customer's Product.
- 4) When using Reference Designs, etc. be sure to request and verify the latest specifications (including the specifications of the products that compose the Reference Design, etc.) separately.
- 5) The customer shall be responsible for implementing safety measures such as derating, redundant design, fire prevention, backup, and fail-safe measures, etc., to prevent personal injury, fire damage, etc., caused by the Customer's Product developed with Reference Designs, etc. ROHM assumes no liability whatsoever for any use in excess of the ratings or in case of failure to observe the instructions for use.
- 6) The application circuit examples, constants, and other information provided in Reference Designs, etc. are intended to illustrate standard operation and usage. Therefore, when designing for mass production, please take into account various external conditions.
- 7) Reference Designs, etc. are intended to show typical operations and examples of application circuits, etc., and do not constitute a license, express or implied, to implement or use any intellectual property rights or any other rights of ROHM or any other company. ROHM shall not be liable for any disputes arising from, related to or in connection with the use of the Reference Designs, etc.
- 8) Please make sure to contact ROHM and obtain ROHM's consent before using the Reference Designs, etc. for the following Customer's Product that requires particularly high reliability. Transportation equipment (in-vehicle, ship, railroad, etc.), trunk line communication equipment, traffic signal equipment, disaster and security equipment, safety equipment, medical equipment, servers, solar cells, power transmission systems, etc.
- 9) Do not use Reference Designs, etc. for the following Customer's Product that requires extremely high reliability. Aerospace equipment, nuclear power control equipment, submarine relay equipment, etc.
- 10) Do not use Reference Designs, etc. for military use, such as development of weapons of mass destruction, or for any other military purpose.
- 11) ROHM does not assume any liability for any accidents or damages caused by non- compliance with the descriptions in this document.
- 12) The information contained in this document has been carefully prepared to ensure accuracy. However, ROHM shall not be liable for any loss or damage incurred by customers due to errors or misprints in this document.
- 13) Do not reproduce or duplicate any part of this document in any form or by any means without ROHM's permission.



Thank you for your accessing to ROHM product informations.

More detail product informations and catalogs are available, please contact us.

## ROHM Customer Support System

http://www.rohm.com/contact/