


Metal plate shunt resistors <ultra low ohmic> **PMR** series

Datasheet

Features

- 1) Ultra low-ohmic resistance range $(1m\Omega \sim)$
- 2) Improved current detection accuracy by trimming-less structure.
- 3) Special low resistance temperature coefficient.
- 4) The unique chip structure minimizes thermal stress during temperature cycling, resulting in greater reliability.
- 5) ROHM resistors have obtained ISO9001 / IATF16949 certification.
- 6) Corresponds to AEC-Q200.



Products list

Part No.	Туре	code	Rated power	Rated ambient Temperature	Rated terminal Temperature	Resistance tolerance	Temperature coefficient	Resistance range	Operating temperature range	Automotive Grade Available (AEC-Q200)
	(mm)	(inch)	(W)	(°C)	(°C)	(%)	(ppm / °C)	(mΩ)	(°C)	(AEC-Q200)
PMR01	1005	0402	0.2	70	-	J(±5%)	0~+200	10	-55 ∼ +155	Yes
PMR03	1608	0603	0.25	70	-	F(±1%) J(±5%)	0~+150	10	-55 ∼ +155	Yes
			1	-	130	F(±1%) J(±5%)	±100	2	-65 ∼ +155	
PMR10	2012	0805	0.5	70	-	F(±1%) J(±5%)	±150	3,4,5,6,7,8,9,10	-55 ∼ +155	Yes
PMR18	3216	1206	1.5	-	130	F(±1%) J(±5%)	±100	1,2	-65 ∼ +155	V
PINIK18	3216	1206	1	70	-	F(±1%) J(±5%)	±100	3,4,5,6,7,8,9,10	-55 ∼ +155	Yes
PMR25	3225	1210	2	-	130	F(±1%) J(±5%)	±75	1	-65 ∼ +175	Yes
PWIK25	3225	1210	1	70	-	F(±1%) J(±5%)	±100	2,3,4,5	-55 ∼ +155	res
PMR50	5025	2010	2	-	130	F(±1%) J(±5%)	±75	1,2	-65 ∼ +175	Yes
PWK50	5025	2010	1	70	-	F(±1%) J(±5%)	±100	3,4,5,6,7,8,9,10	-55 ∼ +155	res
PMR100	6432	2512	3	-	130	F(±1%) J(±5%)	±75 ±150	1,2	-65 ∼ +175	V
PIVIK100	6432	∠512	2	70	-	F(±1%) J(±5%)	±100	3,4,5,6,7,8,9,10	-55 ∼ +155	Yes

Design and specifications are subject to change without notice.

Carefully check the specification sheet supplied with the product before using or ordering it.

Part Number Description

PMR

10

HZP

Special part code $U:5m\sim10m\Omega$

2L0

PMR Metal plate shunt resistors / ultra low ohmic	


Size	(mm)	[inch]
01	(1005)	[0402]
03	(1608)	[0603]
10	(2012)	[0805]
18	(3216)	[1206]
25	(3225)	[1210]
50	(5025)	[2010]
100	(6432)	[2512]

Packaging specifications code					
Part No.	Code	Packaging specifications	Quantity / Reel(pcs)		
PMR01	ZZP	Embossed tape (2mm pitch)	10,000		
PMR03	EZP	Paper tape (4mm pitch)	5,000		
PMR10	EZP	Paper tape (4mm pitch)	5,000		
PMR18	EZP	Paper tape (4mm pitch)	5,000		
PMR25	HZP	Embossed tape (4mm pitch)	2,000		
PMR50	HZP	Embossed tape (4mm pitch)	2,000		
PMR100	HZP	Embossed tape (4mm pitch)	2,000		

Packa	Resistance tolerance			
art No.	Code	Packaging specifications	Quantity / Reel(pcs)	F (±1%) J (±5%)
MR01	ZZP	Embossed tape (2mm pitch)	10,000	
MR03	EZP	Paper tape (4mm pitch)	5,000	
MR10	EZP	Paper tape (4mm pitch)	5,000	
MR18	EZP	Paper tape (4mm pitch)	5,000	
MR25	HZP	Embossed tape (4mm pitch)	2,000	
MR50	HZP	Embossed tape (4mm pitch)	2,000	
#D400	1170	Embossed tape	0.000	

Nominal resistance				
Resistance of 3 or 4 digits.	ode,			
Resistance Resistance tolerance				
value	F	J		
1mΩ	1L00	1L0		
2mΩ	2L00	2L0		
3mΩ	3L00	3L0		
4mΩ	4L00	4L0		
5mΩ	5L00	5L0		
6mΩ	6L00	6L0		
7mΩ	7L00	7L0		
8mΩ	8L00	8L0		
9mΩ	9L00	9L0		
10mΩ	10L0	10L		

•Chip resistor dimensions and markings



<Marking method>


There are four digits used for the calculation number. "L" is used for the decimal point of $m\Omega$. Ex.) $2m\Omega = 2L00$ $10m\Omega = 10L0$

*PMR01/03 are no marking.

(Unit: mm)

Part No.	(mm)	(inch)	Resistance range	L	W	t	а	b	С	Marking	
T art NO.	` ′	(111011)	(mΩ)	_			a		C	existence	
PMR01	1005	0402	10	1.00±0.05	0.50±0.05	0.25±0.10	_	0.25±0.10	_	No	
PMR03	1608	0603	10	1.60±0.15	0.80±0.15	0.25±0.10	_	0.35±0.15	_	No	
		2					0.55±0.25				
		3			0.42±0.15		0.75±0.25				
			4			0.1220.10		0.60±0.25			
			5	2.00±0.15				0.45±0.25			
PMR10	2012	0805	6		1.20±0.15		_	0.55±0.25	_	Yes	
			7			0.32±0.15		0.45±0.25			
			8					0.35±0.25			
			9			0.28±0.15		0.40±0.25			
			10			0.2020.10		0.35±0.25			
			1			0.44±0.15		1.20±0.25			
			2					0.85±0.25			
			3					1.15±0.25			
			4			0.42±0.15		0.90±0.25			
PMR18	3216	1206	5	3.20±0.15	1.60±0.15	15		_	0.70±0.25	_	Ves
1 1011110	0210	1200	6	0.2010.10	1.00±0.10			0.50±0.25		1 63	
			7			0.32±0.15		0.75±0.25			
			8			0.3210.13		0.60±0.25			
			9	0.28±0.15		0.70±0.25					
			10			0.2010.10		0.60±0.25			
			1	3.20±0.20	0.52±0.15 2.50±0.20 0.42±0.15 0.32±0.15		0.90±0.20				
		3225 1210	2			0.0220.10	0.50±0.20	1.00±0.20	1.95±0.20	Yes	
PMR25	3225		3			0.42±0.15		0.80±0.20			
			4			0.32±0.15		0.90±0.20			
			5					0.90±0.20			
			1			0.52±0.15		1.85±0.20			
			2			0.42±0.15	0.50±0.20	1.30±0.20	1.95±0.20	Yes	
			3			0.52±0.15		1.40±0.20			
			4]		0.42±0.15		1.40±0.20			
PMR50	5025	2010	5	5.00±0.20	2.50±0.20	01.12201.10		1.05±0.20			
1 1111100	0020	2010	6	0.0010.20	2.0010.20		0.0010.20	1.40±0.20			
			7					1.10±0.20			
			8			0.32±0.15		0.90±0.20			
			9					1.10±0.20			
			10					0.90±0.20			
			1			0.52±0.15		2.30±0.25			
			2			0.42±0.15		1.60±0.25			
			3			0.52±0.15		1.80±0.25			
			4			0.42±0.15		1.80±0.25	<u>; </u>		
PMR100	6432	2512	5	6.40±0.25	3.20±0.25	0.1220.10	0.50±0.25	1.30±0.25	2.65±0.25	Yes	
	3-102	2012	6	0.7010.20	5.2010.20		0.0010.20	1.70±0.25	2.00±0.20	103	
			7					1.40±0.25			
			8			0.32±0.15		1.10±0.25			
			9					1.35±0.25			
			10					1.10±0.25			

•Land pattern example



(Unit: mm)


Dimensions Part No.	А	В	С	D
PMR01	0.5	1.8	0.5	0.65
PMR03	0.5	2.5	0.9	1.0
PMR10	0.8	3.4	1.3	1.3
PMR18	0.6	4.0	1.8	1.7
PMR25	1.0	4.0	2.8	1.5
PMR50	1.8	6.0	2.8	2.1
PMR100	1.2	6.8	3.4	2.8

Derating curve

When the ambient temperature exceeds 70°C, or terminal temperature in excess 130°C power dissipation must be adjusted according to the derating curve below.


<Ambient temperature>

- ■PMR01
- ■PMR03
- **■**PMR10 (3, 4, 5, 6, 7, 8, 9, 10mΩ)
- **■**PMR18 (3, 4, 5, 6, 7, 8, 9, 10mΩ)
- **■**PMR25 (2, 3, 4, 5mΩ)
- **■**PMR50 (3, 4, 5mΩ)
- **■**PMR100 (3, 4, 5, 6, 7, 8, 9, 10mΩ)




<Terminal temperature>

- **■**PMR10 (2mΩ)
- **■**PMR18 (1, 2mΩ)



- **■**PMR25 (1mΩ)
- **■**PMR50 (1, 2mΩ)
- **■**PMR100 (1, 2mΩ)



PMR series Datasheet

Characteristic

Test items	Guaranteed value	Test conditions
Resistance	See P.1	20°C Measuring method : Measuring under termination by 4 probes. Bottom termination Probe
Variation of resistance with temperature	See P.1	Test condition : See table 1
Overload	See table 2	Test condition : See table 2
Solderability	A new uniform coating of minimum of 95% of the surface being immersed and no soldering damage.	Rosin-ethanol solution(25% mass) Soldering condition : 245±5°C Duration of immersion : 2.0±0.5s
Resistance to soldering heat	±1.0% No remarkable abnormality on the appearance.	Soldering condition : 260±5°C Duration of immersion : 10±1s
Rapid change of temperature	±1.0%	Test condition : See table 3
Temperature humidity storage	See table 4	Test condition : See table 4
Endurance (70°C, Terminal temperature)	See table 5	Test condition : See table 5
Endurance (Ambient temperature)	See table 6	Test condition : See table 6
Resistance to solvent	±0.5%	23±5°C, Immersion cleaning, 5±0.5min Solvent : 2-propanol
Bend strength of the end face plating	Without open.	Endurance with 90mm width Deflection : 3mm(PMR01/03/10/18) Deflection : 1mm(PMR25/50/100)

IEC 60115-1 / IEC 60115-8 JIS C 5201-1 / JIS C 5201-8

Table 1 : Test condition of variation of resistance with temperature

Test condition Resistance range Part No. $(m\Omega)$ (°C) PMR01 10 +25/-55, +25/+125 PMR03 10 +25/-65, +25/+155 PMR10 3,4,5,6,7,8,9,10 +25/-55, +25/+125 +25/-65, +25/+155 PMR18 3,4,5,6,7,8,9,10 +25/-55, +25/+125 +25/-65, +25/+175 PMR25 2,3,4,5 +25/-55, +25/+125 +25/-65, +25/+175 PMR50 3,4,5,6,7,8,9,10 +25/-55, +25/+125 +25/-65, +25/+155 PMR100 3,4,5,6,7,8,9,10 +25/-55, +25/+125

Table 2: Test condition of overload

Part No.	Resistance range (mΩ)	Test condition	Guaranteed value
PMR01	10	Rated power×2.5, 2s	+2.0%
PMR03	10	Rated powerx2.5, 25	±2.0%
PMR10	2	Rated powerx3.0, 5s	±0.5%
PIVIKIU	3,4,5,6,7,8,9,10	Rated powerx2.5, 2s	±2.0%
PMR18	1,2	Rated powerx3.0, 5s	±0.5%
FIVIKIO	3,4,5,6,7,8,9,10	Rated powerx2.5, 2s	±2.0%
PMR25	1	Rated powerx3.0, 5s	±0.5%
FIVIRZS	2,3,4,5	Rated powerx2.5, 2s	±2.0%
PMR50	1,2	Rated powerx3.0, 5s	±0.5%
PIVIKOU	3,4,5,6,7,8,9,10	Rated power×2.5, 2s	±2.0%
PMR100	1,2	Rated powerx3.0, 5s	±0.5%
FINIKIOO	3,4,5,6,7,8,9,10	Rated powerx2.5, 2s	±2.0%

PMR series

Table 3: Test condition of rapid change of temperature

Part No.	Resistance range (mΩ)	Test condition
PMR01	PMR01 10	
PMR03	10	-55°C∼+125°C 5cycles
PMR10	2	-55°C~+155°C 1,000cycles
PIVIKIU	3,4,5,6,7,8,9,10	-55°C∼+125°C 5cycles
PMR18	1,2	-55°C∼+155°C 1,000cycles
PIVIKIO	3,4,5,6,7,8,9,10	-55°C∼+125°C 5cycles
PMR25	1	-55°C~+155°C 1,000cycles
FIVIRZS	2,3,4,5	-55°C∼+125°C 5cycles
PMR50	1,2	-55°C~+155°C 1,000cycles
PINIKOU	3,4,5,6,7,8,9,10	-55°C∼+125°C 5cycles
DMD400	1,2	-55°C~+155°C 1,000cycles
PMR100	3,4,5,6,7,8,9,10	-55°C∼+125°C 5cycles

Table 4: Test condition of temperature humidity storage

Part No.	Resistance range (mΩ)	Test condition	Guaranteed value
PMR01	10	40°C, 93%(Relative Humidity)	. 2. 00/
PMR03	10	Test time : 56days	±3.0%
PMR10	2	85°C, 85%(Relative Humidity) Test time: 1,000h	±1.0%
PMR10	3,4,5,6,7,8,9,10	40°C, 93%(Relative Humidity) Test time: 56days	±3.0%
PMR18	1,2	85°C, 85%(Relative Humidity) Test time: 1,000h	±1.0%
PWK16	3,4,5,6,7,8,9,10	40°C, 93%(Relative Humidity) Test time: 56days	±3.0%
PMR25	1	85°C, 85%(Relative Humidity) Test time: 1,000h	±1.0%
PIVIR25	2,3,4,5	40°C, 93%(Relative Humidity) Test time: 56days	±3.0%
PMR50	1,2	85°C, 85%(Relative Humidity) Test time: 1,000h	±1.0%
PIVINGU	3,4,5,6,7,8,9,10	40°C, 93%(Relative Humidity) Test time: 56days	±3.0%
PMR100	1,2	85°C, 85%(Relative Humidity) Test time: 1,000h	±1.0%
1- IVIIX IOU	3,4,5,6,7,8,9,10	40°C, 93%(Relative Humidity) Test time: 56days	±3.0%

Datasheet

PMR series

Table 5: Test condition of endurance(70°C, Terminal temperature)

Part No.	Resistance range (mΩ)	Test condition	Guaranteed value	
PMR01	10	Ambient temperature : 70°C Rated power 1.5h ON-0.5h OFF	±3.0%	
PMR03	10	Test time: 1,000h	±3.0%	
PMR10	2	Terminal temperature : 130°C Rated power 1.5h ON-0.5h OFF Test time : 1,000h	±1.0%	
PWIKTO	3,4,5,6,7,8,9,10	Ambient temperature : 70°C Rated power 1.5h ON-0.5h OFF Test time : 1,000h	±3.0%	
PMR18	1,2	Terminal temperature : 130°C Rated power 1.5h ON-0.5h OFF Test time : 1,000h	±1.0%	
1 MIK 10	3,4,5,6,7,8,9,10	Ambient temperature : 70°C Rated power 1.5h ON-0.5h OFF Test time : 1,000h	±3.0%	
PMR25	1	Terminal temperature : 130°C Rated power 1.5h ON-0.5h OFF Test time : 1,000h	±1.0%	
PINIKZS	2,3,4,5	Ambient temperature : 70°C Rated power 1.5h ON-0.5h OFF Test time : 1,000h	±3.0%	
PMR50	1,2	Terminal temperature : 130°C Rated power 1.5h ON-0.5h OFF Test time : 1,000h	±1.0%	
PMRSU	3,4,5,6,7,8,9,10	Ambient temperature : 70°C Rated power 1.5h ON-0.5h OFF Test time : 1,000h	±3.0%	
PMR100	1,2	Terminal temperature : 130°C Rated power 1.5h ON-0.5h OFF Test time : 1,000h	±1.0%	
PIVIK 100	3,4,5,6,7,8,9,10	Ambient temperature : 70°C Rated power 1.5h ON-0.5h OFF Test time : 1,000h	±3.0%	

PMR series


Table 6: Test condition of endurance(ambient temperature)

Part No.	Resistance range (mΩ)	I lest condition I	
PMR01	40		0.007
PMR03	10		±3.0%
PMR10	2	155°C	±1.0%
PIVIKIO	3,4,5,6,7,8,9,10	Test time: 1,000h	±3.0%
PMR18	1,2		±1.0%
PIVIKIO	3,4,5,6,7,8,9,10		±3.0%
PMR25	1	175°C Test time : 1,000h	±1.0%
PIVIR25	2,3,4,5	155°C Test time: 1,000h	±3.0%
PMR50	1,2	175°C Test time : 1,000h	±1.0%
PIVIRSU	3,4,5,6,7,8,9,10	155°C Test time: 1,000h	±3.0%
PMR100	1,2	175°C Test time: 1,000h	±1.0%
PIVIKIOU	3,4,5,6,7,8,9,10	155°C Test time: 1,000h ±3.0%	

PMR series Datasheet

•Tape dimensions

■Paper tape




_						
F	Part No.	W	F	E	A0	B0
	PMR03	8.0±0.3	3.5±0.05	1.75±0.1	0.95±0.1	1.75±0.1
	PMR10	8.0±0.3	3.5±0.05	1.75±0.1	1.45+0.2 -0.1	2.30+0.2 -0.1
Г	PMR18	8.0±0.3	3.5±0.05	1.75±0.1	1.95+0.1	3.50+0.15

Part No.	D0	P0	P1	P2	T2
PMR03	Ф1.5+0.1 0	4.0±0.1	4.0±0.1	2.0±0.05	MAX1.1
PMR10	Ф1.5+0.1 0	4.0±0.1	4.0±0.1	2.0±0.05	MAX1.1
PMR18	Ф1.5+0.1 0	4.0±0.1	4.0±0.1	2.0±0.05	MAX1.1

■Embossed tape

· PMR01



(Unit: mm)


(Unit: mm)

(Unit: mm)

Part No.	W	F	Е	A0	B0
PMR01	8.0±0.1	3.5±0.05	1.75±0.1	0.68±0.03	1.12±0.03

Part No.	D0	P0	P1	P2	K
PMR01	Ф1.5+0.1 0	4.0±0.05	2.0±0.05	2.0±0.05	MAX1.1

· PMR25/50/100




Part No.	W	F	E	A0	B0
PMR25	8.0±0.3	3.5±0.05	1.75±0.1	3.0±0.1	3.5±0.1
PMR50	12.0±0.3	5.5±0.05	1.75±0.1	2.9±0.2	5.3±0.2
PMR100	12.0±0.3	5.5±0.05	1.75±0.1	3.5±0.2	6.7±0.2

Part No.	D0	P0	P1	P2	K
PMR25	Ф1.5+0.1 0	4.0±0.1	4.0±0.1	2.0±0.05	MAX1.1
PMR50	Ф1.5+0.1 0	4.0±0.1	4.0±0.1	2.0±0.05	MAX1.1
PMR100	Ф1.5+0.1 0	4.0±0.1	4.0±0.1	2.0±0.05	MAX1.1



•Reel dimensions

Using two kinds of reels for taping.



(Unit: mm)

Part No.	А	В	С	D
PMR01				
PMR03				
PMR10			9 +1.0 0	
PMR18	Ф180 0 -1.5	Ф60 +1.0 0		Ф13±0.2
PMR25				
PMR50			13 +1.0	
PMR100			0	

Notice

Precaution on using ROHM Products

1. If you intend to use our Products in devices requiring extremely high reliability (such as medical equipment (Note 1), aircraft/spacecraft, nuclear power controllers, etc.) and whose malfunction or failure may cause loss of human life, bodily injury or serious damage to property ("Specific Applications"), please consult with the ROHM sales representative in advance. Unless otherwise agreed in writing by ROHM in advance, ROHM shall not be in any way responsible or liable for any damages, expenses or losses incurred by you or third parties arising from the use of any ROHM's Products for Specific Applications.

(Note1) Medical Equipment Classification of the Specific Applications

ſ	JÁPAN	USA	EU	CHINA
Ī	CLASSⅢ	CL ACCIII	CLASS II b	СГУССШ
ſ	CLASSIV	CLASSⅢ	CLASSⅢ	CLASSⅢ

- 2. ROHM designs and manufactures its Products subject to strict quality control system. However, semiconductor products can fail or malfunction at a certain rate. Please be sure to implement, at your own responsibilities, adequate safety measures including but not limited to fail-safe design against the physical injury, damage to any property, which a failure or malfunction of our Products may cause. The following are examples of safety measures:
 - [a] Installation of protection circuits or other protective devices to improve system safety
 - [b] Installation of redundant circuits to reduce the impact of single or multiple circuit failure
- 3. Our Products are not designed under any special or extraordinary environments or conditions, as exemplified below. Accordingly, ROHM shall not be in any way responsible or liable for any damages, expenses or losses arising from the use of any ROHM's Products under any special or extraordinary environments or conditions. If you intend to use our Products under any special or extraordinary environments or conditions (as exemplified below), your independent verification and confirmation of product performance, reliability, etc, prior to use, must be necessary:
 - [a] Use of our Products in any types of liquid, including water, oils, chemicals, and organic solvents
 - [b] Use of our Products outdoors or in places where the Products are exposed to direct sunlight or dust
 - [c] Use of our Products in places where the Products are exposed to sea wind or corrosive gases, including Cl₂, H₂S, NH₃, SO₂, and NO₂
 - [d] Use of our Products in places where the Products are exposed to static electricity or electromagnetic waves
 - [e] Use of our Products in proximity to heat-producing components, plastic cords, or other flammable items
 - [f] Sealing or coating our Products with resin or other coating materials
 - [g] Use of our Products without cleaning residue of flux (Exclude cases where no-clean type fluxes is used. However, recommend sufficiently about the residue.); or Washing our Products by using water or water-soluble cleaning agents for cleaning residue after soldering
 - [h] Use of the Products in places subject to dew condensation
- 4. The Products are not subject to radiation-proof design.
- 5. Please verify and confirm characteristics of the final or mounted products in using the Products.
- 6. In particular, if a transient load (a large amount of load applied in a short period of time, such as pulse, is applied, confirmation of performance characteristics after on-board mounting is strongly recommended. Avoid applying power exceeding normal rated power; exceeding the power rating under steady-state loading condition may negatively affect product performance and reliability.
- 7. De-rate Power Dissipation depending on ambient temperature. When used in sealed area, confirm that it is the use in the range that does not exceed the maximum junction temperature.
- 8. Confirm that operation temperature is within the specified range described in the product specification.
- ROHM shall not be in any way responsible or liable for failure induced under deviant condition from what is defined in this document.

Precaution for Mounting / Circuit board design

- 1. When a highly active halogenous (chlorine, bromine, etc.) flux is used, the residue of flux may negatively affect product performance and reliability.
- 2. In principle, the reflow soldering method must be used on a surface-mount products, the flow soldering method must be used on a through hole mount products. If the flow soldering method is preferred on a surface-mount products, please consult with the ROHM representative in advance.

For details, please refer to ROHM Mounting specification

Precautions Regarding Application Examples and External Circuits

- 1. If change is made to the constant of an external circuit, please allow a sufficient margin considering variations of the characteristics of the Products and external components, including transient characteristics, as well as static characteristics.
- 2. You agree that application notes, reference designs, and associated data and information contained in this document are presented only as guidance for Products use. Therefore, in case you use such information, you are solely responsible for it and you must exercise your own independent verification and judgment in the use of such information contained in this document. ROHM shall not be in any way responsible or liable for any damages, expenses or losses incurred by you or third parties arising from the use of such information.

Precaution for Electrostatic

This Product is electrostatic sensitive product, which may be damaged due to electrostatic discharge. Please take proper caution in your manufacturing process and storage so that voltage exceeding the Products maximum rating will not be applied to Products. Please take special care under dry condition (e.g. Grounding of human body / equipment / solder iron, isolation from charged objects, setting of lonizer, friction prevention and temperature / humidity control).

Precaution for Storage / Transportation

- 1. Product performance and soldered connections may deteriorate if the Products are stored in the places where:
 - [a] the Products are exposed to sea winds or corrosive gases, including Cl₂, H₂S, NH₃, SO₂, and NO₂
 - [b] the temperature or humidity exceeds those recommended by ROHM
 - [c] the Products are exposed to direct sunshine or condensation
 - [d] the Products are exposed to high Electrostatic
- Even under ROHM recommended storage condition, solderability of products out of recommended storage time period
 may be degraded. It is strongly recommended to confirm solderability before using Products of which storage time is
 exceeding the recommended storage time period.
- 3. Store / transport cartons in the correct direction, which is indicated on a carton with a symbol. Otherwise bent leads may occur due to excessive stress applied when dropping of a carton.
- 4. Use Products within the specified time after opening a humidity barrier bag. Baking is required before using Products of which storage time is exceeding the recommended storage time period.

Precaution for Product Label

A two-dimensional barcode printed on ROHM Products label is for ROHM's internal use only.

Precaution for Disposition

When disposing Products please dispose them properly using an authorized industry waste company.

Precaution for Foreign Exchange and Foreign Trade act

Since concerned goods might be fallen under listed items of export control prescribed by Foreign exchange and Foreign trade act, please consult with ROHM in case of export.

Precaution Regarding Intellectual Property Rights

- 1. All information and data including but not limited to application example contained in this document is for reference only. ROHM does not warrant that foregoing information or data will not infringe any intellectual property rights or any other rights of any third party regarding such information or data.
- 2. ROHM shall not have any obligations where the claims, actions or demands arising from the combination of the Products with other articles such as components, circuits, systems or external equipment (including software).
- 3. No license, expressly or implied, is granted hereby under any intellectual property rights or other rights of ROHM or any third parties with respect to the Products or the information contained in this document. Provided, however, that ROHM will not assert its intellectual property rights or other rights against you or your customers to the extent necessary to manufacture or sell products containing the Products, subject to the terms and conditions herein.

Other Precaution

- 1. This document may not be reprinted or reproduced, in whole or in part, without prior written consent of ROHM.
- 2. The Products may not be disassembled, converted, modified, reproduced or otherwise changed without prior written consent of ROHM.
- In no event shall you use in any way whatsoever the Products and the related technical information contained in the Products or this document for any military purposes, including but not limited to, the development of mass-destruction weapons.
- 4. The proper names of companies or products described in this document are trademarks or registered trademarks of ROHM, its affiliated companies or third parties.

Notice-PAA-E Rev.004

General Precaution

- 1. Before you use our Products, you are requested to carefully read this document and fully understand its contents. ROHM shall not be in any way responsible or liable for failure, malfunction or accident arising from the use of any ROHM's Products against warning, caution or note contained in this document.
- 2. All information contained in this document is current as of the issuing date and subject to change without any prior notice. Before purchasing or using ROHM's Products, please confirm the latest information with a ROHM sales representative.
- 3. The information contained in this document is provided on an "as is" basis and ROHM does not warrant that all information contained in this document is accurate and/or error-free. ROHM shall not be in any way responsible or liable for any damages, expenses or losses incurred by you or third parties resulting from inaccuracy or errors of or concerning such information.

Notice – WE Rev.001