Conductive polymer chip capacitors (New Bottom surface electrode type: Extra Large capacitance)


TCSO series PL case

Datasheet


Features

- 1) Conductive polymer used at the cathode for ultra-low ESR.
- 2) New package structure results in the largest capacitance.
- 3) Compact, low profile, ultra-high capacitance contributes to smaller, thinner sets with greater functionality.
- 4) Conductive polymer has a self-healing function that prevents failure, resulting in safe, high reliability operation.

Dimensions



● Part No. Explanation



- ① Series name TCSO
- 2 Case style

PL: 2012-2012(10)size

3 Rated voltage

- 1101100 101101	9.5
CODE	Rated voltage(V)
0E	2.5
0G	4
0J	6.3
1A	10
1C	16
1D	20
1E	25
1V	35
1H	50

- 4 Nominal capacitance
 - Nominal capacitance in pF in 3 digits:
 - 2 significant figures followed by the figure representing the number of 0's.
- (5) Capacitance tolerance

M: ±20%

- 6 Taping
 - 8: Tape width

R: Positive electrode on the side opposite to sprocket hole

7 Discrimination code

Rated table

 $ESR(m\Omega)$

Capac	itance	Rated voltage (V.DC)							
(µI	F)	2.5	4	6.3	10	16	20	25	35
1	(105)								
1.5	(155)								
2.2	(225)								☆500
3.3	(335)								
4.7	(475)							☆300/500	
6.8	(685)								
10	(106)					150			
15	(156)								
22	(226)				200				
33	(336)								
47	(476)			150					
68	(686)			☆150/☆200					
100	(107)								

Marking

The indications listed below should be given on the surface of a capacitor.

- (1) Polarity: The polarity should be shown by bar. (on the anode side)
- (2) Rated DC voltage: A voltage code is shown as below table.
- (3) Capacitance: A capacitance code is shown as below table.

Voltage Code	Rated DC
voltage Code	Voltage (V)
е	2.5
g	4
j	6.3
k	8
Α	10
С	16
D	20
E	25
V	35
Н	50

Capacitance	Nominal	Capacitance	Nominal		
Code	Capacitance (µF)	Code	Capacitance (µF)		
<u>E</u>	0.15	е	15		
<u>N</u>	0.33	j	22		
<u>s</u>	0.47	n	33		
А	1.0	S	47		
E	1.5	8	68		
J	2.2	а	100		
N	3.3	Φ	150		
S	4.7	j	220		
W	6.8	n	330		
а	10	s	470		


Visual typical example

voltage code and capacitance code are variable with parts number.

[TCSO series PL case]

EX.)
$$\frac{j}{(1)}$$
 $\frac{s}{(2)}$

- (1) voltage code
- (2) capacitance code



Characteristics

Item		Performance	Test conditions (based on JIS C 5101-1 and JIS C 5101-3)					
Operating Temp	erature	-55℃~+105℃	Voltage reduction when temperature exceeds +85°C					
Maximum opera	ting	+85℃						
temperature with	no no							
voltage derating								
Rated voltage (V	'.DC)	Refer to " Standard list ".	at 85℃					
Category voltage	e (V.DC)	Refer to " Standard list ".	at 105℃					
Surge voltage (V	'.DC)	Refer to " Standard list ".	at 85℃					
DC Leakage cur	rent	Shall be satisfied the value on	As per 4.9 JIS C 5101-1					
		" Standard list ".	As per 4.5.1 JIS C 5101-3					
			Voltage : Rated voltage for 5min					
Capacitance tole	erance	Shall be satisfied allowance range.	As per 4.7 JIS C 5101-1					
		±20%	As per 4.5.2 JIS C 5101-3					
			Measuring frequency : 120 ± 12Hz					
			Measuring voltage : 0.5Vrms + 1.5V.DC					
			Measuring circuit : DC Equivalent series circuit					
Tangent of loss	angle	Shall be satisfied the value on	As per 4.8 JIS C 5101-1					
(Df,tanδ)		" Standard list ".	As per 4.5.3 JIS C 5101-3					
			Measuring frequency : 120 ± 12Hz					
			Measuring voltage : 0.5Vrms + 1.5V.DC					
			Measuring circuit : DC Equivalent series circuit					
ESR		Shall be satisfied the value on	As per 4.10 JIS C 5101-1					
		" Standard list ".	As per 4.5.4 JIS C 5101-3					
			Measuring frequency : 100 ± 10kHz					
			Measuring voltage : 0.5Vrms or less					
D • · · · ·	Δ	There should be an eight from	Measuring circuit : DC Equivalent series circuit					
Resistance to	Appe-	There should be no significant	As per 4.14 JIS C 5101-1					
Soldering	arance	abnormality. The indications should be clear.	As per 4.6 JIS C 5101-3					
heat	L.C.	Less than 300% of initial limit.	Dip in the solder bath					
	L.O.	Less than 300 % of fillial liffit.	Solder temp : 240 ± 5°C Duration : 10 ± 0.5s					
	⊿C/C	Within ±20% of initial value.	Repetition: 10 ± 0.5s Repetition: 1 After the specimens, leave it at room temperature					
	20/0	VVICINI 220 /0 of finitial value.						
	DF	Less than 300% of initial limit.	for over 24h and then measure the sample.					
	(tanδ)		· '					
Temperature	Appe-	There should be no significant	As per 4.16 JIS C 5101-1					
cycle	arance	abnormality.	As per 4.10 JIS C 5101-3					
		The indications should be clear.	Repetition: 5 cycles					
	L.C.	Less than 1000% of initial limit.	(1 cycle : steps 1 to 4) without discontinuation.					
			Temp. Time					
	⊿C/C	Within ±20% of initial value.	1 -55±3℃ 30±3min					
	5-		2 Room Temp. 3min or less					
	DF	Less than 300% of initial limit.	3 105±2℃ 30±3min					
	(tanδ)		4 Room Temp. 3min or less					
			After the specimens, leave it at room temperature					
			for over 24h and then measure the sample.					
			Initial value for ∠C/C shall be the value after					
			mounted.					

Item		Performance	Test conditions (based on JIS C 5101-1 and JIS C 5101-3)				
Moisture	Appe-	There should be no significant	As per 4.22 JIS C 5101-1				
resistance	arance	abnormality.	As per 4.12 JIS C 5101-3				
resistance	aranco	The indications should be clear.	After leaving the sample under such atmospheric				
	L.C.	Less than 300% of initial limit.	condition that the temperature and humidity are				
	L.O.	Less than 500 % of fillian liftit.	40±2°C and 90 to 95% RH, respectively, for				
	⊿C/C	Within +30/-20% of initial value.	500+12/0h leave it at room temperature for				
	⊿0/0	Within +30/-20% of initial value.					
	DF	Less than 300% of initial limit.	over 24h and then measure the sample.				
		Less than 300% of miliar limit.	Initial value for ∠C/C shall be the value after				
Temperature	(tanδ) Temp. : -	55°C	mounted. As per 4.29 JIS C 5101-1				
Stability	⊿C/C	Within 0/-20% of initial value.	As per 4.13 JIS C 5101-3				
Stability	20/0	Within 0/-20 % of filling value.	Initial value for ∠C/C shall be the value after				
	DF	Shall be satisfied the value on	mounted.				
	(tanδ)	" Standard list "	mounted.				
	L.C.	Staridard list	-				
	L.O.						
	Temp.:-	<u>I</u> +105°C	\dashv				
	⊿C/C	Within +50/0% of initial value.	-				
	DF	Shall be satisfied the value on					
	(tanδ)	" Standard list "					
	L.C.	Less than 1000% of initial limit.					
	<u> </u>						
Surge	Appe-	There should be no significant	As per 4.26JIS C 5101-1				
voltage	arance	abnormality.	As per 4.14JIS C 5101-3				
	1.0	The indications should be clear.	Apply the specified surge voltage via the serial				
	L.C.	Less than 200% of initial limit.	resistance of $1k\Omega$ ever 5 ± 0.5 min. for 30 ± 5 s.				
	40.10	Will cook to in the	each time in the atmospheric condition of				
	⊿C/C	Within ±20% of initial value.	85±2°C. Repeat this procedure 1,000 times.				
	<u> </u>		After the specimens, leave it at room temperature				
	DF (45)	Less than 200% of initial limit.	for over 24h and then measure the sample.				
	(tanδ)		Initial value for ∠C/C shall be the value after mounted.				
Loading at	Appe-	There should be no significant	As per 4.23 JIS C 5101-1				
High	arance	abnormality.	As per 4.25 JIS C 5101-1				
temperature	a.a.ioo	The indications should be clear.	After applying the rated voltage for 1000+72/0 h				
tomperature	L.C.	Less than 400% of initial limit.	without discontinuation via the serial resistance				
	L.O.	Less than 40070 of Illitial Illiti.	of 3Ω or less at a temperature of $85\pm2^{\circ}$ C, leave				
	⊿C/C	Within ±20% of initial value.	the sample at room temperature / humidity for				
	20/0	vviumi ±20/0 01 miliai value.	over 24h and measure the value.				
	DF	Less than 300% of initial limit.	Initial value for ∠C/C shall be the value after				
		Less than 500% of milial limit.					
	(tanδ)		mounted.				

Item		Performance	Test conditions (based on JIS C 5101-1 and JIS C 5101-3)				
Terminal	Capa-	The measured value should be	As per 4.35 JIS C 5101-1				
strength	citance	stable.	As per 4.9 JIS C 5101-3				
55g	Appe-	There should be no significant	A force is applied to the terminal until it bends to				
	arance	abnormality.	1mm and by a prescribed tool maintains the				
			condition for 5s.				
			F(Apply force) R230 F(Apply force) 1.0mm				
Adhesiveness		The terminal should not come off.	As per 4.34 JIS C 5101-1				
			As per 4.8 JIS C 5101-3				
			Apply force of 2N in the two directions shown in				
			the figure below for 10±1s after mounting the				
			terminal on a circuit board.				
			Apply force A circuit board				
Dimensions		Refer to "External dimensions".	Measure using a caliper of JIS B 7507 Class 2 or higher grade.				
Resistance to		The indication should be clear.	As per 4.32 JIS C 5101-1				
solvents			As per 4.18 JIS C 5101-3				
			Dip in the isopropyl alcohol for 30±5s, at room				
			temperature.				
Solderability		3/4 or more surface area of the	As per 4.15.2 JIS C 5101-1				
		solder coated terminal dipped in	As per 4.7 JIS C 5101-3				
		the soldering bath should be	Dip speed=25±2.5mm / s				
		covered with the new solder.	Pre-treatment (accelerated aging):				
			Leave the sample on the boiling distilled water				
			for 1h.				
			Solder temp. : 245±5°C				
			Duration: 3±0.5s				
			Solder: M705				
A file we ti	0	Management I I I I I I I I I I I I I I I I I I I	Flux : Rosin 25% IPA 75%				
Vibration	Capa-	Measure value should not fluctuate	As per 4.17 JIS C 5101-1				
	citance	during the measurement.	Frequency: 10 to 55 to 10Hz/min.				
	Appe-	There should be no significant	Amplitude: 1.5mm				
	arance	abnormality.	Time: 2h each in X and Y directions				
			Mounting: The terminal is soldered on a print				
			circuit board.				


Standard products list

	Rated	Category	Surge	Cap.	Tole-	Leakage	tanδ		ESR	Max	
	voltage	voltage	voltage		rance	current	120Hz			allowable	
	85°C	105℃	85°C	120Hz		25℃				100kHz	ripple
Part No.						1WV	-55℃	25℃	105℃		current
						5min					≦45°C
											100kHz
	(V)	(V)	(V)	(µF)	(%)	(µA)	(%)	(%)	(%)	$(m\Omega)$	(mArms)
TCSOPL0J476M8R-ZF1	6.3	5	8	47	±20	29.7	15	15	20	150	516
* TCSOPL0J686M8R-ZF1	6.3	5	8	68	±20	129.0	15	15	20	150	516
* TCSOPL0J686M8R-ZD1	6.3	5	8	68	±20	129.0	15	15	20	200	447
TCSOPL1A226M8R	10	8	13	22	±20	22.0	15	15	20	200	447
TCSOPL1C106M8R-ZF1	16	12.8	20	10	±20	48.0	10	10	15	150	516
* TCSOPL1E475M8R-ZM1	25	20	29	4.7	±20	11.8	10	10	15	300	365
TCSOPL1E475M8R-ZT1	25	20	29	4.7	±20	11.8	10	10	15	500	283
* TCSOPL1V225M8R-ZT1	35	25	40	2.2	±20	23.1	10	10	15	500	283


^{*} This specification has possibility of charge, due to underdevelopment product.

Please ask for latest specification to our sales.

Packaging specifications



Reel dimensions




Damp proof package

- ①One reel is packed in aluminum bag.
 - The size of aluminum bag is 240(a) x 250(b)mm.

The size up to 230(c)mm is to zipper.

- ②A desiccant is packed with a reel.
- 3The aluminum bag is heat-sealed.
- (4) The label of the same as the label on the reel is placed on the aluminum bag.



Notes

- 1) The information contained herein is subject to change without notice.
- Before you use our Products, please contact our sales representative and verify the latest specifications.
- 3) Although ROHM is continuously working to improve product reliability and quality, semiconductors can break down and malfunction due to various factors. Therefore, in order to prevent personal injury or fire arising from failure, please take safety measures such as complying with the derating characteristics, implementing redundant and fire prevention designs, and utilizing backups and fail-safe procedures. ROHM shall have no responsibility for any damages arising out of the use of our Poducts beyond the rating specified by ROHM.
- 4) Examples of application circuits, circuit constants and any other information contained herein are provided only to illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.
- 5) The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM or any other parties. ROHM shall have no responsibility whatsoever for any dispute arising out of the use of such technical information.
- 6) The Products are intended for use in general electronic equipment (i.e. AV/OA devices, communication, consumer systems, gaming/entertainment sets) as well as the applications indicated in this document.
- 7) The Products specified in this document are not designed to be radiation tolerant.
- 8) For use of our Products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a ROHM representative : transportation equipment (i.e. cars, ships, trains), primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, servers, solar cells, and power transmission systems.
- Do not use our Products in applications requiring extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters.
- 10) ROHM shall have no responsibility for any damages or injury arising from non-compliance with the recommended usage conditions and specifications contained herein.
- 11) ROHM has used reasonable care to ensure the accuracy of the information contained in this document. However, ROHM does not warrants that such information is error-free, and ROHM shall have no responsibility for any damages arising from any inaccuracy or misprint of such information.
- 12) Please use the Products in accordance with any applicable environmental laws and regulations, such as the RoHS Directive. For more details, including RoHS compatibility, please contact a ROHM sales office. ROHM shall have no responsibility for any damages or losses resulting non-compliance with any applicable laws or regulations.
- 13) When providing our Products and technologies contained in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.
- 14) This document, in part or in whole, may not be reprinted or reproduced without prior consent of ROHM.



Thank you for your accessing to ROHM product informations. More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

http://www.rohm.com/contact/

General Precaution

- 1. Before you use our Products, you are requested to care fully read this document and fully understand its contents. ROHM shall not be in an y way responsible or liable for failure, malfunction or accident arising from the use of a ny ROHM's Products against warning, caution or note contained in this document.
- 2. All information contained in this docume nt is current as of the issuing date and subject to change without any prior notice. Before purchasing or using ROHM's Products, please confirm the latest information with a ROHM sale s representative.
- 3. The information contained in this doc ument is provided on an "as is" basis and ROHM does not warrant that all information contained in this document is accurate an d/or error-free. ROHM shall not be in an y way responsible or liable for any damages, expenses or losses incurred by you or third parties resulting from inaccuracy or errors of or concerning such information.

Notice – WE © 2015 ROHM Co., Ltd. All rights reserved. Rev.001