

	ROHM Semiconductor									
	PDT001-EVK001A				LLC_DC	CDC	2.5	KW		
	R1_1									
#	Description	Designator	Comment	PART Description	Package	Quantity	Pins	Total Pins	Manufacturer 1	Manufacturer Part Number 1
1	CAP NP	C100, C101, C102, C105, C106, C107, C114, C115	10nF	CAP NP.TH.Film.10nF.1KV.±5%.[TH 18x10x10 15P].MPP	[TH_18x10x10_15P	8	2	16	KEMET	R76QI21004040J
2	CAP NP	C103, C104, C116, C117	150pF	CAP NP,TH,Film,150pF,2KV,±10%,[TH_8.5x4_7.5P],Y5P	[TH_8.5x4_7.5P]	4	2	8	Vishay / BC Components	S151K25Y5PP6TK7R
3	CAP NP	C109, C110, C111, C112	4.7uF	CAP NP,SMD,Film,4.7uF,100V,±5%,[TH_13x32x25_27.5P],MPP	[TH_13x32x25_27.	4	2	8	KEMET	R75GR44705030J
4	CAP NP	C113, C123, C124	10uF	CAP NP,SMD,Ceramic,10uF,100V,±20%,[5750],X7S	[5750]	3	2	6	KEMET	C5750X7S2A106M230KB
5	CAP NP	C118	4.7nF	CAP NP,TH,Film,4.7nF,630V,±5%,[TH-13x4x9_10P],-	[TH-13x4x9_10P]	1	2	2	KEMET	R75PF1470AA01J
6	CAP NP	C200, C201, C204, C205, C318	10uF	CAP NP,SMD,Ceramic,10uF,25V,±10%,[1206],X7R	[1206]	5	2	10	YAGEO	CC1206KKX7R8BB106
7	CAP NP	C202, C203, C206, C207, C208, C210, C400, C401,	1uF	CAP NP,SMD,Ceramic,1uF,35V,±10%,[1206],X7R	[1206]	12	2	24	Murata	C1206C105K6RACTU
8	CAP NP	C209, C211, C317	10uF	CAP NP,SMD,Ceramic,10uF,35V,±10%,[1206],X5R	[1206]	3	2	6	Murata	GRT31CC8YA106KE01L
9	CAP NP	C300, C301, C302, C304, C315, C319, C320, C406	100nF	CAP NP,SMD,Ceramic,100nF,50V,±10%.[0805],X7R	[0805]	8	2	16	Murata	GCD21BR71H104KA01L
10	CAP NP	C303	1pF	CAP NP,SMD,Ceramic,1pF,50V,±10%,[0805],X7R	[0805]	1	2	2	YAGEO	CC0805CRNPO9BN1R0
11	CAP POL	C108	470uF	CAP POL,TH,Electrolytic,470uF,100V,±20%,TH_16X33_7P5,3.86A-135°C	TH_16X33_7P5	1	2	2	Nichicon	UBY2A471MHL
12	CAP POL	C119, C120, C121	470µF	CAP POL, TH, Electrolytic, 470µF, 450V, ±20%, TH_35x50_10P, 1.85 A-105°C	TH_35x50_10P	3	2	6	Nichicon	LGU2W471MELC
13	CAP POL	C122	4.7uF	CAP POL,TH,Electrolytic,4.7uF,100V,±20%,TH_5X12.5_5P,3.86A-105°C	TH_5X12.5_5P	1	2	2	Nichicon	UPW2A4R7MDD1TA
14	Connector	J104	CON_HDR_8x2	Connector,,,CON_HDR_8x2,,,[TH],	[ТН]	1	16	16	Samtech	SSW-108-01-G-D
15	Connector	J105, J106, J107, J108	CON_HDR_3x2	Connector,,,CON_HDR_3x2,,,[TH],	[тн]	4	6	24	Samtech	SSW-103-01-G-D
16	Connector	J201	CON_HDR_8x2	Connector,,,CON_HDR_8x2,,,[TH],	[ТН]	1	16	16	Samtech	TSW-108-22-G-D-RA
17	Connector	J205, J206, J207, J208	CON_HDR_3x2	Connector,,,CON_HDR_3x2,,,[TH],	[тн]	4	6	24	Samtech	TSW-103-22-G-D-RA
18	Connector	J400	DIP 5.08x2N	Connector,,,DIP 5.08x2N,,,,		1	2	2	Molex	395316002
19	Connector	J401	CON_HDR_14x2	Connector, TH,, CON_HDR_14x2,,,,		1	28	28	Samtech	SSW-114-01-G-D
20	Connector	J403, J406, J408	CON_HDR_4x2	Connector,,,CON_HDR_4x2,,,,		3	8	24	Samtech	SSW-104-01-G-D
21	Connector	J404	CON_HDR_6x2	Connector,,,CON_HDR_6x2,,,,		1	12	12	Samtech	SSW-106-01-G-D
22	Connector	J407	CON_HDR_5x2	Connector,,,CON_HDR_5x2,,,,		1	10	10	Samtech	SSW-105-01-G-D
23	Diode	D100, D101, D300	RR2LAM6STR	Diode,SMD,Rectifier,RR2LAM6STR,600V,-,[SOD-128],2A,-,150°C	[SOD-128]	3	2	6	ROHM	RR2LAM6STR
24	Diode	D102, D103	APT100S20BG	Diode,SMD,RECT,APT100S20BG,200V,-,[TO-247],120A,-,-	[TO-247]	2	2	4	Microsemi	APT100S20BG
25	Diode	D104, D105, D106, D107, D204, D205	RB560VM-40	Diode,SMD,SIGNAL,RB560VM-40,40V,-,[SOD323],500mA,-,-	[SOD323]	6	2	12	ROHM	RB560VM-40
26	Diode	D200, D202	RFN2LAM6S	Diode,SMD,Fast Recovery,RFN2LAM6S,600V,-,[SOD-128],1.5A,-,150°C	[SOD-128]	2	2	4	ROHM	RFN2LAM6S
27	Diode	LED401, LED402, LED403, LED404, LED405	3mm	LED, TH, LED, 3mm, 2V, -, Radial, -, -,-	Radial	5	2	10	Everlight	204-10SURD/S530-A3
28	Diode	Z100	KDZVTF12B	Diode, SMD, ZENER, KDZVTF12B, 12V,-, [SOD123],-,-,-	[SOD123]	1	2	2	ROHM	KDZVTF12B
29	Diode	Z101, Z102, Z103, Z104, Z200, Z201	UFZVFH18B	Diode,SMD,ZENER,UFZVFH18B,18V,-,[SOD-323],-,-,-	[SOD-323]	6	2	12	ROHM	UFZVFH18B
30	Diode	Z300, Z301, Z303, Z304, Z400	RB160MM-40TR	Diode,SMD,Schottky,RB160MM-40TR,40V,-,[SOD123FL],1A,-,-	[SOD123FL]	5	2	10	ROHM	RB160MM-40TR
31	Diode	Z302	UDZVTE-173.3B	Diode,SMD,ZENER,UDZVTE-173.3B,3.3V,-,[SOD-323],20mA,200mW,-55°C ~ 150°C	[SOD-323]	1	2	2	ROHM	YFZVFH3.3B
32	FUSE	F100	60A	FUSE,TH,Slow Blow,60A,58V,,[TH_29.21 x 8.85x21.59_30P],-	[TH_29.21 x 8.85x21.59_30P]	1	2	2	Little fuse	0999060.ZXN
33	GATE DRIVER	U200, U201, U202, U203	BM61M41RFV	GATE DRIVER,SMD,IC,BM61M41RFV,-,,SSOP-B10W,4A	SSOP-B10W	4	10	40	ROHM	BM61M41RFV
34	GATE DRIVER	U204, U205	BD2310G	GATE DRIVER,SMD,IC,BD2310G,-,,SOIC-8,4A,,	SOIC-8	2	5	10	ROHM	BD2310G
35	Inductor	L100	3.3uH	Inductor,TH,,3.3uH,-,20%,TH_36x21.5x35,75A40°C ~+125°C	TH_36x21.5x35	1	2	2	Wurth Electronics	7.44376E+12
36	Inductor	L101	22.5uH	Inductor,TH,PQ2620, Horizontal,22.5uH,-,,PQ3230_12pin,,,,	PQ3230_12pin	1	6	6	Custom	RSM0010



37	Isolator	U300	Si8621BC-B-IS	Isolator,SMD,IC,Si8621BC-B-IS,,,SOIC-8,,,-40°C ~125°C	SOIC-8	1	8	8	Silicon Labs	Si8621BC-B-IS
38	LDO	U306	BA17805FP-E2	LDO,SMD,IC,BA17805FP-E2,5V,,[DPAK],1A,1W,-40°C ~ 85°C	[DPAK]	1	3	3	ROHM	BA17805FP-E2
39	MosFET	Q100, Q101, Q102, Q103	R6042JNZ	MosFET,TH,NCH,R6042JNZ,600V,,TO-247G,42A,495W,-55°C ~ 150°C (TJ)	TO-247G	4	3	12	ROHM	R6042JNZ4C13
40	MosFET	Q107, Q108	FDB1D7N10CL7	MosFET,SMD,N CH,FDB1D7N10CL7,100V,,D2PAK7,268A,250W,-40°C ~ 175°C (TJ)	D2PAK7	2	7	14	ONSemi	FDB1D7N10CL7
41	MosFET	Q300, Q400	RQ5E065AJTCL	MosFET,SMD,NCH,RQ5E065AJTCL,30V,,SOT346,6.5A,1W,-55°C ~ 150°C (TJ)	SOT346	2	3	6	ROHM	RQ5E065AJTCL
42	OPAMP	U302	LM2903BIDR	Comparator,SMD,,LM2903BIDR,36V,,SO-8,	SO-8	1	8	8	TI	LM2903BIDR
43	OPAMP	U304	TLV271SN2T1G	OPAMP,SMD,,TLV271SN2T1G,16V,,[SSOP-5],	[SSOP-5]	1	5	5	Onsemi	TLV271SN2T1G
44	Optoisolator	ISO300	PC817	Optoisolator,SMD,IC,PC817,80V,,4-SMD, Gull Wing,50mA,,-30°C ~ 100°C	4-SMD, Gull Wing	1	4	4	Sharp	PC81710NIP1B
45	Resistor	R100	10K	Resistor,[TH],,10K,-,1%,,		1	2	2	Ohmite	TWM7J10KE
46	Resistor	R101, R102, R105, R106	50R	Resistor,SMD,,50R,-,5%,[TH],3W	[ТН]	4	2	8	Vishay	AC03000005009JAC00
47	Resistor	R103, R104, R120, R121, R120, R129, R134, R224, R225, R226, R227, R303, R304, R327, R328, R406, P407, P408, P414, P412	10K	Resistor,SMD,,10K,-,1%,[0805],1/8W	[0805]	20	2	40	ROHM	SFR10EZPF1002
48	Resistor	R107, R133	200mR x 3	Resistor,SMD,,200mR x 3,-,1%,[2512],-	[2512]	2	2	4	ROHM	MCR100JZHFLR200
49	Resistor	R108, R109, R112, R113	33mR or 100mR x 3	Resistor,SMD,,33mR or 100mR x 3,-,1%,[2512],7W	[2512]	4	2	8	ROHM	GMR100HTBFMR033
50	Resistor	R110, R204, R205, R212, R213, R301, R302, R305, R311, R326, R402, R403, R404, R405, R409, R410	1K	Resistor,SMD,,1K,-,1%,[0805],1/8W	[0805]	16	2	32	ROHM	SFR10EZPF1001
51	Resistor	R111, R130, R131, R132, R200, R201, R208, R209, R216, R217, R228, R324, R325, R413	0R	Resistor,SMD,,0R,-,1%,[0805],1/8W	[0805]	14	2	28	ROHM	SFR10EZPJ000
52	Resistor	R114, R115, R118, R119, R122, R123, R126, R127	10R	Resistor,SMD,,10R,-,1%,[0805],1/8W	[0805]	8	2	16	ROHM	ESR10EZPF10R0
53	Resistor	R136, R137, R138	220K	Resistor,SMD,,220K,200V,1%,[1206],2/5W	[1206]	3	2	6	ROHM Semiconductor	ESR18EZPF2203
54	Resistor	R206, R207, R214, R215	4.7К	Resistor,SMD,,4.7K,-,1%,[0805],1/8W	[0805]	4	2	8	ROHM	SFR10EZPF4702
55	Resistor	R218, R219	47R	Resistor,SMD,,47R,-,1%,[0805],1/8W	[0805]	2	2	4	ROHM	MCR10EZPF47R0
56	Resistor	R220, R221	100R	Resistor,SMD,,100R,-,1%,[0805],1/8W	[0805]	2	2	4	ROHM	SFR10EZPF1000
57	Resistor	R222, R223	12R	Resistor,SMD,,12R,-,1%,[0805],1/8W	[0805]	2	2	4	ROHM	MCR10EZPF12R0
58	Resistor	R300	383K	Resistor,SMD,,383K,-,1%,[0805],1/8W	[0805]	1	2	2	YAGEO	RC0805FR-07383KL
59	Resistor	R307, R308	100K	Resistor,SMD,,100K,-,1%,[0805],1/8W	[0805]	2	2	4	ROHM	SFR10EZPF1003
60	Resistor	R310, R330	20K	Resistor,SMD,,20K,-,1%,[0805],1/8W	[0805]	2	2	4	ROHM	SFR10EZPF2002
61	Resistor	R400, R401	10R	Resistor,SMD,,10R,-,1%,[TH],2W	[ТН]	2	2	4	Stackpole Electronics Inc	RSMF2JT10R0
62	Transformer	T100	90uH	Transformer, TH, ETD54, Vertical, 90uH,-,, ETD54_10pin,	ETD54_10pin	1	15	15	Custom	RSM0011
63	Transistor	Q401, Q402, Q403, Q404, Q405	2SD1484KT146	Transistor,SMD,NPN,2SD1484KT146,50V,-,SOT346,500mA200mW-55°C ~ 150°C	SOT346	5	3	15	Rohm	2SD1484KT146

Important Notes on the Use of Reference Designs

- 1) The contents of this document are subject to change without notice for the purpose of improvement.
- 2) ROHM provides reference designs (including, but not limited to, circuit diagrams, layout data, parts lists, reference boards and their evaluation results, etc.) and all materials related to evaluation boards (hereinafter collectively referred to as "Reference Designs, etc.") to customers for the purpose of referencing them in the development of devices, equipment, software, etc. incorporating ROHM products (hereinafter collectively referred to as "Customer Products"). The design, verification, etc. required for the development of the Customer's Product shall be done at the customer's responsibility and expense. In no event shall the customer use the Reference Designs, etc. for any purpose other than the purpose mentioned above.
- 3) Reference Designs, etc. are provided on an "as is" basis. ROHM disclaims all warranties, express or implied, including, but not limited to, warranties of usefulness, functionality, accuracy, merchantability, and fitness for a particular purpose. In no event shall ROHM be liable for any damages (including, but not limited to, lost profits or other incidental, consequential, or punitive damages) arising out of, related to or in connection with the use of or application of the Reference Designs, etc. whether in contract or tort. For the avoidance of doubt, ROHM does not warrant that the Reference Designs, etc. will work with the Customer's Product.
- 4) When using Reference Designs, etc. be sure to request and verify the latest specifications (including the specifications of the products that compose the Reference Design, etc.) separately.
- 5) The customer shall be responsible for implementing safety measures such as derating, redundant design, fire prevention, backup, and fail-safe measures, etc., to prevent personal injury, fire damage, etc., caused by the Customer's Product developed with Reference Designs, etc. ROHM assumes no liability whatsoever for any use in excess of the ratings or in case of failure to observe the instructions for use.
- 6) The application circuit examples, constants, and other information provided in Reference Designs, etc. are intended to illustrate standard operation and usage. Therefore, when designing for mass production, please take into account various external conditions.
- 7) Reference Designs, etc. are intended to show typical operations and examples of application circuits, etc., and do not constitute a license, express or implied, to implement or use any intellectual property rights or any other rights of ROHM or any other company. ROHM shall not be liable for any disputes arising from, related to or in connection with the use of the Reference Designs, etc.
- 8) Please make sure to contact ROHM and obtain ROHM's consent before using the Reference Designs, etc. for the following Customer's Product that requires particularly high reliability. Transportation equipment (in-vehicle, ship, railroad, etc.), trunk line communication equipment, traffic signal equipment, disaster and security equipment, safety equipment, medical equipment, servers, solar cells, power transmission systems, etc.
- 9) Do not use Reference Designs, etc. for the following Customer's Product that requires extremely high reliability. Aerospace equipment, nuclear power control equipment, submarine relay equipment, etc.
- 10) Do not use Reference Designs, etc. for military use, such as development of weapons of mass destruction, or for any other military purpose.
- 11) ROHM does not assume any liability for any accidents or damages caused by non- compliance with the descriptions in this document.
- 12) The information contained in this document has been carefully prepared to ensure accuracy. However, ROHM shall not be liable for any loss or damage incurred by customers due to errors or misprints in this document.
- 13) Do not reproduce or duplicate any part of this document in any form or by any means without ROHM's permission.



Thank you for your accessing to ROHM product informations.

More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

http://www.rohm.com/contact/