REFPDT007-EVK-001B Parts List



Control PCB

No.	Device	Symbol	Parts Number	Manufacture	Values	Package Size
INO.	Device	C28,C40,C41,C42,C46,C47,	Faits Number	Manufacture	values	rackage Size
1	Condenser Ceramic	C50,C73	GRM188B11H102KA01	MURATA	1000p 50V ±10%	S 1608
-	Candoneau Coramia		GRM188R71E105KA12	MURATA	1µ 25V ±10%	S 1608
	Condenser Ceramic	C29,C36,C37,C38	GRM188R/1E105KA12	MURATA	Iμ 25V ±10%	5 1608
	la	C30,C31,C32,C33,C34,C35,				
3	Condenser Ceramic	C39,C44,C48,C52,C54,C55,	GRM188B31H104KA92	MURATA	0.1µ 50V ±10%	S 1608
		C56,C57				
	Ceramic Condenser	C43,C51	C-S1608	MURATA	TBD	S 1608
	Condenser Ceramic	C45,C49	GRM1851X1H222JA44	MURATA	2200p 50V ±5%	S 1608
6	Condenser Ceramic	C53,C58,C59	GRM185B31E105MA12	MURATA	1μ 25V ±20%	S 1608
7	Chemical Condenser	C60,C61,C62,C63,C64,C69	ELXZ350ELL101MF15D	NIPPON CHEMI-CON	100µ 35V ±20%	D D6.3x15
8	Film Condenser	C65	ECQE6103KF	Panasonic	0.01µ 630V ±10%	D 12x4.5x7.5
9	Chemical Condenser	C66	ELXZ100ELL681MF15D	NIPPON CHEMI-CON	680µ 10V ±20%	D D8x11.5
10	Ceramics Condenser	C67,C68,C72	GRM188R71E104KA01	MURATA	0.1µ 50V ±10%	S 1608
11	Film Condenser	C70	ECQE6104KF	Panasonic	0.1µ 630V ±10%	D 18.5x6.3x14
12	Ceramics Capacitor	C71	DE1E3KX102MA4BN01	MURATA	1000p 250VAC ±20%	D 6x4x9
	Ceramics Condenser	C74	GRM188B11H103KA01	MURATA	10000p 50V ±10%	S 1608
	Connector	CN2	S3B-EH	JST	3A, 3pin	DIP
	Connector Pinheader Side	CN3	PH-1x10RG2	Useconn	10P Side	D 25.4x10.61x2.54
	Connector	CN4	B5B-PH-K-S	JST	5pin	DIP
		CN5	S4B-EH	JST	4pin	DIP
	Test Point	CP9,CP10,CP11,CP12	HOT-2608B	HIROSUGI	Black	D 2.5x1.75
	Diode		SBR1U150A-13	DIODES	150V, 1A	S 4.3x2.6x2.2
		D13,D14,D15,D16,D17				S 4.3X2.6X2.2
	Diode	D18	EG01C	SANKEN	1000V, 0.5A	0.45.05.45
	3Terminal Regulator	IC2	NJM78L05UA	NJRC	12V 500mA	S 4.5x2.5x1.5
	Pinheader 1x4P	J8	PH-1x04SG	Useconn	Pin header 1x4P	D 10.16x2.54x8.5
	Connector]9	PH-2x08SG	Useconn Electronics	Pin header 2x8P	DIP
	Connector Socket	J10,J11,J12	FHU-2×4SG	Useconn Electronics	3A, 8pin,female	D 10.16x5.08x8.5
25		J13	PH-2x04SG	Useconn Electronics	2x4P	D 10.16x5.08x8.5
26	Connector Header	J14	PH-2x09SG	Useconn Electronics	18P(2x9)	D 22.86x5.08x8.5
27	CPU Module	MJ4	PC089-01-00-50P	PAT	36pin	D 28x40x28
28	Photocoupler	PC1	PS2501L-1	NEC	1ch, 80V,50mA	S 6.5x4.6x3.6
29	Transistor	Q7,Q8,Q9,Q10,Q11,Q12	2SC3325	TOSHIBA	50V,0.5A	SMD
30	Resistor	R25,R42,R43,R45,R47,R49, R50,R51,R52,R54,R56,R57, R58,R59,R60,R65,R66,R67, R68,R69,R70,R71,R72,R73, R74,R75,R76,R77,R78,R79, R80	RK73B1JTTD103J	коа	10K 1/10W ±5%	S 1608
31	Resistor	R26,R44,R48,R53,R61,R62, R63	RK73B1JTTD472J	коа	4.7K 1/10W ±5%	S 1608
32	Resistor	R27	RK73B1JTTD102J	KOA	1K 1/10W ±5%	S 1608
33	Resistor	R28,R30,R31,R34,R35,R38, R40,R41,R46,R55	RK73B1JTTD101J	коа	100Ω 1/10W ±5%	S 1608
34	Resistor	R29,R32,R33,R36,R37,R39	RK73B1JTTD271J	KOA	270Ω 1/10W ±5%	S 1608
	Resistor	R64	RK73B1JTTD104J	KOA	100K 1/10W ±5%	S 1608
	Resistor	R81,R92	MOSX1C1R0J	KOA	1Ω, 1W ±1%	φ3x9L
	Resistor	R82	MCR03EZPJ332	ROHM	3.3kΩ, 1/10W ±5%	SMD
	Resistor	R83	MCR03EZPJ103	ROHM	10kΩ, 1/10W ±5%	SMD
	Resistor	R84	MOSX1C334J	KOA	330kΩ, 1W ±5%	DIP
	Resistor	R85,R86,R89,R90	MCR10EZPJ105	ROHM	1MΩ, 1/10W ±5%	SMD
_	Resistor	R87	MCR03EZPJ103	ROHM	1kΩ, 1/10W ±5%	SMD
	Resistor	R88	MCR03EZPJ102	ROHM	1.5kΩ, 1/10W ±5%	SMD
	Resistor	R91	MCR03EZPJ152	ROHM		SMD
	Resistor	R91 R93	MCR03EZPJ101 MCR03ERTJ302	ROHM	100Ω, 1/10W ±5%	SMD
		R93			3kΩ, 1/10W ±5%	
	Resistor		MCR03EZPJ334	ROHM	330kΩ, 1/10W ±5%	SMD
	Transformer	T2	TR10P	PAT	C CHOC I	DIP
47		U5,U6	TC4069UBF	TOSHIBA	6 CMOS Inverter	SMD
48		U7,U8	NJM2732M	JRC	Dual RtoR OP-amp	SMD
	EEPROM	U9	24LC64SN	MICROCHIP	EEPROM	S 4.9x3.9x1.75
50		U10	TA48M05F	TOHSIBA	5V, 0.5A LDO	SMD
51	IC	U11	NJM431U	JRC		SMD
52	IC	U12	STR-A6079M	SANKEN	Flybuck controller 800V, 1.2A	DIP
53	Cermet trimmer	VR1,VR2,VR3	CT-6E-P5KΩ	COPAL	5KΩ 1/2W ±1%	D 7x7x.8
54	Zener Diode	ZD1	UDZS5.1B	ROHM	5.1V, 5mA	SMD
\vdash	·	E.		I		

© 2022 ROHM Co., Ltd. 53 Cermet trimm. 54 Zener Diode

Important Notes on the Use of Reference Designs

- 1) The contents of this document are subject to change without notice for the purpose of improvement.
- 2) ROHM provides reference designs (including, but not limited to, circuit diagrams, layout data, parts lists, reference boards and their evaluation results, etc.) and all materials related to evaluation boards (hereinafter collectively referred to as "Reference Designs, etc.") to customers for the purpose of referencing them in the development of devices, equipment, software, etc. incorporating ROHM products (hereinafter collectively referred to as "Customer Products"). The design, verification, etc. required for the development of the Customer's Product shall be done at the customer's responsibility and expense. In no event shall the customer use the Reference Designs, etc. for any purpose other than the purpose mentioned above.
- 3) Reference Designs, etc. are provided on an "as is" basis. ROHM disclaims all warranties, express or implied, including, but not limited to, warranties of usefulness, functionality, accuracy, merchantability, and fitness for a particular purpose. In no event shall ROHM be liable for any damages (including, but not limited to, lost profits or other incidental, consequential, or punitive damages) arising out of, related to or in connection with the use of or application of the Reference Designs, etc. whether in contract or tort. For the avoidance of doubt, ROHM does not warrant that the Reference Designs, etc. will work with the Customer's Product.
- 4) When using Reference Designs, etc. be sure to request and verify the latest specifications (including the specifications of the products that compose the Reference Design, etc.) separately.
- 5) The customer shall be responsible for implementing safety measures such as derating, redundant design, fire prevention, backup, and fail-safe measures, etc., to prevent personal injury, fire damage, etc., caused by the Customer's Product developed with Reference Designs, etc. ROHM assumes no liability whatsoever for any use in excess of the ratings or in case of failure to observe the instructions for use.
- 6) The application circuit examples, constants, and other information provided in Reference Designs, etc. are intended to illustrate standard operation and usage. Therefore, when designing for mass production, please take into account various external conditions.
- 7) Reference Designs, etc. are intended to show typical operations and examples of application circuits, etc., and do not constitute a license, express or implied, to implement or use any intellectual property rights or any other rights of ROHM or any other company. ROHM shall not be liable for any disputes arising from, related to or in connection with the use of the Reference Designs, etc.
- 8) Please make sure to contact ROHM and obtain ROHM's consent before using the Reference Designs, etc. for the following Customer's Product that requires particularly high reliability. Transportation equipment (in-vehicle, ship, railroad, etc.), trunk line communication equipment, traffic signal equipment, disaster and security equipment, safety equipment, medical equipment, servers, solar cells, power transmission systems, etc.
- 9) Do not use Reference Designs, etc. for the following Customer's Product that requires extremely high reliability. Aerospace equipment, nuclear power control equipment, submarine relay equipment, etc.
- 10) Do not use Reference Designs, etc. for military use, such as development of weapons of mass destruction, or for any other military purpose.
- 11) ROHM does not assume any liability for any accidents or damages caused by non- compliance with the descriptions in this document.
- 12) The information contained in this document has been carefully prepared to ensure accuracy. However, ROHM shall not be liable for any loss or damage incurred by customers due to errors or misprints in this document.
- 13) Do not reproduce or duplicate any part of this document in any form or by any means without ROHM's permission.



Thank you for your accessing to ROHM product informations. More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

http://www.rohm.com/contact/

R2109A www.rohm.com