

Product	Laserdiode
Package	RLD63PZCA

1.試験結果 (Test Result)

試験項目 (Test Item)	n (pcs)	Iop(mA)		Im(mA)		Ith(mA)		λ (nm)		備考
		r (pcs)	P (%)	r (pcs)	P (%)	r (pcs)	P (%)	r (pcs)	P (%)	
温度サイクル (Thermal Cycle)	20	0	0	0	0	0	0	0	0	-
高温通電試験 (High Temp. Endurance)	10	0	0	-	-	-	-	-	-	-
高温保存 (High Temp. Storage/Resistance Solder Heat)	20	0	0	0	0	0	0	0	0	-
低温保存 (Low Temp. Storage)	20	0	0	0	0	0	0	0	0	-
高温高湿保存 (High Temp. High Hum. Storage)	20	0	0	0	0	0	0	0	0	-

n; サンプル数 (Sample Qty)

r; 不良数 (Rejection Qty) P; 不良率 (Percent Rejection)

2.試験条件

試験項目 (Test Item)	準拠規格 (Standard)	試験条件 (Test Condition)
温度サイクル (Thermal Cycle)	JIS C 7021 A-4	-40°C~100°C、 200cyc
高温通電試験 (High Temp. Endurance)	社内規格	50°C、5mW、500hr
高温保存 (High Temp. Storage/Resistance Solder Heat)	JIS C 7021 B-10	100°C、500hr
低温保存 (Low Temp. Storage)	EIAJ ED-4701B-112	-40°C、500hr
高温高湿保存 (High Temp. High Hum. Storage)	JIS C 7021 B-11	65°C、95%、500hr

3.測定項目及び故障判定基準 (Failure Criteria)

測定項目 (Item)	測定条件 (Condition)	故障判定基準 (Criteria)
Ith(mA)	Po=5mW Tc=25°C	初期値±5%以下 (Changing rate of±5%)
Iop(mA)		初期値±5%以下 (Changing rate of±5%)
Im(mA)		初期値±10%以下 (Changing rate of±10%)
λ (nm)		初期値±3nm以下 (Changing of±3nm)

4.高温通電試験測定項目及び故障判定基準 (Failure Criteria of High Temp. Endurance)

測定項目 (Item)	測定条件 (Condition)	故障判定基準 (Criteria)
Iop(mA)	Po=5mW Tc=50°C	初期値+20%以下 (Changing rate of+20%) MTTF≥5000hr

5.判定結果 (Judgement)

各試験項目とも不具合の発生は認められておりません。
(No failure is observed from each test item.)

Notes

- 1) The information contained herein is subject to change without notice.
- 2) Before you use our Products, please contact our sales representative and verify the latest specifications.
- 3) Although ROHM is continuously working to improve product reliability and quality, semiconductors can break down and malfunction due to various factors.
Therefore, in order to prevent personal injury or fire arising from failure, please take safety measures such as complying with the derating characteristics, implementing redundant and fire prevention designs, and utilizing backups and fail-safe procedures. ROHM shall have no responsibility for any damages arising out of the use of our Products beyond the rating specified by ROHM.
- 4) Examples of application circuits, circuit constants and any other information contained herein are provided only to illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.
- 5) The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM or any other parties. ROHM shall have no responsibility whatsoever for any dispute arising out of the use of such technical information.
- 6) The Products are intended for use in general electronic equipment (i.e. AV/OA devices, communication, consumer systems, gaming/entertainment sets) as well as the applications indicated in this document.
- 7) The Products specified in this document are not designed to be radiation tolerant.
- 8) For use of our Products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a ROHM representative : transportation equipment (i.e. cars, ships, trains), primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, servers, solar cells, and power transmission systems.
- 9) Do not use our Products in applications requiring extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters.
- 10) ROHM shall have no responsibility for any damages or injury arising from non-compliance with the recommended usage conditions and specifications contained herein.
- 11) ROHM has used reasonable care to ensure the accuracy of the information contained in this document. However, ROHM does not warrants that such information is error-free, and ROHM shall have no responsibility for any damages arising from any inaccuracy or misprint of such information.
- 12) Please use the Products in accordance with any applicable environmental laws and regulations, such as the RoHS Directive. For more details, including RoHS compatibility, please contact a ROHM sales office. ROHM shall have no responsibility for any damages or losses resulting non-compliance with any applicable laws or regulations.
- 13) When providing our Products and technologies contained in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.
- 14) This document, in part or in whole, may not be reprinted or reproduced without prior consent of ROHM.



Thank you for your accessing to ROHM product informations.
More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

<http://www.rohm.com/contact/>

General Precaution

1. Before you use our Products, you are requested to carefully read this document and fully understand its contents. ROHM shall not be in any way responsible or liable for failure, malfunction or accident arising from the use of any ROHM's Products against warning, caution or note contained in this document.
2. All information contained in this document is current as of the issuing date and subject to change without any prior notice. Before purchasing or using ROHM's Products, please confirm the latest information with a ROHM sales representative.
3. The information contained in this document is provided on an "as is" basis and ROHM does not warrant that all information contained in this document is accurate and/or error-free. ROHM shall not be in any way responsible or liable for any damages, expenses or losses incurred by you or third parties resulting from inaccuracy or errors of or concerning such information.