

## Accelerometer

# KX134ACR-LBZ Power-on Procedure

This technical note is intended to provide information about the proper power-on procedure of KX134ACR-LBZ accelerometers. Regarding detail specification, please refer to the datasheet. The values in this document are reference data and not guaranteed.

## Table of Contents

1.	Power On Procedure.....	3
2.	Software Reset .....	3
	<b>In case of the I2C Interface</b> .....	3
	<b>In case of the 4-wire SPI Interface</b> .....	4
	<b>In case of the 3-wire SPI Interface</b> .....	4
	<b>Software Reset Sequence following Power Up</b> .....	5
	Revision History.....	6

## 1. Power On Procedure

Proper functioning of Power-On Reset is dependent on the specific sequence of VDD and IO\_VDD. For detail information, please consult the datasheet.

## 2. Software Reset

Issuing the Software Reset command after the device power-up is recommended. This is effective against dynamic or non-linear behavior of a power supply or unexpected noise above normal on the power rail during a power-up.

### In case of the I2C Interface

Following the power-up, access following registers using Target Address up to the connection of ADDR pin. If command was acknowledged (ACK received), proceed to the next step. If ACK was not received, the device should be done the Power Cycle.

- (1) Write 00h to the Address 7Fh. If NACK received, the device should be done the Power Cycle.

Register Name	ADDR		Value	
	Hex	Binary	Hex	Binary
-	7Fh	0111 1111b	00h	0000 0000b

- (2) Write 80h to Control Register 2 (CNTL2) to initiate the Software Reset, which performs the OTP re-load routine. If the NACK received, the device should be done the Power Cycle.

Register Name	ADDR		Value	
	Hex	Binary	Hex	Binary
CNTL2	19h	0001 1001b	BFh	1011 1111b

- (3) Wait 2 msec for completion of the Software Reset.

- (4) Read content of WHO AM I register (WHO\_AM\_I). If read value is same as below, proceed to the next step. If not, the Software Reset has failed and the device should be done the Power Cycle.

Register Name	ADDR		Value	
	Hex	Binary	Hex	Binary
WHO_AM_I	0Fh	0000 1111b	CCh	1100 1100b

**In case of the 4-wire SPI Interface**

Following the power-up, access following registers.

- (1) Write 00h to the Address 7Fh.

Register Name	ADDR		Value	
	Hex	Binary	Hex	Binary
-	7Fh	0111 1111b	00h	0000 0000b

- (2) Write 80h to Control Register 2 (CNTL2) to initiate the Software Reset, which performs the OTP re-load routine.

Register Name	ADDR		Value	
	Hex	Binary	Hex	Binary
CNTL2	19h	0001 1001b	BFh	1011 1111b

- (3) Wait 2 msec for completion of the Software Reset.

- (4) Read content of WHO AM I register (WHO\_AM\_I). If read value is same as below, proceed to the next step. If not, the Software Reset has failed and the device should be done the Power Cycle.

Register Name	ADDR		Value	
	Hex	Binary	Hex	Binary
WHO_AM_I	0Fh	0000 1111b	CCh	1100 1100b

**In case of the 3-wire SPI Interface**

Following the power-up, access following registers.

- (1) Write 00h to the Address 7Fh.

Register Name	ADDR		Value	
	Hex	Binary	Hex	Binary
-	7Fh	0111 1111b	00h	0000 0000b

- (2) Write 80h to Control Register 2 (CNTL2) to initiate the Software Reset, which performs the OTP re-load routine.

Register Name	ADDR		Value	
	Hex	Binary	Hex	Binary
CNTL2	19h	0001 1001b	BFh	1011 1111b

- (3) Wait 2 msec for completion of the Software Reset.

- (4) Write 11h to INC1 register to set the device into 3-wire SPI mode.


Register Name	ADDR		Value	
	Hex	Binary	Hex	Binary
INC1	1Ch	0001 1100b	11h	0001 0001b

- (5) Read content of WHO AM I register (WHO\_AM\_I). If read value is same as below, proceed to the next step. If not, the Software Reset has failed and the device should be done the Power Cycle.

Register Name	ADDR		Value	
	Hex	Binary	Hex	Binary
WHO_AM_I	0Fh	0000 1111b	CCh	1100 1100b

**Software Reset Sequence following Power Up**

Following figure shows an example of executing the Software Reset sequence following a power-up. The 2 msec wait time is required for completion of the Software Reset before proceeding.



**Revision History**

Date	Revision	Changes
19.Sep.2023	001	New Release

### Notice

- 1) The information contained in this document is intended to introduce ROHM Group (hereafter referred to as ROHM) products. When using ROHM products, please verify the latest specifications or datasheets before use.
- 2) ROHM products are designed and manufactured for use in general electronic equipment and applications (such as Audio Visual equipment, Office Automation equipment, telecommunication equipment, home appliances, amusement devices, etc.) or specified in the datasheets. Therefore, please contact the ROHM sales representative before using ROHM products in equipment or devices requiring extremely high reliability and whose failure or malfunction may cause danger or injury to human life or body or other serious damage (such as medical equipment, transportation, traffic, aircraft, spacecraft, nuclear power controllers, fuel control, automotive equipment including car accessories, etc. hereafter referred to as Specific Applications). Unless otherwise agreed in writing by ROHM in advance, ROHM shall not be in any way responsible or liable for any damages, expenses, or losses incurred by you or third parties arising from the use of ROHM Products for Specific Applications.
- 3) Electronic components, including semiconductors, can fail or malfunction at a certain rate. Please be sure to implement, at your own responsibilities, adequate safety measures including but not limited to fail-safe design against physical injury, and damage to any property, which a failure or malfunction of products may cause.
- 4) The information contained in this document, including application circuit examples and their constants, is intended to explain the standard operation and usage of ROHM products, and is not intended to guarantee, either explicitly or implicitly, the operation of the product in the actual equipment it will be used. As a result, you are solely responsible for it, and you must exercise your own independent verification and judgment in the use of such information contained in this document. ROHM shall not be in any way responsible or liable for any damages, expenses, or losses incurred by you or third parties arising from the use of such information.
- 5) When exporting ROHM products or technologies described in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, such as the Foreign Exchange and Foreign Trade Act and the US Export Administration Regulations, and follow the necessary procedures in accordance with these provisions.
- 6) The technical information and data described in this document, including typical application circuits, are examples only and are not intended to guarantee to be free from infringement of third parties intellectual property or other rights. ROHM does not grant any license, express or implied, to implement, use, or exploit any intellectual property or other rights owned or controlled by ROHM or any third parties with respect to the information contained herein.
- 7) No part of this document may be reprinted or reproduced in any form by any means without the prior written consent of ROHM.
- 8) All information contained in this document is current as of the date of publication and subject to change without notice. Before purchasing or using ROHM products, please confirm the latest information with the ROHM sales representative.
- 9) ROHM does not warrant that the information contained herein is error-free. ROHM shall not be in any way responsible or liable for any damages, expenses, or losses incurred by you or third parties resulting from errors contained in this document.



Thank you for your accessing to ROHM product informations.  
More detail product informations and catalogs are available, please contact us.

## ROHM Customer Support System

<https://www.rohm.com/contactus>