

Product	Laser diode
Package	RLD85PZJ4
Weight(mg)	317.6671

The RoHS directive, REACH regulation, and other laws and regulations related to the management of environmentally hazardous substances come into effect. When developing products, the global environmental load must be considered. ROHM pursues green procurement and endeavors to increase the detection accuracy of chemicals contained in parts and procured materials while at the same time placing great importance on the internal chemical management system that was built to ensure that no prohibited substances are procured, used, or shipped in order to provide a steady supply of worry-free products.

○ This item is in compliance with RoHS.

○ Pb free

No.	Part Name	Substance Name	CAS No.	Weight [mg]	Content	
1	LD Die	GaAs	7440-38-2	0.1225	98.7650%	
		Titanium (Ti)	7440-32-6	0.0004	0.3066%	
		Aluminium(Al)	7429-90-5	0.0005	0.4179%	
		Gold(Au)	7440-57-5	0.0006	0.5106%	
2	PD Die	Silicon(Si)	7440-21-3	0.2572	99.3779%	
		Aluminium(Al)	7429-90-5	0.0009	0.3284%	
		Gold(Au)	7440-57-5	0.0008	0.2929%	
3	Die attach	Silver(Ag)	7440-22-4	0.0326	72.5000%	
		Bisphenol A Diglycidyl Ether Resin(C18H21ClO3)	2506-83-86	0.0018	4.0000%	
		N,N-Diglycidyl-4-Glycidioxy Aniline(C15H19N04)	5026-74-4	0.0027	6.0000%	
		Epoxy Resin	—	0.0046	10.2500%	
		Dicyandiamide (C2H4N4)	461-58-5	0.0003	0.7500%	
		Diethyleneglycol monoethyl ether acetate	112-15-2	0.0029	6.5000%	
4	Submount Die	Aluminum nitride(AlN)	24304-00-5	0.5300	95.4577%	
		Titanium (Ti)	7440-32-6	0.0006	0.1117%	
		Platinum(Pt)	7440-06-4	0.0072	4.6386%	
		Gold(Au)	7440-57-5	0.0161	2.8998%	
		Tin(Sn)	7440-31-5	0.0013	0.2341%	
5	Die attach	Indium(In)	7440-74-6	0.1300	100.0000%	
6	Stem	Base material	Iron(Fe)	7439-89-6	226.1900	99.3805%
			Carbon (C)	7440-44-0	0.2700	0.1186%
			Mangan (Mn)	7439-96-5	1.1400	0.5009%
		Lead pin	Iron(Fe)	7439-89-6	14.7500	51.0204%
			Nickel(Ni)	7440-02-0	9.2500	31.9958%
			Cobalt(Co)	7440-48-4	4.9100	16.9837%
		Glass	Silicon oxide(SiO2)	7631-86-9	1.9500	65.0000%
			Aluminium oxide(Al2O3)	1344-28-1	0.2100	7.0000%
			Sodium oxide(Na2O)	1313-59-3	0.2100	7.0000%
			Potassium oxide(K2O)	12136-45-7	0.2100	7.0000%
			Lithium oxide(Li2O)	12057-24-8	0.0300	1.0000%
			Barium oxide(BaO)	1304-28-5	0.2700	9.0000%
		Plating	Zinc oxide(ZnO)	1314-13-2	0.1200	4.0000%
			Nickel(Ni)	7440-02-0	6.1600	97.0079%
		Gold(Au)	7440-57-5	0.1900	2.9921%	

No.	Part Name	Substance Name	CAS No.	Weight [mg]	Content	
7	Cap	Base material	Iron(Fe)	7439-89-6	20.4000	50.0000%
			Nickel(Ni)	7440-02-0	20.4000	50.0000%
		Window glass	Silicon Dioxide(SiO ₂)	7631-86-9	2.9400	64.9007%
			Boron trioxide(B ₂ O ₃)	1303-86-2	0.2500	5.5188%
			Zinc oxide(ZnO)	1314-13-2	0.2500	5.5188%
			Titanium dioxide(TiO ₂)	13463-67-7	0.2500	5.5188%
			Aluminium oxide(Al ₂ O ₃)	1344-28-1	0.2500	5.5188%
			Sodium oxide(Na ₂ O)	1313-59-3	0.2500	5.5188%
			Potassium oxide(K ₂ O)	12136-45-7	0.2500	5.5188%
			Calcium oxide(CaO)	1305-78-8	0.0450	0.9934%
	Sulfur(S)	7704-34-9	0.0450	0.9934%		
	Anti Reflection coating	Other	—	0.0140	100.0000%	
	Low-melting glass	Tellurium dioxide(TeO ₂)	7446-07-3	1.3200	42.9967%	
		Barium oxide(BaO)	1304-28-5	0.3200	10.4235%	
		Boron trioxide(B ₂ O ₃)	1303-86-2	0.2200	7.1661%	
		Zinc oxide(ZnO)	1314-13-2	0.1400	4.5603%	
		Zirconium Silicate(ZrSiO ₄)	10101-52-7	1.0700	34.8534%	
Plating	Nickel(Ni)	7440-02-0	2.1400	99.5349%		
	Other	—	0.0100	0.4651%		
8	Bonding wire	Gold(Au)	7440-57-5	0.1300	99.9898%	
		Beryllium(Be)	7440-41-7	0.0000	0.0009%	
		Other	—	0.0000	0.0092%	

Disclaimer

- | |
|---|
| <ul style="list-style-type: none"> •All information in this document is furnished for exploratory or indicative purposes only. •This information provides estimates of the average weights and content of component materials. and does not include impurities or metals diffused in the silicon. •ROHM strives for the accuracy of the information, however, ROHM does not give any representations or warranties as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. •ROHM may make changes to information published in this document at any time and without notice. |
|---|

Notes

- 1) The information contained herein is subject to change without notice.
- 2) Before you use our Products, please contact our sales representative and verify the latest specifications :
- 3) Although ROHM is continuously working to improve product reliability and quality, semiconductors can break down and malfunction due to various factors.
Therefore, in order to prevent personal injury or fire arising from failure, please take safety measures such as complying with the derating characteristics, implementing redundant and fire prevention designs, and utilizing backups and fail-safe procedures. ROHM shall have no responsibility for any damages arising out of the use of our Products beyond the rating specified by ROHM.
- 4) Examples of application circuits, circuit constants and any other information contained herein are provided only to illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.
- 5) The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM or any other parties. ROHM shall have no responsibility whatsoever for any dispute arising out of the use of such technical information.
- 6) The Products are intended for use in general electronic equipment (i.e. AV/OA devices, communication, consumer systems, gaming/entertainment sets) as well as the applications indicated in this document.
- 7) The Products specified in this document are not designed to be radiation tolerant.
- 8) For use of our Products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a ROHM representative : transportation equipment (i.e. cars, ships, trains), primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, servers, solar cells, and power transmission systems.
- 9) Do not use our Products in applications requiring extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters.
- 10) ROHM shall have no responsibility for any damages or injury arising from non-compliance with the recommended usage conditions and specifications contained herein.
- 11) ROHM has used reasonable care to ensure the accuracy of the information contained in this document. However, ROHM does not warrant that such information is error-free, and ROHM shall have no responsibility for any damages arising from any inaccuracy or misprint of such information.
- 12) Please use the Products in accordance with any applicable environmental laws and regulations, such as the RoHS Directive. For more details, including RoHS compatibility, please contact a ROHM sales office. ROHM shall have no responsibility for any damages or losses resulting from non-compliance with any applicable laws or regulations.
- 13) When providing our Products and technologies contained in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.
- 14) This document, in part or in whole, may not be reprinted or reproduced without prior consent of ROHM.



Thank you for your accessing to ROHM product informations.
More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

<http://www.rohm.com/contact/>