

信頼性試験結果/Reliability Test Result

Product	LED
Package	LAMP
Series	SLR-325 * *

1 試験結果(Test Result)

_1.試験結果(lest)	Result)				_
試験項目	参考規格	試験条件	n	Pn	1
Test Items	Reference STD		(pcs)	(pcs)	
半田耐熱	JESD22-B106D	260±5℃のPbフリ−半田槽に			
		端子根元0mmまで10±1秒浸漬	22	0	
Solder Heat Resistance		Immerse the reverse side of the device on the surface	22	I	
for Reflow Soldering		of Pb−free solder bath at 260±5°C for 10±1sec			
半田付性	JESD22-B102E	ロシン系フラックスに5±1秒浸漬し、245±5℃の			
Solderbility		Pbフリー半田槽で製品裏面を3±0.5秒浸漬	22	0	*1
		Immerse into rosin flux for 5±1sec,and the device	22	I	"'
		for 3±0.5sec into Pb-free solder bath at 245±5°C			
落下	JEITA ED-4701	高さ:75cm 楓板上:3回	22	0	
Free Drop	A-124	H=75cm Maple Boad : 3 times	22		
振動	JEITA ED-4701	100~2000Hz 98.1m/S ² X,Y,Zの各方向 2時間			
Vibration	A-121	100∼2000Hz 98.1m/S ²	22	0	
		2hours each on each direction of X,Y,Z			
端子引張強度	JESD22-B105D	荷重:10N(1Kgf) 30秒	22	0	
Lead Pull Test		Load:10N(1Kgf) 30sec	22		
端子折曲げ強度	JESD22-B105D	荷重:1.25N(0.125Kgf) 0°~90°~0°~-90°~0°	22	0	
Lead Bend Test		Load: 1.25N(0.125Kgf) $0^{\circ} \sim 90^{\circ} \sim 0^{\circ} \sim -90^{\circ} \sim 0^{\circ}$	22	l o	
温度サイクル	JESD22-A104E	Ta=Tstg Min.°C(30min.) ~ Tstg Max.°C(30min.)100cycle	22	0	
Thermal Cycle			22		
高温放置	JESD22-A103E	Ta=Tstg Max.+5°C/-0°C 1000hrs			
High Temperature			22	0	
Strage					
高温高湿放置	JEITA ED-4701	Ta=85±2°C 85±5%RH 240hrs			
High Temperature	B-121		22	0	
High Humidity Strage					
低温放置	JESD22-A119A	Ta=Tstg Min.±5°C 1000hrs			
Low Temperature			22	0	
Strage					
動作寿命	JESD22-A108D	Ta=25±5°C IF=IFMAX 1000hrs	22	0	
Load Life			22		

2 測定項目及び故障判定基準(Failure Criteria)

Z.例是我自及URK件引定坐午(Fallule Officia)					
測定項目	測定条件	故障判定基準			
Items	Condition	Criteria			
光度	10mA	初期値の60%			
Luminous Intensity	TomA	60% of the initial value			
順方向電圧	10mA	初期値に対する変化率±10%			
Forward Voltage	TomA	Changing rate of $\pm 10\%$			
逆方向電流	VR=VR Max.	規格最大値			
Reverse Current	VN-VN Max.	Maximum of specification			
外観	目視	著しい変化のないこと			
Physical	Visual Check	No outstanding change in physical			

*1	半田付性	電極部の95%以上が半田で覆われていること	
	Solderbility	More than 95% of the electrode must be covered with solder.	

[※]当データは、特定Lotの実力値であり保証値ではありません。 ※This data is actual value from specific lot and is not guaranteed.

Notes

- 1) The information contained herein is subject to change without notice.
- Before you use our Products, please contact our sales representative and verify the latest specifications:
- 3) Although ROHM is continuously working to improve product reliability and quality, semiconductors can break down and malfunction due to various factors. Therefore, in order to prevent personal injury or fire arising from failure, please take safety measures such as complying with the derating characteristics, implementing redundant and fire prevention designs, and utilizing backups and fail-safe procedures. ROHM shall have no responsibility for any damages arising out of the use of our Poducts beyond the rating specified by ROHM
- 4) Examples of application circuits, circuit constants and any other information contained herein are provided only to illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.
- 5) The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM or any other parties. ROHM shall have no responsibility whatsoever for any dispute arising out of the use of such technical information.
- 6) The Products are intended for use in general electronic equipment (i.e. AV/OA devices, communication, consumer systems, gaming/entertainment sets) as well as the applications indicated in this document.
- 7) The Products specified in this document are not designed to be radiation tolerant.
- 8) For use of our Products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a ROHM representative : transportation equipment (i.e. cars, ships, trains), primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, servers, solar cells, and power transmission systems.
- 9) Do not use our Products in applications requiring extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters.
- 10) ROHM shall have no responsibility for any damages or injury arising from non-compliance with the recommended usage conditions and specifications contained herein.
- 11) ROHM has used reasonable care to ensur the accuracy of the information contained in this document. However, ROHM does not warrants that such information is error-free, and ROHM shall have no responsibility for any damages arising from any inaccuracy or misprint of such information.
- 12) Please use the Products in accordance with any applicable environmental laws and regulations, such as the RoHS Directive. For more details, including RoHS compatibility, please contact a ROHM sales office. ROHM shall have no responsibility for any damages or losses resulting non-compliance with any applicable laws or regulations.
- 13) When providing our Products and technologies contained in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.
- 14) This document, in part or in whole, may not be reprinted or reproduced without prior consent of ROHM.



Thank you for your accessing to ROHM product informations. More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

http://www.rohm.com/contact/