

AC/DC Convertor Non-Isolated Flyback Convertor PWM type 10 W (5 V/2 A) BM2PDA1Y-Z Evaluation Board

User's Guide

< High Voltage Safety Precautions >

Please note that this document covers only the BM2PDA1Y-Z evaluation board (BM2PDA1Y-EVK-002) and its functions. For additional information, please refer to the datasheet.

To ensure safe operation, please carefully read all precautions before handling the evaluation board



Depending on the configuration of the board and voltages used,

Potentially lethal voltages may be generated.

Therefore, please make sure to read and observe all safety precautions described in the red box below.

Before Use

- [1] Verify that the parts/components are not damaged or missing (i.e. due to the drops).
- [2] Check that there are no conductive foreign objects on the board.
- [3] Be careful when performing soldering on the module and/or evaluation board to ensure that solder splash does not occur.
- [4] Check that there is no condensation or water droplets on the circuit board.

During Use

- [5] Be careful to not allow conductive objects to come into contact with the board.
- [6] Brief accidental contact or even bringing your hand close to the board may result in discharge and lead to severe injury or death.

Therefore, DO NOT touch the board with your bare hands or bring them too close to the board. In addition, as mentioned above please exercise extreme caution when using conductive tools such as tweezers and screwdrivers.

- [7] If used under conditions beyond its rated voltage, it may cause defects such as short-circuit or, depending on the circumstances, explosion or other permanent damages.
- [8] Be sure to wear insulated gloves when handling is required during operation.

After Use

- [9] The ROHM Evaluation Board contains the circuits which store the high voltage. Since it stores the charges even after the connected power circuits are cut, please discharge the electricity after using it, and please deal with it after confirming such electric discharge.
- [10] Protect against electric shocks by wearing insulated gloves when handling.

This evaluation board is intended for use only in research and development facilities and should by handled only by qualified personnel familiar with all safety and operating procedures.

We recommend carrying out operation in a safe environment that includes the use of high voltage signage at all entrances, safety interlocks, and protective glasses.

<u>www.rohm.com</u> HVB01E



AC/DC Converter

Non-Isolated PWM type Flyback Convertor 10W 5 V Output BM2PDA1Y-Z Evaluation Board

BM2PDA1Y-EVK-002

Feature

- (1) Adjustable Output Voltage with External Resistor
- (2) High Accuracy Output by Output Direct Monitor of Output Voltage
- (3) 65 kHz Frequency
- (4) Internal Start up Circuit 730 V (peak)
- (5) Internal Super Junction FET 730 V (peak) (Ron = 1.2Ω)
- (6) Internal Current Sense Resistor (Detection Current 0.93 A)
- (7) Contributes to Low EMI by Internal Hopping Function



Figure 1. BM2PDA1Y-EVK-002




Figure 2. BM2PDA1Y-EVK-002 Simple Schematic

Specification

Table 1. Input Range

Parameter	Min	Тур	Max	Units	Conditions
Input Voltage Range	90	230	264	Vac	
Input Frequency Range	47	50 / 60	63	Hz	
Operating Temperature	-10	+25	+65	°C	

Table 2. Evaluation board specification

These are representative values and not a guarantee of the characteristics, unless stated otherwise use VIN = 230 Vac, IOUT = 0.2 A, Ta: 25 ° C.

Parameter	Min	Тур	Max	Units	Conditions
Output Voltage	4.75	5.0	5.25	V	I _{OUT} = 0.2 A
Output Maximum Power	-	-	10	W	louт = 2.0 A
Output Current Range (Note 1)	0	-	2.0	Α	
No Load Power Consumption	-	-	100	mW	lоuт = 0 A
Efficiency	-	79	-	%	
Output Ripple Voltage (Note 2)	-	250	-	mVpp	

(Note 1) Adjust the operating time so that surface temperature of no component exceeds 105 °C

(Note 2) Do not consider spike nois

Operation Procedure

- 1. Operation equipment
 - (1) AC power supply 90 Vac to 264 Vac, 15 W or more
 - (2) Electronic Load capacity 2.0 A
 - (3) Multimeter

2. Connection Instruments

- (1) Turn off each power supply and connect the measuring instrument as shown Figure 3. .
- (2) Turn on the power supply setting between 90 Vac to 264 Vac
- (3) Turn on the electrical load setting between 0 to 2.0 A.
- (4) Connect the multimeter directly to the output and check the voltage by sensing.



Figure 3. Connection Circuit

Circuit

 V_{IN} = 90 Vac to 264 Vac, V_{OUT} = 5 V

Figure 4. Application Circuit
Attention: Place C6 connected between FB and GND_IC terminals as close to the terminal as possible.

BOM List

Item		Specifications	Parts name	Manufacture
	C1	12 μF, 450 V	UCY2W120MP01TD	NICHICON
	C2	12 μF, 450 V	UCY2W120MP01TD	NICHICON
	C3	2.2 μF, 50 V	UMK316B7225KL-T	TAIYO YUDEN
	C4	1000 μF, 25 V	25ZLJ1000M10x20	RUBYCON
Capacitor	C5	1000 pF, 100 V	HMK107B7102KA-T	TAIYO YUDEN
Capacitoi	C6	1000 pF, 100 V	HMK107B7102KA-T	TAIYO YUDEN
	C7	2200 pF, 630 V	SMK316BJ222KF-T	TAIYO YUDEN
	C8	-	NON MOUNTED	1
	C9	-	NON MOUNTED	1
	C10	10 μF, 35 V	GMK316AB7106ML-TR	TAIYO YUDEN
Connector	CN1	-	B02P-NV	JST
	D1	SBD, 15 A, 60 V	RBR15BM60A	ROHM
	D2	FRD, 0.8 A, 700 V	RFN1LAM7S	ROHM
Diode	D3	-	NON MOUNTED	1
	D4	FRD, 0.5 A, 200 V	RF05VAM2S	ROHM
	DB1	1 A, 800 V	D1UBA80	SHINDENGEN
Fuse	F1	1.6 A, 300 V	36911600000	LITTELFUSE
IC	IC1	-	BM2PDA1Y-Z	ROHM
Inductor	L3	470 μΗ	7447471471	WURTH ELECTRONIK
	R1	47 kΩ	KTR18EZPJ473	ROHM
	R2	0 Ω	MCR03EZPJ000	ROHM
	R3	300 kΩ	MCR03EZPFX3003	ROHM
Resistor	R4	200 kΩ	MCR03EZPFX2003	ROHM
	R5	-	NON MOUNTED	1
	R6	10 Ω	MCR10EZPJ100	ROHM
	R7	-	NON MOUNTED	-
Transformer	T1	EE19	XE2512Y C	ALPHA TRANS
Test Pin	TP1	BLACK	LC-2-G-BLACK	MAC8
TEST FIII	TP2	RED	LC-22-G-RED	MAC8

Layout

Size 60 mm x 40 mm




Figure 5. Top Silkscreen (Top view)




Figure 6. Bottom Layout (Bottom view)

Attention: Place C6 connected between FB and GND_IC terminals as close to the terminal as possible.

BM2Pxx1Y Overview

Features

- PWM Current Mode
- Built-in Frequency Hopping Function
- Burst Operation at Light Load
- Built-in 730 V(peak) Starter Circuit
- Built-in 730 V(peak) Super Junction MOSFET
- VCC UVLO (Under Voltage Lockout)
- VCC OVP (Over Voltage Protection)
- Over Current Limiter Function per Cycle
- Soft Start Function
- Sleep Mode




Figure 7. Pin Configuration

Line Up

Model Name	Switching Frequency	Frequency Reduction	OCP Current
BM2PAA1Y-Z	65 kHz	0	1.76 A
BM2PAB1Y-Z	25 kHz	-	1.70 A
BM2PDA1Y-Z	65 kHz	0	0.93 A
BM2PDB1Y-Z	25 kHz	-	0.93 A

Key Specifications

■ Operating Power Supply Voltage Range

VCC 11.10 V to 26.00 V **DRAIN** 730 V (peak)(Max) Operating Current (Normal): 650 µA (Typ) Operating Current (Burst): 350 µA (Typ) Operating Current (Sleep): 65 µA (Typ) Switching Frequency: 25 kHz / 65 kHz (Typ) Operation Temperature: -40 °C to +105 °C MOSFET ON Resistance: 1.2 Ω (Typ)

Application

Washing machine, Air conditioner, Other white goods

 Package
 W(Typ) x D(Typ) x H(Typ)

 DIP7K
 9.27 mm x 6.35 mm x 8.63 mm

 Pitch 2.54 mm




Table 3. BM2Pxx1Y-Z Pin Description


No.	Name	I/O	Function			
1	N.C.	-	Non connection			
2	SLEEP	I	Sleep/Normal modes witching pin			
3	GND_IC	I/O	GND pin			
4	FB	I	Output voltage feedback pin			
5	VCC	I	Input voltage pin			
6	DRAIN	I/O	MOSFET drain pin			
7	DRAIN	I/O	MOSFET drain pin			


Transformer Specification


Manufacture


Alphatrans Co., Ltd. (1-7-2, Bakurou-cho, Chuo-ku, Osaka City, 541-0059, Japan) http//www.alphatrans.jp/












6. 電	気特性/ELECTRICAL	CHARACTERIS	TICS:		
NO.	項	測定端子	仕様	測定条件	検査方法 INSPECTION
NO.	ITEM	TERMINAL	SPECIFICATION	TEST CONDITION	STANDARD
1	インダクタンス INDUCTANCE	31	628. 5uH±10%	f=100kHz, v=1V (CH-1062A 内阻50Ω)	全検 ALL
		PS	AC1000V, 1mA, 1MIN	抜I SAMPL	
2	2 耐電圧 HI-POT TEST	SC	AC1000V, 1mA, 1MIN	f=50Hz	(製造工程全 検ALL 電圧 *120%, 2秒)
		РС	AC1000V, 1mA, 1MIN		
	絶縁抵抗	PS			
3	INSULATION	PC	100MΩ MIN	DC 500V	抜取 SAMPLING
	RESISTANCE	SC			OIDM DITTO
		32	48.0±0.2 TS		
		巻き数比 45 27.0±0.			
4	巻き数比 TURNS RATIO			f=1-100kHz, INPUT: T(3-1)=96TS	全検 ALL
	TORIS RATTO	97	9.0±0.3 TS	1(3-1)-3013	ALL
		21	48.0±0.2 TS		

(Note 1) TEX is used this time because of the versatility of the transformer. There is no need to use TEX for non-isolated applications.

Measurement Data

Constant Load Regulations






Figure 8. VOUT vs. IOUT

Figure 10. Power Loss vs. IOUT

Figure 9. Efficiency vs. IOUT





Figure 11. Frequency vs. IOUT

Measurement Data - Continued

Waveform



| Normal | Property | Normal | Property | P

Figure 12. Vds and IL VIN = 90 Vac, IOUT = 0 A

Figure 13. Vds and IL VIN = 264 Vac, IOUT = 0 A




Figure 14. Vds and IL VIN = 90 Vac, IOUT = 0.2 A




Figure 15. Vds and IL VIN = 264 Vac, IOUT = 0.2 A




Figure 16. Vds and IL VIN = 90 Vac, IOUT = 2.0 A





Figure 17. Vds and IL VIN = 264 Vac, IOUT = 2.0 A

Measurement Data - Continued

Waveform (Start Up)






Figure 18. Vds and Vout VIN = 90 Vac, IOUT = 0 A

Figure 19. Vds and Vout VIN = 264 Vac, IOUT = 0 A




Figure 20. Vds and Vout VIN = 90 Vac, IOUT = 2.0 A




Figure 21. Vds and Vout VIN = 264 Vac, IOUT = 2.0 A

Measurement Data - Continued

Waveform (Load Response)





Figure 22. lout and Vout VIN = 90 Vac, IOUT = 0 A to 2 A

Figure 23. lout and Vout VIN = 90 Vac, IOUT = 2 A to 0 A








Figure 25. lout and Vout VIN = 264 Vac, IOUT = 2 A to 0 A

Measurement Data - Continued

Waveform (Ripple Voltage)







Figure 26. Vout Ripple Voltage (5 MHz Filter) VIN = 90 Vac, IOUT = 2.0 A

Figure 27. Vout Ripple Voltage (5MHz filter) VIN = 264 Vac, IOUT = 2.0 A


Operation Temperature

Condition lout=2.0 A. 20 min


VIN=90 Vac



IC 57.0 °C




Diode 70.9 °C




Inductor 68.2 °C


VIN= 264 Vac



IC 63.2 °C



Diode 71.3 °C



Inductor 73.7 °C

Figure 28. Each device Temperature with maximum output current

Consider selecting parts after checking the temperature range of the parts used.

Measurement Data - Continued

<u>EMI</u>


Limit1: CISPR Pub 22 Class B Limit2: CISPR Pub 22 Class B (AV)

Condition

V_{IN} = 90 Vac $I_{OUT} = 2.0 A$

Margin

QP=17.9 dB (0.91 MHz) AV=17.8 dB (0.91 MHz)



	E	Rea	ding	C,Fac	Res	ults	Lir	mit	Mar	gin		
No.	Freq.	<qp></qp>	<av></av>	C.Fac	<qp></qp>	<av></av>	<qp></qp>	<va>></va>	<qp></qp>	<av></av>	Phase	Comment
	[MHz]	[dBuV]	[dBuV]	[dB]	[dBuV]	[dBuV]	[dBuV]	[dBuV]	[dB]	(dB)		
1	0.91050	27.7	17.8	10.4	38.1	28.2	56.0	46.0	17.9	17.8	VB	
2	3.18015	23.5	13.7	10.5	34.0	24.2	56.0	46.0	22.0	21.8	VB	
3	5.07236	22.4	13.3	10.6	33.0	23.9	60.0	50.0	27.0	26.1	VB	

Figure 29. Conduction Noise VIN = 90 Vac

Condition


V_{IN} = 264 Vac

 $I_{OUT} = 2.0 A$

Margin

QP=16.1 dB (1.11 MHz) AV=14.8 dB (1.11 MHz)

Limit1: CISPR Pub 22 Class B Limit2: CISPR Pub 22 Class B (AV)



	F	Read	ding	C.Fac	Res	ults	Lit	nit	Mar	gin		
No.	Freq.	<qp></qp>	<av></av>	C.Fac	<qp></qp>	<av></av>	<qp></qp>	<av></av>	<qp></qp>	<va></va>	Phase	Comment
	[MHz]	[dBuV]	[dBuV]	[dB]	[dBuV]	[dBuV]	[dBuV]	[dBuV]	[dB]	[dB]		
1	0.81296	25.7	16.6	10.4	36.1	27.0	56.0	46.0	19.9	19.0	VB	
2	1.10809	29.5	20.8	10.4	39.9	31.2	56.0	46.0	16.1	14.8	VB	
3	1.91941	27.2	18.5	10.5	37.7	29.0	56.0	46.0	18.3	17.0	VB	
4	5.00623	25.7	20.4	10.6	36.3	31.0	60.0	50.0	23.7	19.0	VB	

Figure 30. Conduction Noise VIN = 264 Vac

Revision History

Date	Rev.	Changes					
30.Sep.2021	001	New Release					
30.Nov.2021	002	P4 Board size added P6 Transformer electrical characteristics added P13 EMI data added					

Notes

- 1) The information contained herein is subject to change without notice.
- Before you use our Products, please contact our sales representative and verify the latest specifications:
- 3) Although ROHM is continuously working to improve product reliability and quality, semiconductors can break down and malfunction due to various factors. Therefore, in order to prevent personal injury or fire arising from failure, please take safety measures such as complying with the derating characteristics, implementing redundant and fire prevention designs, and utilizing backups and fail-safe procedures. ROHM shall have no responsibility for any damages arising out of the use of our Poducts beyond the rating specified by ROHM.
- 4) Examples of application circuits, circuit constants and any other information contained herein are provided only to illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.
- 5) The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM or any other parties. ROHM shall have no responsibility whatsoever for any dispute arising out of the use of such technical information.
- 6) The Products specified in this document are not designed to be radiation tolerant.
- 7) For use of our Products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a ROHM representative: transportation equipment (i.e. cars, ships, trains), primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, servers, solar cells, and power transmission systems.
- 8) Do not use our Products in applications requiring extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters.
- 9) ROHM shall have no responsibility for any damages or injury arising from non-compliance with the recommended usage conditions and specifications contained herein.
- 10) ROHM has used reasonable care to ensure the accuracy of the information contained in this document. However, ROHM does not warrants that such information is error-free, and ROHM shall have no responsibility for any damages arising from any inaccuracy or misprint of such information.
- 11) Please use the Products in accordance with any applicable environmental laws and regulations, such as the RoHS Directive. For more details, including RoHS compatibility, please contact a ROHM sales office. ROHM shall have no responsibility for any damages or losses resulting non-compliance with any applicable laws or regulations.
- 12) When providing our Products and technologies contained in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.
- 13) This document, in part or in whole, may not be reprinted or reproduced without prior consent of ROHM.



Thank you for your accessing to ROHM product informations. More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

http://www.rohm.com/contact/