



Electronics for the Future

Introduction of Industry Standard 0603 Size LED

~ Single COLOR ~

2024
Module Business Unit
LED Division
Rev.006


No. 65AN024E Rev.006
Oct.2024

Features of ROHM LEDs



ROHM is one of the few LED suppliers that manufactures their own dies

Integrated production




- Quality Management
- Production Control
- Development System

Some products are manufactured by separate processes.


Capable of responding to detailed requests for color and brightness

Color	IR	IR	V	U	U2	D	Y	W	M	P	E	E2	B	WB
Dominant wavelength (nm)	940	850	630	620	615	605	590	580	572	560	525	505	470	White
Chip Type	AlGaAs System		AlGaInP System							InGaN System				

Optical simulation and other support tools are provided for customer development




A wide range of services available from a comprehensive semiconductor manufacturer




“Kyo-no-Hikari-Koyomi”

ROHM has been lighting up the Kyoto Station building since 2010. Created using original LED technology in collaboration with Mikiko Ishii’s design, ‘Kyo no Hikari Koyomi’ expresses Kyoto’s delicate seasonal atmosphere and traditional events through light.

Combining ROHM’s full-color LEDs and LED modules with optimizable color temperature in both vertical and horizontal directions ensures gentle, soft lighting similar to that through shoji (paper sliding door), in harmony with the streetscapes of Kyoto.




〈Schedule〉



On the 16th of every month, we participate in the "DO YOU KYOTO?" light-down campaign promoted by Kyoto City to turn lights. (Unified Action Light-Down calls for turning off outdoor lights, etc.)

Delicate Japanese sensibility is expressed by subtly adjusting the color temperature according to the season.

Overwhelming production volume



0603 size is an all-rounder


Items/Size	PLCC	0805	0603	0402
Mounting area	Fair	Fair	Good	Excellent
Brightness	Excellent	Good	Excellent	Fair
Heat radiation	Excellent	Good	Good	Fair
Handling *	Good	Good	Good	Fair

*Easy handling of LEDs, such as hand soldering during prototyping


ROHM can help you find the 0603 size LED you need

I'm going to be lined a lot of them, so I want to minimize the variation...

[Standard type]
Single rank
SML-D15 Series




[Reflector type]
White narrow rank
CSL11 series




I want to reduce the light intensity drop...

[Standard type]
Long Life
SMLD1 Series



The color is easy for everyone to see...

[Standard type]
SML-D1 Series ■ Orange / SMLD1 Series ■ Blue-Green
● Color Universal Design



Easier to recognize than the color scheme in the current product (red and green)

I want to reduce the size of the product while keeping the LEDs bright...

● **87% reduction** in mounting area



● Equivalent luminous intensity in a small space



[Lens type]
CSL09 Series

[Reflector type]
CSL11 Series

- Please see the next page for details -

Lineup of ROHM 0603 Sizes

Size : mm

Standard type

Basic form of the
0603 series,
Start here



SML-D12 * 8 series
1.6×0.8×0.55t

V U D Y W M P

Details on
page 5

Brightness rank reduction type



SML-D12 * 1 series
1.6×0.8×0.55t

V U D Y W M

Details on
page 5

High brightness standard type



SML-D13(A) series
1.6×0.8×0.55t

V U D Y W M

Details on
page 5

High brightness Single rank type

Variation reduction




SML-D15 series
1.6×0.8×0.55t

V U U2 D Y M

Details on
page 5

Long life type




SMLD12 series
1.6×0.8×0.55t

E E2 E3 B WB

Details on
page 6

Lens type

Replacement of
PLCC and
LED lamps



CSL09 series
1.6×0.8×1.24t

V U D Y W M P E B

Details on
page 7

Reflector type

White LED with high luminous
intensity/ reduced color variation



CSL11 series
1.6×0.8×0.55t

WB

Details on
page 8

Red to Green 2mA sorting type



CSL1901 series
1.6×0.8×0.55t

V U D Y W M

Details on
page 9





Standard Type ①: SML-D1 Series

Wide lineup

※AEC Q102 : Automotive Type(C)

Series		Brightness (mcd) [typ.]			
		SML-D12*8W	SML-D12*1W	SML-D13(A)	SML-D15
AEC Q102		YES	-	YES	YES
Color	Wavelength (nm)	Standard type	Rank reduction type	High brightness type	High brightness and Single rank type
V	630	40	40	55	90
U	620	63	63	85	112
U2	615	-	-	-	140
D	605	100	100	120	224
Y	590	63	100	-	224
W	587	-	-	110	-
M	572	25	30	45	71
P	560	6	-	-	-

High brightness and Single rank type: D15 Series




•Merit of High brightness type

- ① Eliminates light intensity variations within and between products → **Improved performance of application**
- ② No need to evaluate current control for each rank → **Reduction of design man-hours**
- ③ No need to consider rank designation → **No need for brightness adjustment and stable supply**

Case study

IH cooking heater



When heating the glass top plate Red color is displayed in a ring shape


[Request]

They want to display a high-brightness ring-shaped display on the glass top panel during cooking without uneven brightness.



- High brightness display is possible even through a glass top plate.
 - No unevenness in color even if dozens of units are used per unit.
 - No need to adjust light intensity.
- ⇒ Adopted by SML-D15U2W.

*The image is for reference



Standard Type ②: SMLD1 Series

Color lineup

Series		Brightness (mcd) [typ.]
AEC Q102		SMLD12 *
Color		Long life
E	527	140
E2 ※1	505	120
E3 ※1	496	85
B	470	40
WB	(0.295,0.280)	120

※AEC Q102 : Automotive Type(C)

NEW COLOR

Unusual color for a single color

*1) Emission wavelength (around 500nm) is compatible with color universal design.

Color Universal


		P and D type color vision
610		
530		
500		
470		

Both red and green appear to be yellowish.


This is a green color that is easily recognized by people with P and D type color vision.

Appearance Examples

Allows for more recognizable color schemes



Long life



- Long life design that prevents darkening even when the power is on for a long time

Overcoming the weakness of molded LEDs that reduce luminous intensity with blue light

High mountability

Material	Long life (Improvement of degradation)	Mounting (Enhanced mold strength)
New material	Good	Good
Epoxy	Bad	Good
Silicone	Good	Bad

- Successfully enhanced mold strength for better mountability

Case Study

Power supply



[Request]

10 years for industrial equipment
They want long-life products that are white.

● White with Long life
Adopted by **SMLD12WBN**

*The image is for reference




Lens Type: CSL09 Series

Selectable from low to high brightness


※AEC Q102 : Automotive Type(C)

Series		Brightness (mcd) [typ.]		
		CSL0901*	CSL0902*	CSL0903*
AEC Q102		YES		
Color	Wavelength (nm)	Low brightness	Middle brightness	High brightness
V	630	180	250	800
U	620	280	400	1200
D	605	380	500	1500
Y	590	320	520	800
M	571	100	150	—
E	527	360	1,100	—
B	470	56	360	—

- Power saving by increasing brightness compared to standard products



Lens type, but not prone to unevenness of light, can be proposed as a replacement for LED lamps.



Shorter distance to irradiation surface

Space saving
Reduces uneven
brightness with lens

Case study

Power tool



Adopted for operation display unit

[Request]

- 1) Downsizing of the set
- 2) For outdoor use, a small LED with high luminous intensity is desired so that the blue display can be easily seen.

● 0603 size, high luminous intensity lens type

Adopted by CSL0902BT

*The image is for reference



Reflector Type: CSL11 Series




lineup

CSL11series			Brightness(mcd)[typ.]
Type	IF(mA)	Color(x,y)[typ.]	
AEC Q102 ※Automotive Type(C)			
CSL1101xW	5	AW:(0.282,0.249) BW:(0.261,0.261) CW:(0.303,0.294) DW:(0.284,0.303)	155
CSL1102xW	20		1000
CSL1103xW	20		1500
CSL1104xW	20		2000

Small and high brightness


Available from low to high brightness in the same package



Improved color variation

● 4 color variation (AW, BW, CW, DW)

The rank range is defined for each shape name, making it easy to manage!



Improved design and visibility


● Blackout specification

Easier to adjust the transmittance of the cover material, which has been a problem for designers!



● Safe even in high-density mounting

The reflector suppresses light leakage to adjacent symbols, and the chip is placed in the center for easy optical design.



Case study

Electric medical device

Adopted for operation display unit

[Request]

- ① Miniaturization of the set
- ② White color for long-life products is desired.
- ③ High luminous intensity is desired to improve visibility.

↓

● Small size, High brightness, White
 ➔ Adopted by CSL11*WB

*The image is for reference



0603 size 2mA measurement LED: CSL1901 series



lineup

CSL19series			Brightness(mcd[typ.]
Color	IF(mA)	Wavelength (nm)	Low current
V	2	630	4.8
U	2	620	6.0
D	2	605	9.4
Y	2	590	9.4
M	2	570	3.0

Variations in luminous intensity and color at low currents are halved.

Guaranteed 2mA luminous intensity halves the brightness variation

2mA dominant wavelength measurement reduces wavelength shift and color variation



Guarantees brightness integrity at low current lighting
Eliminates color issues with low current lighting

Point

• Reduces brightness and color variations in low-emission applications

Guaranteed luminous intensity at 2mA halves the intensity fluctuation
Dominant wavelength measurement at 2mA reduces wavelength shift and color variation

• Lineup includes energy saving high efficiency light-emitting AlGaInP-based devices

Emits light at 2mA with sufficient brightness even through a diffuser plate

• Five-color lineup optimized for display

PLC eqitment/temperature controller/level meter



【Request】

As an indoor device, 7 segments and indicators are densely placed in a small space area.

7seg and indicator are placed densely in a small space.

If it is too bright, it is difficult to see the display.

If the current is turned down, unevenness in the current in the brightness of the 7 segments display will occur



No uneven brightness in 7 segments.
Good visiblility indoords.

0603 Size Main Products: SML-D1 Series

Package (mm)	Emitting Color	Part No.	Electrical and Optical Characteristics (T _a =25°C)										Absolute Maximum Ratings (T _a =25°C)					
			Dominant Wavelength λ _d / Chromaticity Coordinates (x, y)		Luminous Intensity I _v				Forward Voltage V _F		Reverse Current I _R		Power Dissipation P _D	Forward Current I _F	Peak Forward Current I _{FP}	Reverse Voltage V _R	Operating Temperature T _{opr}	Storage Temperature T _{stg}
			Typ* (nm)	I _F (mA)	Min (mcd)	Typ (mcd)	Max (mcd)	I _F (mA)	Typ (V)	I _F (mA)	Max (μA)	V _R (V)	(mW)	(mA)	(mA)	(V)	(°C)	(°C)
	Red	SML-D12L8W	635	20	10	16	40	20	2.0	20	10	5	50	20	100*5	5	-40 to +85	-40 to +100
		SML-D14VW (A)	630	20	71	100	180	20	2.0	20	10	5	72	30	100*2	5	-40 to +100	-40 to +100
		SML-D15VW			90	112	84						35					
		SML-D13VW (A)			36	55	90						72	30				
		SML-D12V8W			16	40	100						54	20				
		SML-D12V1W			25	63	44						20					
		New CSL1901VW			2	1.6	4.8	6.3	2	1.8	2	44						
		SML-D15UW	620	20	90	112	140	20	2.0	20	10	5	84	35	100*2	5	-40 to +100	-40 to +100
		SML-D13UW (A)			56	85	72						30					
		SML-D13U8W			40	70	160						52	20				
		SML-D12U8W			25	63	54						20					
		SML-D12U1W			40	100	44						20					
		New CSL1901UW			2	2.5	6	10	2	1.8	2	44						
		SML-D14U2W (A)	615	20	90	160	224	20	2.0	20	10	5	72	30	100*2	5	-40 to +100	-40 to +100
		SML-D15U2W			112	140	180						84	35				
		SML-D15DW			180	224	280						84	35				
	Orange	SML-D14DW (A)	605	20	112	200	20	2.0	20	10	5	72	30	100*2	5	-40 to +100	-40 to +100	
		SML-D13DW (A)			71	120						180	54					20
		SML-D12D8W			40	250						44	20					
		SML-D12D1W			63	160						44	20					
		New CSL1901DW			2	6.3	9.4	25	2	1.8	2	44						
		Yellow	SML-D15YW	590	20	180	224	280	20	2.1	20	10	5	87	35	100*2	5	-40 to +100
	SML-D14YW (A)		112			200	75	30										
	SML-D12Y1W		63			100	160	54						20				
	SML-D13Y8W		25			63	44	20										
	SML-D12Y8W		2			6.3	9.4	25	2	1.8	2	44						
	New CSL1901YW		2	6.3	9.4	25	2	1.8	2	44								
	SML-D12W8W (A)		588	2	5	7	9	2	2.0	2	10	12	52	20	100*2	12	-40 to +100	-40 to +100
	SML-D11YW				2	4	6											
	SML-D14WW (A)		587	20	112	180	280	20	2.1	20	10	5	75	30	100*2	5	-40 to +100	-40 to +100
	SML-D13WW (A)				71	110	180						78	30				
	SML-D13Y2W		581	20	40	80	160	20	2.1	20	10	5	78	30	100*2	5	-40 to +85	-40 to +100
	SML-D12Y3W	16			40	100	54						20					
	Yellow Green	SML-D12M1W	572	20	16	30	63	20	2.2	20	10	5	54	20	100*2	5	-40 to +85	-40 to +100
		SML-D13M8W			10	25												
		SML-D12M8W			10	25												
		SML-D15MW	571	20	56	71	90	20	2.1	20	10	5	87	35	100*2	5	-40 to +100	-40 to +100
		SML-D14MW (A)			36	60							75	30				
		SML-D13MW (A)			28	45	71						75	30				
	New CSL1901MW	2			1	3	4	2	1.8	2	10	5	44	20				
	Green	SML-D13FW	565	20	18	22	36	20	2.1	20	10	5	81	30	100*2	5	-40 to +85	-40 to +100
		SML-D12FW			14	18	28						67	25				
		SML-D12P8W			3	6	16	20	2.2	20	10	5	54	20				
		SMLD12EN1W	527	5	56	140	220	5	3.0	5	10	5	70	20	100*2	5	-40 to +100	-40 to +100
	Blue Green	SMLD12E2N1W	505	5	56	120	140	5	2.9	5	10	5	66	20	100*2	5	-40 to +100	-40 to +100
		SMLD12E3N1W	496	5	56	85	140	5	2.9	5	10	5	66	20	100*2	5	-40 to +100	-40 to +100
	Blue	SMLD12BN1W	470	5	14	40	56	5	2.9	5	10	5	66	20	100*2	5	-40 to +100	-40 to +100
White	SMLD12WBN1W	(x, y) (0.295, 0.280)	5	56	120	220	5	2.9	5	10	5	66	20	100*2	5	-40 to +100	-40 to +100	




*1 Duty≤1/5, 200Hz *2 Duty≤1/10, 1kHz *3 Duty≤1/20, 1ms *4 Duty≤1/5, 1kHz *5 Duty≤1/10, pulse width 10ms Max

*Luminous intensity for white color is noted with chromaticity coordinate (x, y).

Note1: PICOLED™ is a trademark or a registered trademark of ROHM Co., Ltd.

Note2: You can order this product by single rank designation.

0603 Size High Brightness Products: CSL09, CSL11 Series

Package (mm)	Emitting Color	Part No.	Electrical and Optical Characteristics (T _a =25°C)										Absolute Maximum Ratings (T _a =25°C)								
			Dominant Wavelength λ _D		Luminous Intensity I _v					Forward Voltage V _F		Reverse Current I _R		Power Dissipation P _D	Forward Current I _F	Peak Forward Current I _{FP}	Reverse Voltage V _R	Operating Temperature T _{opr}	Storage Temperature T _{stg}		
			Typ (nm)	I _F (mA)	Min (mcd)	Typ (mcd)	Max (mcd)	I _F (mA)	Typ (V)	I _F (mA)	Max (μA)	V _R (V)	P _D (mW)	I _F (mA)	I _{FP} (mA)	V _R (V)	T _{opr} (°C)	T _{stg} (°C)			
 1.6×0.8 (t=1.06)	Green	CSL1001ET (C)	527	5	90	140	224	5	3.0	5	10	5	35	10	50*2	5	-40 to +100	-40 to +100			
	Blue	CSL1001BT (C)	470	1	4	6	9	1	2.8	1	10	5	33	10	50*2	5	-40 to +100	-40 to +100			
Package (mm)	Emitting Color	Part No.	Electrical and Optical Characteristics (T _a =25°C)										Absolute Maximum Ratings (T _a =25°C)								
			Dominant Wavelength λ _D / Chromaticity Coordinates (x, y)		Luminous Intensity I _v					Forward Voltage V _F		Reverse Current I _R		Power Dissipation P _D	Forward Current I _F	Peak Forward Current I _{FP}	Reverse Voltage V _R	Operating Temperature T _{opr}	Storage Temperature T _{stg}		
			Typ* (nm)	I _F (mA)	Min (mcd)	Typ (mcd)	Max (mcd)	I _F (mA)	Typ (V)	I _F (mA)	Max (μA)	V _R (V)	P _D (mW)	I _F (mA)	I _{FP} (mA)	V _R (V)	T _{opr} (°C)	T _{stg} (°C)			
 1.6×0.8 (t=0.55)	White	New CSL1101WBAW	(x, y) (0.282, 0.249)	5	90	155	220	5	2.9	5	10	5	68	20	100*2	5	-40 to +110	-40 to +110			
		New CSL1101WBBW	(x, y) (0.261, 0.261)	5	90	155	220	5	2.9	5	10	5	68	20	100*2	5	-40 to +110	-40 to +110			
		New CSL1101WBCW	(x, y) (0.303, 0.294)	5	90	155	220	5	2.9	5	10	5	68	20	100*2	5	-40 to +110	-40 to +110			
		New CSL1101WBDW	(x, y) (0.284, 0.303)	5	90	155	220	5	2.9	5	10	5	68	20	100*2	5	-40 to +110	-40 to +110			
		New CSL1102WBAW	(x, y) (0.282, 0.249)	20	710	1,000	1,400	20	3.2	20	10	5	152	40	100*2	5	-40 to +110	-40 to +110			
		New CSL1102WBBW	(x, y) (0.261, 0.261)	20	710	1,000	1,400	20	3.2	20	10	5	152	40	100*2	5	-40 to +110	-40 to +110			
		New CSL1102WBCW	(x, y) (0.303, 0.294)	20	710	1,000	1,400	20	3.2	20	10	5	152	40	100*2	5	-40 to +110	-40 to +110			
		New CSL1102WBDW	(x, y) (0.284, 0.303)	20	710	1,000	1,400	20	3.2	20	10	5	152	40	100*2	5	-40 to +110	-40 to +110			
		CSL1103WBAW	(x, y) (0.282, 0.249)	20	900	1,500	2,200	20	3.2	20	10	5	152	40	100*2	5	-40 to +110	-40 to +110			
		CSL1103WBBW	(x, y) (0.261, 0.261)	20	900	1,500	2,200	20	3.2	20	10	5	152	40	100*2	5	-40 to +110	-40 to +110			
		CSL1103WBCW	(x, y) (0.303, 0.294)	20	900	1,500	2,200	20	3.2	20	10	5	152	40	100*2	5	-40 to +110	-40 to +110			
		CSL1103WBDW	(x, y) (0.284, 0.303)	20	900	1,500	2,200	20	3.2	20	10	5	152	40	100*2	5	-40 to +110	-40 to +110			
		CSL1104WBAW	(x, y) (0.282, 0.249)	20	1,400	2,000	2,800	20	2.9	20	10	5	144	40	100*2	5	-40 to +110	-40 to +110			
		CSL1104WBBW	(x, y) (0.261, 0.261)	20	1,400	2,000	2,800	20	2.9	20	10	5	144	40	100*2	5	-40 to +110	-40 to +110			
		CSL1104WBCW	(x, y) (0.303, 0.294)	20	1,400	2,000	2,800	20	2.9	20	10	5	144	40	100*2	5	-40 to +110	-40 to +110			
		CSL1104WBDW	(x, y) (0.284, 0.303)	20	1,400	2,000	2,800	20	2.9	20	10	5	144	40	100*2	5	-40 to +110	-40 to +110			
Package (mm)	Emitting Color	Part No.	Electrical and Optical Characteristics (T _a =25°C)										Absolute Maximum Ratings (T _a =25°C)								
			Dominant Wavelength λ _D		Luminous Intensity I _v					Forward Voltage V _F		Reverse Current I _R		Power Dissipation P _D	Forward Current I _F	Peak Forward Current I _{FP}	Reverse Voltage V _R	Operating Temperature T _{opr}	Storage Temperature T _{stg}		
			Typ (nm)	I _F (mA)	Min (mcd)	Typ (mcd)	Max (mcd)	I _F (mA)	Typ (V)	I _F (mA)	Max (μA)	V _R (V)	P _D (mW)	I _F (mA)	I _{FP} (mA)	V _R (V)	T _{opr} (°C)	T _{stg} (°C)			
 1.6×0.8 (t=1.24)	Red	CSL0903VT	630	20	560	800	1,400	20	2.1	20	10	12	87	35	100*2	12	-40 to +100	-40 to +100			
		CSL0902VT			180	280	450						62.5	25	100*2						
		CSL0901VT			112	180	355						62.5	25	100*2						
		CSL0903UT			710	1,200	1,800						87	35	100*2						
	Orange	CSL0902UT	620	20	224	355	560	20	2.1	20	10	12	87	35	100*2	12	-40 to +100	-40 to +100			
		CSL0901UT			140	280	450						62.5	25	100*2						
		CSL0903DT			900	1,400	2,240						87	35	100*2						
		New CSL0902DT			355	560	900						62.5	25	100*2						
	Yellow	CSL0901DT	605	20	224	400	710	20	2.1	20	10	12	62.5	25	100*2	12	-40 to +100	-40 to +100			
		CSL0903YT			560	800	1,400						87	35	100*2						
		CSL0902YT			355	560	900						62.5	25	100*2						
		CSL0901YT			180	320	560						62.5	25	100*2						
	Yellow Green	CSL0901WT	587	20	180	280	560	20	2.1	20	10	12	62.5	25	100*2	12	-40 to +100	-40 to +100			
		New CSL0902MT			112	180	280						87	35	100*2						
		CSL0901MT			56	100	180						62.5	25	100*2						
		CSL0901PT			560	20	14						30	45	20				2.1	20	10
	Green	CSL0902ET	527	5	710	1,100	1,800	20	3.4	20	10	5	95	25	100*2	5	-40 to +100	-40 to +100			
		CSL0901ET			220	360	560						5	3.0	5				70	20	100*2
		CSL0902BT			20	220	360						560	20	3.3				20	95	25
	Blue	CSL0901BT	470	5	36	56	90	5	2.9	5	10	5	68	20	100*2	5	-40 to +100	-40 to +100			

*1 Duty≤1/5, 200Hz *2 Duty≤1/10, 1kHz *3 Duty≤1/20, 1ms *4 Duty≤1/5, 1kHz *5 Duty≤1/10, pulse width 10ms Max *6 Peak wavelength
 *Luminous intensity for white color is noted with chromaticity coordinate (x, y).
 Note: AutomotiveGrade products are indicated by a 'C' at the end of the part number. For details, please contact a sales representative.

Red (V, U) Quick Reference of Luminous intensity

Package Structure	Package Size (mm)	Height (mm)	<div>Luminous Intensity (mcd) I_F (mA)</div>	1.0 to 1.6	1.6 to 2.5	2.5 to 4.0	4.0 to 6.3	6.3 to 10	10 to 16	16 to 25	25 to 40	40 to 63	63 to 100	100 to 160	160 to 250	250 to 400	400 to 630	630 to 1000	1000 to 1600	1600 to 2500	2500 to 3120		
Mini-mold	1608	0.55	2		CSL1901VW																		
					CSL1901UW																		
							SML-D12L8W																
													SML-D15VW										
													SML-D14VW (A)*										
												SML-D13VW (A)*											
												SML-D12V1W											
												SML-D12V8W											
															SML-D15UW								
															SML-D15U2W								
															SML-D14U2W (A)*								
															SML-D13UW (A)*								
Lens	1.24	20									SML-D13U8W												
											SML-D12U1W												
											SML-D12U8W												
													CSL0901VT										
													CSL0901UT										
														CSL0902VT									
												CSL0902UT											
																	CSL0903VT						
																	CSL0903UT						

Yellow Green (M), Green (P, F) Quick Reference of Luminous intensity

Package Structure	Package Size (mm)	Height (mm)	<div>Luminous Intensity (mcd) I_F (mA)</div>	0.63 to 1.0	1.0 to 1.6	1.6 to 2.5	2.5 to 4.0	4.0 to 6.3	6.3 to 10	10 to 16	16 to 25	25 to 40	40 to 63	63 to 100	100 to 160	160 to 250	250 to 400	400 to 630	630 to 1000	1000 to 1800	1800 to 2500
Mini-mold	1608	0.55	2		CSL1901MW																
			20												SML-D15MW						
															SML-D14MW (A)*						
															SML-D13MW (A)*						
														SML-D13FW							
														SML-D13M8W							
														SML-D12P8W							
											SML-D12M1W										
Lens	1.24	20																			

Yellow (Y, W) Quick Reference of Luminous intensity

Package Structure	Package Size (mm)	Height (mm)	Luminous Intensity (mcd) I _F (mA)	1.0 to 1.6	1.6 to 2.5	2.5 to 4.0	4.0 to 6.3	6.3 to 10	10 to 16	16 to 25	25 to 40	40 to 63	63 to 100	100 to 160	160 to 250	250 to 400	400 to 630	630 to 1000	1000 to 1600	1600 to 2800		
Mini-mold	1608	0.55	2		SML-D11YW																	
						SML-D12W8W (A)*																
			20			CSL1901YW																
																		SML-D15YW				
																SML-D14YW (A)*						
															SML-D14WW (A)*							
															SML-D13WW (A)*							
															SML-D13Y8W							
														SML-D13Y2W								
												SML-D12Y3W										
													SML-D12Y1W									
									SML-D12Y8W													
Lens	1.24	20													CSL0901YT							
													CSL0901WT									
														CSL0902YT								
														CSL0903YT								

Green (E)/Blue Green (E2, E3) Quick Reference of Luminous intensity

Package Structure	Package Size (mm)	Height (mm)	Luminous Intensity (mcd) I_F (mA)	9.0 to 14	14 to 22	22 to 36	36 to 56	56 to 90	90 to 140	140 to 220	220 to 360	360 to 560	560 to 900	900 to 1400	1400 to 2200	2200 to 3600	3600 to 5600
Mini-mold	1608	0.55	5					SMLD12EN1W									
								SMLD12E2N1W									
		1.06						SMLD12E3N1W									
Lens	1608	1.24	20					CSL1001ET (C)									
											CSL0901ET						
													CSL0902ET				

Blue (B) Quick Reference of Luminous intensity

Package Structure	Package Size (mm)	Height (mm)	Luminous Intensity (mcd) I_F (mA)	0.9 to 1.4	1.4 to 2.2	2.2 to 3.6	3.6 to 5.6	5.6 to 9.0	9 to 14	14 to 22	22 to 36	36 to 56	56 to 90	90 to 140	140 to 220	220 to 360	360 to 560	560 to 900	900 to 1400
Mini-mold	1608	0.55	5							SMLD12BN1W									
		1.06	1				CSL1001BT (C)												
Lens	1608	1.24	5									CSL0901BT							
			20												CSL0902BT				


White (WB) Quick Reference of Luminous intensity

Package Structure	Package Size (mm)	Height (mm)	Luminous Intensity (mcd) I _F (mA)	9 to 14	14 to 22	22 to 36	36 to 56	56 to 90	90 to 140	140 to 220	220 to 360	360 to 560	560 to 900	900 to 1100	1100 to 1400	1400 to 1800	1800 to 2200	2200 to 2800	2800 to 3600	3600 to 7000	7000 to 8500	
Mini-mold	1608	0.55	5					SMLD12WBN1W														
Reflector								CSL1101WBxW														
			20										CSL1102WBxW									
														CSL1103WBxW								
																CSL1104WBxW						


Outline Drawing and Recommended Pattern

Outline
Drawing


■ SML-D1 Series




■ SMLD1 Series




■ CSL19 Series








■ CSL09 Series



■ CSL11 Series



Recommended
Pattern



Package Lineup

Top view
★ AEC-Q102
★ : Reverse mount available
1608size

SML-E1/EN series 1.6×0.8×0.36t V U D Y M P E B WB	SML-D1 series 1.6×0.8×0.55t V U D Y3 Y W M F P E E2 E3 B WB	CSL19 series 1.6×0.8×0.55t V U D Y M	CSL09 series 1.6×0.8×1.24t V U D Y W M P E B	CSL11 series 1.6×0.8×0.55t WB
SML-P1/P14 series PICOLED 1.0×0.6×0.2t V U U2 D Y3 Y W Y2 M2 M F P E B WB IR	SML-H1 series 2.0×1.25×0.8t V U D Y M P TB	SML-M1/MN series 2.0×1.25×0.8t V U D Y M P E B WB IR	SML-Z1/ZN series PLCC 3.5×2.8×1.9t V U D Y M F P E B WB	CSL10 series 1.6×0.8×1.06t E B

High Power(White)

SMLK1 * series 4.5×2.0×0.6t WB	SML-S1 series 3.2×1.6×1.85t V U D Y M P E B IR	SML-81 series 3.4×1.25×1.1t V U D W M B WB TB	CSL07 series 2.9×2.4×3.1t U D
---	--	---	--

Multi color

SML-P24 series PICOLED-Duo 1.0×1.0×0.2t M U	SML-D22 series 1.6×0.8×0.55t M U V Y	SML-52 series 1.3×1.5×0.6t B U M U M D M Y
SML-82 series 3.4×1.25×1.1t M V	SMLP34RGB PICO-RGB 1.0×1.0×0.2t RGB	SMLP36RGB PICO-RGB 1.5×1.0×0.2t RGB
MSL0402RGB 1.8×1.6×0.5tz RGB	SMLVN6RGB 3.5×2.8×0.6t RGB	

MSL0601RGB 2.9×1.35×1.0t RGB	MSL0104RGB 6.9×2.2×2.15t RGB
---	---

Side view

CSL04 series 2.8×1.2×0.8t WB	SML-A1 series 1.6×1.15×0.55t V U D Y W M P E B WB
---	---

Lamp
unit (mm)

SLI/SLR-343 series

 3φ
 V U D Y M P E B WB

SLI/SLA-560 series

 5φ
 U D Y M E B WB

SLI/SLA-580 series

 5φ
 U D Y M E B

SLR-56 series

 5φ
 V D Y M E B

SLI-430 series

 4φ
 U D Y M

SLR/SLI-325 series

 3.2φ
 V U D Y M

SLR-322 series


 3φ
 V D Y M


① ROHM HP(LED) click

Go to HP for data related !
Can be obtained with individual product data

Tools


MODELS


 SMLD12EN1W SPICE Model

 SMLD12EN1W Ray Data

2D/3D/CAD

 SMLD12EN1W 3D STEP Data

 Parasolid X_T File

 3D eDrawings Data


CHARACTERISTICS DATA

 Electrical Static Discharge (ESD)

Packaging & Quality


MANUFACTURING DATA

 Reliability Test Result


 Factory Information

ENVIRONMENTAL DATA

 About Flammability of Materials

 Compliance of the ELV directive

 MSDS

 Compliance of the RoHS / ELV directive

EXPORT INFORMATION

 About Export Regulations

ROHM YouTube click

~LED Product Videos~



 click



 click



 click



 click



 click



 click

We will continue to distribute product videos

Please check our website and YouTube, which are updated as needed.

- 1) The information contained herein is subject to change without notice.
- 2) Before you use our Products, please contact our sales representative and verify the latest specifications :
- 3) Although ROHM is continuously working to improve product reliability and quality, semiconductors can break down and malfunction due to various factors. Therefore, in order to prevent personal injury or fire arising from failure, please take safety measures such as complying with the derating characteristics, implementing redundant and fire prevention designs, and utilizing backups and fail-safe procedures.
ROHM shall have no responsibility for any damages arising out of the use of our Products beyond the rating specified by ROHM.
- 4) Examples of application circuits, circuit constants and any other information contained herein are provided only to illustrate the standard usage and operations of the Products
The peripheral conditions must be taken into account when designing circuits for mass production.
- 5) The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products.
ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM or any other parties.
ROHM shall have no responsibility whatsoever for any dispute arising out of the use of such technical information.
- 6) The Products specified in this document are not designed to be radiation tolerant.
- 7) For use of our Products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a ROHM representative :
transportation equipment (i.e. cars, ships, trains), primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, servers, solar cells, and power transmission systems.
- 8) Do not use our Products in applications requiring extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters.
- 9) ROHM shall have no responsibility for any damages or injury arising from non-compliance with the recommended usage conditions and specifications contained herein.
- 10) ROHM has used reasonable care to ensure the accuracy of the information contained in this document.
However, ROHM does not warrant that such information is error-free, and ROHM shall have no responsibility for any damages arising from any inaccuracy or misprint of such information.
- 11) Please use the Products in accordance with any applicable environmental laws and regulations, such as the RoHS Directive.
For more details, including RoHS compatibility, please contact a ROHM sales office.
ROHM shall have no responsibility for any damages or losses resulting from non-compliance with any applicable laws or regulations.
- 12) When providing our Products and technologies contained in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.
- 13) This document, in part or in whole, may not be reprinted or reproduced without prior consent of ROHM.



Electronics for the Future