




Automotive Grade N-channel SiC power MOSFET

Datasheet

V _{DSS}	650V
R _{DS(on)} (Typ.)	17mΩ
	118A
P_{D}	427W

Outline

●Inner circuit



(2)

(**3**)

(1) Gate

(2) Drain(3) Source

*Body Diode

● Features

- 1) Qualified to AEC-Q101
- 2) Low on-resistance
- 3) Fast switching speed
- 4) Fast reverse recovery
- 5) Easy to parallel
- 6) Simple to drive
- 7) Pb-free lead plating; RoHS compliant

Application

- Automobile
- Switch mode power supplies

Packaging specifications					
_	Packing	Tube			
	Reel size (mm)	-			
Typo	Tape width (mm)	-			
Туре	Basic ordering unit (pcs)	30			
	Taping code	C11			
	Marking	SCT3017AL			

● Absolute maximum ratings (T_{vj} = 25°C unless otherwise specified)

Parameter		Symbol	Value	Unit
Drain - Source Voltage		V _{DSS}	650	V
Continuous Drain current	T _c = 25°C	I _D *1	118	Α
Continuous Drain current	T _c = 100°C	I _D *1	83	Α
Pulsed Drain current (T _c = 25°C)		I _{D,pulse} *2	295	Α
Gate - Source voltage (DC)		V _{GSS}	-4 to +22	V
Gate - Source surge voltage (t _{surge} < 300nsec)		V _{GSS_surge} *3	-4 to +26	V
Recommended drive voltage		V _{GS_op} *4	0 / +18	V
Virtual Junction temperature		T _{vj}	175	°C
Range of storage temperature		T _{stg}	-55 to +175	°C

ullet Electrical characteristics ($T_{vj} = 25^{\circ}C$ unless otherwise specified)

Parameter	Cumbal	Conditions Min.		Values		
Parameter	Symbol		Min.	Тур.	Max.	Unit
		$V_{GS} = 0V$, $I_D = 1mA$				
Drain - Source breakdown voltage	$V_{(BR)DSS}$	$T_{vj} = 25^{\circ}C$	650	-	-	V
renage		T _{vj} = -55°C	650	-	-	
		$V_{GS} = 0V, V_{DS} = 650V$				
Zero Gate voltage Drain current	I _{DSS}	$T_{vj} = 25^{\circ}C$	-	1	10	μΑ
Diam ourient		T _{vj} = 150°C	-	2	-	
Gate - Source leakage current	I _{GSS+}	$V_{GS} = +22V$, $V_{DS} = 0V$	-	-	100	nA
Gate - Source leakage current	I _{GSS-}	$V_{GS} = -4V$, $V_{DS} = 0V$	-	-	-100	nA
Gate threshold voltage	V _{GS (th)}	$V_{DS} = 10V, I_{D} = 23.5 \text{mA}$	2.7		5.6	V
		$V_{GS} = 18V, I_D = 47A$				
Static Drain - Source on - state resistance	R _{DS(on)} *5	$T_{vj} = 25^{\circ}C$	-	17	22.1	mΩ
on state registance		T _{vj} = 150°C	-	25	-	
Gate input resistance	R_{G}	f = 1MHz, open drain	-	4	-	Ω


●Thermal resistance

Parameter	Symbol	Values			Unit
raianietei		Min.	Тур.	Max.	Offic
Thermal resistance, junction - case	R_{thJC}	-	0.27	0.35	K/W

●Typical Transient Thermal Characteristics

Symbol	Value	Unit
R _{th1}	6.66E-03	
R _{th2}	1.14E-01	K/W
R _{th3}	1.49E-01	

Symbol	Value	Unit
C _{th1}	1.23E-03	
C_{th2}	1.73E-02	Ws/K
C_{th3}	4.86E-02	



ullet Electrical characteristics ($T_{vj} = 25^{\circ}C$ unless otherwise specified)


Doromotor	Parameter Symbol	Conditions		Values		Unit
Parameter		Conditions	Min.	Тур.	Max.	Offit
Transconductance	g fs *5	$V_{DS} = 10V, I_{D} = 47A$	-	16	-	S
Input capacitance	C _{iss}	V _{GS} = 0V	-	2884	-	
Output capacitance	C _{oss}	V _{DS} = 500V	-	148	-	pF
Reverse transfer capacitance	C _{rss}	f = 1MHz	-	65	-	
Effective output capacitance, energy related	C _{o(er)}	$V_{GS} = 0V$ $V_{DS} = 0V \text{ to } 300V$	-	397	-	pF
Total Gate charge	Qg *5	$V_{DS} = 300V$ $I_{D} = 47A$	-	172	-	
Gate - Source charge	Q _{gs} *5	V _{GS} = 18V	-	27	-	nC
Gate - Drain charge	Q _{gd} *5	See Fig. 1-1.	-	91	-	
Turn - on delay time	t _{d(on)} *5	$V_{DS} = 300V$ $I_{D} = 18A$	-	30	-	
Rise time	t _r *5	$V_{GS} = 0V/+18V$	-	44	-	ns
Turn - off delay time	t _{d(off)} *5	$R_G = 0\Omega$ $R_L = 17\Omega$	-	64	-	115
Fall time	t _f *5	See Fig. 1-1, 1-2.	-	31	-	
Turn - on switching loss	E _{on} *5	$V_{DS} = 300V$ $V_{GS} = 0V/18V$, $I_{D} = 47A$ $R_{G} = 0\Omega$, $L = 250\mu H$	-	369	-	,, 1
Turn - off switching loss	E _{off} *5	E_{on} includes diode reverse recovery L_{σ} = 50nH, C_{σ} = 200pF See Fig. 2-1, 2-2.	-	156	-	μJ

ullet Body diode electrical characteristics (Source-Drain) ($T_{vj} = 25^{\circ}$ C unless otherwise specified)

Parameter	Symbol	Conditions		Values	Unit	
r arameter	Symbol	Conditions	Min.	Тур.	Max.	Offic
Body diode continuous, forward current	I _S *1	T _c = 25°C	1	1	118	А
Body diode direct current, pulsed	I _{SM} *2	11 _c = 23 0	ı	ı	295	А
Forward voltage	V _{SD} *5	$V_{GS} = 0V, I_{S} = 47A$	-	3.2	-	V
Reverse recovery time	t _{rr} *5	$I_F = 47A$ $V_R = 300V$	-	31	-	ns
Reverse recovery charge	Q _{rr} *5	di/dt = 1100A/µs	-	206	-	nC
Peak reverse recovery current	I _{rrm} *5	$L_{\sigma} = 50$ nH, $C_{\sigma} = 200$ pF See Fig. 3-1, 3-2.	-	13	-	Α

^{*1} Limited by maximum T_{vi} and for Max. R_{thJC} .

*3 Example of acceptable V_{GS} waveform



*5 Pulsed

^{*2} PW \leq 10 μ s, Duty cycle \leq 1%

 $^{^{*}4}$ Please be advised not to use SiC-MOSFETs with V_{GS} below 13V as doing so may cause thermal runaway.

Fig.1 Power Dissipation Derating Curve




Fig.2 Maximum Safe Operating Area





Fig.3 Typical Transient Thermal Resistance vs. Pulse Width



Pulse Width: PW [s]

Fig.4 Typical Output Characteristics(I)




Fig.5 Typical Output Characteristics(II)








Fig.6 T_{vj} = 25°C 3rd Quadrant Characteristics



Drain - Source Voltage : V_{DS} [V]










Fig.11 Typical Transfer Characteristics (I)




Fig.12 Typical Transfer Characteristics (II)




Fig.13 Gate Threshold Voltage vs. Junction Temperature






Fig.14 Transconductance vs. Drain Current





Resistance vs. Junction Temperature 0.04 $V_{GS} = 18V$ Pulsed Static Drain - Source On-State I_D= 79A $I_D = 47A$ I_D= -47A 0.00 -50 0 50 100 200 150 Junction Temperature : T_{vi} [°C]

Fig.16 Static Drain - Source On - State

Fig.17 Static Drain - Source On - State
Resistance vs. Drain Current

0.1

T_{vj} = 150°C
T_{vj} = 125°C
T_{vj} = 75°C
T_{vj} = 25°C
T_{vj} = -25°C
T_{vj} = -25°C

T_{vj} = -25°C
T_{vj} = -25°C
T_{vj} = -25°C
T_{vj} = -25°C
T_{vj} = -25°C

Voltage vs. Junction Temperature

1.04

1.03

1.02

1.04

1.02

1.04

1.00

1.01

1.00

0.99

0.98

-50

0

50

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.00

1.


ROHM

Fig.18 Normalized Drain - Source Breakdown

Fig.19 Typical Capacitance vs. Drain - Source Voltage 10000 Ciss 1000 C_{oss} Capacitance: C [pF] 100 C_{rss} 10 $T_{vi} = 25^{\circ}C$ f = 1MHz $V_{GS} = 0V$ 1 0.1 10 100 1000 Drain - Source Voltage : V_{DS} [V]

Fig.20 Coss Stored Energy 30 $T_{vi} = 25^{\circ}C$ 25 Coss Stored Energy: Eoss [µJ] 20 15 10 5 0 200 400 Drain - Source Voltage : V_{DS} [V]

Fig.21 Dynamic Input Characteristics






Fig.19 Typical Switching Time vs. Drain Current




Fig.20 Typical Switching Loss vs. Drain - Source Voltage




Fig.21 Typical Switching Loss vs. Drain Current





Fig.22 Typical Switching Loss vs. External Gate Resistance



Measurement circuits and waveforms

Fig.1-1 Gate Charge and Switching Time Measurement Circuit




Fig.2-1 Switching Energy Measurement Circuit




Fig.3-1 Reverse Recovery Time Measurement Circuit




Fig.1-2 Waveforms for Switching Time




Fig.2-2 Waveforms for Switching Energy Loss






Fig.3-2 Reverse Recovery Waveform




●Package Dimensions






Unit: mm



Unit: mm

●Die Bonding Layout





- •Front view of the packaging.
- •Dimensions are design values.
- ·If the heat sink is to be installed, it should be in contact with the die bonding point.

Unit: mm

Notes

- 1) The information contained herein is subject to change without notice.
- Before you use our Products, please contact our sales representative and verify the latest specifications.
- 3) Although ROHM is continuously working to improve product reliability and quality, semiconductors can break down and malfunction due to various factors.

 Therefore, in order to prevent personal injury or fire arising from failure, please take safety measures such as complying with the derating characteristics, implementing redundant and fire prevention designs, and utilizing backups and fail-safe procedures. ROHM shall have no responsibility for any damages arising out of the use of our Poducts beyond the rating specified by ROHM.
- 4) Examples of application circuits, circuit constants and any other information contained herein are provided only to illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.
- 5) The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM or any other parties. ROHM shall have no responsibility whatsoever for any dispute arising out of the use of such technical information.
- 6) The Products specified in this document are not designed to be radiation tolerant.
- 7) For use of our Products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a ROHM representative: transportation equipment (i.e. cars, ships, trains), primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, and power transmission systems.
- 8) Do not use our Products in applications requiring extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters.
- 9) ROHM shall have no responsibility for any damages or injury arising from non-compliance with the recommended usage conditions and specifications contained herein.
- 10) ROHM has used reasonable care to ensure the accuracy of the information contained in this document. However, ROHM does not warrants that such information is error-free, and ROHM shall have no responsibility for any damages arising from any inaccuracy or misprint of such information.
- 11) Please use the Products in accordance with any applicable environmental laws and regulations, such as the RoHS Directive. For more details, including RoHS compatibility, please contact a ROHM sales office. ROHM shall have no responsibility for any damages or losses resulting non-compliance with any applicable laws or regulations.
- 12) When providing our Products and technologies contained in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.
- 13) This document, in part or in whole, may not be reprinted or reproduced without prior consent of ROHM.



Thank you for your accessing to ROHM product informations.

More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

http://www.rohm.com/contact/

General Precaution

- 1. Before you use our Products, you are requested to carefully read this document and fully understand its contents. ROHM shall not be in any way responsible or liable for failure, malfunction or accident arising from the use of any ROHM's Products against warning, caution or note contained in this document.
- 2. All information contained in this document is current as of the issuing date and subject to change without any prior notice. Before purchasing or using ROHM's Products, please confirm the latest information with a ROHM sales representative.
- 3. The information contained in this document is provided on an "as is" basis and ROHM does not warrant that all information contained in this document is accurate and/or error-free. ROHM shall not be in any way responsible or liable for any damages, expenses or losses incurred by you or third parties resulting from inaccuracy or errors of or concerning such information.

Notice – WE Rev.001