

# **Multifunction LCD Segment Driver**

# BU97941FV MAX 104 segments (SEG26×COM4)

#### Features

- Integrated RAM for display data (DDRAM):
   26 x 4 bit (Max 104 Segments)
- LCD drive output:
  - 4 Common output, 26 Segment output
- Integrated 4ch LED driver circuit
- Support standby mode
- Integrated Power-on-Reset circuit (POR)
- Integrated Oscillator circuit
- No external component
- Low power consumption design
- Independent power supply for LCD driving

#### Applications

- Telephone
- FAX
- Portable equipment (POS, ECR, PDA etc.)
- DSC
- DVC
- Car audio
- Home electrical appliance
- Meter equipment


etc.

# ● Key Specifications

Supply Voltage Range: +1.8V to +3.6V
 LCD drive power supply Range: +2.7V to +5.5V
 Operating Temperature Range: -40°C to +85°C
 Max Segments: 104 Segments
 Display Duty: Static, 1/3, 1/4 selectable
 Bias: Static, 1/3
 Interface: 3wire serial interface

# Package

W (Typ.) x D (Typ.) x H (Max.)



# ● Typical Application Circuit




Figure 1. Typical application circuit

# ●Block Diagram / Pin Configuration / Pin Description




Figure 2. Block Diagram

Figure 3. Pin Configuration (TOP VIEW)

Table 1 Pin Description

Pin Name	Pin No.	I/O	Setting when not in use	Function			
CSB	26	I	VDD	Chip select: "L" active			
SCL	27	I	VSS	Serial data transfer clock			
SD	28	I	VSS	Input serial data			
VDD	29	-	-	Power supply for LOGIC			
VSS	25	-	-	External clock input terminal (for display/PWM using selectable) Support Hi-Z input mode at internal clock mode			
VLCD	30	-	-	GND			
COM0 to 3	31 to 34	0	OPEN	Power supply for LCD			
SEG0 to 25	1 to 20 35 to 40	0	OPEN	COMMON output for LCD			
LED1 to 4	21 to 24	0	OPEN	LED driver output			

# ● Absolute Maximum Ratings (VSS=0V)

Item	Symbol	Ratings	Unit	Remarks
Power supply Voltage1	VDD	-0.3 to +4.5	V	Power supply
Power supply Voltage2	VLCD	-0.5 to +7.0	V	Voltage for Liquid crystal Display
Power supply Voltage2	VLED	-0.5 to +7.0	V	Voltage for LED driving port terminal
Power Dissipation	Pd	0.8 <sup>*1</sup>	W	
Input Voltage Range	VIN	-0.5 to VDD+0.5	V	
Operating Temperature Range	Topr	-40 to +85	လ	
Storage Temperature Range	Tstg	-55 to +125	ပ	
Output Current	lout1	5	mA	SEG Output
	lout2	5	mA	COM Output
	lout3	50	mA	LED Output (per 1 port)

<sup>\*</sup>Decreases 8mW per 1°C when using at 1 Ta=25°C or higher. (During ROHM standard board mounting)
(Board size : 74.2mm×74.2mm×1.6mm Material : FR4 Glass-epoxy board Copper foil : Land pattern only)

# ■Recommended Operating Ratings(Ta=-40°C to +85°C,VSS=0V)

Item	Symbol	MIN	TYP	MAX	Unit	Remarks		
Power supply Voltage1	VDD	1.8	-	3.6	V	Power supply		
Power supply Voltage2	VLCD	2.7	-	5.5	V	Voltage for Liquid crystal Display		
Output Current	lout1	-	-	25	mA	LED Output (per LED1 port)		
	lout2	-	-	100	mA	LED Output (LED port current total sum)		

#### ● Electrical Characteristics

DC Characteristics (Ta=-40°C to +85°C, VDD=1.8V to 3.6V, VLCD=2.7V to 5.5V, VSS=0V)

Itam			Limit Valu			Condition	
Item	Symbol	MIN	TYP	MAX	Unit	Condition	
"H" level input voltage	VIH	0.8VDD	-	VDD	V	SD, SCL, CSB	
"L" level input voltage	VIL	VSS	-	0.2VDD	<b>V</b>	SD, SCL, CSB	
Hysteresis width	VH	-	0.2	-	V	SCL, VDD=3.3V, Ta=25°C	
"H" level input current	IIH1	-	-	5	uA	SD,SCL, CSB, VI=3.6V	
LED off leak	OFF LEAK	5	0	5	uA	LED VI=5.5V	
"H" level output voltage	VOH1	VLCD -0.4	-	-	>	Iload=-50uA, VLCD=5.0V SEG0 to SEG25	
(*2)	VOH2	VLCD -0.4	-	-	V	Iload=-50uA, VLCD=5.0V、 COM0 to COM3	
	VOL1	-	-	0.4	٧	Iload= 50uA, VLCD=5.0V、 SEG0 to SEG25	
"L" level output voltage (*2)	VOL2	-	-	0.4	V	Iload= 50uA, VLCD=5.0V, COM0 to COM3	
	VOL4	-	0.11	0.5	V	Iload=20mA、VLCD=5.0V、 LED1 to 4	
output voltage (*2)	VOUT1	2.73	3.33	3.93	V	Iload=+/-50uA, VLCD=5.0V, SEG0 to 25, COM0 to 3	
output voltage ( 2)	VOUT2	1.07	1.67	2.27	V	Iload=+/-50uA, VLCD=5.0V, SEG0 to 25, COM0 to 3	
	IstVDD	-	3	10	uA	Input pin ALL 'L', Display off, Oscillation off	
	IstVLCD	-	0.5	5	uA	Input pin ALL 'L', Display off, Oscillation off	
Supply current (*1)	IVDD1	-	8	15	uA	VDD=3.3V、Ta=25°C、 1/3bias、fFR=64Hz、Output open	
	IVLCD1	-	10	15	uA	VLCD=5.0V、Ta=25°C、 1/3bias、fFR=64Hz、Output open	

<sup>\*1</sup> During Power save mode 1. Frame inversion.

st 2 Iload:When setting the load of 1 pin only.

# ● Electrical Characteristics - continued

Oscillation Frequency Characteristics (Ta=-40°C to +85°C, VDD=1.8V to 3.6V, VLCD=2.7V to 5.5V, VSS=0V)

Item	Symbol	Limit Value			Unit	Condition		
item	Symbol	MIN	TYP	MAX	Ullit	Condition		
Frame Frequency 1	fFR1	76.5	85	93.5	Hz	VDD=3.3V、Ta=25°C、fFR=85Hz setting		
Frame Frequency 2	fFR2	68	85	97.0	Hz	VDD=2.5V to 3.6V fFR=85Hz setting		
Frame Frequency 3	fFR3	59.7	-	68	Hz	VDD=1.8V to 2.5V fFR=85Hz setting		

MPU Interface Characteristics (Ta=-40°C to +85°C, VDD=1.8V to 3.6V, VLCD=2.7V to 5.5V, VSS=0V)

Item	Cumbal		Limit Value	:	Unit	Condition
item	Symbol	MIN	TYP	MAX	Offic	Condition
Input Rise Time	tr	-	-	50	ns	
Input Fall Time	tf	1	-	50	ns	
SCL Cycle	tSCYC	250	-	-	ns	
"H" SCL pulse width	tSHW	50	-	-	ns	
"L" SCL pulse width	tSLW	50	-	-	ns	
SD Setup Time	tSDS	50	-	-	ns	
SD Hold Time	tSDH	50	-	-	ns	
CSB Setup Time	tCSS	50	-	-	ns	
CSB Hold Time	tCSH	50	-	-	ns	
"H" CSB pulse width	tCHW	50	-	-	ns	




Figure 4. Serial Interface Timing

# ●I/O equivalent circuit




Figure 5. I/O equivalent circuit

# ●Example of recommended circuit




Figure 6. Recommended circuit example

# Function Description

OCommand · Data Transfer Method

O3-SPI (3-wire Serial Interface)

This device is controlled by a 3-wire signal: CSB, SCL, SD.

First, Interface Counter is initialized with CSB="H".

Setting CSB = "L" enables SD and SCL inputs.

Each command starts with Command or data judgment bit (D/C) as MSB data,

followed by D6 to D0 (this is while CSB="L).

Internal data is latched at the rising edge of SCL, then the data is converted to an 8-bit parallel data at the falling edge of the 8th CLK.

When CSB changes from "L" to "H" and the data being transferred is less than 8 bits, command and data being transferred will be cancelled.

To start sending command again, please set CSB to "L". Then, be sure to input a 1-byte command .

Also, when DDRAM data becomes input state through RAMWR command, the device cannot accept command inputs. In order to input again, please start up CSB.

If CSB is set to "H", the data input state is cancelled and if "CSB" is set to "L" again, command will be received.





Figure 7. 3-SPI Data Transfer Format

#### O Write and Transfer Method of Display Data

This device has display data ram of 26×4=104bit.

The handling of display data with write and the handling of DDRAM data and Address and display are as follows:



Binary 8-bit data is written to DDRAM. The starting address is set with the Address set command, and is automatically incremented per 4bit data received.

Next, by transferring data, data can be written continuously to DDRAM.

(When continuously writing data to DDRAM, after writing to the final address 19h (SEG25), address will return to 00h (SEG0) through auto increment.)

						I	DDRAM	address					
		00	01	02	03	04	05	06	07	 17h	18h	19h	
	0	а	е	i	m								СОМ0
ВІТ	1	b	f	j	n								COM1
DII	2	С	g	k	0								COM2
	3	d	h	1	р								СОМ3
	•	SEG 0	SEG 1	SEG 2	SEG 3	SEG 4	SEG 5	SEG 6	SEG 7	SEG 23	SEG 24	SEG 25	-

Writing to RAM is done per 4bit. When CSB is set to 'H' and the data is less than 4 bits, the writing of RAM will be cancelled. (Transfer of command is done per 8bit.)




Figure 8. Display Data Transfer Method

# OLCD Driver Bias / Duty Circuit

Voltage is generated for LCD driver.

Buffer amplifier is integrated with low power consumption possible.

- \* Line and frame inversion can be set by MODESET command.
- \* 1/4duty, 1/3duty, and static duty can be set by DISCTL command.

For each liquid crystal display waveform, see "Liquid crystal Display Waveform".

# **OReset Initial State**

The default condition after executing Software Reset is as follows:

- · Display is turned OFF.
- · Each command register enters Reset state.
- · DDRAM address is initialized.

(DDRAM data is not initialized. Therefore, it is recommended to write initial values to all DDRAM before Display on.)

# ●Command / Function Table

**Function Description Table** 

1 dilotti	on bescription rable	
NO	Command	Function
1	Mode Set (MODESET)	Liquid crystal Display setting
2	Display control (DISCTL)	LCD setting1
3	Address set (ADSET)	LCD setting2
4	LED control (LEDCTL)	LED board ON/OFF setting
5	RAM WRITE (RAMWR)	RAM Write Start setting
6	All Pixel ON (APON)	All display ON
7	All Pixel OFF (APOFF)	All display OFF
8	All Pixel On/Off mode off (NORON)	Normal display APON/APOFF setting release)
9	Software Reset (SWRST)	Software reset

# **Command Description**

D/C (MSB) is a bit for command or data judgment.

For details, see 3-wire Serial Interface Command, Data Transfer Method.

## OMode Set Command (MODESET)

**MSB** 

LSB

	D/C	D6	D5	D4	D3	D2	D1	D0	Hex	Reset
1st byte Command	1	0	0	0	0	0	0	1	81h	-
2nd byte Command	0	0	0	0	P3	P2	P1	P0	-	00h

Display setting

Setting	P3	Reset state
Display OFF	0	0
Display ON	1	

Display OFF : Oscillation circuit operation OFF, Liquid crystal power supply circuit operation OFF with frame

cycle. Display OFF state (Output: VSS level)

Display ON : Oscillation circuit operation ON, Liquid crystal power supply circuit ON. Read operation from

DDRAM starts. Display ON state with frame cycle.

 $\boldsymbol{*}$  LED board is not affected by the ON/OFF state of Display.

The output state of LED port is determined by the setting of the LEDCTL command.

Liquid crystal Drive Waveform Setting

Setting	P2	Reset state
Frame inversion	0	0
Line inversion	1	

Power save mode (Low current consumption mode) setting

Setting	P1	P0	Reset state
Power save mode1	0	0	0
Power save mode2	0	1	
Normal mode	1	0	
High power mode	1	1	

<sup>\*</sup> Use high power mode at VLCD>3V or higher.

(Reference Current Consumption Data)

Setting	Current Consumption
Power save mode 1	×1.0
Power save mode 2	×1.7
Normal mode	×2.7
High power mode	×5.0

st The current consumption data above is reference data and changes according to panel load.

# ODisplay control command (DISCTL)

LSB

	D/C	D6	D5	D4	D3	D2	D1	D0	Hex	Reset
1st byte Command	1	0	0	0	0	0	1	0	82h	-
2nd byte Command	0	0	0	0	P3	P2	P1	P0	-	02h

**Duty setting** 

Daty cotting			
Setting	P3	P2	Reset state
1/4duty (1/3bias)	0	0	0
1/3duty (1/3bias)	0	1	
Static (1/1bias)	1	*	

(\*: Don't care)

At 1/3duty, the display / blink data for COM3 are invalid.

(COM3: same waveform with COM1)

At 1/1duty (Static), the display / blink data for COM1 to 3 are invalid.

(COM1 to 3: same waveform with COM0)

Be careful in sending display data.

For sample output waveform of SEG/COM with duty setting, see "Liquid crystal Display Waveform".

Frame Frequency Setting

Setting (When 1/4,1/3,1/1duty)	P1	P0	Reset state
(128Hz, 130Hz, 128Hz)	0	0	
(85Hz, 86hz, 64Hz)	0	1	0
(64Hz, 65Hz, 48Hz)	1	0	
(51Hz, 52Hz, 32Hz)	1	1	

The relationship with frame frequency (FR), internal osc frequency and dividing number is below:

DISCTL		Divide			FR [Hz]	
(P1,P0)	1/4duty	1/3duty	1/1duty	1/4duty	1/3duty	1/1duty
(0,0)	160	156	160	128	131.3	128
(0,1)	240	237	320	85.3	86.4	64
(1,0)	320	315	428	64	65	47.9
(1,1)	400	393	640	51.2	52.1	32

When calculating the OSC frequency from the measurement value of frame frequency, use the following equation:

Dividing number: Using the values of Frame Frequency setting (P1,P0) and duty setting(P3,P2), determine the values from the table above.

Ex) 
$$(P1,P0) = (0,1)$$
  $(P3,P2) = (0,1)$   $\Rightarrow$  Dividing number = 237

\* 1 : The value of FR in the table above is the Frame Frequency calcuated as OSC Frequency = 20.48KHz (typ).

<sup>&</sup>quot;OSC frequency = Frame Frequency (Measurement value) × Dividing number"

#### OAddress set command (ADSET)

VISF

LSB

MSB	D/C	D6	D5	D4	D3	D2	D1	D0	Hex	Reset
1st byte Command	1	0	0	0	0	0	1	1	83h	-
2nd byte Command	0	0	0	P4	P3	P2	P1	P0	-	00h

Sets the starting RAM address for normal display.

Address can be set from 00h to 1Bh.

Setting is prohibited for addresses not written above.

Address during Reset is 00h.

When writing to RAM, a separate RAM WRITE setting is needed.

# OLED control command (LEDCTL)

**MSB** 

LSB

LSB

MSB	D/C	D6	D5	D4	D3	D2	D1	D0	Hex	Reset
1st byte Command	1	0	0	0	0	1	0	1	85h	-
2nd byte Command	0	0	0	0	P3	P2	P1	P0	-	00h

Sets the driver of the LED port. Setting during Reset is 00h.

The relationship between each parameter and the Drive board is as follows:

	LED1 P0	LED2 P1	LED3 P2	LED4 P3
LED ON	1	1	1	1
LED OFF	0	0	0	0

<sup>\*</sup> Please input CSB="H" after LEDCTL command is issued.

**MSB** 

# ORAM WRITE command (RAMWR)

	D/C	D6	D5	D4	D3	D2	D1	D0	Hex	Reset
1st byte Command	1	0	1	0	0	0	0	0	A0h	-
2nd byte Command		Display data								Random
n byte Command		Display data								Random

The input data after command setting is the data input for display.

**MSB** 

Be sure to send this command after setting the ADSET command.

The display data is transferred per 4bit. (For details, see "Write and Transfer Method of Display Data.")

# OAll Pixel ON command (APON)

LSB

	D/C	D6	D5	D4	D3	D2	D1	D0	Hex	Reset
1st byte Command	1	0	0	1	0	0	0	1	91h	-

Regardless of the contents of DDRAM, the SEG output will enter all light up mode. (Pin that selects SEG output)

To avoid noise and reset interface.

# OAll Pixel OFF command (APOFF)

٠.	

LSB
-----

	D/C	D6	D5	D4	D3	D2	D1	D0	Hex	Reset
1st byte Command	1	0	0	1	0	0	0	0	90h	-

Regardless of the contents of DDRAM, the SEG output will enter all light up mode. (Pin that selects SEG output)

# OAII Pixel ON/OFF mode off (NORON)

MSB

LSB

	D/C	D6	D5	D4	D3	D2	D1	D0	Hex	Reset
1st byte Command	1	0	0	1	0	0	1	1	93h	-

APON / OFF mode is cancelled and switches to normal display mode. (Pin that selects SEG output) After reset, NORON is set and becomes normal display state.

# OSoftware Reset command (SWRST)

MSB

LSB

	D/C	D6	D5	D4	D3	D2	D1	D0	Hex	Reset
1st byte Command	1	0	0	1	0	0	1	0	92h	ı

Resets software. This IC is in reset state.

# ●Liquid crystal Drive Waveform




Figure 9. LCD Drive Waveform during Line inversion

Figure 10.LCD Drive Waveform during Frame inversion




Figure 11. LCD Drive Waveform during Line inversion

Figure 12. LCD Drive Waveform during Frame inversion




Figure 13.LCD Drive Waveform during Line inversion

Figure 14. LCD Drive Waveform during Frame inversion

# Initialization Sequence

Execute the following sequence after power supply and start display after the IC has initialized.

```
Power supply

CSB 'H' ...Initialize I/F

CSB 'L' ...Start I/F Data Transfer

Execute Software Reset from SWRST command

MODESET (Display off)

Various command setting

RAM WRITE

MODESET (Display on)

Start display
```


<sup>\*</sup> After inserting power supply, each register value, DDRAM address and DDRAM data are random prior to initialization.

#### ● Caution during Power supply ON/OFF

#### **OPOR** circuit

During power supply rise, because the IC internal circuit and reset pass through an area of unstable low voltage and VDD starts up, there is a risk that the inside of the IC is not completely reset and wrong operation might occur. In order to prevent this, P.O.R circuit and Software Reset functions are incorporated. In order to ensure that operation, do as follows during power supply rise:

- 1. Set power up conditions to meet the recommended tR, tOFF and Vbot specs below in order to ensure POR operation. (POR circuit uses VDET type)
  - (\* The voltage detection of POR differs depending on the used environment etc. In order to to assure the operation of POR, it is recommended to make Vbot = 0.5V or lower.)



 Recommended conditions of tR, tOFF, Vbot

 tR
 tOFF
 Vbot
 VDET

 10ms or lower
 1ms or higher
 0.5V or lower
 TYP 1.2V

\* VDET is integrated POR detection level

Figure 15. Rise Waveform

- 2. When the conditions are not met, do the following countermeasures after power supply ON:
  - (1) Set CSB to 'H'.
  - (2) Turn ON the CSB and execute SWRST command.

In order for the SWRST command to take effect for sure, it is recommended to start up CSB after 1ms after the VDD level has reached 90%.

\*Since the state is irregular until SWRST command input after power supply ON, countermeasure through Software Reset is not the perfect substitute for P.O.R function so it is important to be careful.




Figure 16. SWRST command sequence

# ● Power ON / OFF Sequence

To prevent incorrect display, malfunction and abnormal current, VDD must be turned on before VLCD In power up sequence. VDD must be turned off after VLCD In power down sequence. Please satisfies VLCD≥VDD, t1>0ns, t2>0ns




Figure 17. Power On/Off Sequence

# ● Attention about using LEDCTL(85h) command

Please input CSB="H" after LEDCTL command is issued. To avoid noise and reset interface.




Figure 18. Recommended sequence when using LEDCTL (85h) command

# Attention about input port pull down

Satisfy the following sequence if input terminals are pulled down by external resistors (In case MPU output Hi-Z).




Figure 19. Recommended sequence when input ports are pulled down

BU97941FV adopts a 5V tolerant I/O for the digital input. This circuit includes a bus-hold function to keep the level of HIGH. A pull down resistor of below  $10K\Omega$ shall be connected to the input terminals to transit from HIGH to LOW because the bus-hold transistor turns on during the input's HIGH level. (Refer to the Figure 5. I/O Equivalent Circuit)

A higher resistor than  $10K\Omega$  (approximate) causes input terminals being steady by intermediate potential between HIGH and LOW level so unexpected current is consumed by the system.

The potential depends on the pull down resistance and bus-hold transistor's resistance.

As the bus-hold transistor turns off upon the input level cleared to LOW a higher resistor can be used as a pull down resistor if an MPU sets SD and SCL lines to LOW before it releases the lines.

The LOW period preceding the MPU's bus release shall be at least 50ns as same as a minimum CLK width (tSLW).

#### Operational Notes

#### (1) Absolute maximum ratings

Operating the IC over the absolute maximum ratings may damage the IC. The damage can either be a short circuit between pins or an open circuit between pins. Therefore, it is important to consider circuit protection measures, such as adding a fuse, in case the IC is operated over the absolute maximum ratings.

#### (2) Recommended operating conditions

These conditions represent a range within which the expected characteristics of the IC can be approximately obtained. The electrical characteristics are guaranteed under the conditions of each parameter.

# (3) Reverse connection of power supply

Connecting the power supply in reverse polarity can damage the IC. Take precautions against reverse polarity when connecting the power supply, such as mounting an external diode between the power supply and the IC's power supply terminals.

#### (4) Power supply lines

Design the PCB layout pattern to provide low impedance ground and supply lines. Separate the ground and supply lines of the digital and analog blocks to prevent noise in the ground and supply lines of the digital block from affecting the analog block. Furthermore, connect a capacitor to ground at all power supply pins. Consider the effect of temperature and aging on the capacitance value when using electrolytic capacitors.

#### (5) Ground Voltage

The voltage of the ground pin must be the lowest voltage of all pins of the IC at all operating conditions. Ensure that no pins are at a voltage below the ground pin at any time, even during transient condition.

#### (6) Short between pins and mounting errors

Be careful when mounting the IC on printed circuit boards. The IC may be damaged if it is mounted in a wrong orientation or if pins are shorted together. Short circuit may be caused by conductive particles caught between the pins.

#### (7) Operation under strong electromagnetic field

Operating the IC in the presence of a strong electromagnetic field may cause the IC to malfunction.

## (8) Testing on application boards

When testing the IC on an application board, connecting a capacitor directly to a low-impedance output pin may subject the IC to stress. Always discharge capacitors completely after each process or step. The IC's power supply should always be turned off completely before connecting or removing it from the test setup during the inspection process. To prevent damage from static discharge, ground the IC during assembly and use similar precautions during transport and storage.

#### (9) Regarding input pins of the IC

In the construction of this IC, P-N junctions are inevitably formed creating parasitic diodes or transistors. The operation of these parasitic elements can result in mutual interference among circuits, operational faults, or physical damage. Therefore, conditions which cause these parasitic elements to operate, such as applying a voltage to an input pin lower than the GND voltage should be avoided. Furthermore, do not apply a voltage to the input terminals when no power supply voltage is applied to the IC. Even if the power supply voltage is applied, make sure that the input terminals have voltages within the values specified in the electrical characteristics of this IC.

# (10) GND wiring pattern

When using both small-signal and large-current GND traces, the two ground traces should be routed separately but connected to a single ground at the reference point of the application board to avoid fluctuations in the small-signal ground caused by large currents. Also ensure that the GND traces of external components do not cause variations on the GND voltage. The power supply and ground lines must be as short and thick as possible to reduce line impedance.

#### (11) External Capacitor


When using a ceramic capacitor, determine the dielectric constant considering the change of capacitance with temperature and the decrease in nominal capacitance due to DC bias and others.

#### (12) Unused input terminals


Input terminals of an IC are often connected to the gate of a CMOS transistor. The gate has extremely high impedance and extremely low capacitance. If left unconnected, the electric field from the outside can easily charge it. The small charge acquired in this way is enough to produce a significant effect on the conduction through the transistor and cause unexpected operation of IC. So unless otherwise specified, input terminals not being used should be connected to the power supply or ground line.

# (13) Rush current


When power is first supplied to the IC, rush current may flow instantaneously. It is possible that the charge current to the parasitic capacitance of internal photo diode or the internal logic may be unstable. Therefore, give special consideration to power coupling capacitance, power wiring, width of GND wiring, and routing of connections.



# Marking Diagram



# ●Physical Dimension, Tape and Reel Information



# Revision History

Date	Revision	Changes					
14.Mar.2012	001	New Release					
8.Jan.2013	002	Improved the statement in all pages. Deleted "Status of this document" in page 20. Changed format of Physical Dimension, Tape and Reel Information					
26.Jan.2015	003	Add the condition when power supply in page 18.					
10.Apr.2015	004	Modified figure of Power On/Off Sequence in page 18.					

# **Notice**

#### **Precaution on using ROHM Products**

Our Products are designed and manufactured for application in ordinary electronic equipments (such as AV equipment, OA equipment, telecommunication equipment, home electronic appliances, amusement equipment, etc.). If you intend to use our Products in devices requiring extremely high reliability (such as medical equipment (Note 1), transport equipment, traffic equipment, aircraft/spacecraft, nuclear power controllers, fuel controllers, car equipment including car accessories, safety devices, etc.) and whose malfunction or failure may cause loss of human life, bodily injury or serious damage to property ("Specific Applications"), please consult with the ROHM sales representative in advance. Unless otherwise agreed in writing by ROHM in advance, ROHM shall not be in any way responsible or liable for any damages, expenses or losses incurred by you or third parties arising from the use of any ROHM's Products for Specific Applications.

(Note1) Medical Equipment Classification of the Specific Applications

JAPAN	USA	EU	CHINA		
CLASSⅢ	CLASSⅢ	CLASS II b	CL ACCTI		
CLASSIV	CLASSIII	CLASSⅢ	CLASSⅢ		

- 2. ROHM designs and manufactures its Products subject to strict quality control system. However, semiconductor products can fail or malfunction at a certain rate. Please be sure to implement, at your own responsibilities, adequate safety measures including but not limited to fail-safe design against the physical injury, damage to any property, which a failure or malfunction of our Products may cause. The following are examples of safety measures:
  - [a] Installation of protection circuits or other protective devices to improve system safety
  - [b] Installation of redundant circuits to reduce the impact of single or multiple circuit failure
- 3. Our Products are designed and manufactured for use under standard conditions and not under any special or extraordinary environments or conditions, as exemplified below. Accordingly, ROHM shall not be in any way responsible or liable for any damages, expenses or losses arising from the use of any ROHM's Products under any special or extraordinary environments or conditions. If you intend to use our Products under any special or extraordinary environments or conditions (as exemplified below), your independent verification and confirmation of product performance, reliability, etc, prior to use, must be necessary:
  - [a] Use of our Products in any types of liquid, including water, oils, chemicals, and organic solvents
  - [b] Use of our Products outdoors or in places where the Products are exposed to direct sunlight or dust
  - [c] Use of our Products in places where the Products are exposed to sea wind or corrosive gases, including Cl<sub>2</sub>, H<sub>2</sub>S, NH<sub>3</sub>, SO<sub>2</sub>, and NO<sub>2</sub>
  - [d] Use of our Products in places where the Products are exposed to static electricity or electromagnetic waves
  - [e] Use of our Products in proximity to heat-producing components, plastic cords, or other flammable items
  - [f] Sealing or coating our Products with resin or other coating materials
  - [g] Use of our Products without cleaning residue of flux (even if you use no-clean type fluxes, cleaning residue of flux is recommended); or Washing our Products by using water or water-soluble cleaning agents for cleaning residue after soldering
  - [h] Use of the Products in places subject to dew condensation
- 4. The Products are not subject to radiation-proof design.
- 5. Please verify and confirm characteristics of the final or mounted products in using the Products.
- 6. In particular, if a transient load (a large amount of load applied in a short period of time, such as pulse. is applied, confirmation of performance characteristics after on-board mounting is strongly recommended. Avoid applying power exceeding normal rated power; exceeding the power rating under steady-state loading condition may negatively affect product performance and reliability.
- 7. De-rate Power Dissipation (Pd) depending on Ambient temperature (Ta). When used in sealed area, confirm the actual ambient temperature.
- 8. Confirm that operation temperature is within the specified range described in the product specification.
- 9. ROHM shall not be in any way responsible or liable for failure induced under deviant condition from what is defined in this document.

#### Precaution for Mounting / Circuit board design

- 1. When a highly active halogenous (chlorine, bromine, etc.) flux is used, the residue of flux may negatively affect product performance and reliability.
- 2. In principle, the reflow soldering method must be used on a surface-mount products, the flow soldering method must be used on a through hole mount products. If the flow soldering method is preferred on a surface-mount products, please consult with the ROHM representative in advance.

For details, please refer to ROHM Mounting specification

#### **Precautions Regarding Application Examples and External Circuits**

- 1. If change is made to the constant of an external circuit, please allow a sufficient margin considering variations of the characteristics of the Products and external components, including transient characteristics, as well as static characteristics.
- 2. You agree that application notes, reference designs, and associated data and information contained in this document are presented only as guidance for Products use. Therefore, in case you use such information, you are solely responsible for it and you must exercise your own independent verification and judgment in the use of such information contained in this document. ROHM shall not be in any way responsible or liable for any damages, expenses or losses incurred by you or third parties arising from the use of such information.

#### **Precaution for Electrostatic**

This Product is electrostatic sensitive product, which may be damaged due to electrostatic discharge. Please take proper caution in your manufacturing process and storage so that voltage exceeding the Products maximum rating will not be applied to Products. Please take special care under dry condition (e.g. Grounding of human body / equipment / solder iron, isolation from charged objects, setting of lonizer, friction prevention and temperature / humidity control).

# **Precaution for Storage / Transportation**

- 1. Product performance and soldered connections may deteriorate if the Products are stored in the places where:
  - [a] the Products are exposed to sea winds or corrosive gases, including Cl2, H2S, NH3, SO2, and NO2
  - [b] the temperature or humidity exceeds those recommended by ROHM
  - [c] the Products are exposed to direct sunshine or condensation
  - [d] the Products are exposed to high Electrostatic
- 2. Even under ROHM recommended storage condition, solderability of products out of recommended storage time period may be degraded. It is strongly recommended to confirm solderability before using Products of which storage time is exceeding the recommended storage time period.
- 3. Store / transport cartons in the correct direction, which is indicated on a carton with a symbol. Otherwise bent leads may occur due to excessive stress applied when dropping of a carton.
- 4. Use Products within the specified time after opening a humidity barrier bag. Baking is required before using Products of which storage time is exceeding the recommended storage time period.

## **Precaution for Product Label**

QR code printed on ROHM Products label is for ROHM's internal use only.

#### **Precaution for Disposition**

When disposing Products please dispose them properly using an authorized industry waste company.

#### **Precaution for Foreign Exchange and Foreign Trade act**

Since concerned goods might be fallen under listed items of export control prescribed by Foreign exchange and Foreign trade act, please consult with ROHM in case of export.

#### **Precaution Regarding Intellectual Property Rights**

- 1. All information and data including but not limited to application example contained in this document is for reference only. ROHM does not warrant that foregoing information or data will not infringe any intellectual property rights or any other rights of any third party regarding such information or data.
- 2. ROHM shall not have any obligations where the claims, actions or demands arising from the combination of the Products with other articles such as components, circuits, systems or external equipment (including software).
- 3. No license, expressly or implied, is granted hereby under any intellectual property rights or other rights of ROHM or any third parties with respect to the Products or the information contained in this document. Provided, however, that ROHM will not assert its intellectual property rights or other rights against you or your customers to the extent necessary to manufacture or sell products containing the Products, subject to the terms and conditions herein.

#### **Other Precaution**

- 1. This document may not be reprinted or reproduced, in whole or in part, without prior written consent of ROHM.
- 2. The Products may not be disassembled, converted, modified, reproduced or otherwise changed without prior written consent of ROHM.
- In no event shall you use in any way whatsoever the Products and the related technical information contained in the Products or this document for any military purposes, including but not limited to, the development of mass-destruction weapons.
- 4. The proper names of companies or products described in this document are trademarks or registered trademarks of ROHM, its affiliated companies or third parties.

Notice-PGA-E Rev.001

#### **General Precaution**

- 1. Before you use our Products, you are requested to care fully read this document and fully understand its contents. ROHM shall not be in any way responsible or liable for failure, malfunction or accident arising from the use of a ny ROHM's Products against warning, caution or note contained in this document.
- 2. All information contained in this docume nt is current as of the issuing date and subject to change without any prior notice. Before purchasing or using ROHM's Products, please confirm the latest information with a ROHM sale s representative.
- 3. The information contained in this doc ument is provided on an "as is" basis and ROHM does not warrant that all information contained in this document is accurate an d/or error-free. ROHM shall not be in an y way responsible or liable for any damages, expenses or losses incurred by you or third parties resulting from inaccuracy or errors of or concerning such information.

**Notice – WE** © 2015 ROHM Co., Ltd. All rights reserved. Rev.001