

ROHM

Serial EEPROM Series Standard EEPROM I²C BUS EEPROM (2-Wire) BR24T16-W


General Description

BR24T16-W is a serial EEPROM of I²C BUS Interface Method

Features

- Completely conforming to the world standard I²C BUS.
 All controls queilable by 2 parts of corrispondence.
 - All controls available by 2 ports of serial clock (SCL) and serial data (SDA)
- Other devices than EEPROM can be connected to the same port, saving microcontroller port
- 1.6V to 5.5V Single Power Source Operation most suitable for battery use
- 1.6V to 5.5V wide limit of operating voltage, possible FAST MODE 400KHz operation
- Page Write Mode useful for initial value write at factory shipment
- Self-timed Programming Cycle
- Low Current Consumption
- Prevention of Write Mistake
 - WP (Write Protect) Function added
 - Prevention of Write Mistake at Low Voltage
- More than 1 million write cycles
- More than 40 years data retention
- Noise filter built in SCL / SDA terminal
- Initial delivery state FFh

BR24T16-W



SSOP-B8 3.00mm x 6.40mm x 1.35mm

Figure 1.

2.00mm x 3.00mm x 0.60mm

Capacity	Bit Format	Туре	Power Source Voltage	Package	
		BR24T16-W		DIP-T8 ⁽¹⁾	
		BR24T16-WZ	-	DIP8K	
		BR24T16F-W	-	SOP8	
		BR24T16FJ-W	-	SOP-J8	
	214.0	BR24T16FJ-WSGN	1.6V to 5.5V	SOP-J8A	
16Kbit	2K×8	BR24T16FV-W		SSOP-B8	
		BR24T16FVT-W		TSSOP-B8	
		BR24T16FVJ-W		TSSOP-B8J	
		BR24T16FVM-W	-	MSOP8	
		BR24T16NUX-W		VSON008X2030	

(1) Not Recommended for New Designs. Recommend BR24T16-WZ.

OProduct structure : Silicon monolithic integrated circuit OThis product has no designed protection against radioactive rays

Absolute Maximum Ratings (Ta=25°C)

Parameter	Symbol	Rating	Unit	Remark
Supply Voltage	Vcc	-0.3 to +6.5	V	
		450 (SOP8)		Derate by 4.5mW/°C when operating above Ta=25°C
		450 (SOP-J8)		Derate by 4.5mW/°C when operating above Ta=25°C
		450 (SOP-J8A)		Derate by 4.5mW/°C when operating above Ta=25°C
		300 (SSOP-B8)	-	Derate by 3.0mW/°C when operating above Ta=25°C
		330 (TSSOP-B8)	-	Derate by 3.3mW/°C when operating above Ta=25°C
Power Dissipation	Pd	310 (TSSOP-B8J)	mW	Derate by 3.1mW/°C when operating above Ta=25°C
		310 (MSOP8)	_	Derate by 3.1mW/°C when operating above Ta=25°C
	-	300 (VSON008X2030)		Derate by 3.0mW/°C when operating above Ta=25°C
	-	800 (DIP-T8 ⁽¹⁾)		Derate by 8.0mW/°C when operating above Ta=25°C
		852 (DIP8K)	-	Derate by 8.52mW/°C when operating above Ta=25°C When mounted (on 114.5 mm × 101.5 mm × 1.6 mm thick, glass epoxy on single-layer substrate).
Storage Temperature	Tstg	-65 to +150	°C	
Operating Temperature	Topr	-40 to +85	°C	
Input Voltage / Output Voltage	-	-0.3 to Vcc+1.0	V	The Max value of input voltage / output voltage is not over 6.5V. When the pulse width is 50ns or less, the Min value of input voltage / output voltage is not lower than -1.0V.
Junction Temperature	Tjmax	150	°C	Junction temperature at the storage condition
Electrostatic discharge voltage (human body model)	VESD	-4000 to +4000	V	

(1) Not Recommended for New Designs. Recommend BR24T16-WZ.

Memory Cell Characteristics (Ta=25°C, Vcc=1.6V to 5.5V)

Parameter	Limit					
Farameter	Min	Тур	Max	Unit		
Write Cycles ⁽¹⁾	1,000,000	-	-	Times		
Data Retention ⁽¹⁾	40	-	-	Years		
(1) N. (1000) TEOTED						

(1) Not 100% TESTED

Recommended Operating Ratings

Parameter	Symbol	Rating	Unit
Power Source Voltage	Vcc	1.6 to 5.5	V
Input Voltage	VIN	0 to Vcc	v

DC Characteristics (Unless otherwise specified, Ta=-40°C to +85°C, Vcc=1.6V to 5.5V)

Parameter	Symbol		Limit		Unit	Conditions		
Parameter	Symbol	Min	Тур	Max	Unit	Conditions		
Input High Voltage1	V _{IH1}	0.7Vcc	-	Vcc+1.0	V	1.7V≤Vcc≤5.5V		
Input Low Voltage1	VIL1	-0.3(2)	-	+0.3Vcc	V	1.7V≤Vcc≤5.5V		
Input High Voltage2	VIH2	0.8Vcc	-	Vcc+1.0	V	1.6V≤Vcc<1.7V		
Input Low Voltage2	VIL2	-0.3(2)	-	+0.2Vcc	V	1.6V≤Vcc<1.7V		
Output Low Voltage1	V _{OL1}	-	-	0.4	V	I _{OL} =3.0mA, 2.5V≤Vcc≤5.5V (SDA)		
Output Low Voltage2	V _{OL2}	-	-	0.2	V	I _{OL} =0.7mA, 1.6V≤Vcc<2.5V (SDA)		
Input Leakage Current	ILI	-1	-	1	μA	V _{IN} =0 to Vcc		
Output Leakage Current	ILO	-1	-	1	μA	V _{OUT} =0 to Vcc (SDA)		
Supply Current (Write)	I _{CC1}	-	-	2.0	mA	Vcc=5.5V, f _{SCL} =400kHz, t _{WR} =5ms, Byte write, Page write		
Supply Current (Read)	I _{CC2}	-	-	0.5	mA	Vcc=5.5V, f _{SCL} =400kHz Random read, current read, sequential read		
Standby Current	I _{SB}	-	-	2.0	μA	Vcc=5.5V, SDA,SCL=Vcc A0,A1,A2=GND,WP=GND		

(2) When the pulse width is 50ns or less, it is -1.0V.

AC Characteristics (Unless otherwise specified, Ta=-40°C to +85°C, Vcc=1.6V to 5.5V)
---	---

Deventer	Currence of		1.1		
Parameter	Symbol	Min	Тур	Max	- Unit
Clock Frequency	fscl	-	-	400	kHz
Data Clock High Period	tніgн	0.6	-	-	μs
Data Clock Low Period	tLow	1.2	-	-	μs
SDA,SCL(INPUT) Rise Time ⁽¹⁾	t _R	-	-	1.0	μs
SDA,SCL (INPUT)Fall Time (1)	t _{F1}	-	-	1.0	μs
SDA(OUTPUT)Fall Time ⁽¹⁾	t _{F2}	-	-	0.3	μs
Start Condition Hold Time	thd:sta	0.6	-	-	μs
Start Condition Setup Time	tsu:sta	0.6	-	-	μs
Input Data Hold Time	thd:dat	0	-	-	ns
Input Data Setup Time	tsu:dat	100	-	-	ns
Output Data Delay Time	t _{PD}	0.1	-	0.9	μs
Output Data Hold Time	t _{DH}	0.1	-	-	μs
Stop Condition Setup Time	t _{SU:STO}	0.6	-	-	μs
Bus Free Time	tBUF	1.2	-	-	μs
Write Cycle Time	twr	-	-	5	ms
Noise Spike Width (SDA and SCL)	tı	-	-	0.1	μs
WP Hold Time	thd:wp	1.0	-	-	μs
WP Setup Time	t _{su:wp}	0.1	-	-	μs
WP High Period	thigh:wp	1.0	-	-	μs


(1) Not 100% TESTED.

Condition Input Data Level:VIL=0.2×Vcc VIH=0.8×Vcc

Input Data Timing Reference Level: 0.3×Vcc/0.7×Vcc

Output Data Timing Reference Level: 0.3×Vcc/0.7×Vcc Rise/Fall Time : ≤20ns

Serial Input / Output Timing



OInput read at the rise edge of SCL OData output in sync with the fall of SCL

Figure 2-(a). Serial Input / Output Timing




Figure 2-(b). Start-Stop Bit Timing




Figure 2-(c). Write Cycle Timing




Figure 2-(d). WP Timing at Write Execution




Figure 2-(e). WP Timing at Write Cancel

Block Diagram





Figure 3. Block Diagram


Pin Configuration



Pin Descriptions

Terminal Name	Input/ Output	Descriptions
A0	-	Don't use ⁽¹⁾
A1	-	Don't use ⁽¹⁾
A2	-	Don't use ⁽¹⁾
GND	-	Reference voltage of all input / output, 0V
SDA	Input/ Output	Serial data input serial data output
SCL	Input	Serial clock input
WP	Input	Write protect terminal
VCC	-	Connect the power source.

(1) Pins not used as device address may be set to any of 'H', 'L', and 'Hi-Z'.






Figure 7. Output Low Voltage2 vs Output Low Current (Vcc=1.6V)




Figure 10. Supply Current (Write) vs Supply Voltage Figure 10. Supply Voltage Figure 10. Supply Current (Write) vs Supply Voltage Figure 10. Supply

Figure 11. Supply Current (Read) vs Supply Voltage $(f_{SCL}=400 \text{kHz})$

6/36




Figure 12. Standby Current vs Supply Voltage

Figure 13. Clock Frequency vs Supply Voltage





Figure 14. Data Clock High Period vs Supply Voltage



5

6




Figure 16. Start Condition Hold Time vs Supply Voltage

Figure 17. Start Condition Setup Time vs Supply Voltage





Figure 18. Input Data Hold Time vs Supply Voltage (HIGH)






Figure 22. 'L' Output Data Delay Time vs Supply Voltage

Figure 23. 'H' Output Data Delay Time vs Supply Voltage




Figure 24. Stop Condition Setup Time vs Supply Voltage

Figure 25. Bus Free Time vs Supply Voltage








Figure 27. Noise Spike Width vs Supply Voltage (SCL H)













Figure 33. WP High Period vs Supply Voltage

Timing Chart

1. I²C BUS Data Communication

I²C BUS data communication starts by start condition input, and ends by stop condition input. Data is always 8bit long, and acknowledge is always required after each byte. I²C BUS data communication with several devices is possible by connecting with 2 communication lines: serial data (SDA) and serial clock (SCL).

Among the devices, there should be a "master" that generates clock and control communication start and end. The rest become "slave" which are controlled by an address peculiar to each device, like this EEPROM. The device that outputs data to the bus during data communication is called "transmitter", and the device that receives data is called "receiver"..



2. Start Condition (Start Bit Recognition)

- (1) Before executing each command, start condition (start bit) where SDA goes from 'HIGH' down to 'LOW' when SCL is 'HIGH' is necessary.
- (2) This IC always detects whether SDA and SCL are in start condition (start bit) or not, therefore, unless this condition is satisfied, any command cannot be executed.

3. Stop Condition (Stop Bit Recognition)

(1) Each command can be ended by a stop condition (stop bit) where SDA goes from 'LOW' to 'HIGH' while SCL is 'HIGH'.

4. Acknowledge (ACK) Signal

- (1) The acknowledge (ACK) signal is a software rule to show whether data transfer has been made normally or not. In a master-slave communication, the device (Ex. μ-COM sends slave address input for write or read command, to this IC) at the transmitter (sending) side releases the bus after output of 8bit data.
- (2) The device (Ex. This IC receives the slave address input for write or read command from the μ-COM) at the receiver (receiving) side sets SDA 'LOW' during the 9th clock cycle, and outputs acknowledge signal (ACK signal) showing that it has received the 8bit data.
- (3) This IC, after recognizing start condition and slave address (8bit), outputs acknowledge signal (ACK signal) 'LOW'.
- (4) After receiving 8bit data (word address and write data) during each write operation, this IC outputs acknowledge signal (ACK signal) 'LOW'.
- (5) During read operation, this IC outputs 8bit data (read data) and detects acknowledge signal (ACK signal) 'LOW'. When acknowledge signal (ACK signal) is detected, and stop condition is not sent from the master (μ-COM) side, this IC continues to output data. When acknowledge signal (ACK signal) is not detected, this IC stops data transfer, recognizes stop condition (stop bit), and ends read operation. Then this IC becomes ready for another transmission.

5. Device Addressing

- (1) Slave address comes after start condition from master.
- (2) The significant 4 bits of slave address are used for recognizing a device type.
- The device code of this IC is fixed to '1010'. (3) The most insignificant bit (R/W --- READ / WRITE) of slave address is used for designating write or read operation,
- and is as shown below.

Setting R/\overline{W} to 0 ------ write (setting 0 to word address setting of random read) Setting R/\overline{W} to 1 ------ read

I	Slave Address								Maximum Number of Connected Buses				
	1	0	1	0	P2	P1	P0	R/W	1				

P0 to P2 are page select bits.

Write Command

- 1. Write Cycle
 - (1) Arbitrary data can be written to this EEPROM. When writing only 1 byte, Byte Write is normally used, and when writing continuous data of 2 bytes or more, simultaneous write is possible by Page Write cycle. The maximum number of bytes is specified per device of each capacity. Up to 8 arbitrary bytes can be written.




Figure 35. Byte Write Cycle





Figure 36. Page Write Cycle

- (2) During internal write execution, all input commands are ignored, therefore ACK is not returned.
- (3) Data is written to the address designated by word address (n-th address)
- (4) By issuing stop bit after 8bit data input, internal write to memory cell starts.
- (5) When internal write is started, command is not accepted for t_{WR} (5ms at maximum).
- (6) Using page write cycle, writing in bulk is done as follows: When data of more than 16 bytes is sent, the bytes in excess overwrite the data already sent first.
 (Before to "Intermed Address Incompatible")
 - (Refer to "Internal Address Increment")
- (7) As for page write cycle of BR24T16-W, where 2 or more bytes of data is intended to be written, after the page select bits 'P0', 'P1', and 'P2' of slave address are designated arbitrarily, only the value of 4 least significant bits in the address is incremented internally, so that data up to 16 bytes of memory only can be written.

In the case BR24T16-W, 1 page=16bytes, but the page write cycle time is 5ms at maximum for 16byte bulk write. It does not stand 5ms at maximum x 16byte=80ms(Max)

2. Internal Address Increment

Page write mode (in the case of BR24T16-W)



For example, when it is started from address 0Eh, then, increment is made as below, $0Eh\rightarrow 0Fh\rightarrow 00h\rightarrow 01h\cdots$. Please take note.

*0Eh…0E in hexadecimal, therefore, 00001110 is a binary number.

3. Write Protect (WP) Terminal

Write Protect (WP) Function

When WP terminal is set at Vcc (H level), data rewrite of all addresses is prohibited. When it is set at GND (L level), data rewrite of all address is enabled. Be sure to connect this terminal to Vcc or GND, or control it to H level or L level. Do not leave it open.

In case of using it as ROM, it is recommended to connect it to pull up or Vcc.

At extremely low voltage at power ON / OFF, by setting the WP terminal 'H', write error can be prevented.

Read Command

1. Read Cycle

Read cycle is when data of EEPROM is read. Read cycle could be random read cycle or current read cycle. Random read cycle is a command to read data by designating a specific address, and is used generally. Current read cycle is a command to read data of internal address register without designating an address, and is used when to verify just after write cycle. In both the read cycles, sequential read cycle is available where the next address data can be read in succession.




Figure 37. Random Read Cycle




Figure 38. Current Read Cycle




Figure 39. Sequential Read Cycle (in the case of current read cycle)

- (1) In random read cycle, data of designated word address can be read.
- (2) When the command just before current read cycle is random read cycle, current read cycle (each including sequential read cycle), data of incremented last read address (n)-th, i.e., data of the (n+1)-th address is output.
- (3) When ACK signal 'LOW' after D0 is detected, and stop condition is not sent from master (μ-COM) side, the next address data can be read in succession.
- (4) Read cycle is ended by stop condition where 'H' is input to ACK signal after D0 and SDA signal goes from 'L' to 'H' while SCL signal is 'H'.
- (5) When 'H' is not input to ACK signal after D0, sequential read gets in, and the next data is output. Therefore, read command cycle cannot be ended. To end read command cycle, be sure to input 'H' to ACK signal after D0, and the stop condition where SDA goes from 'L' to 'H' while SCL signal is 'H'.
- (6) Sequential read is ended by stop condition where 'H' is input to ACK signal after arbitrary D0 and SDA is asserted from 'L' to 'H' while SCL signal is 'H'.

Software Reset

Software reset is executed to avoid malfunction after power on and during command input. Software reset has several kinds and 3 kinds of them are shown in the figure below. (Refer to Figure 40-(a), Figure 40-(b), and Figure 40-(c).) Within the dummy clock input area, the SDA bus is released ('H' by pull up) and ACK output and read data '0' (both 'L' level) may be output from EEPROM. Therefore, if 'H' is input forcibly, output may conflict and over current may flow, leading to instantaneous power failure of system power source or influence upon devices.






Figure 40-(a). The Case of Dummy Clock×14 + START+START+ Command Input







*Start command from START input.

Acknowledge Polling

During internal write execution, all input commands are ignored, therefore ACK is not returned. During internal automatic write execution after write cycle input, next command (slave address) is sent. If the first ACK signal sends back 'L', then it means end of write operation, else 'H' is returned, which means writing is still in progress. By the use of acknowledge polling, next command can be executed without waiting for $t_{WR} = 5$ ms.

To write continuously, $R/\overline{W} = 0$, then to carry out current read cycle after write, slave address with $R/\overline{W} = 1$ is sent. If ACK signal sends back 'L', and then execute word address input and data output and so forth..




Figure 41. Case of Continuous Write by Acknowledge Polling

WP Valid Timing (Write Cancel)

WP is usually fixed to 'H' or 'L', but when WP is used to cancel write cycle and so on, pay attention to the following WP valid timing. During write cycle execution, inside cancel valid area, by setting WP='H', write cycle can be cancelled. In both byte write cycle and page write cycle, the area from the first start condition of command to the rise of clock to take in D0 of data(in page write cycle, the first byte data) is the cancel invalid area.

WP input in this area becomes 'Don't care'. The area from the rise of SCL to take in D0 to the stop condition input is the cancel valid area. Furthermore, after the execution of forced end by WP, the IC enters standby status.




Figure 42. WP Valid Timing

Command Cancel by Start Condition and Stop Condition

During command input, by continuously inputting start condition and stop condition, command can be cancelled. (Figure 43.) However, within ACK output area and during data read, SDA bus may output 'L'. In this case, start condition and stop condition cannot be input, so reset is not available. Therefore, execute software reset. When command is cancelled by start-stop condition during random read cycle, sequential read cycle, or current read cycle, internal setting address is not determined. Therefore, it is not possible to carry out current read cycle in succession. To carry out read cycle in succession, carry out random read cycle.




Figure 43. Case of Cancel by Start, Stop Condition during Slave Address Input

I/O Peripheral Circuit

1. Pull-up Resistance of SDA Terminal

SDA is NMOS open drain, so it requires a pull up resistor. As for this resistance value (R_{PU}), select an appropriate value from microcontroller V_{IL} , I_L , and V_{OL} - I_{OL} characteristics of this IC. If R_{PU} is large, operating frequency is limited. The smaller the R_{PU} , the larger is the supply current (Read).

2. Maximum Value of RPU

The maximum value of RPU is determined by the following factors.

- (1) SDA rise time to be determined by the capacitance (C_{BUS}) of bus line and R_{PU} of SDA should be t_R or lower. Furthermore, AC timing should be satisfied even when SDA rise time is slow.
- (2) The bus. electric potential (2) to be determined by the input current leak total (I_L) of device connected to bus at output of 'H' to the SDA line and R_{PU} should sufficiently secure the input 'H' level (V_{IH}) of microcontroller and EEPROM including recommended noise margin of 0.2Vcc.

Vcc - I_LR_{PU} - 0.2 Vcc ≥ ViH




Figure 44. I/O Circuit Diagram

3. Minimum Value of RPU

- The minimum value of R_{PU} is determined by the following factors.
- (1) When IC outputs LOW, it should be satisfied that $V_{OLMAX}=0.4V$ and $I_{OLMAX}=3mA$.

$$\frac{V_{CC} - V_{OL}}{R_{PU}} \le I_{OL}$$

$$R_{PU} \ge \frac{V_{CC} - V_{OL}}{I_{OL}}$$

(2) VOLMAX=0.4V should secure the input 'L' level (VIL) of microcontroller and EEPROM including recommended noise margin 0.1Vcc.

Volmax ≤ VIL - 0.1 Vcc

Ex.) Vcc =3V, VoL=0.4V, IoL=3mA, microcontroller, EEPROM VIL=0.3Vcc

from (1)

$$R_{PU} \ge \frac{3 - 0.4}{3 \times 10^{-3}}$$

$$\ge 867 \ [\Omega]$$
And $V_{OL} = 0.4 \ [V]$
 $V_{IL} = 0.3 \times 3$
 $= 0.9 \ [V]$

Therefore, the condition (2) is satisfied.


3. Pull-up Resistance of SCL Terminal

When SCL control is made at the CMOS output port, there is no need for a pull up resistor. But when there is a time where SCL becomes 'Hi-Z', add a pull up resistor. As for the pull up resistor value, one of several k Ω to several ten k Ω is recommended in consideration of drive performance of output port of microcontroller.

Cautions on Microcontroller Connection

1. Rs

In I²C BUS, it is recommended that SDA port is of open drain input/output. However, when using CMOS input / output of tri state to SDA port, insert a series resistance R_S between the pull up resistor R_{PU} and the SDA terminal of EEPROM. This is to control over current that may occur when PMOS of the microcontroller and NMOS of EEPROM are turned ON simultaneously. R_S also plays the role of protecting the SDA terminal against surge. Therefore, even when SDA port is open drain input/output, R_S can be used.



2. Maximum Value of Rs

The maximum value of R_{S} is determined by the following relations.

- (1) SDA rise time to be determined by the capacitance (C_{BUS}) of bus line and R_{PU} of SDA should be t_R or lower. Furthermore, AC timing should be satisfied even when SDA rise time is slow.
- (2) The bus' electric potential A to be determined by R_{PU} and R_S the moment when EEPROM outputs 'L' to SDA bus should sufficiently secure the input 'L' level (V_{IL}) of microcontroller including recommended noise margin of 0.1Vcc.




Figure 47. I/O Circuit Diagram

 $\frac{(\text{Vcc} - \text{V}_{\text{OL}}) \times \text{R}_{\text{S}}}{\text{R}_{\text{PU}} + \text{R}_{\text{S}}} + \text{VoL} + 0.1 \text{Vcc} \le \text{V}_{\text{IL}}$ $\therefore \text{R}_{\text{S}} \le \frac{\text{V}_{\text{IL}} - \text{V}_{\text{OL}} - 0.1 \text{Vcc}}{1.1 \text{Vcc} - \text{V}_{\text{IL}}} \times \text{R}_{\text{PU}}$ $\text{Ex})\text{Vcc} = 3\text{V} \text{V}_{\text{IL}} = 0.3 \text{Vcc} \text{V}_{\text{OL}} = 0.4 \text{V} \text{R}_{\text{PU}} = 20 \text{k} \Omega$ $\text{R}_{\text{S}} \le \frac{0.3 \times 3 - 0.4 - 0.1 \times 3}{1.1 \times 3 - 0.3 \times 3} \times 20 \times 10^{3}$ $\le 1.67 \text{ [k}\Omega]$

3. Minimum Value of Rs

The minimum value of R_s is determined by over current at bus collision. When over current flows, noises in power source line and instantaneous power failure of power source may occur. When allowable over current is defined as I, the following relation must be satisfied. Determine the allowable current in consideration of the impedance of power source line in set and so forth. Set the over current to EEPROM at 10mA or lower.




Figure 48. I/O Circuit Diagram

I/O Equivalence Circuit

1. Input (SCL, WP)






Figure 49. Input Pin Circuit Diagram

2. Input / Output (SDA)





Vbot

0.3V or below

0.2V or below

Power-Up / Down Conditions

At power ON, the IC's internal circuits may go through unstable low voltage area as the Vcc rises, making the IC's internal logic circuit not completely reset, hence, malfunction may occur. To prevent this, the IC is equipped with POR circuit and LVCC circuit. To assure the operation, observe the following conditions at power ON.

- 1. Set SDA = 'H' and SCL ='L' or 'H'
- 2. Start power source so as to satisfy the recommended conditions of t_R, t_{OFF}, and V_{bot} for operating POR circuit.




Figure 51. Rise Waveform Diagram

3. Set SDA and SCL so as not to become 'Hi-Z'.

When the above conditions 1 and 2 cannot be observed, take the following countermeasures.

(1) In the case when the above condition 1 cannot be observed such that SDA becomes 'L' at power ON . →Control SCL and SDA as shown below, to make SCL and SDA, 'H' and 'H'.




Figure 52. When SCL= 'H' and SDA= 'L'

Figure 53. When SCL='L' and SDA='L'

Recommended conditions of tR, tOFF, Vbot

toff

10ms or larger

10ms or larger

tR

10ms or below

100ms or below

- (2) In the case when the above condition 2 cannot be observed.
- \rightarrow After power source becomes stable, execute software reset (Page 16).
- (3) In the case when the above conditions 1 and 2 cannot be observed.
- \rightarrow Carry out (1), and then carry out (2).

Low Voltage Malfunction Prevention Function

LVCC circuit prevents data rewrite operation at low power, and prevents write error. At LVCC voltage (Typ =1.2V) or below, data rewrite is prevented.

Noise Countermeasures

1. Bypass Capacitor

When noise or surge gets in the power source line, malfunction may occur, therefore, it is recommended to connect a bypass capacitor $(0.1\mu F)$ between IC Vcc and GND pins. Connect the capacitor as close to IC as possible. In addition, it is also recommended to connect a bypass capacitor between board's Vcc and GND.

Operational Notes

- 1. Described numeric values and data are design representative values only, and the values are not guaranteed.
- 2. We believe that the application circuit examples in this document are recommendable. However, in actual use, confirm characteristics further sufficiently. If changing the fixed number of external parts is desired, make your decision with sufficient margin in consideration of static characteristics, transient characteristics, and fluctuations of external parts and our LSI.
- 3. Absolute maximum ratings

If the absolute maximum ratings such as supply voltage, operating temperature range, and so on are exceeded, LSI may be destroyed. Do not supply voltage or subject the IC to temperatures exceeding the absolute maximum ratings. In the case of fear of exceeding the absolute maximum ratings, take physical safety countermeasures such as adding fuses, and see to it that conditions exceeding the absolute maximum ratings should not be supplied to the LSI.

4. GND electric potential

Set the voltage of GND terminal lowest at any operating condition. Make sure that each terminal voltage is not lower than that of GND terminal.

5. Thermal design

Use a thermal design that allows for a sufficient margin by taking into account the permissible power dissipation (Pd) in actual operating conditions.

- Short between pins and mounting errors
 Be careful when mounting the IC on printed circuit boards. The IC may be damaged if it is mounted in a wrong orientation
 or if pins are shorted together. Short circuit may be caused by conductive particles caught between the pins.
- 7. Operating the IC in the presence of strong electromagnetic field may cause malfunction, therefore, evaluate design sufficiently.


Part Numbering

		В	R	2	4	Т	1	6	х	х	х	-	W	ххх	
												-			-
BUS T 24 : I ²															
Opera Power -	Sourc 40°C to	e Volta	age												
Capaci	ty							_							
16=16															
Packag	je														
Blank	:DIP-	T8 ⁽¹⁾ (-W) / D	IP8K ((-WZ)										
F	:SOP	8													
FJ	:SOF	P-J8 (-V	VE2)/\$	SOP-J	8A(-	WSGN	E2)								
FV	: SSC	P-B8													
FVT	: TSS	OP-B8	5												
FVJ	: TSS	OP-B8	IJ												
FVM	: MSC	DP8													
NUX	: VSC	N008>	K 2030												
Double	Cell														
Blank Z SGN	: DIP		SOP8,	SOP-	-J8, S	SOP-B	8, TSS	SOP-E	38, TS	SOP	-B8J,	, MS	OP8, VS	50N008X203	80


E2	: Embossed tape and reel
	(SOP8,SOP-J8,SOP-J8A,SSOP-B8,TSSOP-B8,TSSOP-B8J)
TR	: Embossed tape and reel
	(MSOP8, VSON008X2030)
None	: Tube
	(DIP-T8 ⁽¹⁾ , DIP8K)


(1) Not Recommended for New Designs. Recommend BR24T16-WZ.


Physical Dimension and Packing Information

















Pocket Quadrants

Reel








Physical Dimension and Packing Information - continued MSOP8 Package Name 2. 9 ± 0.1 $4^{\circ + 6^{\circ}}_{-4^{\circ}}$ Max3. 25 (include. BURR) 2 - $4. 0\pm 0.$ $8\pm0.$ 2. 2 $2 9 \pm 0.15$ $6\pm 0.$ 0. 0. 2 3 4 1 0.4751 PIN MARK $0. \ 1\ 4\ 5\ {}^{+\ 0. \ 0\ 5}_{-\ 0. \ 0\ 3}$ S 9 MAX 0. 05 050 $75\pm0.$ $0.8 \pm 0.$ $0. \ 2 \ 2 \ {}^{+ \ 0. \ 0 \ 5}_{- \ 0. \ 0 \ 4}$ 0.65 (UNIT:mm) PKG:MSOP8 0. 0. \bigcirc 0. 08 S Drawing No. EX181-5002 <Tape and Reel information> Таре Embossed carrier tape Quantity 3000pcs TR Direction of feed The direction is the 1pin of product is at the upper right when you hold reel on the left hand and you pull out the tape on the right hand 0 0 0 0 0 0 Ο 0 Ο 0 0 0 E2 TR E2 TR E2 TR E2 TR E2 TR E2 ΤR ΤL ΤL E1 E1 ΤL E1 ΤL E1 ΤL E1 ΤL E1 Direction of feed Pocket Quadrants Reel





Physical Dimension and Packing Inform	
Package Name	VSON008X2030
2. 0±0.	1 I I I I I I I I I I I I I I I I I I I
	$\begin{array}{c} 0. \ 0. \ 0. \ 0. \ 0. \ 0. \ 0 \\ (0. \ 12) \end{array}$
	$ \begin{array}{c} 4 \\ 0 \\ 1 \\ 1 \\ 1 \\ 1 \\ 1 \\ 1 \\ 1 \\ 1 \\ 1 \\ 1$
	(UNIT:mm) PKG:VSON008X2030 Drawing No. EX187-5001
<tape and="" information="" reel=""> Tape Embossed carrier tape Quantity 4000pcs Direction TR (The direction is the 1pin of feed</tape>	of product is at the upper right when you hold) you pull out the tape on the right hand
E2 TR E2 TR E2 TR TL E1 TL E1 TL E1 Pocket Quadra Reel	O O O O E2 TR E2 TR TL E1 TL E1

Marking Diagrams (TOP VIEW)



Marking Diagrams (TOP VIEW) - continued





Revision History

Date	Revision	Changes			
18.May.2012	001	New Release			
25.Feb.2013	002	Update some English words, sentences' descriptions, grammar and formatting. Add tF2 in Serial Input / Output Timing			
31.May.2013	003	P1 Change format of package line-up table. P.2 Add VESD in Absolute Maximum Ratings			
02.Feb.2015	004	P.32 Modified Marking Diagram of SSOP-B8 (Deleted 2 nd row of LOT Number).			
08.Jan.2016	005	P.10 Change data of Figure 26			
30.Aug.2017	006	Add new package information (SOP-J8A)			
20.Dec.2018	007	Add DIP8K Change DIP-T8 to Not Recommended for New Designs Change Physical Dimension Tape and Reel Information Change the fonts and format			
24.Dec.2020	008	Updated packages and part numbers			


Part Numbering

	В	R	24	Т	1 6	FJ	- W	Z	E2
BUS Type 24 : I ² C									
Operating Tem Power Sour -40°C to 1.6 V to	ce Volt +85°C/	age							
Capacity	0.0 V								
16 = 16K									
Package									
FJ : SC	DP-J8A								
Double Cell									
Production sit	e]	
Z : Ad	lded								

Packaging and Forming Specification

E2 : Embossed tape and reel

Marking Diagrams (TOP VIEW)



Physical Dimension and Packing Information Package Name SOP-J8A $4. 9 \pm 0. 1$ Max5. 25 (include. BURR) $0^\circ ~\sim 7^\circ$ 8 7 6 5 ${}^{\rm Cl}$ _ 0 ± 0 . $9\pm0.$ ю. ς. Ω $4 \mathrm{MIN}$ 0. 1 23 4 0.5451 PIN MARK $0.\ 2\,2\pm 0.\ 0\,3$ S- \sim $55 \pm 0.$ _ . 1751. $375\pm0.$ 1.27 $0.\ 4\ 2\pm 0.\ 0\ 7$ 0. □ 0. 1 S (UNIT:mm) PKG:SOP-J8A Drawing No. EX001-0055-2 < Tape and Reel Information >

Tape Quantity	Embossed carrier tape					
•	2500pcs					
Direction of feed	E2					
	The direction is the pin 1 of product is at the upper left					
	when you hold reel on the left hand and you pull out the tape on the right hand					
	C O					

Notice

Precaution on using ROHM Products

1. Our Products are designed and manufactured for application in ordinary electronic equipment (such as AV equipment, OA equipment, telecommunication equipment, home electronic appliances, amusement equipment, etc.). If you intend to use our Products in devices requiring extremely high reliability (such as medical equipment (^{Note 1)}, transport equipment, traffic equipment, aircraft/spacecraft, nuclear power controllers, fuel controllers, car equipment including car accessories, safety devices, etc.) and whose malfunction or failure may cause loss of human life, bodily injury or serious damage to property ("Specific Applications"), please consult with the ROHM sales representative in advance. Unless otherwise agreed in writing by ROHM in advance, ROHM shall not be in any way responsible or liable for any damages, expenses or losses incurred by you or third parties arising from the use of any ROHM's Products for Specific Applications.

(Note1) Medical Equipment Classification of the Specific Applications

JÁPAN	USA	EU	CHINA
CLASSⅢ	CLASSⅢ	CLASS II b	CLASSII
CLASSⅣ	CLASSII	CLASSⅢ	CLASSI

- 2. ROHM designs and manufactures its Products subject to strict quality control system. However, semiconductor products can fail or malfunction at a certain rate. Please be sure to implement, at your own responsibilities, adequate safety measures including but not limited to fail-safe design against the physical injury, damage to any property, which a failure or malfunction of our Products may cause. The following are examples of safety measures:
 - [a] Installation of protection circuits or other protective devices to improve system safety
 - [b] Installation of redundant circuits to reduce the impact of single or multiple circuit failure
- 3. Our Products are designed and manufactured for use under standard conditions and not under any special or extraordinary environments or conditions, as exemplified below. Accordingly, ROHM shall not be in any way responsible or liable for any damages, expenses or losses arising from the use of any ROHM's Products under any special or extraordinary environments or conditions. If you intend to use our Products under any special or extraordinary environments or conditions (as exemplified below), your independent verification and confirmation of product performance, reliability, etc, prior to use, must be necessary:
 - [a] Use of our Products in any types of liquid, including water, oils, chemicals, and organic solvents
 - [b] Use of our Products outdoors or in places where the Products are exposed to direct sunlight or dust
 - [c] Use of our Products in places where the Products are exposed to sea wind or corrosive gases, including Cl₂, H₂S, NH₃, SO₂, and NO₂
 - [d] Use of our Products in places where the Products are exposed to static electricity or electromagnetic waves
 - [e] Use of our Products in proximity to heat-producing components, plastic cords, or other flammable items
 - [f] Sealing or coating our Products with resin or other coating materials
 - [g] Use of our Products without cleaning residue of flux (Exclude cases where no-clean type fluxes is used. However, recommend sufficiently about the residue.); or Washing our Products by using water or water-soluble cleaning agents for cleaning residue after soldering
 - [h] Use of the Products in places subject to dew condensation
- 4. The Products are not subject to radiation-proof design.
- 5. Please verify and confirm characteristics of the final or mounted products in using the Products.
- 6. In particular, if a transient load (a large amount of load applied in a short period of time, such as pulse, is applied, confirmation of performance characteristics after on-board mounting is strongly recommended. Avoid applying power exceeding normal rated power; exceeding the power rating under steady-state loading condition may negatively affect product performance and reliability.
- 7. De-rate Power Dissipation depending on ambient temperature. When used in sealed area, confirm that it is the use in the range that does not exceed the maximum junction temperature.
- 8. Confirm that operation temperature is within the specified range described in the product specification.
- 9. ROHM shall not be in any way responsible or liable for failure induced under deviant condition from what is defined in this document.

Precaution for Mounting / Circuit board design

- 1. When a highly active halogenous (chlorine, bromine, etc.) flux is used, the residue of flux may negatively affect product performance and reliability.
- 2. In principle, the reflow soldering method must be used on a surface-mount products, the flow soldering method must be used on a through hole mount products. If the flow soldering method is preferred on a surface-mount products, please consult with the ROHM representative in advance.

For details, please refer to ROHM Mounting specification

Precautions Regarding Application Examples and External Circuits

- 1. If change is made to the constant of an external circuit, please allow a sufficient margin considering variations of the characteristics of the Products and external components, including transient characteristics, as well as static characteristics.
- 2. You agree that application notes, reference designs, and associated data and information contained in this document are presented only as guidance for Products use. Therefore, in case you use such information, you are solely responsible for it and you must exercise your own independent verification and judgment in the use of such information contained in this document. ROHM shall not be in any way responsible or liable for any damages, expenses or losses incurred by you or third parties arising from the use of such information.

Precaution for Electrostatic

This Product is electrostatic sensitive product, which may be damaged due to electrostatic discharge. Please take proper caution in your manufacturing process and storage so that voltage exceeding the Products maximum rating will not be applied to Products. Please take special care under dry condition (e.g. Grounding of human body / equipment / solder iron, isolation from charged objects, setting of lonizer, friction prevention and temperature / humidity control).

Precaution for Storage / Transportation

- 1. Product performance and soldered connections may deteriorate if the Products are stored in the places where:
 - [a] the Products are exposed to sea winds or corrosive gases, including Cl₂, H₂S, NH₃, SO₂, and NO₂
 - [b] the temperature or humidity exceeds those recommended by ROHM
 - [c] the Products are exposed to direct sunshine or condensation
 - [d] the Products are exposed to high Electrostatic
- 2. Even under ROHM recommended storage condition, solderability of products out of recommended storage time period may be degraded. It is strongly recommended to confirm solderability before using Products of which storage time is exceeding the recommended storage time period.
- 3. Store / transport cartons in the correct direction, which is indicated on a carton with a symbol. Otherwise bent leads may occur due to excessive stress applied when dropping of a carton.
- 4. Use Products within the specified time after opening a humidity barrier bag. Baking is required before using Products of which storage time is exceeding the recommended storage time period.

Precaution for Product Label

A two-dimensional barcode printed on ROHM Products label is for ROHM's internal use only.

Precaution for Disposition

When disposing Products please dispose them properly using an authorized industry waste company.

Precaution for Foreign Exchange and Foreign Trade act

Since concerned goods might be fallen under listed items of export control prescribed by Foreign exchange and Foreign trade act, please consult with ROHM in case of export.

Precaution Regarding Intellectual Property Rights

- 1. All information and data including but not limited to application example contained in this document is for reference only. ROHM does not warrant that foregoing information or data will not infringe any intellectual property rights or any other rights of any third party regarding such information or data.
- 2. ROHM shall not have any obligations where the claims, actions or demands arising from the combination of the Products with other articles such as components, circuits, systems or external equipment (including software).
- 3. No license, expressly or implied, is granted hereby under any intellectual property rights or other rights of ROHM or any third parties with respect to the Products or the information contained in this document. Provided, however, that ROHM will not assert its intellectual property rights or other rights against you or your customers to the extent necessary to manufacture or sell products containing the Products, subject to the terms and conditions herein.

Other Precaution

- 1. This document may not be reprinted or reproduced, in whole or in part, without prior written consent of ROHM.
- 2. The Products may not be disassembled, converted, modified, reproduced or otherwise changed without prior written consent of ROHM.
- 3. In no event shall you use in any way whatsoever the Products and the related technical information contained in the Products or this document for any military purposes, including but not limited to, the development of mass-destruction weapons.
- 4. The proper names of companies or products described in this document are trademarks or registered trademarks of ROHM, its affiliated companies or third parties.

General Precaution

- 1. Before you use our Products, you are requested to carefully read this document and fully understand its contents. ROHM shall not be in any way responsible or liable for failure, malfunction or accident arising from the use of any ROHM's Products against warning, caution or note contained in this document.
- 2. All information contained in this document is current as of the issuing date and subject to change without any prior notice. Before purchasing or using ROHM's Products, please confirm the latest information with a ROHM sales representative.
- 3. The information contained in this document is provided on an "as is" basis and ROHM does not warrant that all information contained in this document is accurate and/or error-free. ROHM shall not be in any way responsible or liable for any damages, expenses or losses incurred by you or third parties resulting from inaccuracy or errors of or concerning such information.