

Automotive 1.0A Variable Output LDO Regulator

BDxxHC0MEFJ-M BDxxHC0VEFJ-M

General Description

BDxxHC0VEFJ-M is a LDO regulator with output current 1.0A. The output accuracy is $\pm 1\%$ of output voltage. With external resistance, it is available to set the output voltage at random (from 1.5V to 7.0V). It has package type: HTSOP-J8. Over current protection (for protecting the IC destruction by output short circuit), circuit current ON/OFF switch (for setting the circuit 0 μ A at shutdown mode), and thermal shutdown circuit (for protecting IC from heat destruction by over load condition) are all built in. It is usable for ceramic capacitor and enables to improve smaller set and long-life.

Features

- High accuracy reference voltage circuit
- Built-in Over Current Protection circuit (OCP)
- Built-in Thermal Shut Down circuit (TSD)
- With shut down switch
- AEC-Q100 Qualified

Key Specifications

Input power supply voltage range: 4.5V to 8.0VOutput voltage range(Variable type): 1.5V to 7.0V


Output voltage(Fixed type): 1.5V/1.8V/2.5V/3.0V/3.3V

5.0V/6.0V/7.0V


■ Output current: 1.0A (Max.)
■ Shutdown current: 0µA(Typ.)

■ Operating temperature range: -40°C to +105°C


●Package HTSOP-J8 (Typ.) (Typ.) (Max.) 4.90mm x 6.00mm x 1.00mm




● Typical Application Circuit



CIN, COUT: Ceramic Capacitor



C_{IN},C_{OUT}: Ceramic Capacitor



Output Voltage	Package	Ordering Code	Production Line ^(Note 1)
Variable		BD00HC0MEFJ-ME2	A
variable		BD00HC0VEFJ-ME2	В
1.5V		BD15HC0MEFJ-ME2	Α
1.57		BD15HC0VEFJ-ME2	В
1.8V		BD18HC0MEFJ-ME2	Α
1.0 V		BD18HC0VEFJ-ME2	В
2.5V		BD25HC0MEFJ-ME2	A
2.5 V		BD25HC0VEFJ-ME2	В
3.0V	HTSOP-J8	BD30HC0MEFJ-ME2	Α
3.0 V		BD30HC0VEFJ-ME2	В
3.3V		BD33HC0MEFJ-ME2	A
3.3 V			BD33HC0VEFJ-ME2
5.0V		BD50HC0MEFJ-ME2	Α
3.0 V		BD50HC0VEFJ-ME2	В
6.0V		BD60HC0MEFJ-ME2	Α
0.00		BD60HC0VEFJ-ME2	В
7.0V		BD70HC0MEFJ-ME2	Α
7.00		BD70HC0VEFJ-ME2	В

(Note1) For the purpose of improving production efficiency, Production Line A and B have a multi-line configuration. Electric characteristics noted in Datasheet does not differ between Production Line A and B. Production Line B is recommended for new product.

Block Diagram

BD00HC0MEFJ-M BD00HC0VEFJ-M




Fig.1 Block Diagram

BDxxHC0MEFJ-M BDxxHC0VEFJ-M (Fixed type)





Fig.2 Block Diagram (Fixed type)

●Pin Configuration



Pin Description

Pin No.	Pin name	Pin Function	
1	Vo	Output pin	
2	FB/Vo_s	Feedback pin	
3	GND	GND pin	
4	N.C.	Non Connection (Used to connect GND or OPEN state.)	
5	EN	Enable pin	
6	N.C.	Non Connection (Used to connect GND or OPEN state.)	
7	N.C.	Non Connection (Used to connect GND or OPEN state.)	
8	Vcc	Input pin	
Reverse	FIN	Substrate(Connect to GND)	

● Absolute Maximum Ratings (Ta=25°C)

Parameter		Symbol	Limits	Unit
Power supply voltage		Vcc	10.0 *1	V
EN voltage		V _{EN}	10.0	V
Power dissipation	HTSOP-J8	Pd*2	2110 *2	mW
Operating Temperatur	re Range	Topr	-40 to +105	°C
Storage Temperature Range		Tstg	-55 to +150	°C
Junction Temperature		Tjmax	+150	°C

^{*1} Not to exceed Pd

● Recommended Operating Ratings (Ta=25°C)

Parameter	Symbol	Min.	Max.	Unit
				01111
Input power supply voltage	Vcc	4.5	8.0	V
EN voltage	V_{EN}	0.0	8.0	V
Output voltage setting range	Vo	1.5	7.0	V
Output current	lo	0.0	1.0	Α


● Electrical Characteristics (Unless otherwise noted, EN=3V, Vcc=6V, R₁=43kΩ, R₂=8.2kΩ)

Parameter	Symbol	Temp	Min.	Тур.	Max.	Unit	Conditions	
Circuit current at shutdown		25°C	-	0	5		V 0V 0FF	
mode	Isd	-40~105°C	-	ı	5	μA	V _{EN} =0V, OFF mode	
Diag assessed		25°C	-	600	900			
Bias current	Icc	-40~105°C	-	ı	1200	μΑ		
Line requisition	Dog	25°C	-	25	50	\/	// (//5:0.0)/) >0.0)/	
Line regulation	Reg.I	-40~105°C	-	ı	50	mV	Vcc =(Vo+0.9V)→8.0V	
	Don't	25°C	-	25	75	\/	1 0 100	
Load regulation	Reg Io	-40~105°C	-	ı	75	mV	I ₀ =0→1.0A	
Minimum due nout Volte de	\	25°C	-	0.6	0.9	V	V 5V L 4 0 A	
Minimum dropout Voltage	Vco	-40~105°C	-	ı	1.2	V	Vcc=5V, Io=1.0A	
Output reference voltage	\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \	25°C	0.792	0.800	0.808	17	I 0 A	
(Variable type)	V _{FB}	-40~105°C	0.776	ı	0.824	>	I _O =0mA	
Output voltage (Fixed type)	\/-	25°C	V ₀ × 0.99	Vo	Vo×1.01	V	I- 0m Λ	
Output voltage(Fixed type)	Vo	-40~105°C	Vo × 0.97	Vo	Vo × 1.03	٧	I _O =0mA	
EN Low voltage	\//1 am	25°C	0	•	8.0	V		
EN Low voltage	V _{EN} (Low)	-40~105°C	0	1	0.8	٧		
EN Lligh voltage	\	25℃	2.4	1	8.0	V		
EN High voltage	V _{EN} (High)	-40~105°C	2.4	1	8.0	V		
EN Diag gurrent	1	25°C	1	3	9			
EN Bias current	I _{EN}	-40~105°C	-	1	9	μΑ		

^{*2} Reduced by 16.9mW/°C for each increase in Ta of 1°C over 25°C. (when mounted on a board 70mm × 70mm × 1.6mm glass-epoxy board, two layer)

●Typical Performance Curves


(Unless otherwise noted, EN=3V, V_{CC} =6V, R1=43k Ω , R2=8.2k Ω)



Vo D SomV/div 1 10usec/div

Fig.3
Transient Response
(0→1.0A)
Co=1µF,Ta=-40°C

Fig.4
Transient Response
(0→1.0A)
Co=1µF,Ta=25°C






Fig.5
Transient Response
(0→1.0A)
Co=1µF,Ta=105°C

Fig.6
Transient Response
(1.0→0A)
Co=1µF,Ta=-40°C








Fig.9 Input sequence 1 Co=1µF,Ta=-40°C


Fig.10 Input sequence 1 Co=1µF,Ta=25°C




















Fig.24 Ta-I_{EN}





Fig.25 I_O-V_O






Fig.27 Vcc-Vo (Io=0mA)




Fig.28 TSD (I_O=0mA)





Fig.29 OCP






Fig.31 ESR Safety area





Fig.32 PSRR (I_O=0mA)








Fig.34 Minimum dropout Voltage 1 (V_{CC}=4.5V)




Fig.35 Minimum dropout Voltage 2 $(V_{CC}=6.0V)$




Fig.36 Minimum dropout Voltage 3 (Vcc=8.0V)




Fig.37 Minimum dropout Voltage 4 (Vcc=10.0V)





Fig.38
Minimum dropout Voltage 5
(Vcc=12.0V)

Power Dissipation



Measure condition: mounted on a ROHM board, and IC

Substrate size: 70mm × 70mm × 1.6mm (Substrate with thermal via)

- Solder the substrate and package reverse exposure heat radiation part
- ① IC only θ i-a=249.5°C/W
- ② 1-layer (copper foil are :0mm × 0mm) θ j-a=153.2°C/W
- ③ 2-layer (copper foil are :15mm × 15mm) θ j-a=113.6°C/W
- ② 2-layer (copper foil are :70mm × 70mm) θ j-a=59.2°C/W
- (5) 4-layer (copper foil are :70mm × 70mm) θ j-a=33.3°C/W

Thermal design should allow operation within the following conditions. Note that the temperatures listed are the allowed temperature limits, and thermal design should allow sufficient margin from the limits.

- 1. Ambient temperature Ta can be no higher than 105°C.
- 2. Chip junction temperature (Tj) can be no higher than 150°C.

Chip junction temperature can be determined as follows:

Calculation based on ambient temperature (Ta)

Tj=Ta+
$$\theta$$
j-a×W

<Reference values>

 θ j-a: HTSOP-J8 153.2°C/W 1-layer substrate (copper foil density 0mm × 0mm) 113.6°C/W 2-layer substrate (copper foil density 15mm × 15mm) 59.2°C/W 2-layer substrate (copper foil density 70mm × 70mm) 33.3°C/W 4-layer substrate (copper foil density 70mm × 70mm) Substrate size: 70mm × 70mm × 1.6mm (substrate with thermal via)

Most of the heat loss that occurs in the BDxxHC0MEFJ-M BDxxHC0VEFJ-M is generated from the output Pch FET. Power loss is determined by the total V_{CC} - V_{O} voltage and output current. Be sure to confirm the system input and output voltage and the output current conditions in relation to the heat dissipation characteristics of the V_{CC} and V_{O} in the design. Bearing in mind that heat dissipation may vary substantially depending on the substrate employed (due to the power package incorporated in the BDxxHC0MEFJ-M BDxxHC0VEFJ-M make certain to factor conditions such as substrate size into the thermal design.

$$Power \ consumption[W] = \Big\{\ Input \ voltage \ (V_{CC}) \ - \ Output \ voltage \ (V_O) \Big\} \times I_O(Ave)$$

Example) Where Vcc=5.0V, Vo=3.3V, Io(Ave) = 0.1A, Power consumption[W] =
$$\{5.0V - 3.3V\} \times 0.1A$$


=0.17W

●Input-to-Output Capacitor

It is recommended that a capacitor is placed nearby pin between Input pin and GND, output pin and GND.

A capacitor, between input pin and GND, is valid when the power supply impedance is high or drawing is long. Also as for a capacitor, between output pin and GND, the greater the capacity, more sustainable the line regulation and it makes improvement of characteristics by load change. However, please check by mounted on a board for the actual application. Ceramic capacitor usually has difference, thermal characteristics and series bias characteristics, and moreover capacity decreases gradually by using conditions.


For more detail, please be sure to inquire the manufacturer, and select the best ceramic capacitor.



(Characteristics example)


● Equivalent Series Resistance ESR (ceramic capacitor etc.)

Please attach an anti-oscillation capacitor between V_0 and GND. Capacitor usually has ESR(Equivalent Series Resistance), and operates stable in ESR-lo range, showed right. Generally, ESR of ceramic, tantalum and electronic capacitor etc. is different for each, so please be sure to check a capacitor which is going to use, and use it inside the stable operating region, showed right. Then, please evaluate for the actual application.



ESR - Io characteristics


●Evaluation Board Circuit



● Evaluation Board Parts List

Designation	Value	Part No.	Company	Designation	Value	Part No.	Company
R1	43kΩ	MCR01PZPZF4302	ROHM	C4	-	-	-
R2	8.2kΩ	MCR01PZPZF8201	ROHM	C5	1μF	CM105X7R105K16AB	KYOCERA
R3	-	-	-	C6			
R4	-	-	-	C7		-	-
R5		-	-	C8	-	-	-
R6	1	-	-	C9	-	-	-
C1	1µF	CM105B105K16A	KYOCERA	C10	-	•	-
C2	-	-		U1	1	BD00HC0MEFJ-M BD00HC0VEFJ-M	ROHM
C3	-	-		U2	_	-	-

Board Layout




- ·Input capacitor C_{IN} of V_{CC} (V_{IN}) should be placed very close to $V_{CC}(V_{IN})$ pin as possible, and used broad wiring pattern. Output capacitor C_{OUT} also should be placed close to IC pin as possible. In case connected to inner layer GND plane, please use several through hole.
- FB pin has comparatively high impedance, and is apt to be effected by noise, so floating capacity should be minimum as possible. Please be careful in wiring drawing
- Please take GND pattern space widely, and design layout to be able to increase radiation efficiency.
- For output voltage setting

Output voltage can be set by FB pin voltage (0.800V typ.) and external resistance R1, R2.


$$V_0 = V_{FB} \times \frac{R1+R2}{R2}$$

(The use of resistors with R1+R2=1k to $90k\Omega$ is recommended)

●I/O Equivalent Circuits (Output Voltage Vairable type)



●I/O Equivalent Circuits (Output Voltage Fixed type)



Operational Notes

(1). Absolute maximum ratings

An excess in the absolute maximum ratings, such as supply voltage, temperature range of operating conditions, etc., can break down the devices, thus making impossible to identify breaking mode, such as a short circuit or an open circuit. If any over rated values will expect to exceed the absolute maximum ratings, consider adding circuit protection devices, such as fuses.

(2). Connecting the power supply connector backward

Connecting of the power supply in reverse polarity can damage IC. Take precautions when connecting the power supply lines. An external direction diode can be added.

(3). Power supply lines

Design PCB layout pattern to provide low impedance GND and supply lines. To obtain a low noise ground and supply line, separate the ground section and supply lines of the digital and analog blocks. Furthermore, for all power supply terminals to ICs, connect a capacitor between the power supply and the GND terminal. When applying electrolytic capacitors in the circuit, not that capacitance characteristic values are reduced at low temperatures.

(4). GND voltage

The potential of GND pin must be minimum potential in all operating conditions.

(5). Thermal design

Use a thermal design that allows for a sufficient margin in light of the power dissipation (Pd) in actual operating conditions.

(6). Inter-pin shorts and mounting errors

Use caution when positioning the IC for mounting on printed circuit boards. The IC may be damaged if there is any connection error or if pins are shorted together.

(7). Actions in strong electromagnetic field

Use caution when using the IC in the presence of a strong electromagnetic field as doing so may cause the IC to malfunction.

(8). ASO

When using the IC, set the output transistor so that it does not exceed absolute maximum ratings or ASO.

(9). Thermal shutdown circuit

The IC incorporates a built-in thermal shutdown circuit (TSD circuit). The thermal shutdown circuit (TSD circuit) is designed only to shut the IC off to prevent thermal runaway. It is not designed to protect the IC or guarantee its operation. Do not continue to use the IC after operating this circuit or use the IC in an environment where the operation of this circuit is assumed.

	TSD ON Temperature[°C] (typ.)	Hysteresis Temperature [°C] (typ.)
BDxxHC0MEFJ-M	175	15
BDxxHC0VEFJ-M		

(10). Testing on application boards

When testing the IC on an application board, connecting a capacitor to a pin with low impedance subjects the IC to stress. Always discharge capacitors after each process or step. Always turn the IC's power supply off before connecting it to or removing it from a jig or fixture during the inspection process. Ground the IC during assembly steps as an antistatic measure. Use similar precaution when transporting or storing the IC.

(11). Regarding input pin of the IC

This monolithic IC contains P+ isolation and P substrate layers between adjacent elements in order to keep them isolated


P-N junctions are formed at the intersection of these P layers with the N layers of other elements, creating a parasitic diode or transistor. For example, the relation between each potential is as follows:

When GND > Pin A and GND > Pin B, the P-N junction operates as a parasitic diode.

When GND > Pin B, the P-N junction operates as a parasitic transistor.

Parasitic diodes can occur inevitable in the structure of the IC.

The operation of parasitic diodes can result in mutual interference among circuits, operational faults, or physical damage. Accordingly, methods by which parasitic diodes operate, such as applying a voltage that is lower than the GND(P substrate) voltage to an input pin, should not be used.



(12). Ground Wiring Pattern.

When using both small signal and large current GND patterns, it is recommended to isolate the two ground patterns, placing a single ground point at the ground potential of application so that the pattern wiring resistance and voltage variations caused by large currents do not cause variations in the small signal ground voltage. Be careful not to change the GND wiring pattern of any external components, either.


Status of this document


The Japanese version of this document is formal specification. A customer may use this translation version only for a reference to help reading the formal version.

If there are any differences in translation version of this document formal version takes priority.


● Physical Dimension Tape and Reel Information

HTSOP-J8





Marking Diagram



Part Number
BD00HC0MEFJ-ME2
BD15HC0MEFJ-ME2
BD18HC0MEFJ-ME2
BD25HC0MEFJ-ME2
BD30HC0MEFJ-ME2
BD33HC0MEFJ-ME2
BD50HC0MEFJ-ME2
BD60HC0MEFJ-ME2
BD70HC0MEFJ-ME2
BD00HC0VEFJ-ME2
BD15HC0VEFJ-ME2
BD18HC0VEFJ-ME2
BD25HC0VEFJ-ME2
BD30HC0VEFJ-ME2
BD33HC0VEFJ-ME2
BD50HC0VEFJ-ME2
BD60HC0VEFJ-ME2
BD70HC0VEFJ-ME2

Revision History

Date	Revision	Changes
31.Aug.2012	001	New Release
11.Oct.2021	002	Add BDxxHC0VEFJ-M Series

Notice

Precaution on using ROHM Products

1. If you intend to use our Products in devices requiring extremely high reliability (such as medical equipment (Note 1), aircraft/spacecraft, nuclear power controllers, etc.) and whose malfunction or failure may cause loss of human life, bodily injury or serious damage to property ("Specific Applications"), please consult with the ROHM sales representative in advance. Unless otherwise agreed in writing by ROHM in advance, ROHM shall not be in any way responsible or liable for any damages, expenses or losses incurred by you or third parties arising from the use of any ROHM's Products for Specific Applications.

(Note1) Medical Equipment Classification of the Specific Applications

ſ	JÁPAN	USA	EU	CHINA
Ī	CLASSⅢ	CL ACCIII	CLASS II b	СГУССШ
ſ	CLASSIV	CLASSⅢ	CLASSⅢ	CLASSⅢ

- 2. ROHM designs and manufactures its Products subject to strict quality control system. However, semiconductor products can fail or malfunction at a certain rate. Please be sure to implement, at your own responsibilities, adequate safety measures including but not limited to fail-safe design against the physical injury, damage to any property, which a failure or malfunction of our Products may cause. The following are examples of safety measures:
 - [a] Installation of protection circuits or other protective devices to improve system safety
 - [b] Installation of redundant circuits to reduce the impact of single or multiple circuit failure
- 3. Our Products are not designed under any special or extraordinary environments or conditions, as exemplified below. Accordingly, ROHM shall not be in any way responsible or liable for any damages, expenses or losses arising from the use of any ROHM's Products under any special or extraordinary environments or conditions. If you intend to use our Products under any special or extraordinary environments or conditions (as exemplified below), your independent verification and confirmation of product performance, reliability, etc, prior to use, must be necessary:
 - [a] Use of our Products in any types of liquid, including water, oils, chemicals, and organic solvents
 - [b] Use of our Products outdoors or in places where the Products are exposed to direct sunlight or dust
 - [c] Use of our Products in places where the Products are exposed to sea wind or corrosive gases, including Cl₂, H₂S, NH₃, SO₂, and NO₂
 - [d] Use of our Products in places where the Products are exposed to static electricity or electromagnetic waves
 - [e] Use of our Products in proximity to heat-producing components, plastic cords, or other flammable items
 - [f] Sealing or coating our Products with resin or other coating materials
 - [g] Use of our Products without cleaning residue of flux (Exclude cases where no-clean type fluxes is used. However, recommend sufficiently about the residue.); or Washing our Products by using water or water-soluble cleaning agents for cleaning residue after soldering
 - [h] Use of the Products in places subject to dew condensation
- 4. The Products are not subject to radiation-proof design.
- 5. Please verify and confirm characteristics of the final or mounted products in using the Products.
- 6. In particular, if a transient load (a large amount of load applied in a short period of time, such as pulse, is applied, confirmation of performance characteristics after on-board mounting is strongly recommended. Avoid applying power exceeding normal rated power; exceeding the power rating under steady-state loading condition may negatively affect product performance and reliability.
- 7. De-rate Power Dissipation depending on ambient temperature. When used in sealed area, confirm that it is the use in the range that does not exceed the maximum junction temperature.
- 8. Confirm that operation temperature is within the specified range described in the product specification.
- ROHM shall not be in any way responsible or liable for failure induced under deviant condition from what is defined in this document.

Precaution for Mounting / Circuit board design

- 1. When a highly active halogenous (chlorine, bromine, etc.) flux is used, the residue of flux may negatively affect product performance and reliability.
- 2. In principle, the reflow soldering method must be used on a surface-mount products, the flow soldering method must be used on a through hole mount products. If the flow soldering method is preferred on a surface-mount products, please consult with the ROHM representative in advance.

For details, please refer to ROHM Mounting specification

Precautions Regarding Application Examples and External Circuits

- 1. If change is made to the constant of an external circuit, please allow a sufficient margin considering variations of the characteristics of the Products and external components, including transient characteristics, as well as static characteristics.
- You agree that application notes, reference designs, and associated data and information contained in this document are presented only as guidance for Products use. Therefore, in case you use such information, you are solely responsible for it and you must exercise your own independent verification and judgment in the use of such information contained in this document. ROHM shall not be in any way responsible or liable for any damages, expenses or losses incurred by you or third parties arising from the use of such information.

Precaution for Electrostatic

This Product is electrostatic sensitive product, which may be damaged due to electrostatic discharge. Please take proper caution in your manufacturing process and storage so that voltage exceeding the Products maximum rating will not be applied to Products. Please take special care under dry condition (e.g. Grounding of human body / equipment / solder iron, isolation from charged objects, setting of lonizer, friction prevention and temperature / humidity control).

Precaution for Storage / Transportation

- 1. Product performance and soldered connections may deteriorate if the Products are stored in the places where:
 - [a] the Products are exposed to sea winds or corrosive gases, including Cl₂, H₂S, NH₃, SO₂, and NO₂
 - [b] the temperature or humidity exceeds those recommended by ROHM
 - [c] the Products are exposed to direct sunshine or condensation
 - [d] the Products are exposed to high Electrostatic
- Even under ROHM recommended storage condition, solderability of products out of recommended storage time period
 may be degraded. It is strongly recommended to confirm solderability before using Products of which storage time is
 exceeding the recommended storage time period.
- 3. Store / transport cartons in the correct direction, which is indicated on a carton with a symbol. Otherwise bent leads may occur due to excessive stress applied when dropping of a carton.
- 4. Use Products within the specified time after opening a humidity barrier bag. Baking is required before using Products of which storage time is exceeding the recommended storage time period.

Precaution for Product Label

A two-dimensional barcode printed on ROHM Products label is for ROHM's internal use only.

Precaution for Disposition

When disposing Products please dispose them properly using an authorized industry waste company.

Precaution for Foreign Exchange and Foreign Trade act

Since concerned goods might be fallen under listed items of export control prescribed by Foreign exchange and Foreign trade act, please consult with ROHM in case of export.

Precaution Regarding Intellectual Property Rights

- 1. All information and data including but not limited to application example contained in this document is for reference only. ROHM does not warrant that foregoing information or data will not infringe any intellectual property rights or any other rights of any third party regarding such information or data.
- 2. ROHM shall not have any obligations where the claims, actions or demands arising from the combination of the Products with other articles such as components, circuits, systems or external equipment (including software).
- 3. No license, expressly or implied, is granted hereby under any intellectual property rights or other rights of ROHM or any third parties with respect to the Products or the information contained in this document. Provided, however, that ROHM will not assert its intellectual property rights or other rights against you or your customers to the extent necessary to manufacture or sell products containing the Products, subject to the terms and conditions herein.

Other Precaution

- 1. This document may not be reprinted or reproduced, in whole or in part, without prior written consent of ROHM.
- 2. The Products may not be disassembled, converted, modified, reproduced or otherwise changed without prior written consent of ROHM.
- In no event shall you use in any way whatsoever the Products and the related technical information contained in the Products or this document for any military purposes, including but not limited to, the development of mass-destruction weapons.
- 4. The proper names of companies or products described in this document are trademarks or registered trademarks of ROHM, its affiliated companies or third parties.

Notice-PAA-E Rev.004

General Precaution

- 1. Before you use our Products, you are requested to carefully read this document and fully understand its contents. ROHM shall not be in any way responsible or liable for failure, malfunction or accident arising from the use of any ROHM's Products against warning, caution or note contained in this document.
- 2. All information contained in this document is current as of the issuing date and subject to change without any prior notice. Before purchasing or using ROHM's Products, please confirm the latest information with a ROHM sales representative.
- 3. The information contained in this document is provided on an "as is" basis and ROHM does not warrant that all information contained in this document is accurate and/or error-free. ROHM shall not be in any way responsible or liable for any damages, expenses or losses incurred by you or third parties resulting from inaccuracy or errors of or concerning such information.

Notice – WE Rev.001