SML-P24MUWT86(R)

1. CONSTRUCTION	Two-color Surface Mount Chip LEDs packed with milky white diffused resi Emitting material Yellow Green ······ AlGalnP Red ···· AlGalnP	n.
2. USAGE ^{*1}	Source of light for display unit.	
3. DIMENSIONS	See Figure.1	
4. ABSOLUTE MAXIMUM R	RATINGS *2	
Power Dissipation	PD Yellow Green (Ta=25°C)	
	PD Red (Ta=25°C)	
Forward Current	IF Yellow Green (Ta=25°C)	
	IF Red (Ta=25°C)	
Peak Forward Current	IFP Yellow Green (Ta=25°C) • • • • • • • 100mA ¹⁾	
	IFP Red (Ta=25°C) • • • • • • • 100mA ¹⁾	
Reverse Voltage	VR (Ta=25°C) • • • • • • • 5V	
Operation Temperature	Topr -40~+85°C	
Storage Temperature	Tstg • • • • • • • • • • • • • • • • • • •	
	¹⁾ Duty 1/10, 1kHz	
	WThe above absolute maximum ratings are valid for the case of lighting	

%The above absolute maximum ratings are valid for the case of lighting a single color. When lighting two colors at the same time, the absolute maximum ratings is 50% of each color.

5. ELECTRO-OPTICAL CHARACTERISTICS (Ta=25°C)

3. ELECTIVO-OF TICAL CHARACTERICTICO (Ta=23 C)						
DISCRIPTION	SYMBOL	CONDITION	MIN.	TYP.	MAX.	UNITS
Forward Voltage	VF Yellow Green	IF=20mA ²⁾	1.2	2.2	2.7	V
Forward voltage	VF Red	IF=20mA ²⁾	1.2	2.1	2.6	V
Reverse Current	IR Yellow Green	VR=5V	-	-	10	μA
Reverse Current	IR Red	VR=5V	-	-	10	μA
Luminous Intensity	IV Yellow Green	IF=20mA ³⁾	10	21	40	mcd
	IV Red	IF=20mA ³⁾	25	52	100	mcd
Dominant Wave Length	λD Yellow Green	IF=20mA ³⁾	569	572	575	nm
	λD Red	IF=20mA ³⁾	615	620	625	nm
2)	2)		4) — .			

²⁾ Lighting time : 1msec ³⁾ Lighting time : 10msec ⁴⁾ Tolerance : ±1nm

6. LUMINOUS CI	ASSIFICATION ³ (Ta=25°C, IF=20mA)			imA)	
SYMBOL	Color	LUMI	LUMINOUS CLASSIFICATION RANGE		
"MP"	Yellow Green	10	~	16	mcd
IVIP	Red	25	~	40	mcd
"NP"	Yellow Green	16	~	25	mcd
NP	Red	25	~	40	mcd
"PP"	Yellow Green	25	~	40	mcd
	Red	25	~	40	mcd
"MQ"	Yellow Green	10	~	16	mcd
	Red	40	~	63	mcd
"NQ"	Yellow Green	16	~	25	mcd
	Red	40	~	63	mcd
"PQ"	Yellow Green	25	~	40	mcd
FQ	Red	40	~	63	mcd
"MR"	Yellow Green	10	~	16	mcd
	Red	63	~	100	mcd
"NR"	Yellow Green	16	~	25	mcd
	Red	63	~	100	mcd
"PR"	Yellow Green	25	~	40	mcd
PK	Red	63	~	100	mcd

6. LUMINOUS CLASSIFICATION *3 (Ta=25°C, IF=20mA)

Tolerance : ±10%

7. PRODUCT WEIGHT

Product weight per piece, approx 0.0003 grm.

8. MSL

Level 3

*1 : This product cannot be used for Automotive & Industrial (base station, smart meters, signal, etc. and social infrastructure) usage. If you are not sure about the usage, please contact ROHM.


*2 : Absolute maximum rating is the limit which must not be exceeded even for an instant, once exceeded, LED device destruction might occur. This is not the value that guarantees intensity of light life and other reliabilities.

Please refer to the derating data ^{*4} & conducting test data, and make sure to keep the value within absolute maximum rating w hile using. *3 : If rank shift occur, we may ask for re-approval of new rank when necessary.

*4 : Even within derating, the reliability and luminosity life may be affected by deterioration of sealing resin and reflector, etc. So please check with your application again.




[Figure 1]



(Unit : mm) ():Reference (Note) Tolerance is within ±0.1mm unless otherwise specified.




[Taping:T86]



⁽Unit : mm) (Note) Tolerance is within ±0.2mm unless otherwise specified.



[STRUCTURE · MATERIAL]



No.	APPELLATION	MATERIAL
1	Printed Wiring Board	Glass epoxy
2	Die Bond	Ag paste
3	LED Chip	AlGaInP
4	Bonding Wire	Gold
5	Resin	Epoxy resin
6	Electrode	Base plating:Cu,Ni Top plating:Au




[PACKAGING REQUIREMENTS]

1. PACKING

- (1) One reel is packed in aluminum bag.
 - The size of aluminum bag is $240(a) \times 250 \sim 280(b)$ mm.
- (2) Aluminum bag is sealed by pressured for all directions.
- (3) Insert the moisture indicator card to the aluminum bag.
- (4) Print the "Electrical-Static Warning mark" label and


"MSL (Moisture Sensitivity Level : JEDEC compatible" label on the back side of aluminum bag.





2. MARKING

The following information shall be described in the label on the aluminum bag.: ROHM Type number, Packing quantity, Luminous intensity rank, and Lot number etc.




Note) Indicates bar code expressed by code 39.



Indicates Pb-free Products.

[EXAMPLE OF LOT NO. MARKING]





Precaution (Surface Mount Device)

1.Storage

If the product is heated during the reflow under the condition of hygroscopic state, it may vaporize and expand which will influence the performance of the product. Therefore, the package is waterproof. Please use the product following the conditions:

Using Conditions

Classification	Temperature	Humidity	Expiration Date	Remark
①Before using	5~30°C	30~70%RH	Within 1 year from Receiving	Storage with waterproof package
②After opening package	5∼30°C	Below 70%RH		Please storing in the airtight container with our desiccant (silica gel)

Baking

Bake the product in case of below:

①The expiration date is passed.

② The color of 5% and 10% on humidity indicator card is not green.

(Even if the product is before expiration date.)

Baking Conditions

Temperature		Time	Humidity
60±3°C		12~24h	Below 20%RH
Remark	 Bake products in reel. Reel and embossed tape are Recommend bake once. 	easy to be deformed when baking, so	please try not to apply stress on it.

2. Application Methods

2-1.Color of sealing resin

This product may differ in the color of the resin due to the influence of the material contained in the sealing resin. There are no problems with the use.

2-2. Precaution for Drive System and Off Mode

Design the circuit without the electric load exceeding the ABSOLUTE MAXIMUM RATING that applies on the products. If drive by constant voltage, it may cause current deviation of the LED and result in deviation of luminous intensity, so we recommend to drive by constant current. (Deviation of VF value will cause deviation of current in LED.) Furthermore, for off mode, please do not apply voltage neither forward nor reverse. Especially, for the products with the Ag-paste used in the die bonding, there's high possibility to cause electro migration and result in function failure.

2-3. About derating

It is considered that derating characteristics will not result in LED chip's electrical destruction. Even within the derating, the reliability and luminous life can be affected depending on operating conditions and ambient environment. So we would be appreciate it if you can confirm with your application again.

2-4. About product life

Depending on operating conditions and environment(applied current, ambient temperature and humidity, corrosive gas), decreasing of luminosity and change of chromaticity may occur even within the specification conditions. Please contact our sales office if you use it for the following applications.

- 1 It requires long luminosity life
- 2 It is always lit

2-5. Applied Stress on Product

No resin hardening agent such as filler is used in the sealing resin of the product. Therefore, please pay attention to the overstress on it which may influence its reliability.

2-6.Usage

The product is LED. We are not responsible for the usage as the diode such as protection chip, rectifier, switching and so on.





3. Others

3-1. Surrounding Gas

Notice that if it is stored under the condition of acid gas (chlorine gas, sulfured gas) or alkali gas (ammonia), it may result in low soldering ability (caused by the change in quality of the plating surface) or optical characteristics changes (light intensity, chrominance) and change in quality of die bonding (Ag-paste) materials. All of the above will cause function failure of the products.

Therefore, please pay attention to the storage environment for mounted product (concern the generated gas of the surrounding parts of the products and the atmospheric environment).

3-2. Electrostatic Damage

The product is part of semiconductor and electrostatic sensitive, there's high possibility to be damaged by the electrostatic discharge. Please take appropriate measures to avoid the static electricity from human body and earthing of production equipment.Especially, InGaN type LEDs have lower resistance value of electrostatic discharge and it is recommended to introduce the ESD protection circuit.The resistance values of electrostatic discharge (actual values) vary with products, therefore, please call our Sales staffs for inquiries.

3-3. Electromagnetic Wave

Applications with strong electromagnetic wave such as, IH cooker, will influence the reliability of LED, therefore please evaluate before using it.



4. Mounting

4-1. Soldering

• No resin hardening agent such as filler is used in the sealing resin of the product. Therefore, resin expansion and moisture absorption at humidity will cause heat stress during soldering process and finally has bad influence on the product's reliability.

• The product is not guaranteed for flow soldering.

• Do not expose the product in the environment of high temperature (over 100°C) or rapid temperature shift (within 3°C/sec. of temperature gradient) during the flow soldering of surrounding parts.

In case of carrying out flow soldering of surrounding parts without recommended conditions, please contact us for inquiries.

· Please set appropriate reflow temperature based on our product usage conditions and specification.

• The max for reflowing is 2 times, please finish the second reflow soldering and flow soldering with other parts within the usage limitation after open the moistureproof package.

• Compare with N2 reflow, during air reflow, because of the heat and surrounding conditions, it may cause the discoloration of the resin.

• For our product that has no solder resist, because of its solder amount and soldering conditions, one of its specific characteristics is that solder will penetrate into LED. Thus, there's high possibility that will influence its reliability. Therefore, please be informed, concerning it before using it.

4-2. Automatic Mounting

4-2-1.Suction nozzle

Excessive load may cause damage inside the LED product, so select an optimal suction nozzle according to the material and shape of the LED product.


4-2-2.Mini Package (Smaller than 1010 size)

Vibration may result in low mounting rate since it will cause the static electricity of product and adhere to top cover tape.

Therefore, the magnet should be set on parts feeder cassette of the mounter to control the product stabilization. In addition, it is recommended to set ionizer to prevent electrostatic charge.

4-3. Mounting Location

The stress like bending stress of circuit board dividing after mounting, may cause LED package crack or damage of LED internal junction, therefore, please concern the mounting direction and position to avoid bending or screwing with great stress of the circuit board.



Stress strength according to the mounting position: A > B > C > D

4-4. Mechanical Stress after Mounting


The mechanical stress may damage the LED after circuit mounting, so please pay attention to the touch on product. <u>4-5. Soldering Pattern for Recommendation</u>

We recommend the soldering pattern that shows on the right. It will be different according to mounting situation of circuit board, therefore, please concern before designing.

The product has adopted the electrode structure that it should solder with back electrode of the product.

Thus, please be informed that the shape of electrode pin of solder fillet formation is not guaranteed.

The through hole on electrode surface is for conduction of front and rear electrodes but not for formation of solder fillet.








4-6. Reflow Profile

For reflow profile, please refer to the conditions below:(%)

 Meaning of marks, Conditions 			
Mark	Meanings	Conditions	
Ts _{max}	Maximum of pre-heating temperature	180°C	
Ts _{min}	Minimum of pre-heating temperature	140°C	
Ts	Time from Ts_{min} to Ts_{max}	Over 60 sec.	
TL	Reference temperature	230~260°C	
tL	Retention time for T_L	Within 40 sec.	
TP	Peak temperature	260°C(MAX.)	
t _P	Time for peak temperature	Within 10 sec.	
$\Delta T_R / \Delta t$	Temperature rising rate	Under 3°C/sec.	
$\Delta T_D / \Delta t$	Temperature decreasing rate	Within -3°C/sec.	



** Above conditions are for reference. Therefore, evaluate by customer's own circuit boards and reflow furnaces before using, because stress from circuit boards and temperature variations of reflow furnaces vary by customer's own conditions.

4-7. Attention Points in Soldering Operation

This product was developed as a surface mount LED especially suitable for reflow soldering. So reflow soldering is recommended. Incase of implementing manual soldering, please take care of following points.

1 SOLDER USED

Sn-Cu, Sn-Ag-Cu, Sn-Ag-Bi-Cu

②HAND SOLDERING CONDITION

LED products do not contain reinforcement material such as a glass fillers.

So thermal stress by soldering greatly influence its reliability.

Please keep following points for manual soldering.

	ITEM	RECOMMENDED CONDITION	Figure-1
a)	Heating method	Condition) Temp. of iron top less than 400 °C within 3 sec. Heating on PCB pattern, not direct to the LED. (Fig-1)	SOLDERING IRON
b)	Handling after soldering	Please handle after the part temp. Goes down to room temp.	SOLDERING LAND

4-8. Cleaning after Soldering

Please follow the conditions below if the cleaning is necessary after soldering.

	5,5
Solvent	We recommend to use alcohols solvent such as, isopropyl alcohols
Temperature	Under 30°C within 3 minutes
Ultrasonic Cleaning	15W / Below 1 liter (capacity of tank)
Drying	Under 100°C within 3 minutes



[MANUFACTORY]


FACTORY	SYMBOL
ROHM Wako Co.,Ltd.	10/
100 Tomioka, Kasaoka, Okayama 714-8585 Japan	W
ROHM-Wako Electronics (Malaysia) Sdn. Bhd.	_
Lot 1320 Kawasan Perindustrian, Pengkalan Chepall, Padang Tembak 16100 Kota Bharu, Kelantan, Malaysia	D
ROHM Semiconductor (China) Co.,Ltd.	
No.7, Weisan Rd, Micro-electronics Ind, Jingang Highway Xiqing Dist, Tianjin 300385	N
HARVATEK CORPORATION (Taiwan OEM)	
No.18, Lane522, Sec.5, JhonghuaRd, Hsinchu City 300, Taiwan 30094	1

* This sheet is mentioned all factory locations of LED products. Please contact us if you need detail information about each package.




12/17





RELATIVE LUMINOUS INTENSITY - ATMOSPHERE TEMPERATURE

RATIO OF MAXIMUM TOLERABLE PEAK CURRENT - PULSE DURATION





13/17

(Note) In case of lighting a single color.

% This data is actual value from specific lot and is not guaranteed.








RELATIVE LUMINOUS INTENSITY - FORWARD CURRENT

% This data is actual value from specific lot and is not guaranteed.






FORWARD CURRENT - FORWARD VOLTAGE




【Red】



% This data is actual value from specific lot and is not guaranteed.



DERATING^{*1、*2}



(Note) In case of lighting a single color.

THERMAL RESISTANCE(JUNCTION/SOLDER POINT)^{*1}

Rθj-s · · · 980°C/W [Yellow Green] Rθj-s · · · 970°C/W [Red]

THERMAL RESISTANCE(JUNCTION/AMBIENT)^{*1}

Rθj-a · · · 1305°C/W [Yellow Green] Rθj-a · · · 1300°C/W [Red]

JUNCTION TEMPERATURE

TjMax ••• 110°C

%1:[Evaluation board]


Glass epoxy(FR4) : 30x10mm,t=0.8mm Pad Size(Cu) : 1.5x1.0mm(Cathode),t=0.035mm

※2: Even within derating, the reliability and luminosity life may be affected by deterioration of sealing resin and reflector, etc. So please check with your application again.

% This data is actual value from specific lot and is not guaranteed.







% This data is actual value from specific lot and is not guaranteed.





Product	LED
Package	SMD
Series	SML-P24MUW_R

1.Test Result

Test Items	Reference STD	Test Condition	n (pcs)	Pn (pcs)	
Solder Heat Resistance for Reflow Soldering	J-STD-020D-01	Prtreatment : Temperature Humidity Strage (30°C/70%RH/168hr) Reflow Peak Temp. : 260°C 10sec Over 230°C/60sec Preheat : 140 to 180°C 60sec Number of reflow : 2 times	22	0	
Solderbility	JESD22-B102E	Immerse into rosin flux for 5 ± 1 sec,and the device for 3 ± 0.5 sec into Pb-free solder bath at $245\pm5^{\circ}$ C	22	0	*1
Drop test	JEITA ED-4701 A-124	H=75cm Maple Boad : 3 times	22	0	
Vibration	JEITA ED-4701 A-121	100~2000Hz 98.1m/s2 2hours each on each direction of X,Y,Z	22	0	1
Thermal Cycle	JESD22-A104E	Ta=Tstg Min.°C(30min.) ~ Tstg Max.°C(30min.) 100cycle	22	0	
High Temperature Strage	JESD22-A103E	Ta=Tstg Max.+5°C∕−0°C 1000hrs	22	0	
High Temperature High Humidity Strage	JEITA ED-4701 B-121	Ta=85±2°C 85±5%RH 240hrs	22	0	1
Low Temperature Strage	JESD22-A119A	Ta=Tstg Min.±5°C 1000hrs	22	0	1
Load Life	JESD22-A108D	Ta=25±5℃ IF=IFMax. 1000hrs <in a="" case="" color="" lighting="" of="" single=""></in>	22	0	1

2.Failure Criteria

Items	Condition	Criteria
Luminous Intensity	IF=20mA	60% of the initial value
Forward Voltage	IF=20mA	Changing rate of $\pm 10\%$
Reverse Current	VR=VR Max.	Maximum of specification
Appearance	Visual Check	No major change in appearance

*1

More than 95% of the electrode must be covered with solder.

%This data is actual value from specific lot and is not guaranteed.

Solderbility



	Notes	
1)	The information contained herein is subject to change without notice.	
2)	Before you use our Products, please contact our sales representative and verify the latest specifica tions.	
3)	Although ROHM is continuously working to improve product reliability and quality, semicon ductors can break down and malfunction due to various factors. Therefore, in order to prevent personal injury or fire arising from failure, please take safet measures such as complying with the derating characteristics, implementing redundant and fire prevention designs, and utilizing backups and fail-safe procedures. ROHM shall have no responsibility for any damages arising out of the use of our Poducts beyond the rating specified b ROHM.	
4)	Examples of application circuits, circuit constants and any other information contained herein are provided only to illustrate the standard usage and operations of the Products. The periphera conditions must be taken into account when designing circuits for mass production.	
5)	The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly any license to use or exercise intellectual property or other rights held by ROHM or any other parties. ROHM shall have no responsibility whatsoever for any dispute arising out of the use of such technical information.	
6)	The Products are intended for use in general electronic equipment (i.e. AV/OA devices, communi- cation, consumer systems, gaming/entertainment sets) as well as the applications indicated in this document.	
7)	The Products specified in this document are not designed to be radiation tolerant.	
8)	For use of our Products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a ROHM representative : transportation equipment (i.e. cars, ships, trains), primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, servers, solar cells, and power transmission systems.	
9)	Do not use our Products in applications requiring extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters.	
10)	ROHM shall have no responsibility for any damages or injury arising from non-compliance with the recommended usage conditions and specifications contained herein.	
11)	ROHM has used reasonable care to ensure the accuracy of the information contained in this document. However, ROHM does not warrants that such information is error-free, and ROHM shall have no responsibility for any damages arising from any inaccuracy or misprint of such information.	
12)	Please use the Products in accordance with any applicable environmental laws and regulations such as the RoHS Directive. For more details, including RoHS compatibility, please contact a ROHM sales office. ROHM shall have no responsibility for any damages or losses resulting non-compliance with any applicable laws or regulations.	
13)	When providing our Products and technologies contained in this document to other countries you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.	
14)	This document, in part or in whole, may not be reprinted or reproduced without prior consent o ROHM.	



Thank you for your accessing to ROHM product informations. More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

http://www.rohm.com/contact/

General Precaution

- 1. Before you use our Products, you are requested to carefully read this document and fully understand its contents. ROHM shall not be in any way responsible or liable for failure, malfunction or accident arising from the use of any ROHM's Products against warning, caution or note contained in this document.
- 2. All information contained in this document is current as of the issuing date and subject to change without any prior notice. Before purchasing or using ROHM's Products, please confirm the latest information with a ROHM sales representative.
- 3. The information contained in this document is provided on an "as is" basis and ROHM does not warrant that all information contained in this document is accurate and/or error-free. ROHM shall not be in any way responsible or liable for any damages, expenses or losses incurred by you or third parties resulting from inaccuracy or errors of or concerning such information.