

ML7662

13.56MHz Wireless charging receiver LSI

■ Overview

ML7662 is a 13.56MHz wireless power receiver LSI. ML7662 realizes a wireless power transfer system by combining with the wireless power transmitter LSI ML7663, and can output 1W to a charging device.

ML7662 is NFC Forum WLC* compliant. ML7662 can output power by combining with the NFC Forum WLC* compliant transmission device.

ML7662 is equipped with a 10-bit SA-ADC for measuring the power charging status and a wireless power charging control function in a 2.28 mm x 2.61 mm (equivalent to 2.44 mm square) WL-CSP chip or a 5 mm square 32-pin WQFN package.

This LSI is ideal for wireless power transfer of small devices. In addition, since it is equipped with the NFC Forum Type 3 Tag function, it is possible to realize NFC functions such as Bluetooth® pairing by touch. Furthermore, ML7662 is equipped with a host interface (SPI / I²C Target) function, and it is possible to update configuration data from an external MCU.

*Note: NFC Forum WLC 2.0.

■ Features

- Charging control
 - Built-in Charging control circuit
 - Built-in setting of output voltage by shunt regulator
 - Voltage/Current supply ON/OFF function to external charging IC
 - 1W receiving available
 - Abnormally detection function by software and hardware control
 - Abnormally notification function to the power transmission side
- Communication control
 - Communication speed: 212kbps, 424kbps
 - 2Kbyte data flash for storing user data
- Host interface
 - 1ch Serial interface (Target), and selectable from SPI or I²C
- Package
 - WL-CSP30pin (S-UFLGA30-2.28x2.61-0.40-W)
 - WQFN32pin (P-WQFN32-0505-0.50-A63)
- Applications
 - NFC charging devices, e.g.
 - smart watches, fitness trackers and smart wristbands
 - smart rings
 - smart glasses
 - true wireless stereos and hearing aids
 - stylus pens, wireless mice and wireless keyboards
 - electric toothbrushes
 - beauty home appliances
 - personal health care devices
 - battery packs

●Product name

ML7662-J01GD(WQFN Packages)
ML7662-J01HB(WLCSP Packages)


■Related Documents

In addition to this document, the following documents should also be read together as necessary.

- ML7663 Data Sheet
- ML7662 / ML7663 Application Note

All names used in this document are trademarks or registered trademarks of their respective developers.

■Block Diagram



¹ only WLCSP 30pin

² only WQFN 32 pin

■ Pin Assignment


● WLCSP 30pin

BOTTOM VIEW

P13 / AIN7	VDD_IO	MCSEL0	AIN1	P14 / SCLK_M	6
P06 / SCS_S	P11 / AIN6	VPP	P17 / SDO_M	P12 / SDI_M	5
P04 / INT_S	P05 / SDO_S	VSS0	P02 / SCL_M	P03 / SDA_M	4
P00 / SDA_S / SDI_S	P01 / SCL_S / SCLK_S	VSS2	P15 / TXD	P16 / AOUT	3
ISO_V	RESET_N	TEST0	RX1	P10 / RXD	2
LDO1V5	LDO1V8	BAT2	RX0	G_SHUNT	1
E	D	C	B	A	

●WQFN 32pin

TOP VIEW



Note : The center square is the PAD on the back side of the package (exposed PAD).
The exposed PAD should be connected to the GND of the board.

■ Pin list

Table 1 Pin list

PIN No. (WLCSP)	PIN No (WQFN)	Pin name (Function name) ³	1 st function	2 nd function	3 rd function
C2	1	TEST0	Debug port	-	-
A3	2	P16/AOUT (BAT_DISCHARGE)	General purpose port	Analog monitor output	-
B3	3	P15/TXD (DEBUG)	General purpose port	UART data output	-
D2	4	RESET_N	Reset pin	-	-
A4	5	P03/SDA_M (INTERFACE)	General purpose port	I ² C Controller data I/O	-
B4	6	P02/SCL_M	General purpose port	I ² C Controller clock output	-
A5	7	P12/SDI_M (POWER)	General purpose port	SPI Controller data input	-
B5	8	P17/SDO_M (ERROR)	General purpose port	SPI Controller data output	-
A6	9	P14/SCLK_M (CHARGE)	General purpose port	SPI Controller clock output	-
-	10	AIN0	General-purpose port 0 (for AD input)	-	-
B6	11	AIN1	General-purpose port 1 (for current measurement)	-	-
-	12	MCSEL1	Capacitor selection signal (for impedance matching)	-	-
C6	13	MCSEL0	Capacitor selection signal (for impedance matching)	-	-
C4	14	VSS0	GND	-	-
D6	15	VDD_IO	Power supply for logic IO	-	-
C5	16	VPP	Power supply pin for test	-	-
E6	17	P13/AIN7 (BAT_CHG)	General purpose port	General-purpose port 7 for AD input	-
D5	18	P11/AIN6 (RFDET)	General purpose port	General-purpose port 6 for AD input	-
E5	19	P06/SCS_S (SCS_S)	General purpose port	SPI Peripheral chip select input	-
D4	20	P05/SDO_S (SDO_S)	General purpose port	SPI Peripheral data output	-
E4	21	P04/INT_S (INT_S)	General purpose port	Host IF INT output	-
D3	22	P01/SCL_S/SCLK_S (SCL_S / SCLK_S)	General purpose port	I ² C Target clock input	SPI Peripheral clock input
E3	23	P00/SDA_S/SDI_S (SDA_S / SDI_S)	General purpose port	I ² C Target data I/O	SPI Peripheral data input
E2	24	ISO_V	Power supply for logic IO (for Host IF)	-	-
E1	25	LDO1V5	Internal power supply	-	-

³ Function name assigned by firmware.

PIN No. (WLCSP)	PIN No (WQFN)	Pin name (Function name) ^{*3}	1 st function	2 nd function	3 rd function
			(1.5V)		
D1	26	LDO1V8	Internal power supply (1.8V)	-	-
C1	27	BAT2	Battery voltage monitor pin	-	-
B2	28	RX1	RF data receiving pin	-	-
B1	29	RX0	RF data receiving pin	-	-
A1	30	G_SHUNT	Shunt transistor control signal	-	-
-	31	P_ANT ^{*4}	Rectifier input voltage	-	-
A2	32	P10/RXD (BAT_SW)	General purpose port	UART data input	-
C3	-	VSS2	GND	-	-

^{*4} If the package is WLCSP, connect to VDD_IO power supply.

■ Pin Description

Notation Definition: Pin state in reset

Index	Notation	Description
In reset	L	"L" level output
	H	"H" level output
	PU	Pull-Up
	PD	Pull-Down
	Z	Floating state

Notation Definition: input/output direction

Index	Notation	Description
I/O	I	Input pin
	O	Output pin
	I/O	Bi-directional pin

● Power, GND, and reference voltage pins

PIN No. (WLCSP)	PIN NO. (WQFN)	Pin name	I/O	Pin description
C4	14	VSS0	-	GND
D6	15	VDD_IO	-	Power supply (for Logic IO)
C5	16	VPP	I	Power supply (for Test)
E2	24	ISO_V	-	Power supply (for Host IF)
E1	25	LDO1V5	-	Power supply for internal use (1.5V)
D1	26	LDO1V8	-	Power supply for internal use (1.8V)
C1	27	BAT2	I	Battery voltage monitor pin
-	31	P_ANT	-	Rectifier input voltage
C3	-	VSS2	-	GND

● Analog signal pin

PIN No. (WLCSP)	PIN No. (WQFN)	Pin name	I/O	Pin description
B2	28	RX1	I	Pins Connected to LSI internal circuits that demodulate communications.
B1	29	RX0	I	

● General purpose port terminal (VDD_IO system)

PIN No. (WLCSP)	PIN No. (WQFN)	Pin name	In reset	I/O	Active Level	Pin description
C2	1	TEST0	Z	I/O	L	Debug port
A3	2	P16 / AOUT	Z	I/O	-	General purpose port Analog monitor output
B3	3	P15 / TXD	Z	I/O	-	General purpose port UART data output
D2	4	RESET_N	PU	I	L	Reset Input Pin L : System reset mode H : Program operation mode
-	10	AIN0	Z	I	-	General-purpose port 0 (for AD input)
B6	11	AIN1	Z	I	-	General-purpose port 1 (for current measurement)
-	12	MCSEL1	PU	O	-	Capacitor selection signal (for impedance matching)
C6	13	MCSEL0	PU	O	-	Capacitor selection signal (for impedance matching)
E6	17	P13 / AIN7	Z	I/O	-	General purpose port General-purpose port 7 (for AD input)
A2	32	P10 / RXD	PU	I/O	-	General purpose port UART data input

● General purpose port terminal (ISO_V system) ¹⁵

PIN No. (WLCSP)	PIN No. (WQFN)	Pin name	In reset	I/O	Pin description
A4	5	P03 / SDA_M	Z	I/O	General purpose port I ² C Controller data I/O
B4	6	P02 / SCL_M	Z	I/O	General purpose port I ² C Controller Clock output
A5	7	P12 / SDI_M	Z	I/O	General purpose port SPI Controller Data input
B5	8	P17 / SDO_M	Z	I/O	General purpose port SPI Controller Data output
A6	9	P14 / SCLK_M	Z	I/O	General purpose port SPI Controller Clock output
D5	18	P11 / AIN6	Z	I/O	General purpose port General-purpose port 6 (for AD input)
E5	19	P06 / SCS_S	Z	I/O	General purpose port SPI Peripheral Chip Select input
D4	20	P05 / SDO_S	Z	I/O	General purpose port SPI Peripheral Data output
E4	21	P04 / INT_S	Z	I/O	General purpose port Host IF INT output
D3	22	P01 / SCL_S / SCLK_S	Z	I/O	General purpose port I ² C Target Clock input SPI Peripheral Clock input
E3	23	P00 / SDA_S / SDI_S	Z	I/O	General purpose port I ² C Target Data I/O SPI Peripheral Data input

¹⁵ When controlled by an MCU or other device, the voltage should be the same as the interface voltage of the MCU.

● General-purpose port pins (P_ANT system)

PIN No. (WLCSP)	PIN No. (WQFN)	Pin name	In reset	I/O	Pin description
A1	30	G_SHUNT	L	O	Shunt transistor control signal

■ Unused pin processing

Pin name	Pin processing
TEST0	Pull-Up
P00~P6、P10~P17 RESET_N AIN0 AIN1 MCSEL0 MCSEL1 G_SHUNT	Open

■Electrical Characteristics

●Absolute Maximum Ratings

Index		Symbol	Condition	Rated value	Unit
Supply voltage	Power supply for logic IO	VDD_IO	-	-0.3~+6.5	V
	Power supply for logic IO (for Host IF)	ISO_V	-	-0.3~+6.5	V
	Rectifier input voltage	P_ANT	-	-0.3~+6.5	V
	Battery voltage monitor	BAT2	-	-0.3~+6.5	V
	Internal power supply	LDO1V5	-	-0.3~+2.0	V
LDO1V8		-	-0.3~+6.5	V	
Input voltage	VDIN	-	-0.3~VDD_IO+0.3	V	
	VDIN _{DIFF}	RX0-RX1 (differential)	14	V	
Input current	I _i	-	-10~+10	mA	
	I _{P_ANT}	-	100	mA	
Output voltage	VDO	-	-0.3~VDD_IO+0.3	V	
Digital output current	IDO	-	-12~+20	mA	
Power dissipation(WQFN)	PD	-	1	W	
Power dissipation (CSP)	PD	-	0.5	W	
Storage temperature	Tstg	-	-55~+150	°C	

●Recommended Operating Conditions

Index	Symbol	Condition	Min.	Typ.	Max.	Unit
Operating voltage range	VDD_IO	-	1.8	-	5.5	V
	ISO_V	-	1.8	-	5.5	V
	P_ANT	During communication	2.0	5.0	5.5	V
	P_ANT	During power transmission	-	-	5.5	V
Operating temperature	T _a	-	-40	+25	+85	°C
Antenna input frequency	F _{ANT}	-	Typ. -0.05%	13.56	Typ. +0.05%	MHz

●Flash Memory Operating Conditions

(VDD_IO=2.7 to 5.5V, P_ANT=2.7 to 5.5V, VSS=0V, T_a=-40 to +85°C)

Index	Symbol	Condition	Range	Unit
Rewrite count	C _{EPD}	Data Flash	10,000	times

●RF Characteristics

(VDD_IO=1.8 to 5.5V, P_ANT=2.0 to 5.5V, VSS=0V, T_a=-40 to +85°C)

Index	Symbol	Condition	Min.	Typ.	Max.	Unit
Input voltage level	V _{RX1}	RX0/RX1	2.0	-	5.9	V
Input data amplitude	V _{RX2}	RX0/RX1	50	-	-	mV
Communication speed	F _{RX}	RX0/RX1	-	212	-	kbps
			-	424	-	kbps

●Notification Characteristics

(VDD_IO=1.8 to 5.5V, P_ANT=2.0 to 5.5V, VSS=0V, T_a=-40 to +85°C)

Index	Symbol	Condition	Min.	Typ.	Max.	Unit
P_ANT limiter	V _{PANT1}	Normal	-	-	5.5	V
	V _{PANT2}	In case of abnormality notice	-	3.0	-	V

●AD Characteristics

(VDD_IO=1.8 to 5.5V, P_ANT=2.0 to 5.5V, VSS=0V, T_a=-40 to +85°C)

Index	Symbol	Condition	Min.	Typ.	Max.	Unit
Resolution	AD _{res}	-	-	10	-	bit
Zero-Scale Error	ZSE	-	-6	-	+6	LSB
Full-Scale Error	FSE	-	-6	-	+6	LSB

● AC Characteristics (I²C Bus Interface)

- Standard Mode 100 kHz


(VDD IO/ISO V=1.8 to 5.5V, P ANT=2.0 to 5.5V, VSS=0V, Ta=-40 to +85°C)

	Index	Symbol	Condition	Min.	Typ.	Max.	Unit
SCL_S	Clock frequency	f _{SCL}	-	-	-	100	kHz
	Hold time (start/repeated start condition)	t _{HD:STA}	-	4.0	-	-	μs
	"L" level time	t _{LOW}	-	4.7	-	-	μs
	"H" level time	t _{HIGH}	-	4.0	-	-	μs
	Setup time (start/repeated start condition)	t _{SU:STA}	-	4.7	-	-	μs
SDA_S	Hold time	t _{HD:DAT}	-	0	-	-	μs
	Setup time	t _{SU:DAT}	-	0.25	-	-	μs
	Setup time (Stop condition)	t _{SU:STO}	-	4.0	-	-	μs
Bus free time		t _{BUF}	-	4.7	-	-	μs

- Fast Mode 400 kHz

(VDD IO/ISO V=1.8 to 5.5V, P ANT=2.0 to 5.5V, VSS=0V, Ta=-40 to +85°C)

	Index	Symbol	Condition	Min.	Typ.	Max.	Unit
SCL_S	Clock frequency	f _{SCL}	-	-	-	400	kHz
	Hold time (start/repeated start condition)	t _{HD:STA}	-	0.6	-	-	μs
	"L" level time	t _{LOW}	-	1.3	-	-	μs
	"H" level time	t _{HIGH}	-	0.6	-	-	μs
	Setup time (repeated start condition)	t _{SU:STA}	-	0.6	-	-	μs
SDA_S	Hold time	t _{HD:DAT}	-	0	-	-	μs
	Setup time	t _{SU:DAT}	-	0.1	-	-	μs
	Setup time (Stop condition)	t _{SU:STO}	-	0.6	-	-	μs
Bus free time		t _{BUF}	-	1.3	-	-	μs




Note : If powering off this LSI, it disables communications of other devices on the I²C bus
 When power is not received from the P_ANT pin and there is a power input to the ISO_V pin of this LSI, the SDA_S/SCL_S pins maintain the Hi-Z state.

●AC Characteristics (Host Interface : SPI Controller)

(VDD_IO/ISO_V=1.8 to 5.5V, P_ANT=2.0 to 5.5V, VSS=0V, Ta=-40 to +85°C)


Index	Symbol	Condition	Min.	Typ.	Max.	Unit	
SCLK_M	Output cycle	t _{scyc}	-	250	SCLK ¹⁶	-	ns
	Output pulse width	t _{sw}	-	t _{scyc} × 0.4	t _{scyc} × 0.5	t _{scyc} × 0.6	ns
SDO_M	Output delay time	t _{sd}	-	-	100	ns	
SDI_M	Input setup time	t _{ss}	-	100	-	-	ns
	Input hold time	t _{sh}	-	60	-	-	ns



●AC Characteristics (Host Interface : SPI Peripheral)

(VDD_IO/ISO_V=1.8 to 5.5V, P_ANT=2.0 to 5.5V, VSS=0V, Ta=-40 to +85°C)

Index	Symbol	Condition	Min.	Typ.	Max.	Unit	
SCLK_S	Input cycle	t _{scyc}	-	500	-	-	ns
	Input pulse width	t _{sw}	-	200	-	-	ns
SCS_S ¹⁷	Setup time	t _{cs1}	-	80	-	-	ns
		t _{cs2}	-	80	-	-	ns
	Hold time	t _{ch1}	-	80	-	-	ns
		t _{ch2}	-	80	-	-	ns
Input pulse width	t _{cw}	-	80	-	-	ns	
SDO_S	Output delay time	t _{sd}	-	-	240	ns	
SDI_S	Input setup time	t _{ss}	-	80	-	-	ns
	Input hold time	t _{sh}	-	80	-	-	ns




¹⁶ SCLK is configurable via register. See the ML7660/ML7661 Application Note for details.

¹⁷ SCS_S polarity (active-high or active-low) is switchable. See the ML7660/ML7661 Application Note for details.

●AC Characteristics (UART)

(VDD_IO/ISO_V=1.8 to 5.5V, P_ANT=2.0 to 5.5V, VSS=0V, Ta=-40 to +85°C)


Index	Symbol	Condition	Min.	Typ.	Max.	Unit
Tx Baud Rate	t _{TBRT}	-	-	-	115.2	kbps
Rx Baud Rate	t _{RBRT}	-	-	-	115.2	kbps



●AC Characteristics (Reset)

(VDD_IO=1.8 to 5.5V, P_ANT=2.0 to 5.5V, VSS=0V, Ta=-40 to +85°C)

Index	Symbol	Condition	Min.	Typ.	Max.	Unit
Reset Pulse Width	P _{RST}	-	2	-	-	ms
Non-reset Pulse Width	P _{NRST}	-	-	-	0.3	μs



●IO Characteristics

 (Unless otherwise specified, VDD_{IO}=1.8 to 5.5V, P_{ANT}=2.0 to 5.5V, VSS=0V, Ta=-40 to +85°C)

Index	Symbol	Condition	Min.	Typ. ¹⁸	Max.	Unit
Output voltage 1	VOH1	IOH=-1.0mA	VDD _{IO} -0.5	-	-	V
	VOL1	IOL=+0.5mA	-	-	0.4	V
Output voltage 2 (LED mode selected)	VOL2	2.7V ≤ V _{DD} ≤ 5.5V IOL=+5.0mA	-	-	0.6	V
		IOL=+2.0mA	-	-	0.4	V
Output voltage 3 (I ² C mode selected)	VOL3	IOL3= +3mA (I ² C spec.) (VDD _{IO} ≥ 2V, ISO_V ≥ 2V)	-	-	0.4	V
Output voltage 4 (I ² C mode selected)	VOL4	IOL4= +2mA (I ² C spec.) (VDD _{IO} < 2V, ISO_V < 2V)	-	-	VDD _{IO} ×0.2	V
Output leakage1	IOOH1	VOH=V _{DD} (at high impedance)	-	-	1	μA
	IOOL1	VOL=VSS (at high impedance)	-1	-	-	μA
Input current 1 (RESET_N)	I _{IH1}	V _{IH1} =V _{DD}	-	-	1	μA
	I _{IL1}	V _{IL1} =VSS	-900	-300	-20	μA
Input current 2 (TEST0)	I _{IH2}	V _{IH2} =V _{DD}	-	-	1	μA
	I _{IL2}	V _{IL2} =VSS	-200	-15	-1	μA
Input current 3	I _{IH3}	V _{IH3} =V _{DD} (when pull-down)	1	15	200	μA
	I _{IL3}	V _{IL3} =VSS (when pull-up)	-200	-15	-1	μA
	I _{IH3Z}	V _{IH3} =V _{DD} (at high impedance)	-	-	1	μA
	I _{IL3Z}	V _{IL3} =VSS (at high impedance)	-1	-	-	μA
Input voltage 1	V _{IH1}	-	0.75× VDD _{IO}	-	VDD _{IO}	V
	V _{IL1}	-	0	-	0.3× VDD _{IO}	V
Input pin capacitance	C _{IN}	f=10kHz V _{rms} =50mV Ta=25°C	-	10	-	pF
Leak current	I _{ISOV}	Voltage supply to the ISO_V pin, no magnetic field input	-	100	-	nA

●Current Consumption

 (VDD_{IO}=1.8 to 5.5V, P_{ANT}=4.5 to 5.5V, VSS=0V, Ta=-40 to +85°C)


Index	Symbol	Condition	Min.	Typ.	Max.	Unit
Current Consumption ¹⁹	P _{ANT}	During communication	0.5	-	-	mA
	P _{ANT}	During power transmission	-	-	10	mA

¹⁸ Typical values are listed for Ta=25°C and VDD_{IO}=3.0V.

¹⁹ Current consumption depends on the antenna design. The smaller the load resistance, the higher the current consumption. External transistor current is not included.

■ Package Dimensions


WLCSP30pin



Notes for Mounting the Surface Mount Type Package

The surface mount type packages are very susceptible to heat in reflow mounting and humidity absorbed in storage. Therefore, before you perform reflow mounting, contact a ROHM sales office for the product name, package name, pin number, package code and desired mounting conditions (reflow method, temperature and times).

WQFN32pin




Notes for Mounting the Surface Mount Type Package

The surface mount type packages are very susceptible to heat in reflow mounting and humidity absorbed in storage. Therefore, before you perform reflow mounting, contact a ROHM sales office for the product name, package name, pin number, package code and desired mounting conditions (reflow method, temperature and times).

■ Application Circuit Example

Please refer to the ML7662 / ML7663 Application Note for details.



■ Revision History

Document No.	Issue Date	Page		Change Contents
		Previous Edition	Current Edition	
FEDL7662-01	2024.6.9	-	-	First edition
FEDL7662-02	2023.12.12	-	1	Add product name and applications description
FEDL7662-03	2024.1.9	16	16	Modified Notes
FEDL7662-04	2025.12.30	16	16	Revise the contents of the notice
FEDL7662-05	2026.1.30	all	all	Revise the datasheet layout Added: AC Characteristics (UART) Added: AC Characteristics (Reset)
		17	17	Delet: Note for the package with exposed die pad

Notice

Precaution on using ROHM Products

1) When using ROHM Products, refer to the latest product information and ensure that usage conditions (absolute maximum ratings^{*1}, recommended operating conditions, etc.) are within the ranges specified. ROHM disclaims any and all liability for any malfunctions, failure or accident arising out of or in connection with the use of ROHM Products outside of such usage conditions specified ranges, or without observing precautions. Even if it is used within such usage conditions specified ranges, semiconductors can break down and malfunction due to various factors. Therefore, in order to prevent personal injury, fire or the other damage from break down or malfunction of ROHM Products, please take safety at your own risk measures such as complying with the derating characteristics, implementing redundant and fire prevention designs, and utilizing backups and fail-safe procedures.

^{*1}: Absolute maximum ratings: a limit value that must not be exceeded even momentarily.

- 2) The Products specified in this document are not designed to be radiation tolerant.
- 3) Descriptions of circuits, software and other related information in this document are provided only to illustrate the standard operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. And the peripheral conditions must be taken into account when designing circuits for mass production. ROHM disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, and other related information.
- 4) No license, expressly or implied, is granted hereby under any intellectual property rights or other rights of ROHM or any third party with respect to ROHM Products or the information contained in this document (including but not limited to, the Product data, drawings, charts, programs, algorithms, and application examples, etc.). Therefore, ROHM shall have no responsibility whatsoever for any dispute, concerning such rights owned by third parties, arising out of the use of such technical information.
- 5) ROHM intends our Products to be used in a way indicated in this document. Please be sure to contact a ROHM sales office if you consider the use of our Products in different way from original use indicated in this document. For use of our Products in medical systems, please be sure to contact a ROHM representative and must obtain written agreement. Do not use our Products in applications which may directly cause injuries to human life, and which require extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters, etc. ROHM disclaims any and all liability for any losses and damages incurred by you or third parties arising by using the Product for purposes not intended by us without our prior written consent.
- 6) Please use the Products in accordance with any applicable environmental laws and regulations, such as the RoHS Directive. ROHM shall have no responsibility for any damages or losses resulting non-compliance with any applicable laws or regulations.
 - 7) When providing our Products and technologies contained in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.
- 8) Please contact a ROHM sales office if you have any questions regarding the information contained in this document or ROHM's Products.
- 9) This document, in part or in whole, may not be reprinted or reproduced without prior consent of ROHM.

(Note) "ROHM" as used in this document means ROHM Co., Ltd.

Other Precaution

- 1) All information contained in this document is subject to change for the purpose of improvement, etc. without any prior notice. Before purchasing or using ROHM Products, please confirm the latest information with a ROHM sales office.
- 2) ROHM has used reasonable care to ensure the accuracy of the information contained in this document, however, ROHM shall have no responsibility for any damages, expenses or losses arising from inaccuracy or errors of such information.